



DESCRIPTION

Prysmian Group's patented AIRGUARD™ cable is a superior replacement for CCW type armored cables. Prysmian has developed a quick and easy termination for AIRGUARD™ cable.

Two-hole lugs can be provided so that a complete kit is ready for the jobsite.

Add "-0" to below product number for outdoor or "-I" for indoor termination kits. If not specified, outdoor rated terminations will be assumed as requested.

Break Out Kits contain all the components needed to prepare the 3/C Cable to install a termination (no termination included).

1/C 5kV Terminations (Indoor or Outdoor)

Termination Kit	Cable Range	Insulation OD
AGT1C5HS	#2 AWG - #1 AWG	0.35" - 0.60"
AGT1CA5-X	1/0 AWG - 3/0 AWG	0.57" - 0.98"
AGT1CB5-X	4/0 AWG - 250 kcmil	0.67" - 1.10"
AGT1CC5-X	350 kcmil - 500 kcmil	0.85" - 1.50"
AGT1CD5-X	750 kcmil - 1000 kcmil	1.08" - 1.97"
AGT1CE5-X	Larger Size	1.41" - 2.56"

3/C 5kV Terminations (Indoor or Outdoor)

Termination Kit	Break Out Kit	Cable Range	Insulation OD
AGT3C5HS	AGTB03C5HS	#2 AWG - #1 AWG	0.35" - 0.60"
AGT3CA5-X	AGTB03C5A	1/0 AWG - 3/0 AWG	0.57" - 0.98"
AGT3CB5-X	AGTB03C5B	4/0 AWG - 250 kcmil	0.67" - 1.10"
AGT3CC5-X	AGTB03C5C	350 kcmil - 500 kcmil	0.85" - 1.50"
AGT3CD5-X	AGTB03C5D	750 kcmil - 1000 kcmil	1.08" - 1.97"
AGT3CE5-X	AGTB03C5E	Larger Size	1.41" - 2.56"

1/C 15kV Terminations (Indoor or Outdoor)

Termination Kit	Cable Range	Insulation OD
AGT1CA15-X	#2 AWG - 3/0 AWG	0.57" - 0.98"
AGT1CB15-X	#1 AWG - 250 kcmil	0.67" - 1.10"
AGT1CC15-X	2/0 AWG - 500 kcmil	0.85" - 1.50"
AGT1CD15-X	350 kcmil - 750 kcmil	1.08" - 1.97"
AGT1CE15-X	1000 kcmil - 1500 kcmil	1.41" - 2.56"

3/C 15kV Terminations (Indoor or Outdoor)

Termination Kit	Break Out Kit	Cable Range	Insulation OD
AGT3CA15-X	AGTB03C15A	#2 AWG - 3/0 AWG	0.57" - 0.98"
AGT3CB15-X	AGTB03C15B	#1 AWG - 250 kcmil	0.67" - 1.10"
AGT3CC15-X	AGTB03C15C	2/0 AWG - 500 kcmil	0.85" - 1.50"
AGT3CD15-X	AGTB03C15D	350 kcmil - 750 kcmil	1.08" - 1.97"
AGT3CE15-X	AGTB03C15E	1000 kcmil - 1500 kcmil	1.41" - 2.56"

1/C 25kV Terminations (Outdoor Only)

Termination Kit	Cable Range	Insulation OD
AGT1CB25-0	#2 AWG - 2/0 AWG	0.67" - 1.10"
AGT1CC25-0	3/0 AWG - 250 kcmil	0.85" - 1.50"
AGT1CD25-0	350 kcmil - 750 kcmil	1.08" - 1.97"
AGT1CE25-0	500 kcmil - 1500 kcmil	1.41" - 2.56"

3/C 25kV Terminations (Outdoor Only)

Termination Kit	Break Out Kit	Cable Range	Insulation OD
AGT3CB25-0	AGTB03C25B	#2 AWG - 2/0 AWG	0.67" - 1.10"
AGT3CC25-0	AGTB03C25C	3/0 AWG - 250 kcmil	0.85" - 1.50"
AGT3CD25-0	AGTB03C25D	350 kcmil - 750 kcmil	1.08" - 1.97"
AGT3CE25-0	AGTB03C25E	500 kcmil - 1500 kcmil	1.41" - 2.56"

1/C 35kV Terminations (Outdoor Only)

Termination Kit	Cable Range	Insulation OD
AGT1CC35-0	1/0 AWG - 4/0 AWG	0.67" - 1.10"
AGT1CD35-0	250 kcmil - 350 kcmil	0.85" - 1.50"
AGT1CE35-0	500 kcmil - 750 kcmil	1.08" - 1.97"
AGT1CF35-0	750 kcmil - 1000 kcmil	1.41" - 2.56"

3/C 35kV Terminations (Outdoor Only)

Termination Kit	Break Out Kit	Cable Range	Insulation OD
AGT3CC35-0	AGTB03C35C	1/0 AWG - 4/0 AWG	0.67" - 1.10"
AGT3CD35-0	AGTB03C35D	250 kcmil - 350 kcmil	0.85" - 1.50"
AGT3CE35-0	AGTB03C35E	500 kcmil - 750 kcmil	1.08" - 1.97"
AGT3CF35-0	AGTB03C35F	750 kcmil - 1000 kcmil	1.41" - 2.56"