

# Air Conditioner Replacement Cords

3-Conductor Grounded • Type SPT-3 • 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PLUG CONFIG.	NEMA CONFIG.	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS						
04194.60.17	3	14	3	Beige	125	15	1875	Straight	5-15P	24	0.3	8	079407041947
04195.60.17	3	14	6	Beige	125	15	1875	Straight	5-15P	24	0.6	15	079407041657
04199.60.17	3	12	6	Beige	250	20	5000	Right Angle	6-20P	24	0.9	22	079407041992



**Product Construction:**

**Conductor:**

- 12 AWG and 14 AWG stranded bare copper per ASTM B174

**Insulation:**

- Premium-grade, color-coded PVC

**Jacket:**

- PVC; beige

**Applications:**

- For replacement use with air conditioners

**Features:**

- Conductor stripped 5/8"
- Free end slit 1 1/2"

**Industry Approvals:**

- UL Listed