

Clamp Light

2-Conductor Polarized • Type SPT-2 • 105°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING		NEMA CONFIG.	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	WATTS					
04170.60.02	2	18	6	White	125	150	1-15P	12	0.8	10	079407041701

Product Construction:

Conductor:

- 18 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade PVC; white
- Voltage rating: 300 volts

Applications:

- Temporary lighting

Features:

- 8 1/2" bell shade
- Clamp with protective vinyl sleeve
- Adjustable ball joint
- Switch socket

Industry Approvals:

- UL Listed

