

Coiled Power Tool Extension Cords and Power Supply Cords

2 and 3 Conductor • Type SJT • 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS					
06014.60.04	3	16	10	Orange	125	13	1625	5-15P/5-15R	10	1.1	11	079407060146
02551.70.01	3	16	12	Black	125	15	1875	5-15P	10	1.1	11	079407025510

Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; orange or black
- Voltage rating: 300 volts

Applications:

- Workshop and tool bench use

Features:

- Coiled cord expands from 3' to 10' or 12'
- Right-angle plug helps prevent the cord from being pulled from the socket

Features (cont'd.):

- 06014.60.04 and 02551.70.01 are 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable

