

Household Powr-Centers®

3-Conductor Grounded • Types SPT-3 and SJT • 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
TYPE SPT-3											
00655.63.04	3	14	3	Orange	125	15	1875	10	0.6	6	079407006557
TYPE SJT											
00565.63.17	3	16	9	Beige	125	13	1625	12	0.7	8	079407005659

Product Construction:

Conductor:

- 16 AWG or 14 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; orange or beige
- Voltage rating: 300 volts

Applications:

- Clocks
- Lamps
- Holiday lighting
- Other household appliances

Features:

- 3 grounded outlets

Industry Approvals:

- UL Listed

