

Major Appliance Cords

3-Conductor Grounded • Type SPT-3 • 15 and 20 Amps • 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS					
00436.63.17	3	14	6	Beige	125	15	1875	5-15P/5-15R	24	0.6	15	079407004362
00439.63.17	3	14	9	Beige	125	15	1875	5-15P/5-15R	24	0.9	21	079407004393
00442.63.17	3	14	12	Beige	125	15	1875	5-15P/5-15R	12	1.2	14	079407004423
00762.63.17	3	12	9	Beige	250	20	5000	6-20P/6-20R	24	1.4	34	079407007622
00772.63.17	3	12	9	Beige	125	20	2500	5-20P/5-20R	24	1.4	34	079407007721



Product Construction:

Conductor:

- 12 and 14 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade PVC; beige

Applications:

- Air conditioners
- Refrigerators
- Freezers
- Microwaves
- Dehumidifiers

Features:

- Molded right-angle plug

Industry Approvals:

- UL Listed