

Metal Guard Utility Light

3-Conductor Grounded • Type SJT • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS					
04455.60.05	3	16	25	Yellow	125	13	1650	15-15P	12	1.8	22	079407044559
04457.60.05	3	16	50	Yellow	125	13	1650	15-15P	6	3.5	21	079407044573



Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; yellow
- Voltage rating: 300 volts

Applications:

- Temporary lighting
- For general use only
- Not for use in hazardous locations

Features:

- Side outlet
- Metal hook
- On/off switch
- 75-watt bulb maximum
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable for general use