

Multiple Pair Aerial Service Wire

Spec. 4298

BELL SYSTEM TYPE

Product Construction:

Conductors:

- 22 AWG solid annealed copper

Insulation:

- Color-coded high density polyethylene

Jacket:

- The pairs and a .083" diameter galvanized steel messenger are enclosed in a black flame-retardant, weather- and abrasion-resistant PVC jacket in a Figure 8 configuration

Application(s):

- Provides multiple line telecommunication service connection to the subscriber

Compliances:

- Telcordia (Bellcore) Specification GR-3163-CORE
- RoHS Compliant (effective 1/1/10)

Packaging:

- Available in coils (CL) and reels (RL)



Nominal Cable Data

CATALOG NUMBER	PAIRS AWG	O.D. (INCHES)	WEIGHT (LBS/MFT)	STANDARD LENGTH (FT)
2091021	6	22	0.380 x 0.615	82 400 CL
2091015	6	22	0.380 x 0.615	82 500 RL
2091016	6	22	0.380 x 0.615	82 3500 RL

Data subject to change without notice. Contact your Customer Service Representative for latest information.