

Outdoor Powr-Center® Extension Cords

3-Conductor Grounded • Types STW, SJE00W and SJWT • -40°C to 60°C • 300 and 600 Volts



CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
STW-600 V											
00594.63.04	3	12	2	Orange	125	15	1875	6	1.0	6	079407005949
00596.61.04	3	12	50	Orange	125	15	1875	2	11.1	22	079407005963
00597.61.04	3	12	100	Orange	125	15	1875	2	21.7	43	079407005970
SJWT-300 V											
00690.63.04	3	14	10	Orange	125	15	1875	12	1.2	15	079407006908
00691.63.04	3	14	25	Orange	125	15	1875	6	2.6	16	079407006915
00692.63.04	3	14	50	Orange	125	15	1875	4	4.7	19	079407006922
00694.63.04	3	12	10	Orange	125	15	1875	12	1.8	22	079407006946
00696.63.04	3	12	50	Orange	125	15	1875	2	7.0	14	079407006960
00697.63.04	3	12	100	Orange	125	15	1875	2	13.4	27	079407006977
ALL WEATHER HIGH VISIBILITY SJE00W-300 V											
00790.63.07	3	14	10	Blue	125	15	1875	12	1.3	16	079407007905
00791.63.07	3	14	25	Blue	125	15	1875	6	2.7	16	079407007912
00792.63.07	3	14	50	Blue	125	15	1875	4	4.8	19	079407007929
00793.63.07	3	14	100	Blue	125	13	1625	2	9.0	18	079407007936
00787.63.05	3	12	50	Yellow	125	15	1875	2	6.5	13	079407007875
00788.63.05	3	12	100	Yellow	125	15	1875	2	13.0	26	079407007882

Product Construction:

- Conductor:**
 - 14 AWG or 12 AWG stranded bare copper per ASTM B174
- Insulation:**
 - Premium-grade, color-coded PVC
- Jacket:**
 - PVC; orange, TPE; blue or yellow
 - Temperature range: -40°C to 60°C
 - Voltage rating: 300 and 600 volts
- NEMA Configuration:**
 - 5-15P/5-15R

Applications:

- General use indoor/outdoor cord
- Chain saws
- Wet/dry vacs
- Orbital sanders
- Other power equipment

Features:

- Indoor/outdoor use
- 3 grounded outlets

Industry Approvals:

- UL Listed
- OSHA Acceptable