

# Plastic Guard Utility Light

3-Conductor Grounded • Type SJT • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
04497.60.05	3	16	50	Yellow	125	13	1650	6	3.5	21	079407044979



## Product Construction:

### Conductor:

- 16 AWG stranded bare copper per ASTM B174

### Insulation:

- Premium-grade, color-coded PVC

### Jacket:

- PVC; yellow
- Voltage rating: 300 volts

## Applications:

- Temporary lighting
- For general use only
- Not for use in hazardous locations

## Features:

- Side outlet
- On/off switch
- 75-watt bulb maximum
- Swivel hook
- Polypropylene guard

## Industry Approvals:

- UL Listed
- OSHA Acceptable for general use