

Power Supply Replacement Cords

3-Conductor Grounded • Types SJ, SJOW and SJOOW • 60°C • 300 Volts



CATALOG NUMBER	CORD TYPE	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PLUG CONFIG.	PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
						VOLTS	AMPS	WATTS						
02685.70.01	SJOOW	3	18	8	Black	125	10	1250	5-15P	Straight	25	0.6	14	079407026852
02686.70.01	SJOW	3	16	8	Black	125	13	1625	5-15P	Straight	35	0.7	24	079407026869
04932.70.01	SJ	3	16	12	Black	125	13	1625	5-15P	Straight	50	0.8	40	079407049325
04929.70.01	SJ	3	16	9	Black	125	13	1625	5-15P	Straight	50	0.6	30	079407049295
04926.70.01	SJ	3	16	6	Black	125	13	1625	5-15P	Straight	50	0.6	28	079407049264

Product Construction:

Conductor:

- 18 AWG or 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded EPDM

Jacket:

- CPE; black

Applications:

- For replacement use

Features:

- For replacement use
- Straight plug

Industry Approvals:

- UL Listed
- CSA