

# Power Supply Replacement Cords with Switch

3-Conductor Grounded • Type SJ • 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	SWITCH SPEED	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS						
02332.70.01	3	16	10	Black	125	10	1250	5-15P	1 Speed (On/Off)	25	0.9	22	079407023325
02333.70.01	4	16	10	Black	125	10	1250	5-15P	2 Speed (On/High/Low)	25	0.9	22	079407023332

**Product Construction:**

**Conductor:**

- 16 AWG stranded bare copper per ASTM B174

**Insulation:**

- Premium-grade, color-coded EPDM

**Jacket:**

- CPE; black

**Applications:**

- For replacement use
- For fan replacements

**Features:**

- Switch
- Straight plug
- Conductor stripped 5/8"
- Jacket removed 2"

**Industry Approvals:**

- UL Listed
- CSA

