

Powr-Reel™ with 3 Outlets

3-Conductor Grounded • Type SJO • 90°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
44623.61.05	3	16	25	Yellow	125	10	1250	4	2.7	11	079407446230



Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded 90°C EPDM

Jacket:

- CPE; yellow
- Voltage rating: 300 volts

Applications:

- Shop tools

Features:

- Tangle-Proof® instant cord storage
- Sturdy metal reel case
- Rubber cord
- 3 grounded outlets
- Cord locks in place; pull on cord to engage retractable reel

Industry Approvals:

- UL Listed
- OSHA Acceptable