

Pro Flex® Rubber Extension Cords

3-Conductor Grounded • Type SJ • 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS					
06610.63.01	3	16	10	Black	125	13	1625	5-15P/5-15R	24	0.7	17	079407066100
06625.63.01	3	16	25	Black	125	13	1625	5-15P/5-15R	24	1.7	40	079407066254
06911.63.01	3	14	25	Black	125	15	1875	5-15P/5-15R	6	2.3	14	079407069118



Product Construction:

Conductor:

- 16 AWG through 14 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded EPDM

Jacket:

- CPE; black
- Temperature: 60°C
- Voltage rating: 300 volts

Applications:

- Floor polishers
- Sanders

Features:

- General use indoor cord
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable for indoor use