

Wood Reel Length Table (Feet)

| Flange (in) | 29.5 PLY | 38 | 48 | 59 | 72 | 78 | 85 | 96 | 96 |
|----------------------|----------|--------|--------|--------|--------|--------|--------|--------|--------|
| Traverse (in) | 18 | 27 | 22 | 40 | 36 | 39.75 | 39.75 | 48 | 52 |
| Drum (in) | 12 | 20 | 24 | 32 | 36 | 40 | 42 | 42 | 42 |
| Outside (in) | 20 | 31 | 26 | 44 | 42 | 46 | 46 | 54 | 58 |
| Weight (lbs) | 40 | 90 | 178 | 300 | 616 | 690 | 830 | 1,150 | 1,150 |
| Cable OD (in) | | | | | | | | | |
| 0.300 | 5,490 | 12,633 | 19,153 | N/A | N/A | N/A | N/A | N/A | N/A |
| 0.325 | 4,827 | 11,180 | 15,782 | 41,010 | 41,010 | N/A | N/A | N/A | N/A |
| 0.350 | 3,955 | 9,264 | 13,561 | 36,943 | 41,010 | N/A | N/A | N/A | N/A |
| 0.375 | 3,513 | 8,205 | 11,675 | 32,060 | 41,010 | N/A | N/A | N/A | N/A |
| 0.400 | 3,088 | 7,193 | 10,674 | 28,019 | 41,010 | N/A | N/A | N/A | N/A |
| 0.425 | 2,682 | 6,334 | 8,962 | 25,459 | 38,016 | 41,010 | N/A | N/A | N/A |
| 0.450 | 2,359 | 5,615 | 8,052 | 21,786 | 34,120 | 41,010 | N/A | N/A | N/A |
| 0.475 | 2,221 | 4,843 | 7,336 | 19,938 | 29,975 | 38,758 | 41,010 | N/A | N/A |
| 0.500 | 1,976 | 4,728 | 6,642 | 18,147 | 26,800 | 34,546 | 41,010 | N/A | N/A |
| 0.525 | 1,689 | 4,090 | 5,832 | 16,419 | 24,535 | 31,882 | 38,790 | 41,010 | N/A |
| 0.550 | 1,614 | 3,568 | 5,335 | 14,759 | 22,682 | 28,386 | 34,901 | 41,010 | N/A |
| 0.575 | 1,398 | 3,385 | 5,130 | 13,368 | 19,845 | 26,291 | 32,524 | 41,010 | N/A |
| 0.600 | 1,372 | 2,973 | 4,529 | 12,034 | 18,446 | 24,249 | 30,195 | 41,010 | N/A |
| 0.625 | N/A | 2,868 | 4,078 | 11,787 | 16,785 | 22,267 | 27,919 | 41,010 | N/A |
| 0.650 | N/A | 2,761 | 3,886 | 10,518 | 15,469 | 20,688 | 24,928 | 41,010 | N/A |
| 0.675 | N/A | 2,385 | 3,465 | 9,475 | 15,069 | 18,826 | 22,824 | 39,850 | 41,010 |
| 0.700 | N/A | 2,286 | 3,390 | 9,235 | 13,801 | 17,347 | 21,172 | 37,129 | 40,405 |
| 0.725 | N/A | 1,941 | 2,992 | 8,249 | 12,578 | 15,917 | 20,630 | 34,999 | 37,650 |
| 0.750 | N/A | 1,903 | 2,918 | 8,015 | 11,647 | 15,770 | 19,398 | 32,903 | 35,473 |
| 0.775 | N/A | 1,811 | 2,843 | 7,090 | 11,268 | 14,388 | 17,836 | 30,349 | 33,334 |
| 0.800 | N/A | 1,771 | 2,475 | 7,004 | 10,376 | 13,061 | 16,329 | 28,834 | 31,237 |
| 0.825 | N/A | 1,467 | 2,404 | 6,134 | 10,003 | 12,905 | 15,199 | 26,871 | 29,187 |
| 0.850 | N/A | 1,431 | 2,065 | 6,049 | 9,155 | 11,637 | 14,694 | 24,960 | 27,188 |
| 0.875 | N/A | 1,394 | 2,080 | 5,833 | 9,012 | 11,477 | 13,610 | 23,106 | 25,245 |
| 0.900 | N/A | 1,403 | 2,013 | 5,154 | 8,198 | 10,513 | 13,420 | 21,721 | 23,361 |
| 0.925 | N/A | 1,365 | 1,943 | 5,070 | 7,850 | 10,112 | 12,083 | 21,104 | 23,173 |
| 0.950 | N/A | 1,097 | 1,712 | 4,984 | 7,088 | 9,203 | 11,889 | 19,764 | 21,345 |
| 0.975 | N/A | 1,064 | 1,649 | 4,350 | 6,948 | 9,044 | 10,897 | 18,454 | 19,960 |
| 1.000 | N/A | 1,070 | 1,660 | 4,270 | 6,405 | 8,177 | 10,705 | 18,239 | 19,758 |
| 1.025 | N/A | N/A | 1,596 | 4,188 | 6,270 | 8,022 | 9,757 | 16,603 | 18,047 |
| 1.050 | N/A | N/A | 1,317 | 4,104 | 6,133 | 7,864 | 9,568 | 16,380 | 17,836 |
| 1.075 | N/A | N/A | 1,325 | 3,527 | 5,449 | 7,051 | 8,666 | 15,165 | 16,544 |
| 1.100 | N/A | N/A | 1,333 | 3,450 | 5,318 | 7,096 | 8,725 | 14,941 | 16,331 |
| 1.125 | N/A | N/A | 1,274 | 3,372 | 5,352 | 6,943 | 8,540 | 13,770 | 15,082 |
| 1.150 | N/A | N/A | 1,282 | 3,293 | 4,708 | 6,173 | 7,680 | 13,547 | 14,868 |
| 1.175 | N/A | N/A | 1,032 | 3,311 | 4,584 | 6,027 | 7,501 | 12,425 | 13,667 |
| 1.200 | N/A | N/A | 1,037 | 2,791 | 4,611 | 6,062 | 7,548 | 12,517 | 13,455 |
| 1.225 | N/A | N/A | N/A | 2,719 | 4,484 | 5,338 | 6,735 | 11,428 | 12,307 |
| 1.250 | N/A | N/A | N/A | 2,732 | 3,894 | 5,200 | 6,563 | 11,213 | 12,098 |
| 1.275 | N/A | N/A | N/A | 2,660 | 3,916 | 5,228 | 6,601 | 10,994 | 11,885 |
| 1.300 | N/A | N/A | N/A | 2,586 | 3,797 | 5,087 | 5,838 | 9,970 | 11,078 |
| 1.325 | N/A | N/A | N/A | 2,598 | 3,817 | 4,577 | 5,870 | 10,036 | 10,873 |
| 1.350 | N/A | N/A | N/A | 2,138 | 3,696 | 4,447 | 5,706 | 9,822 | 10,664 |

Yellow highlighted items cannot be used with armored cable.
 Orange highlighted items are limited to the cable production length.

© DRAKA & PRYSMIAN - Brands of The Prysmian Group. 2016 All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued May 2016.

Wood Reel Length Table (Meters)

| Flange (in) | 29.5 PLY | 38 | 48 | 59 | 72 | 78 | 85 | 96 | 96 |
|----------------------|----------|-------|-------|--------|--------|--------|--------|--------|--------|
| Traverse (in) | 18 | 27 | 22 | 40 | 36 | 39.75 | 39.75 | 48 | 52 |
| Drum (in) | 12 | 20 | 24 | 32 | 36 | 40 | 42 | 42 | 42 |
| Outside (in) | 20 | 31 | 26 | 44 | 42 | 46 | 46 | 54 | 58 |
| Weight (lbs) | 40 | 90 | 178 | 300 | 616 | 690 | 830 | 1,150 | 1,150 |
| Cable OD (mm) | | | | | | | | | |
| 8.0 | 1,509 | 3,464 | 5,137 | 12,500 | 12,500 | N/A | N/A | N/A | N/A |
| 8.5 | 1,332 | 3,104 | 4,492 | 12,110 | 12,500 | N/A | N/A | N/A | N/A |
| 9.0 | 1,187 | 2,796 | 4,148 | 11,097 | 12,500 | N/A | N/A | N/A | N/A |
| 9.5 | 1,070 | 2,500 | 3,557 | 9,766 | 12,500 | N/A | N/A | N/A | N/A |
| 10.0 | 937 | 2,217 | 3,240 | 9,006 | 12,500 | N/A | N/A | N/A | N/A |
| 10.5 | 910 | 1,979 | 2,990 | 7,872 | 11,906 | 12,500 | N/A | N/A | N/A |
| 11.0 | 804 | 1,909 | 2,692 | 7,252 | 11,090 | 12,500 | N/A | N/A | N/A |
| 11.5 | 703 | 1,686 | 2,459 | 6,651 | 9,888 | 12,500 | N/A | N/A | N/A |
| 12.0 | 695 | 1,501 | 2,233 | 6,070 | 9,244 | 11,938 | 12,500 | N/A | N/A |
| 12.5 | 600 | 1,436 | 2,016 | 5,579 | 8,613 | 11,057 | 12,500 | N/A | N/A |
| 13.0 | 591 | 1,264 | 1,945 | 5,105 | 7,996 | 9,906 | 12,500 | N/A | N/A |
| 13.5 | 502 | 1,226 | 1,784 | 4,954 | 7,057 | 9,213 | 11,709 | 12,500 | N/A |
| 14.0 | 493 | 1,066 | 1,587 | 4,501 | 6,590 | 8,658 | 10,645 | 12,500 | N/A |
| 14.5 | 426 | 1,053 | 1,561 | 4,127 | 6,452 | 7,998 | 9,892 | 12,500 | N/A |
| 15.0 | 417 | 1,016 | 1,413 | 3,983 | 5,899 | 7,471 | 9,299 | 12,500 | N/A |
| 15.5 | N/A | 890 | 1,387 | 3,628 | 5,462 | 6,956 | 8,718 | 12,500 | N/A |
| 16.0 | N/A | 856 | 1,211 | 3,286 | 5,128 | 6,802 | 8,150 | 12,500 | N/A |
| 16.5 | N/A | 842 | 1,185 | 3,206 | 4,715 | 6,305 | 7,597 | 12,500 | N/A |
| 17.0 | N/A | 726 | 1,054 | 2,883 | 4,582 | 5,824 | 7,414 | 12,111 | 12,500 |
| 17.5 | N/A | 713 | 1,029 | 2,854 | 4,270 | 5,359 | 6,879 | 11,420 | 12,413 |
| 18.0 | N/A | 699 | 1,037 | 2,774 | 3,887 | 5,306 | 6,477 | 10,743 | 11,705 |
| 18.5 | N/A | 593 | 913 | 2,472 | 3,839 | 4,858 | 5,972 | 10,081 | 11,012 |
| 19.0 | N/A | 580 | 889 | 2,442 | 3,548 | 4,804 | 5,908 | 10,020 | 10,803 |
| 19.5 | N/A | 567 | 865 | 2,199 | 3,426 | 4,374 | 5,422 | 9,371 | 10,127 |
| 20.0 | N/A | 555 | 752 | 2,127 | 3,149 | 4,319 | 5,356 | 8,740 | 9,614 |
| 20.5 | N/A | 542 | 757 | 2,097 | 3,101 | 3,991 | 4,991 | 8,268 | 8,968 |
| 21.0 | N/A | 448 | 734 | 1,871 | 2,835 | 3,936 | 4,636 | 8,197 | 8,762 |
| 21.5 | N/A | 436 | 629 | 1,842 | 2,788 | 3,543 | 4,474 | 7,597 | 8,275 |
| 22.0 | N/A | 438 | 633 | 1,813 | 2,739 | 3,489 | 4,137 | 7,148 | 7,798 |
| 22.5 | N/A | 427 | 611 | 1,784 | 2,488 | 3,191 | 4,071 | 7,074 | 7,598 |
| 23.0 | N/A | 414 | 615 | 1,574 | 2,441 | 3,137 | 4,005 | 6,635 | 7,136 |
| 23.5 | N/A | 417 | 593 | 1,546 | 2,393 | 3,083 | 3,684 | 6,434 | 7,064 |
| 24.0 | N/A | 335 | 522 | 1,518 | 2,216 | 2,870 | 3,707 | 6,013 | 6,614 |
| 24.5 | N/A | 324 | 502 | 1,489 | 2,170 | 2,817 | 3,394 | 5,936 | 6,420 |
| 25.0 | N/A | 325 | 504 | 1,297 | 2,124 | 2,764 | 3,331 | 5,529 | 5,989 |
| 25.5 | N/A | N/A | 484 | 1,271 | 1,900 | 2,496 | 3,267 | 5,451 | 5,915 |
| 26.0 | N/A | N/A | 487 | 1,276 | 1,911 | 2,445 | 2,973 | 5,059 | 5,498 |
| 26.5 | N/A | N/A | 421 | 1,250 | 1,866 | 2,458 | 2,990 | 5,092 | 5,425 |
| 27.0 | N/A | N/A | 403 | 1,222 | 1,656 | 2,203 | 2,927 | 4,709 | 5,023 |
| 27.5 | N/A | N/A | 405 | 1,048 | 1,665 | 2,154 | 2,647 | 4,634 | 5,056 |
| 28.0 | N/A | N/A | 387 | 1,053 | 1,622 | 2,165 | 2,661 | 4,558 | 4,982 |
| 28.5 | N/A | N/A | 389 | 1,028 | 1,631 | 2,115 | 2,601 | 4,194 | 4,593 |
| 29.0 | N/A | N/A | 391 | 1,032 | 1,588 | 1,878 | 2,336 | 4,220 | 4,521 |
| 29.5 | N/A | N/A | 372 | 1,007 | 1,393 | 1,887 | 2,348 | 4,144 | 4,447 |
| 30.0 | N/A | N/A | 315 | 981 | 1,400 | 1,840 | 2,290 | 3,794 | 4,174 |

Yellow highlighted items cannot be used with armored cable.

Orange highlighted items are limited to the cable production length.

© DRAKA & PRYSMIAN - Brands of The Prysmian Group. 2016 All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued May 2016.