

Type SVT

60°C, 300 Volt, UL/CSA Portable Cord



TYPE SVT – 300 VOLT – UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WEIGHT LBS/M ^(S)	STD. CTN.
				INCHES	mm	INCHES	mm			
86002	2	18	41/34	0.015	0.38	0.235	5.97	10	35	1000'
86003	3	18	41/34	0.015	0.38	0.240	6.10	10	40	1000'

† Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).

® Actual shipping weight may vary.

Product Construction:

Conductors:

- 18 AWG annealed stranded bare copper

Insulation:

- Premium-grade, color-coded PVC
- Color code: See chart below

Jacket:

- Polyvinyl Chloride (PVC)
- Colors available: black, white, gray
- Temperature range: -20°C to +60°C
- Ribbed jacket

Jacket Marking:

- (SIZE) (mm²) 60°C SVT (UL) E# --- CSA LL# FT2 ROHS MADE IN USA 300 V

Applications:

- Vacuum cleaners
- Food mixers
- Office equipment

Features:

- Resists:
 - Acids
 - Alkalies
 - Ozone

Industry Approvals:

- UL Listed
- CSA Certified
- RoHS Compliant

Packaging:

- 250' (76.2 m)
- Other sizes and put-ups available on special order

COLOR CODE CHART

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green