

Irrigation & Landscape Lighting

SOLUTIONS GUIDE

Underground Feeder (UF) Cable 600 V Single Conductor, PVC Insulated

Applications:

- For use in irrigation as described in Article 339 of the National Electric Code (NEC)
- 18 AWG and 16 AWG are not permitted to be UL Listed as Type UF*

Standard Put-Ups:

- 500'
- 1000'
- 2500'

Standard Colors:

- Please consult customer service for information on available colors



ISOTEC PART NUMBER	AWG/STRANDING	INSULATION THICKNESS INCHES	NOMINAL O.D. INCHES	WEIGHT PER MFT
181UF*	18 (Solid)	0.045	0.134	13
161UF*	16 (Solid)	0.045	0.144	17
141UF	14 (Solid)	0.060	0.186	28
121UF	12 (Solid)	0.060	0.205	37
101UF	10 (Solid)	0.060	0.225	52

Note: PE UF cable is available upon special request. Please consult customer service.