

Irrigation & Landscape Lighting

SOLUTIONS GUIDE

Underground Low-Voltage Landscape Lighting Cable 150 V Flat Parallel, PVC Insulated

Applications:

- For use in wiring low-voltage outdoor landscape lighting and security lighting circuits where cable must be suitable for direct burial

Standard Put-Ups:

- 250'
- 500'
- 1000'

Standard Jacket Color:

- Black



ISOTEC PART NUMBER	AWG/STRANDING	NOM. INS. THICKNESS INCHES	NOMINAL O.D. INCHES	WEIGHT PER MFT
182ULC00	18 16/30 B/C	0.041	.209 X .145	26
162ULC00	16 26/30 B/C	0.041	.315 X .155	36
142ULC00	14 41/30 B/C	0.041	.350 X .170	46
122ULC00	12 65/30 B/C	0.041	.390 X .195	86
102ULC00	10 105/30 B/C	0.062	.470 X .240	122
802ULC00	8 133/.0125 B/C	0.078	.630 X .316	199