

MV Cable Accessories

Pre-Attached Single-Use Cable Pulling Lugs

Prysmian
MV ACCESSORIES



Simple, Easy, Reliable, Durable, Low Cost

KEY BENEFITS

- Beveled edge for easier pulls around corners.
- Use once and then recycle along with scrap wire.
- Available in 18 sizes (8 AWG through 1000 mcm) to be used in sets to accommodate jobs of different sizes.
- Works on 600 volts through 35 KV wire and rated for both copper and aluminum wire.
- The lanyards are available in a variety of lengths to make staggering multiple wire pulls effortless especially through and around nineties.
- The small pulling head reduces friction - no need to oversize conduit to accommodate the pulling head.
- Installed in the factory.
- Items highlighted are for 1/C Cables (shortest lanyard)
- Additional lanyards can be added for 1/C Triplexed and Paralleled cable configurations up to 4X 1/C

MV Cable Accessories

Pre-Attached Single-Use Cable Pulling Lugs

Product Selection Chart

Product Description	Catalog Number	Maximum Loading Per Phase
SU 8 AWG Pulling Eye w/11" lanyard	98120	130
SU 8 AWG Pulling Eye w/15" lanyard	98117	130
SU 8 AWG Pulling Eye w/19" lanyard	98118	130
SU 8 AWG Pulling Eye w/23" lanyard	98119	130
SU 6 AWG Pulling Eye w/11" lanyard	98137	210
SU 6 AWG Pulling Eye w/15" lanyard	98138	210
SU 6 AWG Pulling Eye w/19" lanyard	98139	210
SU 6 AWG Pulling Eye w/23" lanyard	98140	210
SU 4 AWG Pulling Eye w/11" lanyard	98133	300
SU 4 AWG Pulling Eye w/15" lanyard	98134	300
SU 4 AWG Pulling Eye w/19" lanyard	98135	300
SU 4 AWG Pulling Eye w/23" lanyard	98136	300
SU 3 AWG Pulling Eye w/11" lanyard	98129	400
SU 3 AWG Pulling Eye w/15" lanyard	98130	400
SU 3 AWG Pulling Eye w/19" lanyard	98131	400
SU 3 AWG Pulling Eye w/23" lanyard	98132	400
SU 2 AWG Pulling Eye w/11" lanyard	98125	500
SU 2 AWG Pulling Eye w/15" lanyard	98126	500
SU 2 AWG Pulling Eye w/19" lanyard	98127	500
SU 2 AWG Pulling Eye w/23" lanyard	98128	500
SU 1 AWG Pulling Eye w/11" lanyard	98121	669
SU 1 AWG Pulling Eye w/15" lanyard	98122	669
SU 1 AWG Pulling Eye w/19" lanyard	98123	669
SU 1 AWG Pulling Eye w/23" lanyard	98124	669
SU 1/0 AWG Pulling Eye w/14" lanyard	98141	844
SU 1/0 AWG Pulling Eye w/21" lanyard	98142	844
SU 1/0 AWG Pulling Eye w/28" lanyard	98143	844
SU 1/0 AWG Pulling Eye w/35" lanyard	98144	844
SU 2/0 AWG Pulling Eye w/14" lanyard	98145	1000
SU 2/0 AWG Pulling Eye w/21" lanyard	98146	1000
SU 2/0 AWG Pulling Eye w/28" lanyard	98147	1000
SU 2/0 AWG Pulling Eye w/35" lanyard	98148	1000
SU 3/0 AWG Pulling Eye w/14" lanyard	98149	1250
SU 3/0 AWG Pulling Eye w/21" lanyard	98150	1250
SU 3/0 AWG Pulling Eye w/28" lanyard	98151	1250
SU 3/0 AWG Pulling Eye w/35" lanyard	98152	1250

Product Description	Catalog Number	Maximum Loading Per Phase
SU 4/0 AWG Pulling Eye w/14" lanyard	98153	1650
SU 4/0 AWG Pulling Eye w/21" lanyard	98154	1650
SU 4/0 AWG Pulling Eye w/28" lanyard	98155	1650
SU 4/0 AWG Pulling Eye w/35" lanyard	98156	1650
SU 250 MCM Pulling Eye w/14" lanyard	98157	2000
SU 250 MCM Pulling Eye w/21" lanyard	98158	2000
SU 250 MCM Pulling Eye w/28" lanyard	98159	2000
SU 250 MCM Pulling Eye w/35" lanyard	98160	2000
SU 300 MCM Pulling Eye w/14" lanyard	98161	2400
SU 300 MCM Pulling Eye w/21" lanyard	98162	2400
SU 300 MCM Pulling Eye w/28" lanyard	98163	2400
SU 300 MCM Pulling Eye w/35" lanyard	98164	2400
SU 350 MCM Pulling Eye w/14" lanyard	98165	2400
SU 350 MCM Pulling Eye w/21" lanyard	98166	2400
SU 350 MCM Pulling Eye w/28" lanyard	98167	2400
SU 350 MCM Pulling Eye w/35" lanyard	98168	2400
SU 400 MCM Pulling Eye w/14" lanyard	98169	2400
SU 400 MCM Pulling Eye w/21" lanyard	98170	2400
SU 400 MCM Pulling Eye w/28" lanyard	98171	2400
SU 400 MCM Pulling Eye w/35" lanyard	98172	2400
SU 500 MCM Pulling Eye w/14" lanyard	98173	4000
SU 500 MCM Pulling Eye w/21" lanyard	98174	4000
SU 500 MCM Pulling Eye w/28" lanyard	98175	4000
SU 500 MCM Pulling Eye w/35" lanyard	98176	4000
SU 600 MCM Pulling Eye w/14" lanyard	98177	4200
SU 600 MCM Pulling Eye w/21" lanyard	98178	4200
SU 600 MCM Pulling Eye w/28" lanyard	98179	4200
SU 600 MCM Pulling Eye w/35" lanyard	98180	4200
SU 750 MCM Pulling Eye w/14" lanyard	98181	4300
SU 750 MCM Pulling Eye w/21" lanyard	98182	4300
SU 750 MCM Pulling Eye w/28" lanyard	98183	4300
SU 750 MCM Pulling Eye w/35" lanyard	98184	4300
SU 1000 MCM Pulling Eye w/14" lanyard	98185	5000
SU 1000 MCM Pulling Eye w/21" lanyard	98186	5000
SU 1000 MCM Pulling Eye w/28" lanyard	98187	5000
SU 1000 MCM Pulling Eye w/35" lanyard	98188	5000