


Telecom Product Line

Loose Tube, Ribbon, Drop and Specialty Fiber Cables




LOOSE TUBE CABLES




	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY	Fiber Count
1	LT 2.0™	All-Dielectric	E2G1JKT	E2D1JKT	4-456
		SA/SJ	E2G1A1J	E2D1A1J	4-456
		SA/DJ	E2G1A2J	E2D1A2J	4-456
		DA/DJ	E2G2A2J	E2D2A2J	4-288
		DA/TJ	E2G2A3J	E2D2A3J	4-288
		Dual Jacket NA	E2GNA2J	E2DNA2J	4-288
2	ExpressLT™	All-Dielectric	ETH1JKT	EDH1JKT	4-432
		SA/SJ	ETH1A1J	EDH1A1J	4-432
		SA/DJ	ETH1A2J	EDH1A2J	4-432
		DA/DJ	ETH2A2J	EDH2A2J	4-288
		DA/TJ	ETH2A3J	EDH2A3J	4-288
		Dual Jacket NA	ETHNA2J	EDHNA2J	4-288
		Dielectric Armor	ETHDA2J	EDHDA2J	4-288
3	CentralLT 600	SA/SJ	C6H1A1J	D6H1A1J	2-12
4	MicroUnitube™	All-Dielectric	UMH1JKT	--	2-12
		SA/SJ	UMR1A1J	--	2-24

OSP RIBBON CABLES




	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY TUBES	Fiber Count
1	FusionLink™ RICT (Gel)	All-Dielectric	RCG1JKT	--	12-864
		SA/SJ	RCG1A1	--	12-864
	Dry FusionLink™ RICT (Coupled)	All-Dielectric	--	RCD1JKT	60-432, 612-864
		SA/SJ	--	RCD1A1J	60-432, 612-864
	Dry FusionLink™ RICT (Uncoupled)	All-Dielectric	--	RCU1JKT	12-48, 576
		SA/SJ	--	RCU1A1J	12-48, 576
FusionLink™ with FlexRibbon	All-Dielectric	--	RCF1JKT	96-432	
	SA/SJ	--	RCF1A1J	96-432	
MicroDuct with FlexRibbon	All-Dielectric	--	RCFMD51JKT	288-864	
2	MassLink™ Multi-Tube Ribbon	All-Dielectric	RLG1JKT	--	288-1728
		SA/SJ	RLG1A1J	--	288-1728
		SA/DJ	RLG1A2J	--	288-432
	MassLink™ with FlexRibbon	DA/DJ	--	RLF1JKT	432-6912
DA/TJ		--	RLF1A1J	432-864	
		Dual Jacket NA	--	RLF1A2J	1728

DROP CABLES




	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY TUBE	Fiber Count
1	ResiLink™ Flat Drop	A Dielectric	DFD1JKT	--	1-24
		B Toneable	DFDNATJ	--	1-24
2	ResiLink™ Universal Service Drop	Dielectric	D3D1JKT	--	1
		Toneable	D3DNATJ	--	1
3	Central LT 300	SA/SJ, with Ripcords	C3R1A1J	D3R1A1J	1-12
		SA/SJ, w/o Ripcords	C3H1A1J	D3H1A1J	1-12
4	ezDrop™ Figure 8	Non-Armored	DF81JKT	--	1-6
	FlexDrop	Dielectric	--	RFD1JKT	12 or 24

APPLICATION SPECIFIC CABLES



	Product Family	Sheath Design	Family P/N GEL TUBE	Family P/N DRY TUBE	Fiber Count
1	ezMicroDuct™	≥ 10 mm ID duct	MDS1JKT	--	6-72
		≥ 10 mm ID duct	MDM1JKT-24	--	96-288
		≥ 12 mm ID duct	MDS1JKT	--	84-96
		≥ 12 mm ID duct	MDM1JKT-12	--	96-144
		≥ 13 mm ID duct	MDM1JKT-12	--	156-288
		≥ 13 mm ID duct	MDS1JKT-24	--	144
		≥ 14 mm ID duct	MDM1JKT-24	--	312-528
2	AeroLink™ Figure 8	All-Dielectric	F8A1JKT	F8D1JKT	12-216
		SA/SJ	F8A1A1J	F8D1A1J	12-216
3	ADSS EZSPAN™ Span	Single Jacket	ADES	ADFS	6-144
		Dual Jacket	ADED	--	6-144
4	ADSS Long Span	Single Jacket	ADLS	--	6-432
		Dual Jacket	ADLD	--	6-432
		Track Resistant Jacket	ADLT	--	6-432

INDOOR/OUTDOOR CABLES




	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY TUBE	Fiber Count
1	Indoor/Outdoor ezDistribution™	A Single Jacket, Non-Unitized	C1181-00	Riser	2 to 24
		B Interlock Armor	C1181AJ-00	Conductive Riser	2 to 24
		A Single Jacket, Unitized	C1181-12	Riser	24 to 144
		B Interlock Armor	C1181AJ-12	Conductive Riser	24 to 144
		A LSZH Single Jacket, Non-Unitized	700-00	Riser - LS	2 to 24
		C LSZH Interlock Armor	700AJ-00	Conductive Riser - LS	2 to 24
		A Single Jacket, non-unitized	C1182-00	Plenum	2 to 24
B Interlock Armor	C1182AJ-00	Conductive Plenum	2 to 24		
2	Indoor/Outdoor CampusLink™ Stranded Loose Tube Gel-Filled Tube	A Single Jacket	DRLTB-12	Riser	2 to 144
		A Double Jacket	DRLTC-12	Riser	2 to 144
		B Double Jacket with Corrugated Steel Armor	DRLTD-12	Conductive Riser	2 to 144
		B Interlock Armor	DRLTBAJ-12	Conductive Riser	2 to 144
	Indoor/Outdoor CampusLink™ Stranded Loose Tube Gel-Free Tube	A Single Jacket	DRLDB-12	Riser	2 to 288
		A Double Jacket	DRLDC-12	Riser	2 to 144
		B Double Jacket with Corrugated Steel Armor	DRLDD-12	Conductive Riser	2 to 144
		B Interlock Armor	DRLDBAJ-12	Conductive Riser	2 to 288
3	Indoor/Outdoor CampusLink™ Central Loose Tube Gel-Free Tube	A Single Jacket	DPLDB-12	Plenum	2 to 144
		B Interlock Armor	DPLDB-12	Conductive Plenum	2 to 144
		A Single Jacket	DRLDB-00	Riser	2 to 12
		B Interlock Armor	DRLDBAJ-00	Conductive Riser	2 to 12
		A LSZH - Single Jacket	DDLSZHB-00	Riser	2 to 12
		B LSZH - Interlock Armor	DDLSZHBAJ-00	Conductive Riser	2 to 12
3	Indoor/Outdoor CampusLink™ Central Loose Tube Gel-Free Tube	A Single Jacket	DPLDB-00	Plenum	2 to 12
		B Interlock Armor	DPLDBAJ-00	Conductive Plenum	2 to 12

MFC CABLES



	Product Family	Sheath Design	Family P/N	Unit Size	Units	Flame Rating	Fiber Count
1	Micro Fiber Cable	Single Jacket	MFC14	1.4 mm	12f - Multi	Plenum	12-48
		Single Jacket	MFCL14	1.4 mm	12f - Multi	LSZH Riser	12-48
		Single Jacket	MFC20	2 mm	Single Unit	Plenum	8-12
		Single Jacket	MFC20	2 mm	8 or 12f - Multi	Plenum	8-216
		Interlock Armor	MFC20AJ	2 mm	8 or 12f - Multi	Plenum	8-144
		Single Jacket	MFC30	3 mm	Single Unit	Plenum	8-24
		Interlock Armor	MFC30AJ	3 mm	Single Unit	Plenum	8-24
		Single Jacket	MFC	3 mm	Single Unit	Plenum	8-12
		Single Jacket	MFC	3.8 mm	Single Unit	Plenum	16-24
		Single Jacket	MFC	3 mm	8 or 12f - Multi	Plenum	8-72
		Interlock Armor	MFCAJ	3 mm	8 or 12f - Multi	Plenum	8-72
		Double Jacket	MFCDJ	3 mm	Single Unit	Plenum	8-12
		Single Jacket	MFCL	3 mm	Single Unit	LSZH Riser	8-12
		Single Jacket	MFCL	3.8 mm	Single Unit	LSZH Riser	16-24
		Single Jacket Zipcord	MFCZ	3 mm	2 x 12f	Plenum	16-24
		Single Jacket	MFC36	3.6 mm	Single Unit	Plenum	16-24
		Single Jacket	MFCL36	3.6 mm	Single Unit	Plenum	16-24

INDOOR & INDOOR/OUTDOOR RIBBON CABLES




	Product Family	Sheath Design	Family P/N	Tube	Indoor or Indoor/Outdoor	Flame Rating	Fiber Count
1	COLink™ Ribbon Central Tube	Single Jacket	RRC DK	Dry	Indoor	Riser	12-432
		Interlock Armor	RRC DKAJ	Dry	Indoor	Riser	12-432
		Single Jacket	RPC DK	Dry	Indoor	Plenum	12-144
2	FusionLink™ Ribbon Central Tube	Single Jacket	RRIODCK	Dry	Indoor/Outdoor	Riser	12-48 & 240-864
		Interlock Armor	RRIODCAJ	Dry	Indoor/Outdoor	Riser	12-48 & 240-864
		Single Jacket	RZIODCK	Dry	Indoor/Outdoor	LSZH	48-144
		Single Jacket	RRCTK	Gel	Indoor/Outdoor	Riser	12-216 & 576-864
		Interlock Armor	RRCTKAJ	Gel	Indoor/Outdoor	Riser	12-216 & 576-864
	FusionLink™ 200µm fiber Central Tube with FlexRibbon	Single Jacket	RRCFK	Dry	Indoor	Riser	288 & 432
		Single Jacket	RRIODCFK	Dry	Indoor/Outdoor	Riser	288 & 432
3	MicroDuct 200µm with FlexRibbon	Single Jacket	RRCFKMD	Dry	Indoor	Riser	288
		Single Jacket	RRIODCFKMD	Dry	Indoor/Outdoor	Riser	288
4	COLink™ Multi-Tube Ribbon	Single Jacket	RRLDK	Dry	Indoor	Riser	144-576
		Interlock Armor	RRLDKAJ	Dry	Indoor	Riser	144-576
5	MassLink™ Multi-Tube Ribbon	Single Jacket	RRLTK	Gel	Indoor/Outdoor	Riser	288-432
		Interlock Armor	RRLTKAJ	Gel	Indoor/Outdoor	Riser	288-432
		Single Jacket	RZLTK	Gel	Indoor/Outdoor	LSZH	288-432
		Single Jacket	RRIOLDK	Dry	Indoor/Outdoor	Riser	864-1728
	MassLink™ Multi-Tube FlexRibbon	Single Jacket	RRLFk	Dry	Indoor	Riser	200 & 250µm fiber 864-1728
		Single Jacket	RRIOLFk	Dry	Indoor/Outdoor	Riser	200 & 250µm fiber 864-1728
		Single Jacket	RZLFk	Dry	Indoor	LSZH/OFNG	250µm fiber 1728
		Single Jacket	RZIOLFk	Dry	Indoor/Outdoor	LSZH/OFNG	250µm fiber 1728
		Single Jacket	RRZLFk	Dry	Indoor	LSZH/Riser/CPR	200µm fiber 864-3456
		Single Jacket	RRZIOLFk	Dry	Indoor	LSZH/Riser/CPR	200µm fiber 864-3456

INDOOR CABLES




	Product Family	Sheath Design	Family P/N	Flame Rating	Fiber Count
1	ezInterconnect™	A Simplex	516/520/529	Riser	1
			816/820/829	Plenum	1
			LSZH16/LSZH20/LSZH29	Riser - Low Smoke	1
		Zipcord	516Z/520Z/529Z	Riser	2
			816Z/820Z/829Z	Plenum	2
			LSZH16Z/LSZH20Z/LSZH29Z	Riser - Low Smoke	2
		B Duplex	529R	Riser	2
			829R	Plenum	2
		Quadplex	548R	Riser	4
			848R	Plenum	4

INDOOR CABLES



	Product Family	Sheath Design	Family P/N	Flame Rating	Fiber Count
1	Indoor ezDistribution™	Single Jacket, Non-Unitized	400-00	Riser	2 to 24
		Interlock Armor	400AJ-00	Conductive Riser	2 to 24
		Single Jacket, Unitized	400-12	Riser	24 to 144
		Interlock Armor	400AJ-12	Conductive Riser	24 to 144
		LSZH Single Jacket, Non-Unitized	600-00	Riser - LS	2 to 24
		LSZH Interlock Armor	600AJ-00	Conductive Riser - LS	2 to 24
		LSZH Single Jacket, Unitized	600-12	Riser - LS	24 to 144
		LSZH Interlock Armor	600AJ-12	Conductive Riser - LS	24 to 144
		Single Jacket, Non-Unitized	800-00	Plenum	2 to 24
		Interlock Armor	800AJ-00	Conductive Plenum	2 to 24
		Single Jacket, Unitized	800-12	Plenum	24 to 144
		Interlock Armor	800AJ-12	Conductive Plenum	24 to 144

SPECIALTY CABLES



	Product Family	Sheath Design	Family P/N	Tube	Indoor/Outdoor	Flame Rating	Fiber Count
1	Airguard™ XP Oil & Gas Chemical Resistant	Double Jacket All-Dielectric	XPRLTM	Gel	Yes	OFNG-ST1/FT4 ST1	2 to 288
		Single Jacket	XPRLTMB	Gel	Yes	OFN	2 to 216
		Double Jacket Single Armor	XPRLTMD	Gel	Yes	OFCG-ST1/FT4 ST1	2 to 288
2	Industrial LSZH	Double Jacket All-Dielectric	IRZHC	Dry	Yes	OFNR-ST1/FT4 ST1	1 to 288
		Single Jacket	IRZHB	Dry	Yes	OFNG-ST1/FT4 ST1	1 to 288
		Double Jacket Single Armor	IRZHD	Dry	Yes	OFCR-ST1/FT4 ST1	1 to 288
		Double Jacket Interlock Armor	IRZHBAJ	Dry	Yes	OFCG-ST1/FT4 ST1	1 to 288
3	Mining	Double Jacket All-Dielectric	RLTM	Gel	Yes	OFNR/FT4	2-144
4	Transit	Single Jacket	DDLSZHB	Dry	Yes	OFNG-ST1/FT4 ST1	1 to 288
		Double Jacket All-Dielectric	DDLSZHC	Dry	Yes	OFNR-ST1/FT4 ST1	1 to 288
		Single Jacket Single Armor	DDLSZHE	Dry	Yes	OFCG-ST1/FT4	1 to 288
		Double Jacket Interlock Armor	DDLSZHBAJ	Dry	Yes	OFCG-ST1/FT4 ST1	1 to 288
5	Pipeline Sensing	Custom	EDS	Dry	OSP Only	NA	Custom
		Custom	ETS	Gel	OSP Only	NA	Custom
6	FAA/Airport	Double Jacket	FAACF	Gel	OSP Only	NA	2 to 60



Prysmian Group, is the corporate brand which includes the three distinct commercial brands of Prysmian, Draka and General Cable – is a world leader in the energy and telecom cable systems industry. With over 140 years of experience, sales of over €11 billion, 29,000 employees in over 50 countries and 112 plants, the Group is strongly positioned in high-tech markets and offers the widest possible range of products, services, technologies and know-how.



PRYSMIAN GROUP

4 Tesseneer Drive, Highland Heights, KY 41076
+1-859-572-8000 / na.prysmiangroup.com

Telecom Product Line 03/23

Follow us:

