


# Anaconda® Brand Type MP-GC, Mine Power Feeder w/Ground-Check, XLPE/PVC 15000 Volts, 90°C, Three Conductor



**Product Construction**

**Conductor:**

- 2 AWG thru 500 kcmil annealed compact bare copper, in accordance with ASTM B8

**Extruded Strand Shield (ESS):**

- Extruded thermosetting semi-conducting stress control layer over the conductor

**Insulation:**

- Cross-Linked Polyethylene (XLPE) insulation

**Extruded Insulation Shield (EIS):**

- Extruded thermosetting semi-conducting layer, free stripping from insulation with a color-coded (black, white and red) marker strip placed under the copper tape

**Insulation Shield:**

- Overlapped annealed copper tape

**Ground-Check Conductor:**

- Annealed copper Class B strand, insulated with yellow compound

**Grounding Conductors:**

- Two bare annealed copper conductors, Class B strand

**Jacket:**

- Heavy-duty Polyvinyl Chloride (PVC)

**Jacket Marking:**

- GENERAL CABLE® ANACONDA® BRAND (SIZE) 3/C TYPE MP-GC 15000 VOLTS P-125-25 MSHA

**Options:**

- Colored jackets are available
- CSA compliance available upon request

**Applications:**

- Provides high-voltage distribution intended for permanent installations
- Designed for use:
  - In underground mining and bore holes
  - In aerial installations, ducts or direct burial

**Features:**

- Excellent moisture, oil, chemical and corona resistance
- High dielectric strength
- Electrical stability under stress
- Low dielectric loss
- Tough and reliable
- Highly resistant to tearing, punctures, abrasions and oils

**Compliances:**

- ICEA S-75-381 Portable and Power Feeder Cables for use in mines and similar applications
- Meets flame test requirements and is accepted for listing by MSHA
- Meets CAN/CSA C22.2 No. 96.1 Mine Power Feeder Cables

**Packaging:**

- Material cut to length and shipped on non-returnable reels

**2 AWG THRU 500 KCMIL CONDUCTORS, THREE CONDUCTOR, MINE POWER FEEDER W/GROUND-CHECK, TYPE MP-GC - 15000 VOLTS**

| CATALOG NUMBER | NO. OF COND. | COND. SIZE (AWG) | COND. STRAND | NOMINAL INSULATION THICKNESS |      | GRD. COND. SIZE (AWG) | GRD-CHECK COND. SIZE (AWG) | NOMINAL JACKET THICKNESS |     | NOMINAL CABLE O.D. |       | COPPER WEIGHT |       | NET WEIGHT  |       | AMPACITY |
|----------------|--------------|------------------|--------------|------------------------------|------|-----------------------|----------------------------|--------------------------|-----|--------------------|-------|---------------|-------|-------------|-------|----------|
|                |              |                  |              | INCHES                       | mm   |                       |                            | INCHES                   | mm  | INCHES             | mm    | LBS/1000 FT   | kg/km | LBS/1000 FT | kg/km |          |
| 37032.99.01    | 3            | 2                | 7            | 0.175                        | 4.46 | 6                     | 8                          | 0.140                    | 3.6 | 1.95               | 49.50 | 938           | 1396  | 1972        | 2935  | 164      |
| 37035.99.01    | 3            | 2/0              | 19           | 0.175                        | 4.46 | 3                     | 8                          | 0.140                    | 3.6 | 2.13               | 54.10 | 1808          | 2691  | 3105        | 4621  | 246      |
| 37037.99.01    | 3            | 4/0              | 19           | 0.175                        | 4.46 | 1                     | 8                          | 0.140                    | 3.6 | 2.36               | 59.90 | 2688          | 4000  | 4150        | 6176  | 325      |
| 37038.99.01    | 3            | 250              | 37           | 0.175                        | 4.46 | 1/0                   | 8                          | 0.140                    | 3.6 | 2.50               | 63.58 | 3317          | 4936  | 4997        | 7436  | 359      |
| 37040.99.01    | 3            | 350              | 37           | 0.175                        | 4.46 | 2/0                   | 8                          | 0.140                    | 3.6 | 2.75               | 69.85 | 4311          | 6415  | 6270        | 9330  | 438      |
| 37042.99.01    | 3            | 500              | 37           | 0.175                        | 4.46 | 4/0                   | 8                          | 0.170                    | 4.3 | 3.10               | 78.74 | 6330          | 9420  | 8682        | 12920 | 536      |

Stock items are available in long lengths for cutting to your specifications. All lengths are subject to a tolerance of +/-5%. Dimensions and weights shown are nominal, subject to standard industry tolerances. Actual shipping weight may vary. These ampacities are based on a conductor temperature of 90°C and an ambient air temperature of 40°C, per ICEA S-75-381, NEMA WC58. For ampacities per National Electrical Code® requirements, refer to the latest NEC edition.

