

Double Jacketed Buried Service and Distribution Wire Spec. 3503

BELL SYSTEM TYPE—GOPHER-RESISTANT



Nominal Cable Data

CATALOG NUMBER	PAIRS AWG		O.D. (INCHES)	WEIGHT (LBS/MFT)	STANDARD LENGTH (FT)
2095102	3	19	0.42	99	5000
2095106	6	19	0.51	152	5000
2095089	3	22	0.34	67	1200
2095090	3	22	0.34	67	3000
2095091	3	22	0.34	67	5000
2095094	6	22	0.40	95	800
2095095	6	22	0.40	95	3000
2095096	6	22	0.40	95	5000

Data subject to change without notice. Contact your Customer Service Representative for latest information.

Product Construction:

Conductors:

- 22 or 19 AWG solid annealed copper

Insulation:

- High density polyethylene

Pairing:

- Varying pair lays

Core Filling:

- 80°C filling compound

Inner Jacket:

- Linear low density polyethylene

Shield:

- 0.005" corrugated copper-clad alloy steel tape

Rip Cords:

- Under each jacket

Outer Jacket:

- Black, linear low density polyethylene

Application(s):

- Intended for use in buried service application to the subscriber loops
- The shielding material provides resistance to gopher damage

Compliances:

- Telcordia (Bellcore) Specification GR-3163-CORE
- RoHS Compliant (effective 1/1/10)

Packaging:

- Non-returnable plywood reels in lengths as shown above