

Glass Supported Drop Wire 2, 3 and 6 Pair

BELL SYSTEM TYPE AND RDUP (RUS)

Spec. 4292-4294



Product Construction:

Conductors:

- 22 AWG solid annealed copper

Insulation:

- Color-coded high density polyethylene

Assembly:

- 2, 3 or 6 twisted pairs and rip cord placed parallel between the glass strength members

Jacket:

- Black, flame-retardant, weather- and abrasion-resistant PVC compound extruded over core assembly

Application(s):

- Self-supporting drop wire intended for aerial service connection to the subscriber
- Compatible with "P" Clamp/Wedge type hardware
- Glass strength member is lightweight, easy to install
- No need for support wire grounding
- Not affected by salt air and corrosive environments

Compliances:

- Telcordia (Bellcore) Specification GR-3163-CORE
- Rural Development Utility Program (RDUP) Bulletin 1753 F-204
- RoHS Compliant (effective 1/1/10)

Packaging:

- Available in Pull-Pac® cartons (PP), coils (CL), reels (RL) and reelsaver (RS)

Nominal Cable Data

| CATALOG NUMBER | PAIRS | AWG | O.D. (INCHES) | WEIGHT (LBS/MFT) | STANDARD LENGTH (FT) |
|----------------|-------|-----|---------------|------------------|----------------------|
| 2090021 | 2 | 22 | 0.20 x 0.40 | 39 | 500 RS |
| 2090008* | 2 | 22 | 0.20 x 0.40 | 39 | 750 PP |
| 2090012 | 2 | 22 | 0.20 x 0.40 | 39 | 750 CL |
| 2090010 | 2 | 22 | 0.20 x 0.40 | 39 | 1000 CL |
| 2090053 | 2 | 22 | 0.20 x 0.40 | 39 | 3500 RL |
| 2090052* | 3 | 22 | 0.28 x 0.44 | 56 | 600 PP |
| 2090018* | 6 | 22 | 0.27 x 0.50 | 79 | 400 PP |
| 2090014 | 6 | 22 | 0.27 x 0.50 | 79 | 400 CL |
| 2090055 | 6 | 22 | 0.27 x 0.50 | 79 | 500 CL |
| 2090051 | 6 | 22 | 0.27 x 0.50 | 79 | 1000 RL |
| 2090056 | 6 | 22 | 0.27 x 0.50 | 79 | 2500 RL |
| 2090013 | 6 | 22 | 0.27 x 0.50 | 79 | 3500 RL |

Data subject to change without notice. Contact your Customer Service Representative for latest information.
 * These Telecommunications wire items have sequential markings.

