


GenFree® Uniblend® High Speed

EPR/Copper Tape Shield/LSZH, Medium-Voltage Power, Shielded
15 kV, UL Type MV-105/ST1, 133% Ins. Level, 220 Mils



Features (cont'd.):

- Meets cold bend test at -35°C
- 105°C rating for continuous operation
- 140°C rating for emergency overload conditions
- 250°C rating for short circuit conditions

Compliances:

- National Electrical Code (NEC)
- UL 1072
- ICEA S-93-639/NEMA WC74
- ICEA S-97-682
- ICEA T-33-655
- AEIC CS8
- UL listed as Type MV-105 for use in accordance with NEC, UL File # E90501
- UL 1685 (Sizes 1/0 AWG and larger) UL Flame Exposure Test
- UL 1685 Vertical Flame and ST1 Smoke Release Test
- Sizes 1/0 AWG and larger are listed and marked "Sunlight-Resistant FOR CT USE" in accordance with NEC
- IEEE 1202 (70,000 BTU/hr)/CSA FT4
- EPA 40 CFR, Part 261 for leachable lead content per TCLP method
- OSHA Acceptable
- RoHS Compliant

Product Construction:

Conductor:

- 2 AWG thru 1000 kcmil annealed bare copper compact Class B strand

Extruded Strand Shield (ESS):

- Extruded thermoset semi-conducting stress-control layer over conductor

Insulation:

- Lead-free Ethylene Propylene Rubber (EPR) insulation, contrasting in color to the black semi-conducting shield layers

Extruded Insulation Shield (EIS):

- Thermoset semi-conducting polymeric layer free stripping from insulation

Metallic Shield:

- 5 mil annealed copper tape with an overlap of 25%

Overall Jacket:

- Lead-free, moisture- and sunlight-resistant Low-Smoke, Zero-Halogen Polyolefin (LSZH)

Options:

- STRANDFILL® – blocked conductor. Tested in accordance with ICEA T-31-610

Applications:

- Superior performance in petrochemical plants, pulp and paper mills, sewage and water treatment plants, environmental protection systems, railroads, mines, utility power generating stations, steel mills, textile plants and other industrial three-phase applications
- For use in wet or dry locations when installed in accordance with NEC
- For use in aerial, conduit, open tray and underground duct installations
- For use in direct burial if installed in a system with a ground conductor that is in close proximity, and conforms with NEC 250.4(A)(5)

Features:

- Rated at 105°C
- Excellent heat, moisture and sunlight resistance
- Excellent flame resistance
- Outstanding corona resistance
- Flexibility for easy handling
- High Speed low friction technology for easy cable pulling
- High dielectric strength
- Low moisture absorption
- Electrical stability under stress
- Low dielectric loss
- Chemical-resistant

Packaging:

- Material cut to length and shipped on non-returnable wood reels. Lengths in excess of 10,000 lbs. are provided on returnable steel reels that require a deposit
- Extra charges apply for cuts less than 1000 ft., lagging, pulling eyes, paralleling and triplexing

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NOMINAL CONDUCTOR DIAMETER		INSULATION DIAMETER INCHES		NOMINAL JACKET THICKNESS		NOMINAL CABLE				COPPER WEIGHT		AMPACITY						CONDUIT SIZING (4) (INCHES)
		INCHES		MIN.	MAX.	INCHES	mm	DIAMETER		WEIGHT		LBS/1000 FT	kg/km	CONDUIT IN AIR (1)		UNDERGROUND DUCT (2)		TRAY (3)		
								INCHES	mm	LBS/1000 FT	kg/km	LBS/1000 FT	kg/km	90°C	105°C	90°C	105°C	90°C	105°C	
15 kV[‡], UL TYPE MV-105, 133% INS. LEVEL, 220 MILS																				
17231.130205*	2	0.27	0.710	0.800	0.080	2.03	0.99	25.14	658	979	276	411	150	165	155	165	-	-	3	
17231.130105*	1	0.31	0.745	0.830	0.080	2.03	1.02	25.91	733	1090	332	494	170	190	175	185	-	-	3.5	
17231.135105*	1/0	0.34	0.780	0.865	0.080	2.03	1.06	26.92	825	1228	403	600	195	215	200	215	195	220	3.5	
17231.135205*	2/0	0.38	0.820	0.905	0.080	2.03	1.10	27.94	938	1396	492	732	225	255	230	245	225	250	3.5	
17231.135305*	3/0	0.43	0.865	0.955	0.080	2.03	1.14	28.95	1078	1604	603	897	260	290	260	275	260	290	3.5	
17231.135405*	4/0	0.48	0.920	1.005	0.080	2.03	1.21	30.73	1261	1876	743	1105	295	330	295	315	300	335	4	
17231.136005*	250	0.53	0.970	1.060	0.080	2.03	1.25	31.75	1407	2093	866	1289	330	365	325	345	335	370	4	
17231.136205*	350	0.62	1.070	1.155	0.080	2.03	1.35	34.29	1783	2653	1184	1761	395	440	390	415	415	460	5	
17231.136505*	500	0.74	1.190	1.275	0.080	2.03	1.47	37.34	2331	3468	1657	2466	480	535	465	500	515	575	5	
17231.137005*	750	0.91	1.370	1.460	0.080	2.03	1.65	41.91	3234	4812	2445	3638	585	655	565	610	665	745	6	
17231.137505*	1000	1.06	1.520	1.610	0.110	2.79	1.86	47.24	4219	6278	3228	4803	675	755	640	690	795	890	6	

Dimensions and weights are nominal. Subject to industry tolerances.

* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.

(1) Ampacities are in accordance with Table 310.60(C)(73) of the NEC for triplexed or three single conductor copper cables in isolated conduit in air based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient air temperature of 40°C (104°F).

(2) Ampacities are in accordance with Table 310.60(C)(77) of the NEC for triplexed or three single conductor copper cables in underground ducts (three conductors per duct), based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient earth temperature of 20°C (68°F), electrical duct arrangement per Figure 310.60 Detail 1, 100% load factor, and earth thermal resistance (rho) of 90.

(3) Ampacities are based on single conductor Type MV-105 sizes #1/0 AWG and larger in an uncovered tray in accordance with Section 392.80(B)(2) of the NEC at an ambient air temperature of 40°C (104°F) the ampacities are based on 75% of the values per Table 310.60(C)(69), operating temperature denoted in column header. For cable trays with unventilated covers for more than 6 feet, the ampacities shall not exceed 70% of the values per Table 310.60(C)(69).

(4) Based on nominal cable diameters, three single cables in the duct (PVC Schedule 40) with no ground wire and a maximum of 40% fill. Jam ratio has been considered but should be checked for individual installations.

‡ 100% insulation level is available upon request.

Note: a) Sizes smaller than 1/0 AWG do not include "FOR CT USE".

b) The NESC Lightning bolt symbol is on all Uniblend® constructions.

