


# Multi-Conductor, Rubber, Unshielded



## Product Construction:

### Conductor:

- 20 AWG fully annealed stranded tinned copper per ASTM B33

### Insulation:

- Premium-grade, color-coded rubber
- Color code: See chart below

### Jacket:

- Rubber, black
- Temperature range: -20°C to +60°C

## Applications:

- Energy management systems
- Control circuits
- Fire alarm control
- Broadcast and studio requirements
- Suggested voltage rating: 350 volts

## Features:

- Excellent impact resistance
- High level of abrasion resistance
- High flexibility
- Excellent mechanical strength
- Excellent moisture resistance

## Compliances:

- RoHS Compliant Directive 2011/65/EU

## Packaging:

- Please contact Customer Service for packaging and color options

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INSULATION THICKNESS		NOM. JACKET THICKNESS		NOMINAL O.D.	
				in	mm	in	mm	in	mm
<b>C3602</b>	2	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3603</b>	3	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3604</b>	4	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3605</b>	5	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3606</b>	6	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3607</b>	7	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3608</b>	8	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406
<b>C3610</b>	10	20	26/34	0.020	0.51	0.035	0.89	0.016	0.406

Data subject to change.

## Color Code Chart

NO. OF COND.	COLOR
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	Yellow
8	Brown
9	White/Black
10	Red/Black