




Draka

A brand of the

Prysmian Group

Power and Control Tray Cable

with XHHW-2 conductors / 14 AWG to 750 KCMIL / PVC or CPE jacket / 600 volt



Applications

For important power or control circuits where low-loss, high temperature flame-retardant cables are desired. The cables are UL listed in accordance with Article 340 of the NEC and are approved for use where exposed to direct sunlight or directly buried.

These cables may be used for cable trays in accordance with NEC Article 318 (these cables meet the requirements of the 70,000 BTU/hr vertical tray flame test in UL 1277, IEEE 383 and the ICEA 70,000 and 210,000 BTU/hr vertical tray flame tests as detailed in ICEA T-29-520 and T-30-520), in Class 1 division 2 hazardous locations in accordance with Article 501, and for Class 1 control circuits in accordance with Article 725.

These cables are tough with excellent resistance to moisture and corrosion and have high dielectric properties. The insulated conductors are UL listed XHHW-2.

Specifications and Ratings

- UL Standards 44 and 1277
- ICEA S-73-532 (NEMA WC-57)
- ICEA T-29-520, T-30-520, IEEE 383
- National Electrical Code Articles 310, 336



Prysmian Group

4 Tesseneer Drive | Highland Heights, KY 41076 | +1 859-572-8000 | www.na.prysmiangroup.com

Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764
One Tamaqua Blvd. | Schuylkill Haven PA 17972

Design Parameters

CONDUCTORS: Bare soft copper per ASTM B 3, Class B concentrically stranded per ASTM B 8.

INSULATION: High dielectric strength, heat and moisture-resistant colored crosslinked polyethylene (XLP) rated for continuous use at 90°C dry and wet to meet UL 44 for XHHW-2 wire. Ethylene Propylene Rubber insulation (FREP XHHW-2) is available as an option.

CONDUCTOR JACKET: Sheathed with a clear nylon jacket meeting UL 83 for THHN or THWN

CIRCUIT IDENTIFICATION: Insulation is coded in accordance with NEMA WC-57 Color Code.

ASSEMBLY: Individual conductors are cabled, using non-hygroscopic fillers where necessary, to form a round compact core and wrapped with a binder.

JACKET: Abrasion, oil and chemical resistant and highly flame retardant PVC or CPE jacket to meet UL Standard 1277. Thermoset Chlorinated polyethylene (CPE) jacket is available as an option.

Shield Options:

- Corrugated longitudinally-applied
- .005 or .010 copper
- Flat helically-applied .005 or .010 copper
- Aluminum/mylar tape (with or without a drain wire)
- Longitudinally-applied copper or aluminum copolymer-bonded shield
- Copper braid (specify percentage of coverage for optimum EMI protection)



Draka

A brand of the

Prysmian Group

Power and Control Tray Cable

with XHHW-2 conductors / 14 AWG to 750 KCMIL / PVC or CPE jacket / 600 volt

Part Number	Conductor Number	Conductor AWG	Nominal Insulation Thickness in (mm)	Ground AWG	Nominal Jacket Thickness in (mm)	Nominal Cable O.D. in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
104023	2	14	.030 (.76)	-	.045 (1.1)	.235 x .375 (6.0 x 9.5)	67 (99)
104033	3	14	.030 (.76)	-	.045 (1.1)	.400 (10.2)	102 (151)
104043	4	14	.030 (.76)	-	.045 (1.1)	.435 (11.0)	126 (186)
104053	5	14	.030 (.76)	-	.045 (1.1)	.475 (12.1)	150 (222)
104073	7	14	.030 (.76)	-	.045 (1.1)	.520 (13.2)	191 (283)
104093	9	14	.030 (.76)	-	.060 (1.5)	.650 (16.5)	274 (406)
104123	12	14	.030 (.76)	-	.060 (1.5)	.710 (18.0)	340 (503)
106023	2	12	.030 (.76)	-	.045 (1.1)	.255 x .415 (6.5 x 10.5)	92 (1362)
106033	3	12	.030 (.76)	-	.045 (1.1)	.440 (11.2)	131 (194)
106043	4	12	.030 (.76)	-	.045 (1.1)	.485 (12.3)	164 (243)
106053	5	12	.030 (.76)	-	.045 (1.1)	.530 (13.5)	202 (299)
106073	7	12	.030 (.76)	-	.060 (1.5)	.610 (15.5)	283 (419)
106093	9	12	.030 (.76)	-	.060 (1.5)	.715 (18.2)	357 (528)
108023	2	10	.030 (.76)	-	.045 (1.1)	.280 x .465 (7.1 x 11.8)	121 (1791)
108033	3	10	.030 (.76)	-	.045 (1.1)	.500 (12.7)	185 (2738)
108043	4	10	.030 (.76)	-	.060 (1.5)	.575 (14.6)	257 (3804)
108053	5	10	.030 (.76)	-	.060 (1.5)	.630 (16.0)	308 (4558)
108073	7	10	.030 (.76)	-	.060 (1.5)	.690 (17.5)	397 (5876)
108093	9	10	.030 (.76)	-	.060 (1.5)	.805 (20.4)	496 (734)
108123	12	10	.030 (.76)	-	.080 (2.0)	.935 (23.7)	661 (978)
112030	3 + ground	8	.045 (1.4)	10	.060 (1.5)	.665 (16.9)	296 (438)
113030	3 + ground	6	.045 (1.4)	8	.060 (1.5)	.750 (19.1)	413 (611)
114030	3 + ground	4	.045 (1.4)	8	.080 (2.0)	.910 (23.1)	634 (938)
115030	3 + ground	2	.045 (1.4)	6	.080 (2.0)	1.035 (26.3)	915 (1354)
118249	3 + ground	1/0	.055 (1.4)	6	.080 (2.0)	1.240 (31.5)	1471 (2177)
118349	3 + ground	2/0	.055 (1.4)	6	.080 (2.0)	1.340 (34.0)	1778 (2631)
118549	3 + ground	4/0	.055 (1.4)	4	.080 (2.0)	1.580 (40.1)	2734 (4046)
118649	3 + ground	250	.065 (1.7)	4	.110 (2.8)	1.840 (46.7)	3300 (4884)
118849	3 + ground	350	.065 (1.7)	3	.110 (2.8)	2.030 (51.6)	4385 (6490)
119149	3 + ground	500	.065 (1.7)	2	.110 (2.8)	2.320 (58.9)	6092 (9016)
119649	3 + ground	750	.080 (2.0)	1	.140 (3.6)	2.860 (72.6)	8976 (13284)

Part numbers shown are for XLP/PVC jacketed cables only. Optional features available are: 1) Flexible stranded conductors; 2) Tin-coated copper conductors per ASTM B33; 3) Ethylene Propylene Rubber insulation (FREP XHHW-2); 4) CPE or Chlorosulfonated Polyethylene jackets; 5) 2000 volt rating.

The data herein is approximate and subject to normal manufacturing tolerances. These specifications are subject to change without notice.

Consult factory for a variety of alternate constructions for specific applications.

© DRAKA - A Brand of The Prysmian Group. 2018 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued December 2018.

Prysmian Group

4 Tesseneer Drive | Highland Heights, KY 41076 | +1 859-572-8000 | www.na.prysmiangroup.com

Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764

One Tamaqua Blvd. | Schuylkill Haven PA 17972