



**CABLE - METRIC  
LOW VOLTAGE - INSULATED  
SINGLE - CORE  
FCA - MS-13229 EFBT**

**Features**

Copper Conductors  
Insulation: 125°C EPDM  
RoHS Compliant

**Applications**

Cables used for transportation vehicle systems  
Suitable for use inside the engine compartment  
Low Voltage Electrical Systems up to 60V  
Temperature range -40°C to 125°C

**Product Design Options**

Various colors for base and stripe combinations  
Packaging options: Drums or Reels

**Compliance**

FCA: MS.13229  
ISO: 6722-1

FCA Product Code	Cable size (mm <sup>2</sup> )	Number of Strands	Strand Diameter Nom. (mm)	Conductor Nom. (mm)	Conductor Resistance (Max. mΩ/m)	Insulation Thickness Nom. (mm)	Insulation Thickness Min. (mm)	Cable OD Min. (mm)	Cable OD Max. (mm)
EFBT	10	80	0.41	4.09	1.82	0.60	0.48	5.30	6.00
EFBT	12	240	0.26	4.50	1.52	0.60	0.48	5.80	6.50
EFBT	16	280	0.27	5.16	1.16	0.65	0.52	6.40	7.20
EFBT	20	440	0.24	5.66	0.955	0.65	0.52	7.00	7.80
EFBT	25	798	0.20	6.88	0.743	0.65	0.52	7.90	8.70
EFBT	35	704	0.24	7.75	0.527	0.80	0.64	9.40	10.40
EFBT	40	760	0.25	8.00	0.473	0.90	0.71	10.00	11.10
EFBT	50	912	0.26	9.12	0.368	0.90	0.71	11.00	12.20
EFBT	60	1064	0.26	9.86	0.315	1.00	0.80	12.00	13.30
EFBT	70	1140	0.28	11.93	0.259	1.00	0.80	13.00	14.40