




# GenSPEED® Micro Fiber MFC | 1.4mm Units

Micro Fiber Cable (MFC)

# Prysmian



## OVERVIEW

GenSPEED MFC is the ideal cable for data center, co-location and central office facilities where a small diameter, highly flexible cable is desired. GenSPEED offers 12 fiber, 250 micron color coded fibers in 1.4 mm diameter subunits, to deliver high performance and high density. Subunits can be directly terminated to MPO style connectors.

## SPECIFICATIONS / RATINGS

<b>Applications</b>	Routing and patching for indoor communication network locations
<b>Subunit Size</b>	1.4 mm diameter subunits
<b>Fiber</b>	250 µm fibers, 12 fibers per subunit
<b>Flame Ratings</b>	Plenum (OFNP/FT6), LSZH Riser (OFNR-LS/FT4-ST1) IEC 60332-1 and IEC 60332-3-24
<b>Fiber Count</b>	12 to 48 Fibers
<b>Fiber Types</b>	Single-mode and multimode
<b>Standards</b>	ANSI / ICEA S-83-596, Telcordia GR-409, CE RoHS Compliant
<b>Registered Supplier</b>	ISO 9001, ISO 14001, TL 9000, and OHSAS 18001



## FEATURES AND BENEFITS

### Flexible Routing & Termination

- Very flexible with no preferential bend
- Subunits can be directly terminated to MPO connections
- Compatible with routing in trays, racks and under raised floors in network communication centers
- Enables installation around tight corners and in confined spaces
- Fully compatible with commercially available multi-fiber connectors, such as MPO
- Smaller diameter than traditional micro fiber cable style cables
- 24% smaller diameter than MFC20 (2mm unit 48f)

### Flame-Retardant Safety

- NFPA-262/CSA FT6 OFNP Plenum
- UL1666, UL1685 LSZH Riser
- IEC 60332

### Reliable Performance

- Incorporating bend-insensitive single-mode or multimode fibers to address the most challenging placement conditions
- Rugged thermoplastic jacket for crush resistance
- Designed and tested to standards-based performance criteria

**Prysmian**

A Brand of Prysmian Group

**Prysmian Group**

4 Tesseneer Drive, Highland Heights, KY 41076  
+1-859-572-8000 / na.prysmiangroup.com  
TLS-DS-C-201-1021

# GenSPEED® Micro Fiber MFC | 1.4mm Units

Micro Fiber Cable (MFC)

# Prysmian

Fiber Count	Fibers Per Subunit	Recommended Part Number	Diameter		Cable Weight		Bend Radius UNDER LOAD		Bend Radius NO LOAD		Max Installation LOAD (pull strength)		Max Operation LOAD	
			Prysmian*	inches	mm	lb/kft	kg/km	inches	cm	inches	cm	lbs	newtons	lbs

### Plenum OFNP/FT6 | MFC14 Series | (1.4 mm sub-units)

12	1-unit of 12	MFC14-12-AA-012-BB	0.177	4.5	12.5	18.6	3.5	9.0	2.0	4.5	100	444	32	142
24	2-units of 12	MFC14-12-AA-024-BB	0.200	5.1	18.3	27.2	4.0	11.0	2.0	5.1	150	667	45	200
48	4-units of 12	MFC14-12-AA-048-BB	0.223	6.7	21.1	31.4	4.6	11.4	2.3	5.7	150	667	45	200

### LSZH Riser OFNR-LS/FT4-ST1 | MFCL14 Series | (1.4 mm sub-units)

12	1-unit of 12	MFCL14-12-AA-012-BB	0.190	4.8	15.7	23.3	3.8	9.6	1.9	4.8	150	667	45	200
24	2-units of 12	MFCL14-12-AA-024-BB	0.213	5.4	21.4	31.9	4.6	11.6	2.3	5.8	150	667	45	200
48	4-units of 12	MFCL14-12-AA-048-BB	0.240	6.1	23.8	35.4	4.8	12.2	2.4	6.1	150	667	45	200

\* Where AA equals glass type and BB equals attenuation code

### Outer Jacket Color Identification

Orange Multimode OM1 and OM2+  
 Aqua Multimode OM3 and OM4  
 Yellow Single-mode  
 Black Hybrid

### Temperature Range

Shipping and Storage: -40° F to +176° F (-40° C to +70° C)  
 Installation: +32° F to +140° F (0° C to +60° C)  
 Operation: +32° F to +176° F (0° C to +70° C)

## Ordering Guide

The Prysmian Group part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

**Example:** GenSPEED 48 fiber micro fiber MFC14 cable, 1.4 mm subunits, with bend-insensitive single mode fibers (printed in feet)

1	2	3	4	5	6	7
LENGTH MARKINGS	PRODUCT FAMILY	CONSTRUCTION	FIBER GROUPING	FIBER TYPE	FIBER COUNT	FIBER GRADE
F	MFC14	BLANK	12	B2	048	E1

PART NUMBER CONSTRUCTION	
<b>1</b>	<b>LENGTH MARKINGS</b>
F = Feet or M = Meters	
<b>2</b>	<b>PRODUCT FAMILY</b>
MFC14 = 12 to 48f Plenum	
MFCL14 = 12 to 48f LSZH Riser	
<b>3</b>	<b>CONSTRUCTION</b>
(BLANK) = None	
<b>4</b>	<b>FIBER GROUPING</b>
12 = 12f per unit	

Note: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help. Other cable constructions and fiber performance grades available on request.

FIBER INFORMATION				
<b>5</b>	<b>FIBER TYPE</b>			
<b>SINGLE-MODE</b>				
B2 = Bend-Insensitive Single-Mode (ITU G.657.A2 & .B2, & G.652.D)				
<b>MULTIMODE</b>				
	Wavelength (nm)	Bandwidth (MHz)	1 GbE Dist (m)	10 GbE Dist (m)
G6 = OM1 (62.5µm)	850/1300	200/500	300/550	33/___
G5 = OM2+ BIF (50µm)	850/1300	700/500	800	150/___
G3 = OM3 BIF (50µm)	850/1300	1500/500	1000	300/___
G4 = OM4 BIF (50µm)	850/1300	3500/500	1100	550/___
GW = OM5 (50µm)	850/1300	3500/500	1200	550/___
<b>6</b>	<b>FIBER COUNT</b>			
12 to 48 fibers				
<b>7</b>	<b>FIBER GRADE</b>			
<b>SINGLE-MODE</b>				
Attenuation (dB/km)	Wavelength (nm)	Fiber Type		
E1 = 0.40/0.40/0.30	1310/1383/1550	B2		
<b>MULTIMODE</b>				
Attenuation (dB/km)	Wavelength (nm)			
M2 = 3.5/1.0	850/1300			
M3 = 3.0/1.0	850/1300			

# Prysmian

A Brand of Prysmian Group

## Prysmian Group

4 Tesseneer Drive, Highland Heights, KY 41076  
 +1-859-572-8000 / na.prysmiangroup.com  
 TLS-DS-C-201-1021