


Type SJT

105°C, 300 Volt, UL/CSA Portable Cord



TYPE SJT – 300 VOLT – UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS [†]	APPROX. NET WEIGHT LBS/M ^(§)	STD. CTN.
				INCHES	mm	INCHES	mm			
86112*	2	18	16/30	0.030	0.76	0.285	7.24	10	45	1000 ^l
86113	3	18	16/30	0.030	0.76	0.310	7.87	10	55	1000 ^l

* Non-stock item; minimum quantity purchase required.

† Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).

§ Actual shipping weight may vary.

Product Construction:

Conductors:

- 18 AWG fully annealed stranded bare copper

Insulation:

- Premium-grade, color-coded PVC
- Color code: See chart below

Jacket:

- Polyvinyl Chloride (PVC), white
- Temperature range: -20°C to +105°C

Jacket Marking:

- (SIZE) (mm²) 105°C SJT E# (UL) --- CSA LL# FT2 ROHS MADE IN USA 300 V

Applications:

- For use in most hospital equipment

Features:

- Resists:
 - Acids
 - Alkalies
 - Ozone

Industry Approvals:

- UL Listed
- CSA Certified
- RoHS Compliant

Packaging:

- 250' (76.2 m)
- Other sizes and put-ups available on special order

COLOR CODE CHART

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green

