




Uniblend® PVC High Speed EPR/Copper Tape Shield with Overall PVC Jacket, Medium-Voltage Power, Shielded, 25 kV and 35 kV UL Type MV-105, 133%/100% Ins. Level, 345 MILS, Three Conductor



Features (cont'd.):

- Low moisture absorption
- Electrical stability under stress
- Low dielectric loss
- Chemical-resistant
- Meets cold bend test at -35°C
- 105°C rating for continuous operation
- 140°C rating for emergency overload conditions
- 250°C rating for short circuit conditions

Product Construction:

Conductor:

- 1/0 AWG thru 750 kcmil annealed bare copper compact Class B strand

Extruded Strand Shield (ESS):

- Extruded thermoset semi-conducting stress control layer over conductor

Insulation:

- Lead-free Ethylene Propylene Rubber (EPR) insulation, contrasting in color to the black semi-conducting shield layers

Extruded Insulation Shield (EIS):

- Thermoset semi-conducting polymeric layer free stripping from insulation

Metallic Shield:

- 5 mil annealed copper tape with an overlap of 25%

Grounding Conductor:

- 1 bare grounding conductor may be in contact with metallic shielding tape

Overall Jacket:

- Low-friction, lead-free, flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC)

Options:

- STRANDFILL® - blocked conductor. Tested in accordance with ICEA T-31-610

Applications:

- Suited for use in a broad range of commercial, industrial and utility applications, where reliability is the major concern, space is limited and ease of installation is critical
- Suitable for use in wet or dry locations when installed in accordance with NEC
- In aerial, direct burial, conduit, open tray and underground duct installations

Features:

- Rated at 105°C
- High Speed low friction technology for easy cable pulling
- Excellent heat, moisture and sunlight resistance
- Outstanding corona resistance
- Flexibility for easy handling
- High dielectric strength

Compliances:

- National Electrical Code (NEC)
- UL 1072
- ICEA S-93-639/NEMA WC74
- ICEA S-97-682
- AEIC CS8
- UL listed as Type MV-105 for use in accordance with NEC, UL File # E90501
- UL 1685 (70,000 BTU/hr)
- EPA 40 CFR, Part 261 for leachable lead content per TCLP method
- OSHA Acceptable
- RoHS Compliant

Optional Flame Tests:

- IEEE 1202 (70,000 BTU/hr)/CSA FT4

Packaging:

- Material cut to length and shipped on non-returnable wood reels. Lengths in excess of 10,000 lbs. are provided on returnable steel reels that require a deposit
- Extra charges apply for cuts less than 1000 ft., lagging, pulling eyes, paralleling and triplexing

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NOMINAL CONDUCTOR DIAMETER		INSULATION DIAMETER INCHES		GROUND WIRE (AWG)	NOMINAL JACKET THICKNESS		NOMINAL CABLE				COPPER WEIGHT		AMPACITY						
		INCHES	MIN.	MAX.	INCHES		mm	DIAMETER		WEIGHT		LBS/1000 FT	kg/km	LBS/1000 FT	kg/km	CONDUIT IN AIR (1)		UNDERGROUND DUCT (2)		TRAY (3)	
								INCHES	mm	LBS/1000 FT	kg/km					90°C	105°C	90°C	105°C	90°C	105°C
25 kV* & 35 kV**, UL TYPE MV-105, 133%/100% INS. LEVEL, 345 MILS, THREE CONDUCTOR																					
15493.485105*	1/0	0.34	1.020	1.120	4	0.110	2.79	2.73	69.34	3672	5464	1410	2098	195	215	195	210	215	240		
15493.485205*	2/0	0.38	1.060	1.160	4	0.110	2.79	2.81	71.37	4061	6042	1675	2492	220	245	220	235	245	275		
15493.485405*	4/0	0.48	1.160	1.260	3	0.140	3.56	3.10	78.74	5313	7906	2465	3668	290	320	285	305	325	360		
15493.486005*	250	0.53	1.210	1.315	2	0.140	3.56	3.21	81.53	6214	9246	2879	4284	315	350	310	335	360	400		
15493.486205*	350	0.62	1.310	1.410	2	0.140	3.56	3.42	86.86	7138	10621	3834	5705	385	430	375	400	435	490		
15493.486505*	500	0.74	1.430	1.530	1	0.140	3.56	3.68	93.47	9012	13410	5312	7904	470	525	450	485	535	600		
15493.487005*	750	0.91	1.610	1.710	1/0	0.140	3.56	4.10	104.14	12030	17901	7750	11532	570	635	545	585	670	745		

Dimensions and weights are nominal. Subject to industry tolerances.

* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.

(1) Ampacities are in accordance with Table 310.60(C)(75) of the NEC for three conductor copper cable in isolated conduit in air based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient air temperature of 40°C (104°F).

(2) Ampacities are in accordance with Table 310.60(C)(79) of the NEC for three conductor copper cable in underground ducts (three conductors per duct), based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient earth temperature of 20°C (68°F), electrical duct arrangement per Figure 310.60 Detail 1, 100% load factor, and earth thermal resistance (rho) of 90.

(3) Ampacities are based on three conductor Type MV-105 cables in single layer in an uncovered tray with maintained spacing of not less than one cable diameter between cables, in accordance with Section 392.80(B)(1) of the NEC at an ambient air temperature of 40°C (104°F); the ampacities are per Table 310.60(C)(71), operating temperature denoted in column header. For cable trays with unventilated covers for more than 6 feet, the ampacities shall not exceed 95% of the values in NEC Table 310.60(C)(75).

¥ 100% insulation level is available upon request.

¥¥ 133% insulation level is available upon request.

Note: a) All sizes are "FOR CT USE".

b) The NESC Lightning bolt symbol is on all Uniblend® constructions.

