

# Uniblend® PVC High Speed

EPR/Copper Tape Shield/PVC, Medium-Voltage Power, Shielded  
35 kV, UL Type MV-105, 133% Ins. Levels, 420 Mils



## Product Construction:

### Conductor:

- 1/0 AWG thru 1000 kcmil annealed bare copper compact Class B strand

### Extruded Strand Shield (ESS):

- Extruded thermoset semi-conducting stress-control layer over conductor

### Insulation:

- Lead-free Ethylene Propylene Rubber (EPR) insulation, contrasting in color to the black semi-conducting shield layers

### Extruded Insulation Shield (EIS):

- Thermoset semi-conducting polymeric layer free stripping from insulation

### Metallic Shield:

- 5 mil annealed copper tape with an overlap of 25%

### Jacket:

- Low-friction, lead-free, flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC)

### Options:

- STRANDFILL® - blocked conductor. Tested in accordance with ICEA T-31-610

## Applications:

- Superior performance in petrochemical plants, pulp and paper mills, sewage and water treatment plants, environmental protection systems, railroads, mines, utility power generating stations, steel mills, textile plants and other industrial three-phase applications



## Applications (cont'd.):

- For use in wet or dry locations when installed in accordance with NEC
- For use in aerial, conduit, open tray and underground duct installations
- For use in direct burial if installed in a system with a ground conductor that is in close proximity, and conforms with NEC 250.4(A)(5)

## Features:

- Rated at 105°C
- High Speed low friction technology for easy cable pulling
- Excellent heat, moisture and sunlight resistance
- Excellent flame resistance
- Outstanding corona resistance
- Flexibility for easy handling
- High dielectric strength
- Low moisture absorption
- Electrical stability under stress
- Low dielectric loss
- Chemical-resistant
- Meets cold bend test at -35°C
- 105°C rating for continuous operation
- 140°C rating for emergency overload conditions
- 250°C rating for short circuit conditions

## Compliances:

- National Electrical Code (NEC)
- UL 1072
- ICEA S-93-639/NEMA WC74
- ICEA S-97-682
- AEIC CS8
- UL listed as Type MV-105 for use in accordance with NEC, UL File # E90501
- IEEE 1202 (70,000 BTU/hr)/CSA FT4
- EPA 40 CFR, Part 261 for leachable lead content per TCLP method
- OSHA Acceptable
- RoHS Compliant

## Packaging:

- Material cut to length and shipped on non-returnable wood reels. Lengths in excess of 10,000 lbs. are provided on returnable steel reels that require a deposit
- Extra charges apply for cuts less than 1000 ft., lagging, pulling eyes, paralleling and triplexing

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NOMINAL CONDUCTOR DIAMETER		INSULATION DIAMETER INCHES		NOMINAL JACKET THICKNESS		NOMINAL CABLE				COPPER WEIGHT		AMPACITY						CONDUIT SIZING (4) (INCHES)	
		INCHES	MIN.	MAX.	INCHES	mm	INCHES	mm	DIAMETER		WEIGHT		LBS/1000 FT	kg/km	CONDUIT IN AIR (1)		UNDERGROUND DUCT (2)		TRAY (3)		
									90°C	105°C	90°C	105°C			90°C	105°C					
<b>35 kV, UL TYPE MV-105, 133% INS. LEVEL, 420 MILS</b>																					
17071.135105*	1/0	0.34	1.060	1.265	0.080	2.03	1.47	37.34	1253	1864	437	650	195	215	200	215	195	220	5		
17071.135205*	2/0	0.38	1.200	1.305	0.080	2.03	1.49	37.85	1378	2050	525	781	225	255	230	245	225	250	5		
17071.135305*	3/0	0.43	1.245	1.355	0.080	2.03	1.53	38.86	1532	2280	636	946	260	290	260	275	260	285	5		
17071.135405	4/0	0.48	1.300	1.405	0.080	2.03	1.59	40.39	1716	2553	776	1155	295	330	295	315	295	335	5		
17071.136005*	250	0.53	1.350	1.460	0.080	2.03	1.64	41.66	1888	2809	899	1338	330	365	325	345	330	370	6		
17071.136205	350	0.62	1.450	1.555	0.110	2.79	1.79	45.47	2396	3565	1217	1811	395	440	390	415	410	455	6		
17071.136505	500	0.74	1.570	1.675	0.110	2.79	1.91	48.50	2986	4443	1690	2515	480	535	465	500	510	565	6		
17071.137005	750	0.91	1.750	1.860	0.110	2.79	2.09	53.09	3954	5884	2477	3685	585	655	565	610	655	730	8		
17071.137505*	1000	1.06	1.900	2.010	0.110	2.79	2.25	57.15	4885	7269	3263	4855	675	755	640	690	780	870	8		

Dimensions and weights are nominal. Subject to industry tolerances.

\* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.

(1) Ampacities are in accordance with Table 310.60(C)(73) of the NEC for triplexed or three single conductor copper cables in isolated conduit in air based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient air temperature of 40°C (104°F).

(2) Ampacities are in accordance with Table 310.60(C)(77) of the NEC for triplexed or three single conductor copper cables in underground ducts (three conductors per duct), based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient earth temperature of 20°C (68°F), electrical duct arrangement per Figure 310.60 Detail 1, 100% load factor, and earth thermal resistance (rho) of 90.

(3) Ampacities are based on single conductor Type MV-105 sizes #1/0 AWG and larger in an uncovered tray in accordance with Section 392.80(B)(2) of the NEC at an ambient air temperature of 40°C (104°F) the ampacities are based on 75% of the values per Table 310.60(C)(69), operating temperature denoted in column header. For cable trays with unventilated covers for more than 6 feet, the ampacities shall not exceed 70% of the values per Table 310.60(C)(69).

(4) Based on nominal cable diameters, three single cables in the duct (PVC Schedule 40) with no ground wire and a maximum of 40% fill. Jam ratio has been considered but should be checked for individual installations.

Note: a) All sizes are "FOR CT USE".

b) The NESC Lightning bolt symbol is on all Uniblend® constructions.