



GenSPEED® FusionLink™ Indoor/Outdoor

Ribbon Central Tube Riser (Dry) Cable



Prysmian

12-432f Dielectric & Armored




Flame Retardant Jacket
Strength Member
Ripcord
Ribbon Stack
Dry Buffer Tube
Water Blocking Tape
Flame Retardant Tape

864f Armored



Flame Retardant Jacket
Aluminum Interlock Armor
Buffer Tube
Ribbon Stack
Ripcord
Inner Jacket
Strength Yarns

864f Dielectric



Flame Retardant Jacket
Buffer Tube
Ribbon Stack
Ripcord
Strength Yarns

FEATURES AND BENEFITS

Indoor/Outdoor Design

- Saves space and time by eliminating splices at the cable vault
- Can be installed using typical loose tube cable methods and hardware

Compact Design

- Efficient packaging of higher fiber counts
- Lightweight and easy to handle during installation

Easily Removable Ribbon Matrix

- Allows for ease of stripping and fiber breakout
- Improves mid-span strippability

Precision Ribbon Geometry

- Time and labor savings during fiber splicing
- Superior fiber alignment produces low skew and ease of connectorization

Flexible Buffer Tube

- Superior kink resistance
- Eliminates need for closure transportation tubing
- Facilitates route management in closures

Dry Water-Blocking Technology

- Buffer tube and core are completely dry – no gel
- Permits rapid cable preparation and termination
- Water-blocking materials are easily removed

UL and c(UL) Listed

- OFNR and OFN-FT4 rated for riser applications
- Indoor/outdoor applications

Performance

- Meets or exceeds the requirements of Telcordia GR-20 & ICEA 640 and is tested in accordance with relevant EIA/TIA-455 series FOTPs for fiber optic cables
- RDUP listed (tested in accordance with PE-90)
- The complete cable and all subcomponents are RoHS-compliant

Registered Supplier

- ISO 9001, ISO 14001, TL 9000, and OHSAS 18001



PERFORMANCE SPECIFICATIONS

PERFORMANCE SPECIFICATIONS		
Bend Radius		
Dynamic	20 x Cable OD	
Static	10 x Cable OD	
Tensile Rating	N	lbf
Installation	2,700	600
Residual	800	180
Crush Resistance	N/cm	lbf/in
Short/ long Term	220/110	125/63
Temperature Ratings	°C	°F
Operation	-40 to +70	-40 to +158
Installation*	-30 to +60	-22 to +140
Storage/Shipping	-40 to +75	-40 to +167

* Installation Temperature Range for the 576 to 864 fiber counts is -10C to +60C (-4F to 140F)

Prysmian

A Brand of Prysmian Group

Prysmian Group

4 Tesseneer Drive, Highland Heights, KY 41076
+1-859-572-8000 / na.prysmiangroup.com
TLS-DS-B-101-0823

Fiber Count Range	Recommended Fiber Count	Recommended Prysmian** Part Number	Fibers / Ribbon	Number of Ribbons	Buffer Tube OD		Cable OD		Approx. Cable Weight		Max. Reel Length	
					Inches	mm	Inches	mm	lb/kft	kg/km	feet	meters

RRIODCK

12-72	12	RRIODCK-12-AA-012-BB	12	1-6	0.35	8.8	0.64	16.2	144	214	31,022	9,458
	24	RRIODCK-12-AA-024-BB										
	48	RRIODCK-12-AA-048-BB										
	72	RRIODCK-12-AA-072-BB										
84-144	144	RRIODCK-12-AA-144-BB	12	7-12	0.42	10.6	0.71	18.0	168	250	31,022	9,458
240-432	432	RRIODCK-24-AA-432-BB	24	10-18	0.61	15.4	0.90	22.8	245	364	17,864	5,445
576-864	576	RRIODCK-24-AA-576-BB	24	24	0.81	20.6	1.06	26.8	330	490	12,500	3,800
	864	RRIODCK-36-AA-864-BB	24									

RRIODKAJ

12-72	12	RRIODKAJ-12-AA-012-BB	12	1-6	0.35	8.8	0.99	25.2	381	567	18,175	5,540
	24	RRIODKAJ-12-AA-024-BB										
	48	RRIODKAJ-12-AA-048-BB										
	72	RRIODKAJ-12-AA-072-BB										
84-144	144	RRIODKAJ-12-AA-144-BB	12	7-12	0.42	10.6	1.06	27.0	428	637	15,435	4,705
240-432	432	RRIODKAJ-24-AA-432-BB	24	10-18	0.61	15.4	1.26	32.0	567	844	11,220	3,420
576-864	576	RRIODKAJ-24-AA-576-BB	24	24	0.81	20.6	1.4	35.6	723	1,076	9,500	2,900
	864	RRIODKAJ-36-AA-864-BB	24									

* **Note:** This design uses 24 fiber ribbons for counts of 240 to 576 fibers and 36 fiber ribbons for 612 to 864 fibers.
If on reel testing is required for the 612-864 fiber designs, a reel with 60" drum must be specified on the order.

**Where AA equals glass type and BB equals attenuation code

Ordering Guide

The Prysmian Group part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

GenSPEED® FusionLink™ Indoor/Outdoor Riser Rated Dry Cable:

Example: GenSPEED® FusionLink™ 432 count, riser rated, dry cable with G.652.D LWP single-mode fiber and 0.40/0.40/0.30 attenuation (printed in feet)

1	LENGTH MARKINGS	2	PRODUCT FAMILY	3	FIBER GROUPING	4	FIBER TYPE	5	FIBER COUNT	6	FIBER GRADE
	F		RRIOCDK		24		HB		432		E1

PART NUMBER CONSTRUCTION	
1	LENGTH MARKINGS
	F = Feet or M = Meters
2	PRODUCT FAMILY & CONSTRUCTION
	RRIOCDK = Dry GenSPEED® Indoor/Outdoor (Riser)
	RRIOCDKAJ = Dry GenSPEED® Aluminum Interlock Armor I/O (Riser)
3	FIBER GROUPING
	12 = 12f Ribbons (12-144)
	24 = 24f Ribbons (240-576)
	36 = 36f Ribbons (864)

Note: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help.

FIBER INFORMATION			
4	FIBER TYPE		
	SINGLE-MODE		
	HB = Single-Mode (ITU G.652 C & D) Low Water Peak – 12-432f only		
	ES = Enhanced Single-Mode (ITU G.652 C & D) – 12-432f only		
	CE = Corning™ SMF28e+ Single-Mode – 12-432f only		
	B1 = Bend-Insensitive Single-Mode (ITU G.657.A1 & G.652.D)		
	CU = Corning™ SMF-28® Ultra Single-Mode (ITU G.657.A1 & G.652.D)		
	B2 = Bend-Insensitive Single-Mode (ITU G.657.A2 & .B2, & G.652.D)		
5	FIBER COUNT		
	012 to 864 fibers		
6	FIBER GRADE		
	SINGLE-MODE		
	Attenuation (dB/km)	Wavelength (nm)	
	Fiber Type		
	E1 = 0.40/0.40/0.30	1310/1383/1550	HB, ES, CE, B1, CU, or B2
	E3 = 0.35/0.35/0.25	1310/1383/1550	HB, ES, CE, B1, CU, or B2

*576 to 864 fibers limited to E1 attenuation code