



**General Cable**

# Cable Solutions

FOR THE INDUSTRIAL AUTOMATION MARKET



- Industrial Ethernet
- Industrial Communication Protocols
- Instrumentation and Control
- Portable Power and Cord
- Variable Frequency Drive

# Industrial Automation

SERVING THE NEEDS OF THE INDUSTRIAL AUTOMATION MARKET

This catalog contains in-depth information on the most comprehensive line of automation cables available today. It features the latest information on products, along with detailed technical and specification data in indexed sections — with an easy-to-use “spec-on-a-page” format. The “spec-on-a-page” format was developed to meet your needs. It features up-to-the-minute product information, from applications and constructions to detailed technical and specification data. There’s also a comprehensive technical section for additional assistance. And, of course, if you need any further data, General Cable’s Customer Service staff provides the answers you need quickly and efficiently.

## QUALITY

General Cable is committed to meeting customer requirements through continuous quality improvements. As a significant part of our commitment to quality, General Cable’s manufacturing facilities are certified to the ISO 9001:2000 quality standard. Our telecommunications cable manufacturing facility has received TL 9000 quality standards registration as a supplement to the ISO program. This quality system is based on the ISO 9001 program with added telecommunications-specific performance metrics. We strive to provide value optimization through innovation and quality solutions.



- Our in-house testing capabilities are extensive, with strict adherence to our product specifications as well as industry standards.
- Cables are safety listed and verified.
- Third-party testing labs like ETL and UL are utilized to quantify and confirm our quality and provide final qualification data that sets the foundation for our extended product warranty.
- General Cable products have stood the test of time with proven reliability and performance.

## CUSTOMER SERVICE

General Cable is dedicated to customer service and satisfaction. Call our team of professionally trained sales associates with any questions to meet your application needs.

**800-950-3512 GENERALCABLE.COM**



All information in this catalog is presented solely as a guide to product selection and is believed to be reliable. All printing errors are subject to correction in subsequent releases of this catalog. Although General Cable has taken precautions to ensure the accuracy of the product specifications at the time of publication, the specifications of all products contained herein are subject to change without notice.

GENERAL CABLE, 17 FREE, CAROL BRAND, CCW, CVTC, EXZEL, FREP, GENCLEAN, GENFREE, GENSPEED, GENSPEED 10 MTP, GEPCO BRAND, NEXTGEN, SUPER VU-TRON, TC-FLEX and TRU-MARK are trademarks of General Cable Technologies Corporation.

HART is a registered trademark of the HART Communication Foundation. ControlNet and DeviceNet are registered trademarks of Open DeviceNet Vendor Association, INC. (ODVA). Hytel, Kevlar, Mylar and Tefzel are registered trademarks of E.I. du Pont de Nemours and Company. Foundation Fieldbus is a trademark of Fieldbus Foundation. Seriplex is a registered trademark of Square D. SOCAPEX is a trademark of Amphenol Corporation.

© 2015. General Cable Technologies Corporation.  
Highland Heights, KY 41076  
All rights reserved. Printed in USA.





# MINIMIZE YOUR RISK

## Drive Cables that Provide Control & Ensure Confidence

**Selecting the proper drive cables for Variable Frequency Drive (VFD) applications reduces the risk of electromagnetic interference (EMI), high ground currents and reflected waves in your cable systems.**

General Cable's line of CVTC® VFD Type TC-ER unarmored and CCW® VFD Type MC-HL (continuously corrugated welded) armored cables is specially engineered and designed to handle the challenges presented in a VFD environment. Delivering reliable performance for sustained and continuous operations, General Cable's VFD cables are used in a wide range of applications.



**General Cable has the people, equipment and experience to help define the right solution for your VFD application. Give us a call!**

 **General Cable**

[www.generalcable.com](http://www.generalcable.com) 1.888.593.3355

# Table of Contents

<b>INTRODUCTION</b> .....	<b>2-5</b>
<b>GENERAL CABLE PRODUCT SOLUTIONS FOR:</b>	
<b>Industrial Ethernet</b> .....	<b>6-28</b>
Multi-Conductor Category 5e Industrial Ethernet . . . .	8-18
Multi-Conductor Category 6 Industrial Ethernet . . . .	19-22
Fiber Optic .....	23-28
<b>Industrial Communication Protocol Cables</b> .....	<b>29-41</b>
Coax and Twinax .....	32-33
Multi-Paired/Conductor Shielded .....	34-40
Multi-Paired/Conductor Unshielded .....	41
<b>Instrumentation &amp; Control Cable</b> .....	<b>42-60</b>
<b>Instrumentation</b>	
FREP® (Specs 2100, 2150, 2200) .....	44-46
GenFree® (Specs 2600, 2625, 2650) .....	47-49
<b>Control</b>	
FREP® (Specs 4300, 4310, 4325, 4350) .....	50-53
GenFree® (Specs 4900, 4925, 4950) .....	54-56
TC-Flex™ (Specs 4775, 4780, 4785, 4790) .....	57-60
<b>Portable Power and Cord</b> .....	<b>61-71</b>
Super Vu-Tron® .....	62-70
Super Vu-Tron® with GenClean™ .....	71
<b>Variable Frequency Drive (VFD)</b> .....	<b>72-96</b>
<b>CCW®</b>	
Specs 9600, 9605, 9615, 9675, 9700, 9800, 9805, 9815 . . . .	76-91
<b>CVTC®</b>	
Specs 4560, 4565, 4570, 4575, 4580 .....	92-96
<b>Technical Information</b> .....	<b>97</b>
Industrial Automation General Cable to Belden	
Cross-Reference .....	98-99
Industrial Communication Protocol Cables	
Cross-Reference .....	100-112
Catalog Number Index .....	113-117

# Here to Serve

For more than 165 years, General Cable has provided wire and cable solutions that keep goods moving, products assembled and services delivered around the world. Through innovative design and engineering expertise, General Cable delivers the wire and cables that maintain ongoing productivity for an array of industrial automation and electrical distribution customers that represent a virtual “who’s who” of the markets we serve.

General Cable recognizes and values the importance of total customer satisfaction, and we have the experience and know-how to achieve it. Our people may come to work for us, but on the job, our *Wire Wizards* work for you. Put us to work and see what we can do for you.

AUTOMOTIVE & CONSUMER PRODUCTS • HEALTH CARE & MEDICAL DEVICE MANUFACTURERS • PULP & PAPER INDUSTRIAL EQUIPMENT MANUFACTURERS • LIFTS & CRANES • MAINTENANCE & REPAIR OPERATIONS MINING EQUIPMENT MANUFACTURERS • PLANTS & FACILITIES MANAGEMENT • PUMPS & FOUNTAINS PORTABLE & TEMPORARY POWER GENERATION • MILITARY • REFRIGERATION & FREEZER MANUFACTURERS





# World-Wide Single Source Solutions

As a Fortune 500 company with approximately 14,000 associates globally and 38 manufacturing facilities operating in core markets around the world, General Cable is positioned to meet the needs of today's industrial automation and electrical distribution customers with a diverse, industry-leading global product offering—whenever and wherever it's needed. Our products comply with major safety and performance standards and regulations around the world—from UL, IEEE, ODVA and IEC to TIA, TÜV, RoHS and CSA.

Whether it's data, power, signal or control in the office, on the factory floor, inside the wind turbine or onboard an oil rig, General Cable has the electronic, industrial, data, fiber and specialty cable to keep power and information flowing and goods and services moving while ensuring maximum safety, value and long-term reliability. From special wire colors, print legends and TRU-Mark® sequential footage marking to unique materials and manufacturing requirements, General Cable has the people, equipment and experience to produce the custom cable you need.

## World-Class Service & Support

Uniquely positioned to respond to the evolving needs of industrial applications, General Cable works side-by-side with customers to design innovative, cost-effective solutions that meet exact specifications while providing value-added services. Backed by an organization that is flexible and responsive with a commitment to maintaining lasting customer relationships, you can count on General Cable for superior service and support.

- Innovative cable designs for any industrial application
- Superior engineering expertise and production processes
- Advanced vertical integration capabilities
- Strong supply chain and inventory support
- Dedicated service, technical support and sales expertise

## Commitment to Quality & the Environment

General Cable is always searching for new and better ways to put quality in your product. The right mix of R&D experience, manufacturing expertise and stringent testing by the most qualified team of engineers ensures that every cable meets industry standards and offers the highest quality possible. Our Lean Six Sigma philosophy eliminates waste, non-value-added processes and sources of variation while reducing cycle-time and improving capacity, space utilization and productivity.

- ISO 9001 certified manufacturing facilities
- Ongoing process control and production management
- Quality assurance initiatives and rigorous performance standards
- R&D and innovative material development expertise
- Stringent in-house and third-party testing

General Cable is an environmentally conscious company committed to reducing and, where possible, eliminating hazardous substances. Through environmentally sound materials and production processes, our facilities have fully implemented an ISO 14001-equivalent environmental management system with strict oversight. All applicable products meet RoHS standards, and we consistently work to comply with evolving REACH requirements pertaining to wire and cable products and materials. Our revolutionary **17 FREE®** line of halogen-free datacom, fiber, cord and electronics cables features substantiated green properties and may qualify for credits under environmental incentive programs.

# Condensed Production Capabilities – Copper Products

## Conductor:

**Size Range (Multi-Conductor):** 26 AWG thru 4/0 AWG

**Size Range (Single Conductor):** 28 AWG thru 1000 kcmil

**Construction:** Stranded and Solid

**Material:** Copper, Copper Covered Steel, Galvanized Steel, Copper Alloy, Silver Plated Copper

**Coating:** Tin, Silver, Nickel

## Insulation:

### Low Temp Ranges:

**Ethylene Propylene Rubber:** Flexible (-40°C to +105°C)

**Tyrene Butadiene Rubber:** Flexible (-55°C to +60°C)

### PVC:

– Semi-Rigid, Conventional, Flexible, Clear, PVC/Nylon (-35°C to +105°C)

– For Plenum Cables, 75°C

**Polyethylene:** LD, HD, Solid, Chemical Foam, Gas Injection, Flame-Retardant (-76°C to +80°C)

**Polypropylene:** Solid, Chemical Foam (-25°C to +105°C)

**Zero-Halogen Polyolefin:** Solid or Foam (-40°C to +105°C)

### High Temp Ranges:

FEP (-100°C to +200°C), PVDF (-40°C to +150°C), Halar (-74°C to +150°C), Tefzel® (-50°C to +150°C), PVC (-40°C to +105°C), TPR (-65°C to +125°C), Hytrel® (-40°C to +105°C), Nylon (-65°C to +125°C)

## Identification:

Stripes or number printing, multiple color combinations using 1, 2 or 3 spiral stripes, number/legend printing (online), band marking (online or offline), up to 144 color combinations plus 1 or 2 spiral or parallel TRU-Mark® sequential footage marking

**Twinning:** 10 AWG thru 28 AWG

## Cabling:

500 MCM thru 28 AWG, 2 to 100 conductors, 1.25" maximum cable core diameter

## Shielding:

Braid or serve; combination of braid and aluminum shield, braid coverage up to 98%

**Materials:** Nylon, Fiberglass, Tinned Copper, Bare Copper, Silver Plated Copper, Aluminum, Bronze, Kevlar®, Aluminum and Aluminum Mylar® Tape Options

## Jacketing:

Up to 3.75" in cable diameter, 108" max. reel take-up

**CPE:** Flexible, oil resistance, flame-retardant (-50°C to +105°C)

**Neoprene:** Flexible, oil resistance, flame-retardant (-55°C to +90°C)

**Silicone:** High temperature ignition wire jacket (200°C)

**PVC:** Conventional, flexible, oil resistance, UV-resistant

**Polyolefin:** LD, MD, HD, solid, flame-retardant, zero-halogen

**Other:** TPR, Polyurethane, FR-Polyurethane, FEP, Halar, SOLEF, Tefzel

## Packaging:

– Reels, Plastic or Wood up to 72" diameter

– Reel-in-a-Box

– Spool-Pac®

– Pull-Pac®

## Testing:

– Complete mechanical and electrical/electronic testing

– Capabilities in accordance with UL, CSA, ETL and MSHA requirements

– General Cable's Willimantic, CT; Highland Heights, KY; and Indianapolis, IN laboratories have a wide range of mechanical test capabilities, including fire testing

## Certifications:

– UL Listed

– MSHA

– CSA Approvals

– TÜV

– ETL

– RoHS/CE Compliant

– IEEE

– REACH

– AWM

– ODVA

– TIA

Please consult your General Cable representative for additional information on product designs and constructions.

# Applications & Products

## Manufacturing Floor

### Carol® Brand Cord

- Type S00W – 300 V and 600 V Rubber Portable Cord
- Type SE00W – 600 V Plastic Portable Cord (junior available)
- Type ST0W – 600 V Plastic Portable Cord (junior available)
- Welding Cable
- Bus Drop Cable
- MTW Hook-Up Wire
- Industrial Flex Cables – 2 kV
- Type S00W – 300 V and 600 V Rubber Portable Cord with 17 FREE®

### Industrial & Specialty

- Instrumentation Tray Cables – 300 V and 600 V
- Control & Power Tray Cables – 600 V
- Variable Frequency Drive (VFD) Cables
- CCW® Armored Power and Instrumentation Cables
- Single Conductor Low-Voltage Cables
- Medium-Voltage Power Cables – 2.4 kV – 35 kV
- Industrial Armored Cables – 600 V – 35 kV

### NextGen® Brand Fiber

- LSZH Tight Buffer Distribution
- LSZH Loose Tube
- LSZH Heavy-Duty Breakout
- LSZH Heavy-Duty Armored Breakout
- LSZH Extra-Heavy-Duty Breakout
- LSZH Extra-Heavy-Duty Armored Breakout

### Carol® Brand Electronics

- EXZEL® High-Endurance Multi-Conductor & Multi-Pair Cable (Foil, Braid Shield)
- EXZEL High-Endurance LSZH Multi-Conductor & Multi-Pair Cable (Foil, Braid Shield)
- Communication and Control Multi-Conductor & Multi-Pair Cable (Unshielded, Shielded)
- Power Limited Tray Cable
- Coaxial Cable – Types RG-6, RG-11 and RG-59 Plenum Rated
- Twinaxial Cable
- DeviceNet Cable
- PVC Hook-Up Wire
- Computer Multi-Conductor & Multi-Pair Cable (Unshielded, Shielded)
- Type RG-59 Standard & Siamese Coaxial Cables with 17 FREE

### Datacom

- Carol Brand & GenSPEED® Category 6 Cable – UTP and F/UTP (ScTP)
- Carol Brand & GenSPEED Category 5e Cable – UTP and F/UTP (ScTP)
- GenSPEED Category 6 and 5e Cable with 17 FREE

## Data Center

### Datacom

- GenSPEED® 10 MTP™ Category 6A 10 Gig Cable
- Carol Brand & GenSPEED Category 6 Cable – UTP and F/UTP (ScTP)
- Central Office Cable
- GenSPEED 10,000 Category 6a and 6 with 17 FREE

### Carol® Brand Electronics

- Access Control Cable
- Type RG-59 Standard and Siamese Coaxial Cables with 17 FREE

### NextGen® Brand Fiber

- Tight Buffer Distribution
- Tight Buffer Distribution Interlock Armored
- Tight Buffer Breakout
- Tight Buffer Simplex
- Tight Buffer Duplex
- Loose Tube
- LSZH Tight Buffer Distribution with 17 FREE

### Industrial

- Single Conductor Low-Voltage for Battery Back-Up

## Back Office

### Datacom

- Carol Brand & GenSPEED Category 6 Cable – UTP and F/UTP (ScTP)
- Carol Brand & GenSPEED Category 5e Cable – UTP and F/UTP (ScTP)
- Central Office Cable
- GenSPEED Category 6 and 5e Cable with 17 FREE

### NextGen® Brand Fiber

- Tight Buffer Distribution
- Tight Buffer Distribution Interlock Armored
- Tight Buffer Breakout
- Tight Buffer Simplex
- Tight Buffer Duplex
- Loose Tube
- LSZH Tight Buffer Distribution with 17 FREE

### Carol® Brand Electronics

- Fire Alarm Cable
- Coaxial Cable – Types RG-6 and RG-59

### Carol® Brand Cord

- Thermostat Wire – 105 V
- Lamp Cord
- Cordsets

## Conference/Training Center

### Gepco® Brand Commercial Cables

- Component Video RGB Coaxial Cable
- Composite Access Control Cable – Video + Audio or Data
- High-Definition Coaxial Cable – HDTV
- Speaker & Control Multi-Conductor Cable – Shielded, Unshielded
- Microphone Cable
- Automation Control Cable
- Lighting Control Cable

## Security Office

### Carol® Brand Electronics

- Access Control Cable
- Security Multi-Conductor Cable – Shielded
- Coaxial Cable – Types RG-6, RG-11 and RG-59
- Burglar Alarm Cable

### Datacom


- GenSPEED 10 MTP Category 6A 10 Gig Cable
- Carol Brand & GenSPEED Brand Category 6 Cable
- Central Office Cable
- GenSPEED 10,000 Category 6a and 6 with 17 FREE



# Industrial Ethernet

The presence of harsh conditions and demanding applications in industrial environments makes choosing a high quality industrial Ethernet cable with the appropriate features critical. General Cable's new line of industrial Ethernet wire makes that decision easy by providing cables that meet the needs of harsh conditions on the plant floor by offering sustainable solutions in Category 5e and 6 cables.

Whatever your needs, General Cable has you covered. Whether it's a Category 5e or Category 6, unshielded, shielded, armored or outside plant, General Cable's offering of industrial Ethernet product is the perfect cable for an imperfect environment.




Part Number	Product Construction				Conductor Type	Jacket Grade	600 V AWM	CMR
	Category	Pairs	Shielded	Unshielded				
<b>GCR1402</b>	5e - UTP	2		•	Solid	Industrial - PVC	•	•
<b>GCR1404</b>	5e - UTP	4		•	Solid	Industrial - PVC	•	•
<b>GCR1408</b>	5e - UTP PLTC	4		•	Solid	Industrial - PVC	•	•
<b>GCR1410</b>	5e - UTP, Armored	4		•	Solid	Interlocked Armor	•	•
<b>GCR1403</b>	5e - F/UTP	2	•		Solid	Industrial - PVC	•	•
<b>GCR1419</b>	5e - F/UTP	4	•		Solid	Industrial - PVC		•
<b>GCR1405</b>	5e - F/UTP Enhanced	4	•		Solid	Industrial - PVC	•	•
<b>GCR1407</b>	5e - SF/UTP Enhanced	4	•		Solid	Industrial - PVC	•	•
<b>5136100</b>	5e - OSP	4		•	Solid	OSP - Halogen Free		
<b>5136101</b>	5e - OSP, Armored	4		•	Solid	OSP - Halogen Free Armor		
<b>GCR1440</b>	6 - UTP	4		•	Solid	Industrial - PVC		•
<b>GCR1450</b>	6 - UTP Enhanced	4		•	Solid	Industrial - PVC	•	•
<b>GCR1452</b>	6 - F/UTP	4	•		Solid	Industrial - PVC	•	•
<b>7136100</b>	6 - OSP	4		•	Solid	OSP - Halogen Free		

# Table of Contents

## INDUSTRIAL ETHERNET

	CATALOG NO.	DESCRIPTION	PAGE
<b>Category 5e</b>	GCR1402	Cat 5e UTP 2 Pair 600 V AWM	8
	GCR1404	Cat 5e UTP 4 Pair 600 V AWM	9
	GCR1408	Cat 5e 22 UTP PLTC 4 Pair 600 V AWM	10
	GCR1403	Cat 5e F/UTP 2 Pair 600 V AWM	11
	GCR1419	Cat 5e F/UTP 4 Pair	12
	GCR1405	Cat 5e F/UTP 4 Pair Enhanced 600 V AWM	13
	9899.CT02104000	Cat 5e CCW®	14
	GCR1407	Cat 5e SF/UTP 4 Pair 600 V AWM	15
	5136100	Cat 5e OSP 4 Pair	16
	5136101	Cat 5e OSP Armored 4 Pair	17
	GCR1410	Cat 5e Interlocking Armored 4 Pair	18
<b>Category 6</b>	GCR1440	Cat 6 UTP 4 Pair	19
	GCR1450	Cat 6 UTP 4 Pair Enhanced 600 V AWM	20
	GCR1452	Cat 6 F/UTP 4 Pair 600 V AWM	21
	7136100	Cat 6 OSP 4 Pair	22
<b>Fiber Optic</b>		NextGen® Brand Plus Corning® Optical Fiber Cross-Reference	23-24
		Tight Buffer Distribution Riser Cable, Indoor	25
		Tight Buffer Distribution Plenum Cable, Indoor	25
		Tight Buffer Distribution Interlock Armored Riser Cable, Indoor	26
		Tight Buffer Distribution Interlock Armored Plenum Cable, Indoor	26
		Tight Buffer Distribution Riser Cable, Indoor/Outdoor	27
		Tight Buffer Distribution Plenum Cable, Indoor/Outdoor	27
		Loose Tube Single Jacket Plenum Cable, Indoor/Outdoor	27
		Loose Tube Single Jacket Cable, Outdoor	28
		Loose Tube Dual Jacket Cable, Outdoor	28

# Industrial Ethernet Category 5e - 2 Pair Unshielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- UV RES per UL 444
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- Third-party verified for guaranteed performance
- TRU-Mark® print legend
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\*GENERAL CABLE\* GCR1402 INDUSTRIAL CAT 5E 2PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C UV RES---VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E AWM 21047 75C 600 V---FT4 OIL RES ODVA ETHERNET/IP (TM) VEN 1293 PAT 5767441 ##-## ##### CAT 5E

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1402	7507	0.200	5.080	18	8	2	24	1: Orange/White, Orange 2: Green/White, Green	HDPE	Unshielded	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR (dB/100 m)	PSACR (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8
200	32.4	30.8	27.8	—	—	17.8	14.8	18.0
250	36.9	29.3	26.3	—	—	15.8	12.8	17.3
300	41.0	28.1	25.1	—	—	14.3	11.3	16.6
350	44.9	27.1	24.1	—	—	12.9	9.9	16.3

Values over 200 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**


Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-200 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	20 lbs.
Minimum Bend Radius	0.25"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 5e - 4 Pair Unshielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- UV RES per UL 444
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)
- MSHA Signaling Cable P-07-KA140022-MSHA

**Features and Benefits:**

- Third-party verified for guaranteed performance
- TRU-Mark® print legend
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\*GENERAL CABLE\* GCR1404 INDUSTRIAL CAT 5E 4PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C UV RES VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E AWM 21047 75C 600 V---FT4 OIL RES P-07-KA140022-MSHA ODVA ETHERNET/IP (TM) VEN 1293 PAT 5767441 ##-## ##### CAT 5E

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1404	7500	0.225	5.715	24	11	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Unshielded	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)		Next (dB)		PSNext (dB)		ACR (dB/100 m)		PSACR (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		Return Loss (dB)	
	max.		min.		min.		min.		min.		min.		min.		min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0								
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6								
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0								
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0								
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0								
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5								
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0								
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5								
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5								
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8								
200	32.4	30.8	27.8	—	—	17.8	14.8	18.0								
250	36.9	29.3	26.3	—	—	15.8	12.8	17.3								
300	41.0	28.1	25.1	—	—	14.3	11.3	16.6								
350	44.9	27.1	24.1	—	—	12.9	9.9	16.3								

Values over 200 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-200 MHz)	Ohms: 100±15


**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	25 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C





# Industrial Ethernet Category 5e - 4 Pair PLTC Unshielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- NEC/CEC Type PLTC (UL 13)
- UL AWM Style 2570 (UL: 80°C, 600 V)
- SUN RES per UL 444 and UL 13
- UL OIL RES I and II per UL 13
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- Third-party verified for guaranteed performance
- TRU-Mark® print legend contains footage markings
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\* FEET GENERAL CABLE® GCR1408 INDUSTRIAL CAT 5E CATEGORY 5E 4PR/22AWG RISER CABLE C(UL)US CMX OUTDOOR - CMR 75C VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E---AWM 2570 80C 600 V---(UL) PLTC SUN RES OIL RES I---FT4 ETHERNET/IP (TM) PAT 5767441  
 \*\*.\* \*AAAAA CAT 5

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1408	7503	0.295	7.490	38	14	4	22	1: White/Blue, Blue 2: White/Orange, Orange 3: White/Green, Green 4: White/Brown, Brown	HDPE	Unshielded	Polyester	Oil- and Sunlight-Resistant PVC	0.042	1.070	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR (dB/100 m)	PSACR (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	21.6
200	32.4	30.8	27.8	—	—	17.8	14.8	21.0
250	36.9	29.3	26.3	—	—	15.8	12.8	20.5
300	41.0	28.1	25.1	—	—	14.3	11.3	20.1
350	44.9	27.1	24.1	—	—	12.9	9.9	19.8

Values over 200 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**


Maximum DC Resistance	5.6 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-200 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	40 lbs.
Minimum Bend Radius	1.2"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-25°C to +75°C



# Industrial Ethernet Category 5e - 2 Pair F/UTP Shielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- Noisy (EMI) Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- SUN RES per UL 444
- UL OIL RES I and II
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- Foil shield reduces electromagnetic interference (EMI) for optimal performance
- Third-party verified for guaranteed performance
- TRU-Mark® print legend contains footage markings
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\* FEET GENERAL CABLE F GCR1403 INDUSTRIAL F/UTP CAT 5E 2PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C SUN RES VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E AWM 21047 75C 600 V---FT4 OIL RES II ODVA ETHERNET/IP (TM) VEN 1293 PAT 5767441 \*\*-\* \*AAAAA CAT 5E

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1403	7506	0.230	5.842	23	10	2	24	1: Orange/White, Orange 2: Green/White, Green	HDPE	100% F/UTP	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR (dB/100 m)	PSACR (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8
200	32.4	30.8	27.8	—	—	17.8	14.8	18.0
250	36.9	29.3	26.3	—	—	15.8	12.8	17.3
300	41.0	28.1	25.1	—	—	14.3	11.3	16.8
350	44.9	27.1	24.1	—	—	12.9	9.9	16.3

Values over 200 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**


Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedence (Frequency 1-200 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	20 lbs.
Minimum Bend Radius	0.5"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 5e - 4 Pair F/UTP Shielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- Noisy (EMI) Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- SUN RES per UL 444
- UL OIL RES I and II
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)
- MSHA Signaling Cable P-07-KA140025-MSHA

**Features and Benefits:**

- Foil shield reduces electromagnetic interference (EMI) for optimal performance
- Third-party verified for guaranteed performance
- TRU-Mark® print legend contains footage markings
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\* GENERAL CABLE® GCR1419 INDUSTRIAL F/UTP CAT 5E 4PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C SUN RES VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E---FT4 OIL RES II P-07-KA140022-MSHA ODVA ETHERNET/IP (TM) VEN 1293 PAT 5767441 #- #-# ##### CAT 5E

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1419	7508	0.270	6.858	34	15	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	100% F/UTP	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)		Next (dB)		PSNext (dB)		ACR (dB/100 m)		PSACR (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		Return Loss (dB)	
	max.		min.		min.		min.		min.		min.		min.		min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0								
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6								
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0								
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0								
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0								
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5								
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0								
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5								
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5								
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8								
200	32.4	30.8	27.8	—	—	17.8	14.8	18.0								
250	36.9	29.3	26.3	—	—	15.8	12.8	17.3								
300	41.0	28.1	25.1	—	—	14.3	11.3	16.8								
350	44.9	27.1	24.1	—	—	12.9	9.9	16.3								

Values over 100 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**


Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-200 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	25 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 5e - 4 Pair Enhanced F/UTP Shielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- Noisy (EMI) Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- SUN RES per UL 444
- UL OIL RES I and II
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)
- MSHA Signaling Cable P-07-KA140025-MSHA

**Features and Benefits:**

- Foil shield reduces electromagnetic interference (EMI) for optimal performance
- Third-party verified for guaranteed performance
- TRU-Mark® print legend contains footage markings
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\* GENERAL CABLE \* GCR1405 INDUSTRIAL F/UTP CAT 5E 4PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C SUN RES VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E AWM 21047 75C 600 V---FT4 OIL RES II P-07-KA140025-MSHA ODVA ETHERNET/IP (TM) VEN 1293 PAT 5767441 ##-## ##### CAT 5E

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1405	7501	0.270	6.858	34	15	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	100% F/UTP	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)		Next (dB)		PSNext (dB)		ACR (dB/100 m)		PSACR (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		Return Loss (dB)	
	max.		min.		min.		min.		min.		min.		min.		min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0								
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6								
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0								
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0								
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0								
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5								
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0								
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5								
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5								
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8								
200	32.4	30.8	27.8	—	—	17.8	14.8	18.0								
250	36.9	29.3	26.3	—	—	15.8	12.8	17.3								
300	41.0	28.1	25.1	—	—	14.3	11.3	16.8								
350	44.9	27.1	24.1	—	—	12.9	9.9	16.3								

Values over 200 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedence (Frequency 1-200 MHz)	Ohms: 100±15


**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	25 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C





# Industrial Ethernet Category 5e - 4 Pair CCW<sup>®</sup>



**Applications:**

- For high speed data transmission. Tested to 100 MHz
- CID1 applications
- Recognized for use in Class I and III, Divisions 1 and 2; Class II, Division 2; or Class 1, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- Installed indoors or outdoors, in wet or dry locations, in a raceway, as aerial cable on a messenger, in cable trays, or for direct burial

**Compliances:**

- TIA/EIA 568-B.2 Category 5e
- UL Listed, NEC Type ITC-HL, 300 V, CT USE, SUN RES, DIR BUR, -40°C

**Features and Benefits:**

- CCW armor provides an impervious barrier to moisture, gas and liquids
- Meets cold bend at -55°C
- Insulation and inner jacket passes ASTM D746-04 brittleness temperature impact test at -73°C
- Arctic-grade PVC inner sheath and outer jacket passes ASTM D746-04 brittleness temperature impact test at -60°C

CATALOG NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
	INCHES	mm	LBS	kg								INCHES	mm	
9899.CT02104000	0.930	23.62	382	173	4	21	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	Fluoropolymer	Unshielded	Polyester	Fluoropolymer	0.180	4.57	Light Blue

Frequency (MHz)	Insertion Loss (dB/100 m) max.	Next (dB/100 m) min.	PSNext (dB/100 m) min.	ACRF (dB/100 m) min.	PSACRF (dB/100 m) min.	Char. Impedance (Ohms) (+/-15)	Return Loss (dB) min.
1	2.0	66.3	65.3	63.8	60.8	100	20.0
4	4.1	56.3	53.3	51.7	48.7	100	23.0
8	5.8	51.8	48.8	45.7	42.7	100	24.5
10	6.5	50.3	47.3	43.8	40.8	100	25.0
16	8.2	47.3	44.3	39.7	36.7	100	25.0
20	9.3	45.8	42.8	37.7	34.7	100	25.0
25	10.4	44.3	41.3	35.8	32.8	100	24.3
31.25	11.7	42.9	39.9	33.9	30.9	100	23.6
62.5	17.0	38.4	35.4	27.8	24.8	100	21.5
100	22.0	35.3	32.3	23.8	20.8	100	20.1

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	9.3 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	5%
Nominal Velocity of Propagation	70%
Characteristic Impedance (Frequency 1-350 MHz)	Ohms: 100±15



# Industrial Ethernet Category 5e - 4 Pair SF/UTP Shielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- Noisy (EMI) Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- SUN RES per UL 444
- UL OIL RES I and II
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- Foil shield reduces electromagnetic interference (EMI) for optimal performance
- Third-party verified for guaranteed performance
- TRU-Mark® print legend contains footage markings
- Industrial-grade oil- and sunlight-resistant jacket
- Additional braid shield for added low frequency EMI protection

**Print Legend:**

\*\*\*\* GENERAL CABLE \* GCR1407 INDUSTRIAL SF/UTP CAT 5E 4PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C SUN RES VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E AWM 21047 75C 600 V--- FT4 OIL RES II ODVA ETHERNET/IP (TM) VEN 1293 PAT 5767441 ##-## ##### CAT 5E\*AAAAA:

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1407	7502	0.305	7.239	47	21	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	100%/80% SF/UTP	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)		Next (dB)		PSNext (dB)		ACR (dB/100 m)		PSACR (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		Return Loss (dB)	
	max.		min.		min.		min.		min.		min.		min.		min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0								
4	4.1	56.3	53.3	52.2	49.2	51.7	48.7	23.6								
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	26.0								
16	8.2	47.3	44.3	39.0	36.1	39.7	36.7	26.0								
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	26.0								
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	25.5								
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	25.0								
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	23.5								
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	22.5								
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8								
200	32.4	30.8	27.8	—	—	17.8	14.8	18.0								
250	36.9	29.3	26.3	—	—	15.8	12.8	17.3								
300	41.0	28.1	25.1	—	—	14.3	11.3	16.8								
350	44.9	27.1	24.1	—	—	12.9	9.9	16.3								

Values over 200 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-200 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	40 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 5e Outside Plant Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Non-armored design is recommended for duct installation

**Compliances:**

- ANSI/TIA 568-C.2
- UL 444
- RoHS Compliant Directive 2011/65/EU
- ANSI/TIA 862 (Building Automation)
- ICEA S-90-661
- ISO/IEC 11801 Ed. 2.0 (Class D)
- Telcordia (Bellcore) Specification GR-421-CORE Water Penetration Requirements

**Features and Benefits:**

- Protects against environmental elements that can cause electrical performance failures
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Prevents moisture migration
- Made in U.S.A.
- Gel-filled construction to prevent moisture migration in underground and wet applications

**Print Legend:**

XXXXXX FEET CAT 5e GENERAL CABLE (F) 4PR24AWG  
GENSPEED 5000 OUTDOOR - DIR BUR UTP CAT.5e  
AAAAA PAT 5767441 MO/YR

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
5136100	N/A	0.230	5.842	25	11	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Unshielded	Polyester	UV and Abrasion Resistant Zero-Halogen Polyethylene	0.032	0.813	Black

Frequency (MHz)	Insertion Loss (dB/100 m)		Next (dB)		PSNext (dB)		ACR* (dB/100 m)		PSACR* (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		Return Loss (dB)	
	max.		min.		min.		min.		min.		min.		min.		min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0								
4	4.1	56.3	53.3	52.2	49.2	51.7	48.8	23.0								
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25.0								
16	8.2	47.2	44.2	39.0	36.0	39.7	36.7	25.0								
20	9.3	45.8	42.8	36.5	33.5	37.7	34.8	25.0								
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	24.3								
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6								
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.9	21.5								
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1								
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	—								
200	32.4	30.8	27.8	—	—	17.8	14.8	—								
250	36.9	29.3	26.3	—	—	15.8	12.8	—								
300	41.0	28.1	25.1	—	—	14.3	11.3	—								
350	44.9	27.1	24.1	—	—	12.9	9.9	—								

Values above 100 MHz are for informational purposes.  
\*PSACR & ACR not specified in ANSI/TIA 568-C.2.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	9.38 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	4%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	69% Speed of Light
Characteristic Impedance (Frequency 1-100 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	25 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-30°C to +60°C
Operation Temperature Rating	-45°C to +80°C



# Industrial Ethernet Category 5e - 4 Pair Outside Plant Armored Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Armored: aerial, duct and buried installations

**Compliances:**

- ANSI/TIA 568-C.2
- UL 444
- RoHS Compliant Directive 2011/65/EU
- ANSI/TIA 862 (Building Automation)
- ICEA S-90-661
- ISO/IEC 11801 Ed. 2.0 (Class D)
- Telcordia (Bellcore) Specification GR-421-CORE Water Penetration Requirements

**Features and Benefits:**

- Protects against environmental elements that can cause electrical performance failures
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Prevents moisture migration
- Made in U.S.A.
- Gel-filled construction to prevent moisture migration in underground and wet applications

**Print Legend:**

XXXXXX FEET CAT 5e GENERAL CABLE (F) 4PR24AWG GENSPEED 5000 ARMORED OUTDOOR - DIR BUR UTP CAT.5e AAAAA Pat 5767441 MO/YR

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
5136101	N/A	0.340	8.636	50	23	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Aluminum Armor	Polyester	UV Abrasion-Resistant Polyethylene	0.032	0.813	Black

Frequency (MHz)	Insertion Loss (dB/100 m)		Next (dB)		PSNext (dB)		ACR* (dB/100 m)		PSACR* (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		Return Loss (dB)	
	max.		min.		min.		min.		min.		min.		min.		min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0								
4	4.1	56.3	53.3	52.2	49.2	51.7	48.8	23.0								
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25.0								
16	8.2	47.2	44.2	39.0	36.0	39.7	36.7	25.0								
20	9.3	45.8	42.8	36.5	33.5	37.7	34.8	25.0								
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	24.3								
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6								
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.9	21.5								
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1								
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	-								
200	32.4	30.8	27.8	-	-	17.8	14.8	-								
250	36.9	29.3	26.3	-	-	15.8	12.8	-								
300	41.0	28.1	25.1	-	-	14.3	11.3	-								
350	44.9	27.1	24.1	-	-	12.9	9.9	-								

Values above 100 MHz are for informational purposes.  
\*PSACR & ACR not specified in ANSI/TIA 568-C.2.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	9.38 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	4%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	69% Speed of Light
Characteristic Impedance (Frequency 1-100 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	25 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-30°C to +60°C
Operation Temperature Rating	-45°C to +80°C





# Industrial Ethernet Category 5e Interlocking Armored Cable



**Applications:**

- IEEE 802.3: 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- ODVA EtherNet/IP™

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 5e
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- UV RES per UL 444
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- Protects against environmental elements that can cause electrical performance failures
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Prevents moisture migration
- Made in U.S.A.

**Print Legend:**

\*\*\* GENERAL CABLE F GCR1410 INDUSTRIAL ARMORED CAT 5E 4PR/24AWG RISER C(UL) US CMX OUTDOOR - CMR 75C UV RES VERIFIED (UL) ANSI/TIA-568C.2 CAT 5E AWM 21074 75C 600 V---FT4 OIL RES ODVA ETHERNET/IP™ VEN 1293 PAT 5767441 ##### CAT 5E

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1410	7508	0.270	6.858	34	15	4	24	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Unshielded	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR* (dB/100 m)	PSACR* (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0
4	4.1	56.3	53.3	52.2	49.2	51.7	48.8	23.0
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25.0
16	8.2	47.2	44.2	39.0	36.0	39.7	36.7	25.0
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	25.0
25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	24.3
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	21.5
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	—
200	32.4	30.8	27.8	—	—	17.8	14.8	—
250	36.9	29.3	26.3	—	—	15.8	12.8	—
300	41.0	28.1	25.1	—	—	14.3	11.3	—
350	44.9	27.1	24.1	—	—	12.9	9.9	—

Values above 100 MHz are for informational purposes.  
\*PSACR & ACR not specified in ANSI/TIA 568-C.2.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	9.38 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	69% Speed of Light
Characteristic Impedance (Frequency 1-100 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Nominal Cable Diameter	0.340"
Nominal Cable Weight	50 lbs.
Maximum Pulling Force	25 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-30°C to +60°C
Operation Temperature Rating	-40°C to +80°C



# Industrial Ethernet Category 6 - 4 Pair Unshielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 6
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UV RES per UL 444
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- TRU-Mark® print legend
- Third-party verified for guaranteed performance
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\* GENERAL CABLE \* GCR1440 INDUSTRIAL CAT 6 4PR/23AWG RISER C(UL)US CMX OUTDOOR - CMR 75C VERIFIED (UL) ANSI/TIA-568C.2 CAT-6---FT4 OIL RES UV RES PAT 5767441 ##-## ##### CAT 6

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1440	7509	0.270	6.858	38	17	4	23	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Unshielded	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR (dB/100 m)	PSACR (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.0	74.3	72.3	72.3	70.3	67.8	64.8	20.0
4	3.8	65.3	63.3	61.5	59.3	55.7	52.8	23.6
10	6.0	59.3	57.3	53.3	51.3	47.8	44.8	26.0
16	7.6	56.2	54.2	48.7	46.7	43.7	40.7	26.0
20	8.5	54.8	52.8	46.3	44.3	41.7	38.8	26.0
31.25	10.7	51.9	49.9	41.2	39.2	37.9	34.9	26.0
62.5	15.4	47.4	45.4	32.0	29.9	31.8	28.9	25.5
100	19.8	44.3	42.3	24.5	22.5	27.8	24.8	22.5
150	24.7	41.7	39.7	16.9	14.9	24.3	21.3	18.9
200	29.0	39.8	37.8	10.8	8.8	21.8	18.8	18.0
250	32.8	38.3	36.3	5.5	3.5	19.8	16.8	17.3
350	39.8	36.1	34.1	-	-	16.9	13.9	16.3
500	48.9	33.8	31.8	-	-	13.8	10.8	15.2

Values over 250 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-350 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	41 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-10°C to +60°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 6 - 4 Pair Enhanced Unshielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 6
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- UV RES per UL 444
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- TRU-Mark® print legend
- Third-party verified for guaranteed performance
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

\*\*\*\* GENERAL CABLE \* GCR1450 INDUSTRIAL CAT 6 4PR/23AWG RISER C(UL)US CMX OUTDOOR - CMR 75C VERIFIED (UL) ANSI/TIA-568C.2 CAT-6 AWM 21047 75C 600 V---FT4 OIL RES UV RES PAT 5767441 ##-## ##### CAT 6

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1450	7504	0.270	6.858	38	17	4	23	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Unshielded	Polyester	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR (dB/100 m)	PSACR (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.0	79.3	77.3	77.3	75.3	72.8	69.8	20.0
4	3.8	70.2	68.3	66.5	64.5	60.7	57.7	23.6
10	5.9	64.3	62.3	58.4	56.4	52.8	49.8	26.0
16	7.5	61.3	59.3	53.8	51.7	48.7	45.7	26.0
20	8.4	59.8	57.6	51.4	49.4	46.7	43.7	26.0
31.25	10.6	56.9	54.9	46.3	44.3	42.9	39.9	26.0
62.5	15.3	52.4	50.4	37.1	35.1	36.8	33.8	25.5
100	19.7	49.3	47.3	29.6	27.6	32.8	29.8	22.5
150	24.7	46.7	44.7	22.0	20.0	29.3	26.3	21.6
200	29.0	44.8	42.8	15.8	13.8	26.8	23.8	21.0
250	32.6	43.3	41.3	10.7	8.7	24.8	21.6	20.5
350	39.5	41.2	39.2	1.7	-	21.9	18.9	19.8
500	48.6	38.8	36.6	-	-	18.8	15.8	19.0

Values over 350 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	8.9 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	3%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedance (Frequency 1-350 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	41 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 6 - 4 Pair F/UTP Shielded Twisted Pair Cable



**Applications:**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- CDDI, Token Ring, ATM
- Broadband and Baseband Analog Video
- Voice, T1
- Harsh Industrial Environments
- Noisy (EMI) Environments

**Compliances:**

- UL Verified to ANSI/TIA 568-C.2 Category 6
- NEC/CEC Type: UL Listed CMX OUTDOOR - CMR
- NEC/CEC Type CMR (UL 1666)
- UL AWM Style 21047 (UL: 75°C, 600 V)
- UV RES per UL 444
- RoHS II Compliant (EU DIRECTIVE 2011/65/EU)

**Features and Benefits:**

- Foil shield reduces electromagnetic interference (EMI) for optimal performance
- Third-party verified for guaranteed performance
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Industrial-grade oil- and sunlight-resistant jacket

**Print Legend:**

4 PAIR 23 AWG SCREENED TWISTED PAIR (SCTP) CABLE, FOR HIGH SPEED DATA TRANSMISSION AND IS TESTED TO 500 MHZ. THIS CABLE IS CMX OUTDOOR - CMR RATED AND UL VERIFIED TO CATEGORY 6 ELECTRICALS.

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
GCR1452	7505	0.385	8.509	46	21	4	23	1: White, Blue 2: White, Orange 3: White, Green 4: White, Brown	HDPE	100% Foil	Non-Applicable	Oil- and Sunlight-Resistant PVC	0.032	0.813	Red, Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR (dB/100 m)	PSACR (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.1	74.3	72.0	72.2	70.2	67.8	64.8	20.0
4	3.8	65.3	63.3	61.5	59.5	55.8	52.8	23.6
10	5.9	59.3	57.3	53.4	51.4	47.8	44.8	26.0
16	7.5	56.2	54.2	48.8	46.8	43.7	40.7	26.0
20	8.4	54.8	52.8	46.4	44.4	41.8	38.8	26.0
31.25	10.5	51.9	49.9	41.4	39.4	37.9	34.9	25.5
62.5	15.0	47.4	45.4	32.4	30.4	31.9	28.9	23.5
100	19.1	44.3	42.3	25.2	23.2	27.8	24.8	22.5
150	23.7	41.7	39.7	18.0	16.0	24.3	21.3	18.9
200	27.6	39.8	37.8	12.2	10.2	21.8	18.8	18.0
250	31.1	38.3	36.3	7.2	5.2	19.8	19.8	17.3
300	34.3	37.1	35.1	2.9	0.9	18.3	18.3	16.8
400	40.1	35.3	33.3	—	—	15.8	15.8	15.9
500	45.3	33.8	31.8	—	—	13.8	13.8	15.2

Values over 350 Mhz are for informational purposes.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	9.38 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	4%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	35 ns/100 m
Nominal Velocity of Propagation	70% Speed of Light
Characteristic Impedence (Frequency 1-350 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Maximum Pulling Force	40 lbs.
Minimum Bend Radius	2.50"
Installation Temperature Rating	-20°C to +75°C
Operation Temperature Rating	-40°C to +75°C



# Industrial Ethernet Category 6 - 4 Pair Outside Plant Cable



**Applications**

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+
- ANSI/TIA 854: 1000 BASE-TX
- CDDI, Token Ring, ATM
- Digital Video
- Broadband and Baseband Analog Video
- Duct and conduit installations
- Not to be used aerially or direct buried

**Compliances:**

- ANSI/TIA 568-C.2
- UL 444
- RoHS Compliant Directive 2011/65/EU
- ANSI/TIA 862 (Building Automation)
- ICEA S-116-732
- ICEA S-102-700
- ISO/IEC 11801 Ed. 2.0 (Class E)
- Telcordia (Bellcore) Specification GR-421-CORE Water Penetration Requirement

**Features and Benefits:**

- Innovative cross-web design allowing for maximum pair separation, increasing key electrical performance parameters
- Gel-filled construction to prevent moisture migration in underground and wet applications
- Wide temperature range for extreme weather environments
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Made in U.S.A.

**Print Legend:**

XXXXXX FEET CAT 6 GENERAL CABLE (F) 4PR23AWG GENSPEED 6000 OUTDOOR - DIR BUR UTP CAT.6 AAAAA PAT 5767441 MO/YR

CATALOG NUMBER	SPEC NUMBER	NOMINAL O.D.		CABLE WEIGHT MFT		NO. PAIRS	COND. AWG SIZE	PAIR COLOR CODE	INSULATION MATERIAL	SHIELD COVERAGE	RIPCORD	JACKET MATERIAL	JACKET THICKNESS		JACKET COLORS
		INCHES	mm	LBS	kg								INCHES	mm	
7136100	N/A	0.250	6.350	32	14.5	4	23	1: Blue/White, Blue 2: Orange/White, Orange 3: Green/White, Green 4: Brown/White, Brown	HDPE	Unshielded	Polyester	UV and Abrasion Resistant Zero-Halogen Polyethylene	0.032	0.813	Black

Frequency (MHz)	Insertion Loss (dB/100 m)	Next (dB)	PSNext (dB)	ACR* (dB/100 m)	PSACR* (dB/100 m)	ACRF (dB/100 m)	PSACRF (dB/100 m)	Return Loss (dB)
	max.	min.	min.	min.	min.	min.	min.	min.
1	2.0	74.3	72.3	72.3	70.3	67.8	64.8	20.0
4	3.8	65.3	63.3	61.5	59.3	55.8	52.8	23.0
10	6.0	59.3	57.3	53.3	51.3	47.8	44.8	25.0
16	7.6	56.2	54.2	48.7	46.7	43.7	40.7	25.0
20	8.5	54.8	52.8	46.3	44.3	41.8	38.8	25.0
31.25	10.7	51.9	49.9	41.2	39.2	37.9	34.9	23.6
62.5	15.4	47.4	45.4	32.0	29.9	31.9	28.9	21.5
100	19.8	44.3	42.3	24.5	22.5	27.8	24.8	20.1
200	29.0	39.8	37.8	10.8	8.8	24.3	18.8	18.0
250	32.8	38.3	36.3	5.5	3.5	21.8	16.8	17.3

\*PSACR & ACR not specified in ANSI/TIA 568-C.2.

**ELECTRICAL CHARACTERISTICS**

Maximum DC Resistance	9.38 Ohms/100 m @ 20° C
Maximum DC Resistance Unbalance, Ind Pair	4%
Maximum Mutual Capacitance	17 pF/ft @ 1 KHz
Maximum Delay Skew	45 ns/100 m
Nominal Velocity of Propagation	69% Speed of Light
Characteristic Impedance (Frequency 1-250 MHz)	Ohms: 100±15

**MECHANICAL CHARACTERISTICS**

Nominal Cable Diameter	0.250"
Nominal Cable Weight	32 lbs.
Maximum Pulling Force	32 lbs.
Minimum Bend Radius	1.00"
Installation Temperature Rating	-30°C to +60°C
Operation Temperature Rating	-45°C to +80°C





# Optical Fiber Code Cross-Reference

FIBER TYPE	NEXTGEN® BRAND	CORNING® OPTICAL FIBER	DESCRIPTION
Standard Loose Tube SM	AQ	SMF-28® Ultra	Full spectrum, low water peak singlemode, ITU-T Recommendation G.657.A1, IEC 60793-2-50 for B1.3 and B6_a1 class fibers, TIA/EIA-492CAAB and Telcordia GR-20-CORE, Issue 3
Performance Loose Tube SM	AT	SMF-28® Ultra	Full spectrum, high performance low water peak singlemode with 0.35/0.25 attenuation, ITU-T Recommendation G.657.A1, IEC 60793-2-50 for B1.3 and B6_a1 class fibers, TIA/EIA-492CAAB and Telcordia GR-20-CORE, Issue 3
Tight Buffer SM	AP	SMF-28® Ultra	Full spectrum, low water peak singlemode with 900 µm PVC buffer, ITU-T Recommendation G.657.A1, IEC 60793-2-50 for B1.3 and B6_a1 class fibers, TIA/EIA-492CAAB and Telcordia GR-20-CORE, Issue 3
Long-Haul SM	AL	LEAF® Fiber	Large $A_{eff}$ , low water peak, NZ-DSF singlemode, ITU-T G.655
Ultra-Bendable SM	AZ	ClearCurve® ZBL	Full spectrum with best macrobending performance, ITU-T G.652.D and ITU-T G.657.A
62.5 µm MM	CG	InfiniCor® 300 Fiber	1 Gb/s ≤ 300 m at 850 nm, OM1* 1 Gb/s ≤ 550 m at 1300 nm
62.5 µm MM	CL	InfiniCor® CL™ 1000 Fiber	1 Gb/s ≤ 500 m at 850 nm, OM1* 1 Gb/s ≤ 1000 m at 1300 nm
Ultra-bendable 50 µm MM	BI	ClearCurve® OM2 Fiber	10 Gb/s ≤ 150 m at 850 nm, OM2* 1 Gb/s ≤ 750 m at 850 nm
Ultra-bendable 50 µm MM	BE	ClearCurve® OM3 Fiber	10 Gb/s ≤ 300 m at 850 nm, OM3* 1 Gb/s ≤ 1000 m at 850 nm
Ultra-bendable 50 µm MM	BL	ClearCurve® OM4 Fiber	10 Gb/s ≤ 550 m at 850 nm, OM4* 1 Gb/s ≤ 1100 m at 850 nm
Ultra-bendable 50 µm MM	BM	ClearCurve® OM4 Fiber	10 Gb/s ≤ 600 m at 850 nm, OM4+* 1 Gb/s ≤ 1100 m at 850 nm

\* Designation per ISO 11801 Fiber Standards



SMF-28 Ultra is a trademark and Corning, LEAF, InfiniCor and Plus Corning Optical Fiber are registered trademarks of Corning Incorporated, Corning, NY, U.S.A.

# Fiber Specification and Selection

## MULTIMODE FIBER SELECTION GUIDE

Optical Characteristics:		50/125 PRODUCT FAMILY				62.5/125 PRODUCT FAMILY		UNITS
		OM2 Type-BI	OM3 Type-BE	OM4 Type-BL	OM4 Type-BM	OM1 Type-CG	OM1 Type-CL	
Maximum Finished Cable Attenuation Coefficient	@850 nm	3.0	3.0	3.0	3.0	3.5	3.5	dB/km
	@1300 nm	1.0	1.0	1.0	1.0	1.0	1.0	dB/km
Overfill Launch Bandwidth	@850 nm	700	1500	1500	1500	200	200	MHz.km
	@1300 nm	500	500	500	500	500	500	MHz.km
Laser Bandwidth	@850 nm	850	2000	4700	5350*	220	385	MHz.km
Gigabit Ethernet Link Length (1 Gbps)	1000 BASE-SX (850 nm)	750	1000	1100	1100	300	500	meters
	1000 BASE-LX (1300 nm)	550	550	550	550	550	1000	meters
10 Gigabit Ethernet Link Length (10 Gbps)	10G BASE-SR (850 nm)	150	300	550	600	33	33	meters

\* Using 3.0 dB cable attenuation and 0.7 dB connector allocation



## SINGLEMODE FIBER SELECTION GUIDE

FIBER DESCRIPTION	FIBER TYPE	TYPICAL ATTENUATION (dB/km)				GIGABIT ETHERNET DISTANCE (METERS)	10 GIGABIT ETHERNET DISTANCE (METERS)	
		1310 nm	1383 nm	1550 nm	1625 nm	1310 nm	1310 nm	1550 nm
<b>OS2 SINGLEMODE - LOOSE TUBE</b>								
Premium	AQ	0.40	0.40	0.30	0.35	10,000	5,000	30,000
High Performance	AT	0.35	0.35	0.25	0.30	10,000	5,000	30,000
<b>OS2 SINGLEMODE - TIGHT BUFFER</b>								
Distribution	AP	0.65	-	0.65	-	10,000	5,000	30,000
Breakout	AP	1.00	-	1.00	-	10,000	5,000	30,000

## SPECIALTY FIBERS – SINGLEMODE

FIBER DESCRIPTION	FIBER TYPE	TYPICAL ATTENUATION (dB/km)				TYPICAL APPLICATION
		1310 nm	1383 nm	1550 nm	1625 nm	
<b>Singlemode (NZDS)</b>						
Large Effective Area	AL	-	-	0.30	0.30	DWDM
<b>Singlemode</b>						
Bend-Insensitive	AZ	0.40	0.40	0.30	0.30	SMALL BEND RADIUS

Use the code in the "Fiber Type" column to replace the XX notation in the catalog number shown on the catalog page. This identifies the fiber that will be provided with the cable choice.

The fibers in all completed cables are tested 100% at the factory for attenuation, and each fiber must meet the minimum requirements specified by the customer.

# Tight Buffer Distribution Riser Cable Type OFNR, CSA FT4, Indoor\*




CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021PNR	2	—	0.19	5	14	20	225	1000	65	290
XX0061PNR	6	—	0.20	5	18	27	225	1000	65	290
XX0121PNR	12	—	0.25	6	24	36	320	1425	112	500
XX0241P1R	24	4	0.34	9	47	70	330	1425	112	500

XX denotes glass type.

NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.

\*Not for aerial or direct burial applications.

# Tight Buffer Distribution Plenum Cable Type OFNP, CSA FT6, Indoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021PNU	2	—	0.17	4	12	17	225	1000	65	290
XX0061PNU	6	—	0.18	5	16	24	225	1000	65	290
XX0121PNU	12	—	0.22	6	23	34	320	1423	112	500
XX0241PNU	24	—	0.32	8	45	67	320	1423	112	500

XX denotes glass type.

NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.

\*Not for aerial or direct burial applications.

## Tight Buffer Distribution Interlock Armored Riser Cable Type OFCR, CSA FT4, Indoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021PNR-ILRA	2	—	0.52	13	85	126	550	2447	165	734
XX0041PNR-ILRA	4	—	0.57	14	95	141	550	2447	165	734
XX0061PNR-ILRA	6	—	0.57	14	98	146	550	2447	165	734
XX0121PNR-ILRA	12	—	0.57	14	104	155	550	2447	165	734
XX0241PNR-ILRA	24	—	0.67	17	144	214	550	2447	165	734

XX denotes glass type.

NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.

\*Not for aerial or direct burial applications.

## Tight Buffer Distribution Interlock Armored Plenum Cable Type OFCP, CSA FT6, Indoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021PNU-ILPA	2	—	0.49	12	80	119	550	2447	165	734
XX0041PNU-ILPA	4	—	0.49	12	82	122	550	2447	165	734
XX0061PNU-ILPA	6	—	0.49	12	84	125	550	2447	165	734
XX0121PNU-ILPA	12	—	0.49	12	100	149	550	2447	165	734
XX0241PNU-ILPA	24	—	0.59	15	138	205	550	2447	165	734

XX denotes glass type.

NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.

\*Not for aerial or direct burial applications.

# Tight Buffer Distribution Riser Cable Type OFNR, CSA FT4, Indoor/Outdoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021ANR.BK	2	—	0.19	5	14	20	300	1334	90	400
XX0061ANR.BK	6	—	0.20	6	18	27	320	1423	96	427
XX0121ANR.BK	12	—	0.25	6	24	36	400	1780	120	534
XX0241ANR.BK	24	—	0.34	9	47	70	320	1425	112	500

XX denotes glass type.  
NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.  
\*Not for aerial or direct burial applications.

# Tight Buffer Distribution Plenum Cable Dry Water Block, Type OFNP, CSA FT6, Indoor/Outdoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021ANU.BK	2	—	0.17	4	11.7	17.4	300	1334	90	400
XX0061ANU.BK	6	—	0.20	5	16.0	23.8	320	1423	96	427
XX0121ANU.BK	12	—	0.23	6	22.7	33.8	400	1780	120	534
XX0241ANU.BK	24	—	0.32	8	45.0	67.0	320	1423	112	500

XX denotes glass type.  
NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.  
\* Not for aerial or direct burial applications.

# Loose Tube Single Jacket Plenum Cable Type OFNP, CSA FT6, Indoor/Outdoor\*




CATALOG NUMBER	FIBER COUNT	NO. OF LOOSE TUBES	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0064M1D-DT	6	1	0.31	8	48	71	300	1334	100	445
XX0124M1D-DT	12	2	0.31	8	47	69	300	1334	100	445
XX0244M1D-DT	24	4	0.31	8	44	65	300	1334	100	445

XX denotes glass type.  
NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.  
\* Not for aerial or direct burial applications.





# Loose Tube Single Jacket Cable Outdoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF LOOSE TUBES	NO. OF FILLERS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
				IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
								LBS	N	LBS	N
XX0124M1A-DWB	12	1	4	0.44	11.1	55	82	600	2700	180	800
XX0244M1A-DWB	24	2	3	0.44	11.1	55	82	600	2700	180	800
XX0484M1A-DWB	48	4	1	0.44	11.1	55	82	600	2700	180	800
XX0724M1A-DWB	72	6	0	0.47	12.0	66	98	600	2700	180	800

XX denotes glass type.

NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.

\* Not for aerial or direct burial applications.

# Loose Tube Dual Jacket Cable Outdoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF LOOSE TUBES	NO. OF FILLERS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
				IN	mm	LBS/1000'	kg/km	INSTALLATION		IN-SERVICE	
								LBS	N	LBS	N
XX0124H1A-DWB	12	1	4	0.51	13.0	78	116	600	2700	180	800
XX0244H1A-DWB	24	2	3	0.51	13.0	78	116	600	2700	180	800
XX0484H1A-DWB	48	4	1	0.51	13.0	78	116	600	2700	180	800
XX0724H1A-DWB	72	6	0	0.54	13.7	90	134	600	2700	180	800

XX denotes glass type.

NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.

# Industrial Communication Protocol Cables

No matter if your design is brand new or you are repairing an older design, General Cable has you covered with our comprehensive list of protocol cables. Be certain that cabling will not cause you downtime.

General Cable's list of protocol cables includes CC-Link®, ControlNet®, DataHighway®, DeviceNet®, Foundation Fieldbus, Interbus®-S, LonWorks®, Modbus, Profibus®, RS-485/HART/Can Open, Seriplex® and Smart Distribution System.



# Table of Contents

## PROTOCOL

	CATALOG NO.	DESCRIPTION	PAGE
<b>Coax &amp; Twinax</b>	GCR1309	RG-6 Quad Shield FR-PVC	32
	GCR1309A	RG-6 Quad Shield FR-PVC Aluminum Interlock Armor	32
	GCR1309CC	RG-6 Quad Shield FR-PVC With CCW® Armor	32
	GCR1309F	RG-6 Quad Shield FR-PVC Flexible	32
	GCR1309FC	RG-6 Quad Shield FR-PVC Flexible Tinned Copper	32
	GCR1309S	RG-6 Quad Shield FR-PVC Steel Interlock Armor	32
	GCR1309P	RG-6 Quad Shield FR-PVC Plenum	32
	GCR1300	18 AWG 2 Pair 600 V Twinax	33
	GCR1314	20 AWG 1 Pair Twinax	33
	GCR1314A	20 AWG 1 Pair Twinax Aluminum Interlock Armor	33
	GCR1314D	20 AWG 1 Pair Twinax Outdoor	33
	GCR1314F	20 AWG 1 Pair Twinax Flexible	33
	GCR1314P	20 AWG 1 Pair Twinax Plenum Outdoor	33
	GCR1314S	20 AWG 1 Pair Twinax Steel Interlock Armor	33
	GCR1314T	20 AWG 1 Pair Twinax Heavy-Duty	33
	GCR1314ZH	20 AWG 1 Pair Twinax Low-Smoke Zero-Halogen	33
	GCR1314CC	20 AWG 1 Pair Twinax With CCW® Armor	33
	GCR1324	20 AWG 2 Pair Twinax	33
	GCR1324A	20 AWG 2 Pair Twinax Armored	33
	<b>Multi-Paired Shielded</b>	GCR1302	18 AWG 1 Pair Foil PVC
GCR1303		22 AWG 1 Pair Foil PVC	34
GCR1304		22 AWG 1 Pair Foil + Braid PVC	34
GCR1304F		22 AWG 1 Pair Foil + Braid PVC Flexible	34
GCR1315		20 AWG 3 Cond Foil + Braid PVC	34
GCR1316		20 AWG 3 Cond Foil + Braid + 18 AWG 2 Cond	34
GCR1332		16 AWG 1 Pair Foil + 20 AWG 1 Pair PVC	34
GCR1334		22 AWG 1 Pair Foil + 22 AWG 1 Pair Foil PVC	34
9899.PB02201000		22 AWG 1 Pair CCW®	35
9899.FB01801120		18 AWG 1 Pair CCW®	35
9899.FB01802120		18 AWG 2 Pair CCW®	35
9899.FB01804120		18 AWG 4 Pair CCW®	35
9899.FB01601118		16 AWG 1 Pair CCW®	35
9899.FB01602118		16 AWG 2 Pair CCW®	35
9899.FB01604118		16 AWG 4 Pair CCW®	35
GCR1305		15 AWG 1 Pair Foil + 18 AWG 1 Pair Foil + Braid PVC	36
GCR1305F		15 AWG 1 Pair Foil + 18 AWG 1 Pair Foil + Braid PVC Flexible	36
GCR1306		15 AWG 1 Pair Foil + 18 AWG 1 Pair Foil + Braid CPE	36
GCR1307		22 AWG 1 Pair Foil + 24 AWG 1 Pair Foil PVC	36
GCR1307F		22 AWG 1 Pair Foil + 24 AWG 1 Pair Foil PVC Flexible	36
GCR1308		22 AWG 1 Pair Foil + 24 AWG 1 Pair Foil CPE	36
GCR1311		16 AWG 1 Pair Ind Foil + 18 AWG 1 Pair Foil + Braid PVC	36
GCR1312		15 AWG 1 Pair Foil + 18 AWG 1 Pair Foil + Braid PVC	36
GCR1313	18 AWG 1 Pair + 20 AWG 1 Pair PVC	36	

## PROTOCOL

	CATALOG NO.	DESCRIPTION	PAGE	
<b>Multi-Paired Shielded (Cont'd.)</b>	GCR1317	18 AWG 1 Pair Foil + 20 AWG 1 Pair Foil + Braid PVC	36	
	C9530ZH	20 AWG 2 Pair Foil + Braid LSZH	36	
	C8651	22 AWG 1 Pair Foil PVC	37	
	C8611	22 AWG 1 Pair Foil FEP	37	
	GCR1330	22 AWG 1 Pair + 18 AWG 1 Pair Foil PVC	37	
	GCR1330A	22 AWG 1 Pair + 18 AWG 1 Pair Foil PVC Armored	37	
	GCR1331	22 AWG 1 Pair + 16 AWG 1 Pair Foil PVC	37	
	GCR1331A	22 AWG 1 Pair + 16 AWG 1 Pair Foil PVC Armored	37	
	GCR1333	22 AWG 1 Pair + 16 AWG 1 Pair + 12 AWG 1 Pair Foil PVC	37	
	GCR1333A	22 AWG 1 Pair + 16 AWG 1 Pair + 12 AWG 1 Pair Foil PVC Armored	37	
	GCR1318	24 AWG 3 Pair + 18 AWG 3 Cond Foil Braid	37	
	GCR1319	24 AWG 3 Pair Foil TPU	37	
	GCR1310	22 AWG 1 Pair + 1 Cond Foil + Braid	38	
	GCR1320	22 AWG 3 Pair Individually Foil Shielded	38	
	GCR1320A	22 AWG 3 Pair Individually Foil Shielded Armored	38	
	GCR1320S	22 AWG 3 Pair Individually Foil Shielded Steel Armored	38	
	GCR1320P	22 AWG 3 Pair Individually Foil Shielded Low-Smoke PVC	38	
	GCR1320FP	22 AWG 3 Pair Individually Foil Shielded FEP	38	
	C7112A	22 AWG 1 Pair Copper Braid	39	
	C7112AF	22 AWG 1 Pair Copper Braid Flex	39	
	C7114A	22 AWG 2 Pair Copper Braid	39	
	C7114AF	22 AWG 2 Pair Copper Braid Flex	39	
	C7116A	22 AWG 3 Pair Copper Braid	39	
	C7116AF	22 AWG 3 Pair Copper Braid Flex	39	
	C7118A	22 AWG 4 Pair Copper Braid	39	
	C7118AF	22 AWG 4 Pair Copper Braid Flex	39	
	C4841A	24 AWG 1 Pair Foil + Braid	39	
	C4842A	24 AWG 2 Pair Foil + Braid	39	
	C4843A	24 AWG 3 Pair Foil + Braid	39	
	C4844A	24 AWG 4 Pair Foil + Braid	39	
	C4851A	24 AWG 1 Pair Foil + Braid Plenum	40	
	C4852A	24 AWG 2 Pair Foil + Braid Plenum	40	
	GCR1301	18 AWG 2 Pair Foil + Copper Braid PVC	40	
	C2534A	18 AWG 1 Pair Foil PVC	40	
	C8123	18 AWG 1 Pair Foil Low-Smoke PVC	40	
	C8101	18 AWG 1 Pair Foil FEP	40	
	<b>Multi-Paired Unshielded</b>	C8661	16 AWG 1 Pair Unshielded	41
		C8621	16 AWG 1 Pair Unshielded Plenum	41
		C8641	22 AWG 1 Pair Unshielded	41
		C8601	22 AWG 1 Pair Plenum	41

# Coax



**Product Construction:**

**Conductors:**

- Copper per ASTM B3
- Copper-clad steel per ASTM B869

**Insulation:**

- Gas Injected Foam Polyethylene or Gas Injected Foam FEP

**Shield:**

- Aluminum quad shield or tin copper quad shield

**Applications:**

- ODVA ControlNet™
- Industrial type applications
- Interlocked armored (steel or aluminum)
- Continuous Corrugated Welded Aluminum Armor (CCW) for harsh environments

**Compliances:**

- CL2R, CMR, CMG and CATVR
- CL2P, CMP and CATVP
- RoHS/CE
- UL or ETL
- FT4 or FT6

**Packaging:**


- 1000' reels
- Multiple colors available

CATALOG NUMBER NEC-TYPE	AWG TYPE DCR (Nom.)	INSULATION TYPE	INSULATION NOMINAL O.D.		SHIELD TYPE DCR (Nom.)	JACKET TYPE	COAX NOMINAL O.D.		OVERALL ARMOR TYPE	NOM. CAP. pF/FT	VELOCITY OF PROPAGATION (NOM.)	NOM. IMP. OHMS	NOMINAL ATTENUATION	
			INCHES	mm			INCHES	mm					MHz	dB/100'
<b>GCR1309</b> RG 6/U Type NEC-CL2R, CMR, CATVR & CMG/FT4 -20C to +80C	18 Solid CCS (28.9 Ohm)	Foam Polyethylene	0.180	4.57	Quad Shield 100% Foil Bonded, 60% AL-Braid, 100% Foil, 40% AL-Braid (5.2 Ohm)	PVC	0.298	7.57	N/A	16.20	83%	75	1 10 100 200 500 1000 3000	0.35 0.59 1.97 2.82 4.58 6.59 12.65
<b>GCR1309A</b> RG 6/U Type NEC-CL2R, CMR, CATVR & CMG/FT4 -20C to +80C	18 Solid CCS (28.9 Ohm)	Foam Polyethylene	0.180	4.57	Quad Shield 100% Foil Bonded, 60% AL-Braid, 100% Foil, 40% AL-Braid (5.2 Ohm)	PVC	0.590	14.99	Aluminum Interlock Armor/PVC	16.20	83%	75	1 10 100 200 500 1000 3000	0.35 0.59 1.97 2.82 4.58 6.59 12.65
<b>GCR1309CC</b> RG 6/U Type NEC-CL2R, CMR, CATVR & CMG/FT4 -20C to +80C	18 Solid CCS (28.9 Ohm)	Foam Polyethylene	0.180	4.57	Quad Shield 100% Foil Bonded, 60% AL-Braid, 100% Foil, 40% AL-Braid (5.2 Ohm)	PVC	0.560	14.22	Aluminum CCW® Armor/PVC	16.20	83%	75	1 10 100 200 500 1000 3000	0.35 0.59 1.97 2.82 4.58 6.59 12.65
<b>GCR1309F</b> RG 6/U Type NEC-CL2R, CMR, CATVR & CMG/FT4 -20C to +80C	20 105/40 BC (10.5 Ohm)	Foam Polyethylene	0.183	4.64	Quad Shield 100% Foil Bonded 60% AL-Braid, 100% Foil, 40% AL-Braid (5.2 Ohm)	PVC	0.300	7.62	N/A	16.20	83%	75	1 10 100 200 500 1000 3000	0.25 0.81 2.64 3.83 6.30 9.32 17.90
<b>GCR1309FC</b> RG 6/U Type NEC-CL2R, CMR, CATVR & CMG/FT4 -20C to +80C	20 105/40 BC (10.5 Ohm)	Foam Polyethylene	0.183	4.64	Quad Shield 100% Foil Bonded, 60% TC-Braid, 100% Foil, 40% TC-Braid (2.9 Ohm)	PVC	0.295	7.49	N/A	16.20	83%	75	1 10 100 200 500 1000 3000	0.25 0.81 2.64 3.83 6.30 9.32 17.90
<b>GCR1309S</b> RG 6/U Type NEC-CL2R, CMR, CATVR & CMG/FT4 -20C to +80C	18 Solid CCS (28.9 Ohm)	Foam Polyethylene	0.180	4.57	Quad Shield 100% Foil Bonded, 60% AL-Braid, 100% Foil, 40% AL-Braid (5.2 Ohm)	PVC	0.590	14.99	Galvanized Steel Interlock Armor/PVC	16.20	83%	75	1 10 100 200 500 1000 3000	0.35 0.59 1.97 2.82 4.58 6.59 12.65
<b>GCR1309P</b> RG 6/U Type NEC-CL2P, CMP, CATVP/FT6 -40C to +150C	18 Solid CCS (28.9 Ohm)	Foam FEP	0.170	4.32	Quad Shield 100% Foil Bonded, 60% AL-Braid, 100% Foil, 40% AL-Braid (5.2 Ohm)	PVDF	0.274	6.96	N/A	16.20	83%	75	1 10 100 200 500 1000 3000	0.36 0.66 2.10 3.10 5.00 7.30 14.28





# Twinax



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper per ASTM B33

**Insulation:**

- Premium grade Polyethylene
- Premium grade LSZH
- Premium grade FEP (GCR1314P)
- Premium grade Polyolefin (GCR1300)

**Jacket:**

- PVC
- FEP (GCR1314P)
- LSZH-Polyolefin (GCR1314ZH)
- Polyethylene (GCR1314D)

**Shield:**

- Overall foil shield and tinned copper braid

**Applications:**

- Data Highway and Data Highway Plus (DH+) applications
- Interlocked armored (steel or aluminum)
- Continuous Corrugated Welded Aluminum Armor (CCW) for harsh and HL environments

**Compliances:**

- UL, c(UL)
- See below for individual product compliances

CATALOG NUMBER	NO. OF COND.	AWG TYPE DCR (NOM) PER/MFT	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE DCR (NOM.)	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		OVERALL ARMOR TYPE	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	COND. COLOR CODE
			INCHES	mm				INCHES	mm	INCHES	mm					
GCR1300	2	18 7/26 TC (6.9 Ohm)	0.108	2.74	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.2 Ohm)	PVC	0.048	1.22	0.336	8.53	N/A	19.50	78.00	TC, PLTC, ITC, CMG FT4 -40C to +80C	Blue, White
GCR1314	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.9 Ohm)	PVC	0.035	0.89	0.242	6.15	N/A	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1314A	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.9 Ohm)	PVC	0.035	0.89	0.558	14.17	Aluminum Interlock Armor/PVC	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1314D (Gel Water Block)	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.9 Ohm)	Polyethylene	0.035	0.89	0.242	6.15	N/A	19.70	78.00	-60C to +80C	Blue, Natural
GCR1314F	2	20 41/30 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 85% Tinned Copper Braid (3.0 Ohm)	PVC	0.035	0.89	0.242	6.15	N/A	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1314P	2	20 7/28 TC (9.5 Ohm)	0.072	1.83	FEP	100% Flex Foil + 76% Tinned Copper Braid (3.6 Ohm)	FEP	0.016	0.41	0.203	5.16	N/A	19.70	78.00	CL2P, CMP -70C to +200C	Blue, Natural
GCR1314S	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.9 Ohm)	PVC	0.035	0.89	0.558	14.17	Galvanized Steel Interlock Armor/PVC	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1314T	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.9 Ohm)	PVC	0.100	2.54	0.380	9.65	N/A	19.70	78.00	PLTC-ER, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1314ZH	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	LSZH	100% Flex Foil + 85% Tinned Copper Braid (3.0 Ohm)	LSZH	0.035	0.89	0.242	6.15	N/A	19.70	78.00	CL2, CM -20C to +80C	Blue, Natural
GCR1314CC	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 60% Tinned Copper Braid (3.9 Ohm)	PVC	0.035	0.89	0.510	12.95	Aluminum (CCW <sup>®</sup> ) Armor/PVC	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1324	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 85% Tinned Copper Braid (3.9 Ohm)	PVC	0.060	1.52	0.385	9.78	N/A	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural
GCR1324A	2	20 7/28 TC (9.5 Ohm)	0.078	1.98	Polyethylene	100% Flex Foil + 85% Tinned Copper Braid (3.9 Ohm)	PVC	0.065	1.65	0.750	19.05	Aluminum Armor/PVC	19.70	78.00	CL2, CM, AWM 2464 -20C to +80C	Blue, Natural



# Multi-Paired, Shielded



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper per ASTM B33
- Fully annealed solid bare copper per ASTM B3

**Insulation:**

- Polyolefin and Foam Injected Polyolefin
- Foam HDPE
- PVC

**Jacket:**

- PVC
- Fluoropolymer

**Shield:**

- Flex Foil
- Tinned copper braid

**Applications:**

- High speed Profibus DP communication for use in factory automation systems
- CC-Link applications
- SDS applications
- Interlocked armored (steel or aluminum)
- Industrial type applications
- Recognized for use in Class I and III, Divisions 1 and 2; Class II, Division 2; or Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505 (9899.PB02201000 only)
- Recognized for use in Class I, II and III, Divisions 1 and 2; or Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505 (9899.FB01801120, 9899.FB01802120, 9899.FB01804120, 9899.FB01601118, 9899.FB01602118, 9899.FB01604118 only)

**Compliances:**

- UL, c(UL)
- See below for individual product compliances

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
GCR1302	1	18	7/26 TC	0.106	2.69	FR-Polyolefin	100% Flex Foil	PVC	0.038	0.97	0.290	7.37	65%	24.0	100.0	PLTC-ER, ITC, CM, CMG c(UL) FT4 -40C to +75C/300 V	Blue, Orange
GCR1303	1	22	7/30 TC	0.060	1.52	Polyolefin	100% Flex Foil	PVC	0.035	0.89	0.196	4.98	66%	22.0	100.0	CM, c(UL) -20C to +75C/300 V	Blue, Orange
GCR1304	1	22	Solid	0.103	2.62	Foam-Polyolefin	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.038	0.97	0.315	8.00	78%	8.5	150.0	PLTC, CM, CMG c(UL), FT4, AWM 20201 -20C to +75C/600 V	Red, Green
GCR1304F	1	22	19/34 TC	0.110	2.79	Foam-Polyolefin	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.038	0.97	0.321	8.15	78%	8.5	150.0	PLTC, CM, CMG c(UL), FT4, AWM 20201 -20C to +75C / 600V	Red, Green
GCR1315	3	20	7/28 TC	0.096	2.44	Foam-HDPE	100% Flex Foil + 78% Tinned Copper Braid	PVC	0.035	0.89	0.300	7.62	78%	12.5	110.0	CM, c(UL) -20C to +75C	Blue, Yellow, White
GCR1316	2	18 (Power)	7/26 TC	0.078	1.98	PVC	N/A	PVC	0.053	1.35	0.512	13.00	53%	N/A	N/A	PLTC, CM, c(UL) -20C to +75C	Black, White
	3	20 (Signal)	7/28 TC	0.096	2.44	Foam-HDPE	100% Flex Foil + 78% Tinned Copper Braid						78%	12.5	110.0		
GCR1332	2	16 (Power)	19/0117 TC	0.120	3.05	PVC	100% Foil, over each pair	PVC	0.042	1.07	0.398	10.11	53%	N/A	N/A	CL2, CM, c(UL), AWM 2464 -20C to +80C/300 V	Black, Brown
		20 (Data)	19/32 TC	0.126	3.20	Foam-Polyolefin							78%	12.0	120.0		
GCR1334	2	22 (Power)	19/34 TC	0.063	1.60	PVC	100% Foil, over each pair	PVC	0.035	0.89	0.290	7.37	53%	N/A	N/A	CL2, CM, c(UL), AWM 2464 -20C to +80C / 300V	Brown, Blue
		22 (Data)	19/34 TC	0.101	2.57	Foam-Polyolefin							78%	12.0	120.0		



# Multi-Paired, Shielded



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper per ASTM B33
- Fully annealed solid bare copper per ASTM B3

**Insulation:**

- Polyolefin and Foam Injected Polyolefin
- Foam HDPE
- PVC

**Jacket:**

- PVC
- Fluoropolymer

**Shield:**

- Flex Foil
- Tinned copper braid

**Applications:**

- High speed Profibus DP communication for use in factory automation systems
- CC-Link applications
- SDS applications
- Interlocked armored (steel or aluminum)
- Industrial type applications
- Recognized for use in Class I and III, Divisions 1 and 2; Class II, Division 2; or Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505 (9899.PB02201000 only)
- Recognized for use in Class I, II and III, Divisions 1 and 2; or Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505 (9899.FB01801120, 9899.FB01802120, 9899.FB01804120, 9899.FB01601118, 9899.FB01602118, 9899.FB01604118 only)


**Compliances:**

- UL, c(UL)
- See below for individual product compliances

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
9899.PB02201000	1	22	Solid	0.106	2.69	Fluoropolymer	65% Tinned Copper Braid	Inner: Fluoropolymer Outer: PVC	0.038	0.97	0.940	23.88	78%	8.5	100.0	ITC-HL, 300 V, CT Use, CSA FT4, IEEE 1202	Red, Green
9899.FB01801120	1	18	7/26 TC	0.106	2.69	XLPE	100% Foil, over ea. pair	Inner: PVC Outer: PVC	0.040	1.01	0.640	16.13	TBD	TBD	100.0	MC-HL, 600 V, SUN RES, DIR BUR, -40°C	Blue, Orange
9899.FB01802120	2	18	7/26 TC	0.480	12.07	XLPE	100% Overall Shield	Inner: PVC Outer: PVC	Inner: .040 Outer: .050	Inner: 1.01 Outer: 1.27	0.900	22.73	TBD	TBD	100.0	MC-HL, 600 V, SUN RES, DIR BUR, -40°C	Blue, Orange
9899.FB01804120	4	18	7/26 TC	0.570	14.48	XLPE	100% Overall Shield	Inner: PVC Outer: PVC	Inner: .040 Outer: .050	Inner: 1.01 Outer: 1.27	0.990	25.02	TBD	TBD	100.0	MC-HL, 600 V, SUN RES, DIR BUR, -40°C	Blue, Orange
9899.FB01601118	1	16	7/26 TC	0.290	7.37	XLPE	100% Overall Shield	Inner: PVC Outer: PVC	Inner: .040 Outer: .050	Inner: 1.01 Outer: 1.27	0.660	16.76	TBD	TBD	100.0	MC-HL, 600 V, SUN RES, DIR BUR, -40°C	Blue, Orange
9899.FB01602118	2	16	7/26 TC	0.520	13.21	XLPE	100% Overall Shield	Inner: PVC Outer: PVC	Inner: .040 Outer: .050	Inner: 1.01 Outer: 1.27	0.940	23.88	TBD	TBD	100.0	MC-HL, 600 V, SUN RES, DIR BUR, -40°C	Blue, Orange
9899.FB01604118	4	16	7/26 TC	0.620	15.75	XLPE	100% Overall Shield	Inner: PVC Outer: PVC	Inner: .040 Outer: .050	Inner: 1.01 Outer: 1.27	1.080	27.31	TBD	TBD	100.0	MC-HL, 600 V, SUN RES, DIR BUR, -40°C	Blue, Orange



# Multi-Paired, Shielded



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper per ASTM B33

**Insulation**

- Polyolefin and Foam Injected Polyolefin
- PVC/Nylon
- PVC

**Jacket**

- PVC
- CPE (GCR1308)
- LSZH (C9530ZH)

**Shield**

- Flex Foil
- Tinned copper braid

**Applications:**

- ODVA DeviceNet™ applications
- Industrial type applications
- CPE jacket for harsh industrial environments


**Compliances:**

- UL, c(UL)
- See below for individual product compliances

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
GCR1305	2	15 (Power)	19/28 TC	0.107	2.72	PVC	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.060	1.52	0.475	12.07	53%	N/A	N/A	PLTC, CL2, CM C(UL), AWM 20201 -20C to +75C/600 V	Black, Red
		18 (Data)	19/30 TC	0.155	3.94	Foam-Polyolefin											White, Lt. Blue
GCR1305F	2	15 (Power)	65/33 TC	0.110	2.79	PVC	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.060	1.52	0.480	12.19	53%	N/A	N/A	PLTC, CL2, CM C(UL), AWM 20201 -20C to +75C/600 V	Black, Red
		18 (Data)	65/36 TC	0.156	3.96	Foam-Polyolefin											White, Lt. Blue
GCR1306	2	15 (Power)	19/28 TC	0.107	2.72	PVC	100% Flex Foil each pair, o/a 65% TC Braid	CPE	0.060	1.52	0.475	12.07	53%	N/A	N/A	PLTC, CL2, CM CMG C(UL) -40C to +75C/300 V	Black, Red
		18 (Data)	19/30 TC	0.155	3.94	Foam-Polyolefin											White, Lt. Blue
GCR1307	2	22 (Power)	19/34 TC	0.061	1.55	PVC	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.035	0.89	0.280	7.11	53%	N/A	N/A	PLTC, CL2, CM C(UL), AWM 20201 -20C to +75C/600 V	Black, Red
		24 (Data)	19/36 TC	0.077	1.96	Foam-Polyolefin											White, Lt. Blue
GCR1307F	2	22 (Power)	41/38 TC	0.060	1.52	PVC	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.035	0.89	0.280	7.11	53%	N/A	N/A	PLTC, CL2, CM C(UL), AWM 20201 -20C to +75C/600 V	Black, Red
		24 (Data)	41/40 TC	0.077	1.96	Foam-Polyolefin											White, Lt. Blue
GCR1308	2	22 (Power)	19/34 TC	0.061	1.55	PVC	100% Flex Foil each pair, o/a 65% TC Braid	CPE	0.040	1.02	0.285	7.24	53%	N/A	N/A	CL2, CM CMG C(UL) -40C to +75C/300 V	Black, Red
		24 (Data)	19/36 TC	0.077	1.96	Foam-Polyolefin											White, Lt. Blue
GCR1311	2	16 (Power)	19/29 TC	0.098	2.49	PVC/Nylon	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.065	1.65	0.525	13.34	55%	N/A	N/A	TC-ER -40C to +75C/600 V	Black, Red
		18 (Data)	19/30 TC	0.178	4.52	Foam FR-Polyolefin											White, Lt. Blue
GCR1312	2	15 (Power)	19/28 TC	0.105	2.67	PVC/Nylon	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.060	1.52	0.460	11.68	55%	N/A	N/A	TC-ER -40C to +75C/600 V	Black, Red
		18 (Data)	19/30 TC	0.139	3.53	Foam-FEP											White, Lt. Blue
GCR1313	2	16 (Power)	19/29 TC	0.098	2.49	PVC/Nylon	Unshielded	PVC	0.060	1.52	0.430	10.92	55%	N/A	N/A	TC-ER, CSA AWM VII A/B FT1 -40C to +75C/600 V	Black, Red
		18 (Data)	19/30 TC	0.139	3.53	FR-Polyolefin											White, Lt. Blue
GCR1317	2	18 (Power)	19/30 TC	0.081	2.06	PVC	100% Flex Foil each pair, o/a 65% TC Braid	PVC	0.052	1.32	0.385	9.78	55%	N/A	N/A	PLTC, CL2, CMG C(UL) FT4, AWM 20201 -20C to +75C/600 V	Black, Red
		20 (Data)	19/32 TC	0.126	3.20	Foam-Polyolefin											White, Lt. Blue
C9530ZH	2	20 AWG	7/28 TC	0.070	1.78	LSZH	100% Flex Foil + 85% TC Braid	LSZH	0.042	1.07	0.35	8.89	66%	22.0	70.0	UL-CL3, PLTC-ER, CM C(UL) -40C to +105C	Black, Red Black, White



# Multi-Paired, Shielded



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper per ASTM B33

**Insulation:**

- Foam HDPE
- PVC
- HD - Polyethylene (GCR1319)
- SR-PVC (GCR1318)

**Jacket:**

- PVC

**Shield:**

- Overall Flexfoil shield
- Tinned copper braid (GCR1318 & GCR1319)

**Applications:**

- Seriplex applications
- Interbus-S applications
- Interlocked armored (steel or aluminum)
- Industrial type applications

**Compliances:**


- UL, c(UL)
- See below for individual product compliances

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		OVERALL ARMOR TYPE	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
C8651	1	22	7/.0096 BC	0.059	1.49	Foam-HDPE	100% Flex Foil over all	PVC	0.030	0.76	0.195	4.95	N/A	14.5	100.0	CM, CSA, c(UL), NEC -20C to +75C	White/Blue, Blue
C8611	1	22	7/.0096 BC	0.059	1.49	Foam-FEP	100% Flex Foil over all	Flexguard	0.015	0.38	0.160	4.06	N/A	14.5	100.0	CMP, CSA, c(UL) -10C to +75C	White/Blue, Blue
GCR1330	2	18 (Power)	16/30 TC	0.096	2.44	Foam-HDPE	100% Flex Foil over all	PVC	0.035	0.89	0.308	7.82	N/A	11.5	120.0	CM, CL2, AWM 20201 -20C to +75C/600 V	Black, Red
		22 (Data)	7/30 TC	0.096	2.44	Foam-HDPE								9.0	150.0		Green, White
GCR1330A	2	18 (Power)	16/30 TC	0.096	2.44	Foam-HDPE	100% Flex Foil over all	PVC	0.035	0.89	0.600	15.24	Aluminum Interlock Armor/ PVC	11.5	120.0	CM, CL2, AWM 20201 -20C to +75C/600 V	Black, Red
		22 (Data)	7/30 TC	0.096	2.44	Foam-HDPE								9.0	150.0		Green, White
GCR1331	2	16 (Power)	26/30 TC	0.110	2.79	Foam-HDPE	100% Flex Foil over all	PVC	0.045	1.14	0.360	9.14	N/A	16.0	120.0	CM, CL2, AWM 20201 -20C to +75C/600 V	Black, Red
		22 (Data)	7/30 TC	0.110	2.79	Foam-HDPE								9.0	150.0		Green, White
GCR1331A	2	16 (Power)	26/30 TC	0.110	2.79	Foam-HDPE	100% Flex Foil over all	PVC	0.045	1.14	0.690	17.53	Aluminum Interlock Armor/ PVC	16.0	120.0	CM, CL2, AWM 20201 -20C to +75C/600 V	Black, Red
		22 (Data)	7/30 TC	0.110	2.79	Foam-HDPE								9.0	150.0		Green, White
GCR1333	3	16 (Control)	26/30 TC	0.105	2.67	Foam-HDPE	100% Flex Foil over all	PVC	0.040	1.02	0.434	11.02	N/A	28.0	N/A	CL2, AWM 20201 -20C to +75C/600 V	White/Orange, White/Blue
		22 (Data)	7/30 TC	0.110	2.79	Foam-HDPE								16.0	N/A		Green, White
		12 (Power)	65/30 TC	0.122	3.10	PVC								N/A	N/A		Black, Red
GCR1333A	3	16 (Control)	26/30 TC	0.105	2.67	Foam-HDPE	100% Flex Foil over all	PVC	0.040	1.02	0.770	19.56	Aluminum Interlock Armor/ PVC	28.0	N/A	CL2, AWM 20201 -20C to +75C/600 V	White/Orange, White/Blue
		22 (Data)	7/30 TC	0.110	2.79	Foam-HDPE								16.0	N/A		Green, White
		12 (Power)	65/30 TC	0.122	3.10	PVC								N/A	N/A		Black, Red
GCR1318	3/C 18	18 (Power)	7/26 TC	0.068	1.73	SR-PVC	100% Flex Foil + 90% Tinned Copper Braid	TPU Polyurethane	0.035	0.89	0.333	8.46	53%	N/A	N/A	AWM 20233 -40C to +80C/300 V	Blue, Red, Green/Yellow
	3/P 24	24 (Data)	7/32 TC	0.048	1.22	HD-Polyethylene											66%
GCR1319	3	24	7/32 TC	0.048	1.22	HD-Polyethylene	100% Flex Foil + 90% Tinned Copper Braid	TPU Polyurethane	0.035	0.89	0.275	6.99	66%	15.4	100.0	AWM 20233 -40C to +80C/300 V	White, Brown Pink, Gray Yellow, Green





# Multi-Paired, Shielded/Individually Shielded



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper per ASTM B33

**Insulation:**

- Foam-Polyethylene
- Polypropylene
- FEP
- Foam - HDPE
- Polyolefin (GCR1301)

**Jacket:**

- PVC
- Flexguard
- FEP (C8101)

**Shield:**

- Flexfoil with tinned copper braid
- Flexfoil

**Applications:**

- Modbus applications
- HART® applications
- RS-485 applications
- Interlocked armored (steel or aluminum)
- Industrial type applications

**Compliances:**

- UL, c(UL)
- See below for individual product compliances

**INDIVIDUALLY FOIL SHIELDED**

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		OVERALL ARMOR TYPE	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
GCR1310	1.5	22	7/30 TC	0.090	2.29	Foam-Polyethylene/PVC	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.285	7.24	N/A	11.0	120.0	PLTC, CM CMG C(UL), FT4 -20C to +75C/300 V	1/P: White/Orange Orange/White 1/C: Blue/White
GCR1320	3	22	7/30 TC	0.052	1.32	Polypropylene	100% Flex Foil over each pair	PVC	0.035	0.89	0.280	7.11	N/A	30.0	50.0	CM, AWM 2919 -20C to +80C/300 V	Black, Red Black, White Black, Green
GCR1320A	3	22	7/30 TC	0.052	1.32	Polypropylene	100% Flex Foil over each pair	PVC	0.035	0.89	0.590	14.99	Aluminum Interlock Armor/PVC	30.0	50.0	CM, AWM 2919 -20C to +80C/300 V	Black, Red Black, White Black, Green
GCR1320S	3	22	7/30 TC	0.052	1.32	Polypropylene	100% Flex Foil over each pair	PVC	0.035	0.89	0.590	14.99	Galvanized Steel Interlock Armor/PVC	30.0	50.0	CM, AWM 2919 -20C to +80C/300 V	Black, Red Black, White Black, Green
GCR1320P	3	22	7/30 TC	0.050	1.27	FEP	100% Flex Foil over each pair	Flex-Guard	0.015	0.38	0.234	5.94	N/A	30.0	50.0	CMP c(UL) -10C to +75C/300 V	Black, Red Black, White Black, Green
GCR1320FP	3	22	7/30 TC	0.050	1.27	FEP	100% Flex Foil over each pair	FEP	0.015	0.38	0.230	5.84	N/A	30.0	50.0	CMP c(UL) -70C to +200C/300 V	Black, Red Black, White Black, Green

# Multi-Paired, Shielded/Individually Shielded

## OVERALL FOIL AND BRAID SHIELD

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
C7112A	1	22	7/30 TC	0.078	1.98	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.038	0.97	0.255	6.48	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White
C7112AF	1	22	26/36 TC	0.078	1.98	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.038	0.97	0.255	6.48	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White
C7114A	2	22	7/30 TC	0.066	1.68	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.330	8.38	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White
C7114AF	2	22	26/36 TC	0.066	1.68	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.330	8.38	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White
C7116A	3	22	7/30 TC	0.062	1.57	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.335	8.51	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White, White/Green, Green/White
C7116AF	3	22	26/36 TC	0.062	1.57	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.335	8.51	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White, White/Green, Green/White
C7118A	4	22	7/30 TC	0.062	1.57	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.365	9.27	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White, White/Green, Green/White, White/Brown, Brown/White
C7118AF	4	22	26/36 TC	0.062	1.57	Foam-HDPE	100% Flex Foil + 65% Tinned Copper Braid	PVC	0.045	1.14	0.365	9.27	76%	11.0	120.0	PLTC, CM c(UL) -20C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White, White/Green, Green/White, White/Brown, Brown/White
C4841A	1	24	7/30 TC	0.072	1.83	Polyethylene	100% Flex Foil + 90% Tinned Copper Braid	PVC	0.035	0.89	0.235	5.97	76%	14.6	120.0	CM, CMH c(UL), AWM 2919 -20C to +80C/300 V	White/Blue, Blue/White
C4842A	2	24	7/32 TC	0.072	1.83	Polyethylene	100% Flex Foil + 90% Tinned Copper Braid	PVC	0.035	0.89	0.304	7.72	76%	11.7	120.0	CM, CMH c(UL), AWM 2919 -20C to +80C/300 V	White/Blue, Blue/White, White/Orange, Orange/White
C4843A	3	24	7/32 TC	0.072	1.83	Polyethylene	100% Flex Foil + 90% Tinned Copper Braid	PVC	0.035	0.89	0.360	9.14	76%	11.9	120.0	CM, CMH c(UL), AWM 2919 -20C to +80C/300 V	White/Blue, Blue/White, White/Orange, Orange/White, White/Green, Green/White
C4844A	4	24	7/32 TC	0.072	1.83	Polyethylene	100% Flex Foil + 90% Tinned Copper Braid	PVC	0.035	0.89	0.390	9.91	76%	11.9	120.0	CM, CMH c(UL), AWM 2919 -20C to +80C/300 V	White/Blue, Blue/White, White/Orange, Orange/White, White/Green, Green/White, White/Brown, Brown/White



# Multi-Paired, Shielded/Individually Shielded

### OVERALL FOIL AND BRAID SHIELD (CONT'D.)


CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
C4851A	1	24	7/32 TC	0.076	1.93	Foam-FEP	100% Flex Foil + 90% Tinned Copper Braid	Flex-guard	0.015	0.38	0.210	5.33	78%	12.0	120.0	CMP c(UL) -10C to +75C/300 V	White/Blue, Blue/White
C4852A	2	24	7/32 TC	0.062	1.57	Foam-FEP	100% Flex Foil + 90% Tinned Copper Braid	Flex-guard	0.015	0.38	0.263	6.68	78%	12.0	120.0	CMP c(UL) -10C to +75C/300 V	White/Blue, Blue/White, White/Orange, Orange/White
GCR1301	2	18	7/26 TC	0.164	4.17	Polyolefin	100% Flex Foil + 60% Tinned Copper Braid (3.2 Ohm)	PVC	0.055	1.40	0.460	11.68	N/A	12.0	124.0	TC, PLTC, ITC, CMG, FT4 -40C to +80C	Blue, White

### OVERALL FOIL SHIELD

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	SHIELD TYPE	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm				INCHES	mm	INCHES	mm					
C2534A	1	18	16/30 TC	0.078	1.98	Polyethylene	100% Flex Foil	PVC	0.020	0.51	0.205	5.21	66%	25.5	60.0	CM, CMH c(UL), AWM 2092 -20C to +80C/300 V	Black, Natural
C8123	1	18	19/30 TC	0.064	1.63	FEP	100% Flex Foil	Flex-guard	0.015	0.38	0.160	4.06	69%	40.0	38.0	CMP c(UL) -10C to +75C/300 V	Black, Red
C8101	1	18	19/30 TC	0.064	1.63	FEP	100% Flex Foil	FEP	0.015	0.38	0.160	4.06	69%	40.0	38.0	CMP c(UL) -70C to +200C/300 V	Black, Red



# Multi-Paired, Unshielded



**Product Construction:**

**Conductor:**

- Fully annealed stranded tinned copper or bare copper per ASTM B33

**Insulation:**

- PVC
- HDPE
- Flexguard

**Jacket:**

- PVC
- Flexguard

**Applications:**

- LonWorks applications
- Industrial type applications

**Compliances:**

- UL, c(UL)
- See below for individual product compliances

CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND	INSULATION NOMINAL O.D.		INSULATION MATERIAL	JACKET TYPE	NOM. JACKET THICKNESS		CABLE NOMINAL O.D.		VEL. OF PROP.	NOM. CAP. pF/FT	NOM. IMP. OHMS	NEC UL C(UL)US TYPE	PAIRS COLOR CODE
				INCHES	mm			INCHES	mm	INCHES	mm					
C8661	1	16	19/.0117 TC	0.088	2.23	PVC	PVC	0.032	0.81	0.246	6.24	69%	30.0	65.0	CM, CL2, CSA FT4 (-20C to +75C)	Black, White
C8621	1	16	19/.0117 TC	0.088	2.23	Flexguard	Flexguard	0.015	0.38	0.182	4.57	69%	35.0	55.0	CL2P, CMP, CSA FT6 (-10C to +75C)	Black, White
C8641	1	22	7/.0096 BC	0.049	1.24	HDPE	PVC	0.022	0.56	0.145	3.68	69%	17.0	100.0	CM, CSA FT4 (-20C to +75C)	White/Blue, Blue
C8601	1	22	7/.0096 BC	0.049	1.24	Flexguard	Flexguard	0.015	0.38	0.130	3.30	69%	17.0	100.0	CMP, CSA FT6 (-10C to +75C)	White/Blue, Blue



# Portable & Temporary Power Cord

General Cable's Carol® Brand is the most recognized name in flexible cords for temporary power. The extensive line includes portable cord, portable power cable and premium-grade cable for commercial and industrial applications.



## Rubber Cord

Thermoset rubber cord products have evolved over the last 50 years from simple and unsophisticated to a product line where specialized, technologically advanced products are in demand for exacting commercial and industrial applications.

No longer are rubber cord products used only in applications where flexibility is needed. Today, typical applications require cord to perform well in environments of extreme heat and cold as well as on job sites and factory floors where resistance to oil, chemicals and abrasion is required.

General Cable's role as the producer of premier Carol Brand rubber cord products is to ensure that new product development, product innovation and quality not only keep pace with industry requirements but also set the trends.

Our rubber cord products carry a full range of listings and certifications with Underwriters Laboratories, Inc. and the Canadian Standard Association. In addition, many products meet or exceed the requirements of OSHA, MSHA and other relevant industry standards.

## Table of Contents

	DESCRIPTION	PAGE
<b>Super Vu-Tron®</b>	Super Vu-Tron Type S0	62
	Super Vu-Tron Multi-Conductor Type S00W	63-64
	Super Vu-Tron Single Conductor	65
	Super Vu-Tron Multi-Conductor Type W Round	66
	Super Vu-Tron Type G and Type G-GC Round	67
	Super Vu-Tron Canadian Type G-GC Round	68
	Super Vu-Tron III Types SJ00W/S00W	69
	Super Vu-Tron Supreme Types SJ00W/S00W	70
<b>Super Vu-Tron with GenClean™</b>	Super Vu-Tron Supreme Types SJ00W/S00W with GenClean	71

# Super Vu-Tron® Type SO

90°C, 600 Volt



**Product Construction:**

**Conductors:**

- 18 through 10 AWG stranded bare copper

**Insulation:**

- Premium-grade 90°C EPDM

**Jacket:**

- Super Vu-Tron®, black
- Temperature range: -40°C to +90°C

**Jacket Marking:**

- (SIZE) TYPE SO 600 VOLT CAROL SUPER VU-TRON® 90°C P-123-MSHA<sup>(1)</sup> (TRU-MARK SEQUENTIAL FOOTAGE)

**Applications:**

- Portable tools and equipment
- Portable appliances
- Small motors and associated machinery
- Flexible power leads

**Features:**

- Excellent resistance to oil and moisture
- Good tensile strength, elongation and aging characteristics
- High flexibility
- Excellent abrasion resistance
- Ozone-, sunlight (UV)- and weather-resistant
- TRU-Mark® sequential footage marking

**Industry Approvals:**

- MSHA Approved<sup>(1)</sup>
- RoHS Compliant

**Packaging:**

- Lengths cut to order



**TYPE SO, NON-UL – 600 VOLT**

CATALOG NUMBER	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(5)</sup>
			INCHES	mm	INCHES	mm		
<b>77493*</b>	18	16/30	0.030	0.76	0.180	4.57	10	19
<b>77483*</b>	16	26/30	0.030	0.76	0.200	5.08	13	25
<b>77473*</b>	14	41/30	0.045	1.14	0.240	6.09	18	40
<b>77463*</b>	12	65/30	0.045	1.14	0.265	6.60	25	50
<b>77453*<sup>(1)</sup></b>	10	104/30	0.045	1.14	0.305	7.75	30	75

† Ampacities based on NEC Table 400.5(A)(1).

\* Non-stock item; minimum quantity purchase required.

<sup>(5)</sup> Actual shipping weight may vary.

<sup>(1)</sup> Only 10 AWG construction is MSHA Approved.



# Super Vu-Tron® Multi-Conductor Type S00W

90°C, 600 Volt, UL/CSA Portable Cord



**Product Construction:**

**Conductors:**

- 18 and 16 AWG fully annealed stranded bare copper

**Insulation:**

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below

**Jacket:**

- Super Vu-Tron® 90°C, black
- Temperature range: -40°C to +90°C

**Jacket Marking:**

- CAROL SUPER VU-TRON® (SIZE) (mm<sup>2</sup>) 90°C (UL) WATER RESISTANT SOOW CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA

**Applications:**

- Control circuits
- Tools
- Heavy industrial, processing and construction equipment

**Features:**

- Extra-flexible stranding
- Abrasion-resistant
- Resists oils and solvents
- Flame-resistant
- Ozone-resistant
- 90°C rated conductors and jacket
- Water-resistant\*
- UL Listed and CSA Certified for indoor and outdoor use
- Ozone-, sunlight (UV)- and weather-resistant

**Industry Approvals:**

- UL Flexible Cord - UL 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- RoHS Compliant

**Packaging:**

- 5- through 8-conductor available on 250' (76.2 m), 500' (152.4 m), and 1000' (304.8 m) reels
- 9+ cond. available on long-length reels
- Other put-ups available on special order

\*Suitable for immersion in water if properly sealed and terminated.

**TYPE S00W – 600 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>
				INCHES	mm	INCHES	mm		
09805	5	18	16/30	0.030	0.76	0.465	11.81	5.6	131
09806	6	18	16/30	0.030	0.76	0.495	12.57	5.6	142
09807	7	18	16/30	0.030	0.76	0.520	13.21	5.6	161
09808	8	18	16/30	0.030	0.76	0.530	13.46	4.9	173
09810	10	18	16/30	0.030	0.76	0.595	15.11	4.9	221
09812	12	18	16/30	0.030	0.76	0.600	15.24	3.5	235
09814	14	18	16/30	0.030	0.76	0.630	16.00	3.5	262
09816	16	18	16/30	0.030	0.76	0.700	17.78	3.5	306
09818*	18	18	16/30	0.030	0.76	0.760	19.30	3.5	341
09820	20	18	16/30	0.030	0.76	0.795	20.19	3.5	377
09822*	22	18	16/30	0.030	0.76	0.805	20.45	3.1	400
09824	24	18	16/30	0.030	0.76	0.850	21.59	3.1	453
09827*	27	18	16/30	0.030	0.76	0.865	21.97	3.1	475
09830*	30	18	16/30	0.030	0.76	0.915	23.24	3.1	524
09605	5	16	26/30	0.030	0.76	0.495	12.57	8.0	152
09606	6	16	26/30	0.030	0.76	0.520	13.21	8.0	184
09607	7	16	26/30	0.030	0.76	0.540	13.72	8.0	210
09608	8	16	26/30	0.030	0.76	0.575	14.61	7.0	228
09609	9	16	26/30	0.030	0.76	0.600	15.24	7.0	255
09610	10	16	26/30	0.030	0.76	0.620	15.75	5.0	260
09612	12	16	26/30	0.030	0.76	0.660	16.76	5.0	319
09614	14	16	26/30	0.030	0.76	0.730	18.54	5.0	343
09616	16	16	26/30	0.030	0.76	0.740	18.80	5.0	367
09618*	18	16	26/30	0.030	0.76	0.770	19.56	5.0	405
09620	20	16	26/30	0.030	0.76	0.810	20.57	5.0	444
09622*	22	16	26/30	0.030	0.76	0.900	22.86	4.5	510
09624	24	16	26/30	0.030	0.76	0.925	23.50	4.5	547
09626*	26	16	26/30	0.030	0.76	0.965	24.51	4.5	611
09630	30	16	26/30	0.030	0.76	1.010	25.65	4.5	685

† Values shown are for current-carrying conductors. A grounding conductor, or one which carries only the unbalance current from other conductors, is NOT counted in determining current carrying capacity. Ampacities based on NEC Table 400.5(A)(1).


\* Non-stock item; minimum quantity purchase required.

<sup>(S)</sup>Actual shipping weight may vary.

**COLOR CODE CHART**

NO. OF COND.	COLOR	TRACER	NO. OF COND.	COLOR	TRACER	NO. OF COND.	COLOR	TRACER
1	Black	—	8	Red	Black	15	Blue	White
2	White	—	9	Green	Black	16	Black	Red
3	Red	—	10	Orange	Black	17	White	Red
4	Green	—	11	Blue	Black	18	Orange	Red
5	Orange	—	12	Black	White	19	Blue	Red
6	Blue	—	13	Red	White	20	Red	Green
7	White	Black	14	Green	White	21	Orange	Green

Note: Colors repeat after 21 conductors.



# Super Vu-Tron® Multi-Conductor Type S00W

90°C, 600 Volt, UL/CSA Portable Cord

**Product Construction:**

**Conductors:**

- 14 through 10 AWG fully annealed stranded bare copper

**Insulation:**

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below

**Jacket:**

- Super Vu-Tron® 90°C, black
- Temperature range: -40°C to +90°C

**Jacket Marking:**

- CAROL SUPER VU-TRON® (SIZE) (mm<sup>2</sup>) 90°C (UL) WATER RESISTANT S00W CSA (-40°C) FT2 P-7K-123033 MSHA 600 VOLT ROHS MADE IN USA

**Applications:**

- Control circuits
- Tools
- Heavy industrial, processing and construction equipment

**Features:**

- Extra-flexible stranding
- Abrasion-resistant
- Resists oils and solvents
- Flame-resistant
- Ozone-resistant
- 90°C rated conductors and jacket
- Water-resistant\*
- UL Listed and CSA Certified for indoor and outdoor use
- Ozone-, sunlight (UV)- and weather-resistant

**Industry Approvals:**

- UL Flexible Cord - UL 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- RoHS Compliant


**Packaging:**

- 5- through 8-conductor available on 250' (76.2 m), 500' (152.4 m), and 1000' (304.8 m) reels
- 9+ cond. available on long-length reels
- Other put-ups available on special order

\* Suitable for immersion in water if properly sealed and terminated.

**COLOR CODE CHART**

NO. OF COND.	COLOR	TRACER	NO. OF COND.	COLOR	TRACER
1	Black	—	12	Black	White
2	White	—	13	Red	White
3	Red	—	14	Green	White
4	Green	—	15	Blue	White
5	Orange	—	16	Black	Red
6	Blue	—	17	White	Red
7	White	Black	18	Orange	Red
8	Red	Black	19	Blue	Red
9	Green	Black	20	Red	Green
10	Orange	Black	21	Orange	Green
11	Blue	Black	Note: Colors repeat after 21 conductors. Refer to page 63 for color diagram.		



**TYPE S00W – 600 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(6)</sup>
				INCHES	mm	INCHES	mm		
09405	5	14	41/30	0.045	1.14	0.645	16.26	12.0	266
09406	6	14	41/30	0.045	1.14	0.710	18.03	12.0	313
09407	7	14	41/30	0.045	1.14	0.755	19.18	12.0	326
09408	8	14	41/30	0.045	1.14	0.810	20.57	10.5	366
09409*	9	14	41/30	0.045	1.14	0.860	21.84	10.5	419
09410	10	14	41/30	0.045	1.14	0.875	22.23	10.5	436
09412	12	14	41/30	0.045	1.14	0.900	22.86	7.5	516
09414	14	14	41/30	0.045	1.14	1.000	25.40	7.5	597
09416	16	14	41/30	0.045	1.14	1.030	26.16	7.5	658
09418*	18	14	41/30	0.045	1.14	1.100	27.94	7.5	720
09420	20	14	41/30	0.045	1.14	1.155	29.34	7.5	799
09424	24	14	41/30	0.045	1.14	1.260	32.00	6.7	998
09428*	28	14	41/30	0.045	1.14	1.330	33.78	6.7	1080
09430*	30	14	41/30	0.045	1.14	1.335	33.97	6.0	1146
09205	5	12	65/30	0.045	1.14	0.715	18.16	16.0	326
09206	6	12	65/30	0.045	1.14	0.740	18.80	16.0	362
09207	7	12	65/30	0.045	1.14	0.790	20.07	16.0	415
09208	8	12	65/30	0.045	1.14	0.825	20.96	14.0	464
09209	9	12	65/30	0.045	1.14	0.900	22.86	14.0	510
09210	10	12	65/30	0.045	1.14	0.950	24.13	14.0	602
09212	12	12	65/30	0.045	1.14	1.010	25.65	10.0	662
09214	14	12	65/30	0.045	1.14	1.020	25.91	10.0	724
09216	16	12	65/30	0.045	1.14	1.135	28.83	10.0	869
09218*	18	12	65/30	0.045	1.14	1.175	29.85	10.0	912
09220	20	12	65/30	0.045	1.14	1.175	29.84	10.0	977
09224	24	12	65/30	0.045	1.14	1.360	34.54	9.0	1236
09226	26	12	65/30	0.045	1.14	1.380	35.05	9.0	1309
09227*	27	12	65/30	0.045	1.14	1.390	35.30	9.0	1335
09228*	28	12	65/30	0.045	1.14	1.455	36.95	9.0	1375
09230	30	12	65/30	0.045	1.14	1.455	36.96	9.0	1512
09005	5	10	104/30	0.045	1.14	0.770	19.56	20.0	423
09006	6	10	104/30	0.045	1.14	0.875	22.23	20.0	508
09007	7	10	104/30	0.045	1.14	0.900	22.86	20.0	549
09008*	8	10	104/30	0.045	1.14	0.935	23.75	17.5	625
09010	10	10	104/30	0.045	1.14	1.020	25.91	17.5	755
09012	12	10	104/30	0.045	1.14	1.070	27.18	12.5	867
09016*	16	10	104/30	0.045	1.14	1.230	31.24	12.5	1142
09020*	20	10	104/30	0.045	1.14	1.325	33.66	12.5	1445

† Values shown are for current-carrying conductors. A grounding conductor, or one which carries only the unbalance current from other conductors, is NOT counted in determining current carrying capacity. Ampacities based on NEC Table 400.5(A)(1).

\* Non-stock item; minimum quantity purchase required.

<sup>(6)</sup> Actual shipping weight may vary.



# Super Vu-Tron® Single Conductor

90°C (UL), Type W, 2000 Volt and Type RHH/RHW  
600 Volt Portable Power Cable



**Product Construction:**

**Conductor:**

- 8 AWG through 500 kcmil fully annealed stranded bare copper

**Insulation:**

- Premium-grade 90°C EPDM

**Jacket:**

- Super Vu-Tron® 90°C, black
- Temperature range: -40°C to +90°C
- Voltage rating: 600 volts Type RHH/RHW, 2000 volts Type W
- An open polyester braid reinforcement is applied between the insulation and jacket for mechanical strength

**Jacket Marking:**

- 8-1 AWG: CAROL SUPER VU-TRON® TYPE W PORTABLE POWER CABLE (UL) DRY 90°C WET 75°C 2000 V SUNLIGHT RESISTANT P-7K-123049-MSHA (SIZE) TYPE RHH OR RHW (UL) 600 V MADE IN USA
- 1/0-500 kcmil: CAROL SUPER VU-TRON® TYPE W PORTABLE POWER CABLE (UL) DRY 90°C WET 75°C 2000 V SUNLIGHT RESISTANT P-7K-123049-MSHA (SIZE) TYPE RHH OR RHW (UL) 600 V FOR CT USE --- CSA TYPE W (-40°C) 2 KV FT5 MADE IN USA

**Applications:**

- Portable power systems
- Entertainment industry activities such as theatre, television, night clubs, motion pictures, mobile communication vans, spotlights and sound systems
- Other similar applications that would require permanent or temporary power
- Permanent wiring of 600 volt power supplies, hoists, cranes and other applications where flexible power leads must be installed in conduit or raceways

**Features:**

- Water-resistant\*
- Sunlight-resistant
- Designed to withstand severe environmental conditions
- Withstands exposure to oil, acids, alkalies, heat, flame, moisture and chemicals
- Meets or exceeds flame test requirements of MSHA and UL

**Industry Approvals:**

- UL Type W
- UL Type RHH or RHW
- MSHA Approved
- RoHS Compliant

**Packaging:**

- Lengths cut to order

\* Suitable for immersion in water if properly sealed and terminated.

**TYPE W 2000 VOLT (UL) AND TYPE RHH/RHW 600 VOLT (UL)**

CATALOG NUMBER	NO. OF COND.	AWG OR kcmil	COND. STRAND	NOMINAL COND. O.D.		NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS		APPROX. NET WT. LBS/ M <sup>(S)</sup>
				INCHES	mm	INCHES	mm	INCHES	mm	(1)	(2)	
83008*	1	8	133	0.160	4.06	0.060	1.52	0.470	11.94	55	80	145
83006	1	6	259	0.198	5.03	0.060	1.52	0.545	13.84	75	105	205
83004	1	4	259	0.245	6.22	0.060	1.52	0.595	15.11	95	140	270
83002	1	2	259	0.294	7.47	0.060	1.52	0.670	17.02	130	190	380
83001	1	1	259	0.346	8.79	0.080	2.03	0.730	18.54	150	220	465
83010	1	1/0†	259	0.384	9.75	0.080	2.03	0.790	20.07	170	260	550
83020	1	2/0†	259	0.441	11.20	0.080	2.03	0.865	21.97	195	300	675
83030	1	3/0†	259	0.482	12.24	0.080	2.03	0.910	23.11	225	350	790
83040	1	4/0†	259	0.555	14.10	0.080	2.03	0.960	24.38	260	405	940
83250	1	250†	627	0.615	15.62	0.105	2.67	1.045	26.54	290	455	1125
83350	1	350†	855	0.725	18.42	0.105	2.67	1.145	29.08	350	570	1465
83500	1	500†	1235	0.880	22.35	0.105	2.67	1.315	33.40	430	700	2010

\* Non-stock item; minimum quantity purchase required.

<sup>(1)</sup> Ampacities based on 90°C conductor and 30°C ambient temperature based on Table 310-16 in the National Electrical Code® for RHH/RHW with not more than three current-carrying conductors in raceway, cable or earth.

<sup>(2)</sup> Ampacities based on 90°C conductor and 30°C ambient temperature based on Table 310-17 and Table 400.5(A)(2) in the National Electrical Code® for single-conductor cables.

<sup>(S)</sup> Actual shipping weight may vary.

† Designated for CT use.



# Super Vu-Tron® Multi-Conductor Type W Round

90°C (UL), Type W, 2000 Volt Portable Power Cable

**Product Construction:**

**Conductor:**

- 8 AWG through 500 kcmil fully annealed stranded bare copper

**Insulation:**

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below

**Jacket:**

- Super Vu-Tron® 90°C, black
- Temperature range: -40°C to +90°C

**Jacket Marking:**

- SIZES SMALLER THAN 2-1/4" – CAROL SUPER VU-TRON® (SIZE) TYPE W PORTABLE POWER CABLE (UL) 2000 V DRY 90°C WET 75°C SUN RES P-7K-123049-MSHA---CSA TYPE W (-40°C) 2 KV FT5 MADE IN USA
- SIZES 2-1/4" AND LARGER – (SIZE) TYPE W CAROL SUPER VU-TRON® 90°C DRY AND WATER RESISTANT 75°C 2000 V SUN RES (UL) P-7K-123049 MSHA LR27161 MADE IN USA

**Applications:**

- Industrial and light- to medium-duty mining applications
- Heavy-duty service as power supply cable
- AC systems (grounded and ungrounded)
- Mobile and portable electrical equipment
- Motor and battery leads
- 2-conductor cables—use on DC or AC single-phase systems where grounding is not required
- 3-conductor cables—use on AC systems where no grounding is required or on DC systems with one conductor for grounding
- 4-conductor cables—use on two- or three-phase AC systems with one conductor used for grounding
- 5-conductor cables—use in applications where separating the system neutral from the frame ground is required

**Features:**

- Withstands severe environmental conditions
- Suitable for immersion in water\*
- Indent-printed for easy identification
- Withstands exposure to oil, acids, alkalis, heat, moisture and most chemicals
- Rope lay stranding for maximum flex life
- Excellent impact resistance
- Cable core bound for superior flexibility and toughness
- Sunlight-resistant

**Industry Approvals:**

- CSA
- MSHA Approved
- UL Type W
- RoHS Compliant


**Packaging:**

- Lengths cut to order

\* Suitable for immersion in water if properly sealed and terminated.

**COLOR CODE CHART**

NO. OF CONDUCTORS	COLOR**
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Green, Orange



CATALOG NUMBER	NO. OF COND.	AWG OR kcmil	COND. STRAND	NOMINAL COND. O.D.		NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS <sup>(1)</sup>	APPROX. NET WT. LBS/M <sup>(5)</sup>
				INCHES	mm	INCHES	mm	INCHES	mm		
<b>2 CONDUCTOR – TYPE W – 2000 VOLT</b>											
81312	2	8	133	0.160	4.06	0.060	1.52	0.770	19.56	74	325
81622	2	6	259	0.198	5.03	0.060	1.52	0.910	23.11	99	470
81642	2	4	259	0.245	6.22	0.060	1.52	1.020	25.91	130	620
81662	2	2	259	0.297	7.54	0.080	2.03	1.210	30.73	174	935
81372*	2	1	259	0.353	8.97	0.080	2.03	1.370	34.80	202	1305
81382*	2	1/0	259	0.385	9.78	0.080	2.03	1.435	36.45	234	1555
81392*	2	2/0	259	0.442	11.23	0.080	2.03	1.555	39.50	271	1860
81402*	2	3/0	259	0.480	12.19	0.080	2.03	1.670	42.42	313	2230
81412*	2	4/0	259	0.555	14.10	0.080	2.03	1.815	46.10	361	2655
<b>3 CONDUCTOR – TYPE W – 2000 VOLT</b>											
81313	3	8	133	0.160	4.06	0.060	1.52	0.945	24.00	74	470
81623	3	6	259	0.198	5.03	0.060	1.52	1.020	25.91	99	625
81643	3	4	259	0.245	6.22	0.060	1.52	1.135	28.83	130	810
81663	3	2	259	0.297	7.54	0.080	2.03	1.345	34.16	174	1190
81373*	3	1	259	0.353	8.97	0.080	2.03	1.455	36.96	202	1655
81383	3	1/0	259	0.385	9.78	0.080	2.03	1.585	40.26	234	1965
81393	3	2/0	259	0.442	11.23	0.080	2.03	1.675	42.55	271	2350
81403*	3	3/0	259	0.480	12.19	0.080	2.03	1.815	46.10	313	2890
81413*	3	4/0	259	0.555	14.10	0.080	2.03	1.950	49.53	361	3285
81423*	3	250	627	0.615	15.62	0.095	2.41	2.390	60.71	402	5070
81443*	3	350	855	0.725	18.42	0.095	2.41	2.680	68.07	495	6570
81473*	3	500	1235	0.880	22.35	0.095	2.41	3.030	76.96	613	8700
<b>4 CONDUCTOR – TYPE W – 2000 VOLT</b>											
81314	4	8	133	0.160	4.06	0.060	1.52	0.980	24.89	65	615
81624	4	6	259	0.198	5.03	0.060	1.52	1.070	27.18	87	800
81644	4	4	259	0.245	6.22	0.060	1.52	1.210	30.73	114	1040
81664	4	2	259	0.297	7.54	0.080	2.03	1.435	36.45	152	1580
81374	4	1	259	0.353	8.97	0.080	2.03	1.595	40.51	177	2045
81384	4	1/0	259	0.385	9.78	0.080	2.03	1.705	43.31	205	2430
81394	4	2/0	259	0.442	11.23	0.080	2.03	1.845	46.86	237	2950
81404	4	3/0	259	0.480	12.19	0.080	2.03	1.965	49.91	274	3430
81414	4	4/0	259	0.555	14.10	0.080	2.03	2.145	54.48	316	3885
<b>5 CONDUCTOR – TYPE W – 2000 VOLT</b>											
81315	5	8	133	0.160	4.06	0.060	1.52	1.030	26.16	52	650
81625	5	6	259	0.198	5.03	0.060	1.52	1.170	29.72	69	915
81645	5	4	259	0.245	6.22	0.060	1.52	1.360	34.54	91	1320
81665	5	2	259	0.297	7.54	0.080	2.03	1.595	40.51	121	1925
81375*	5	1	259	0.353	8.97	0.080	2.03	1.820	46.23	141	2675
81385	5	1/0	259	0.385	9.78	0.080	2.03	1.900	48.26	164	2885
81395*	5	2/0	259	0.442	11.23	0.080	2.03	2.060	52.32	189	3630
81405*	5	3/0	259	0.480	12.19	0.080	2.03	2.260	57.40	219	4900
81415*	5	4/0	259	0.555	14.10	0.080	2.03	2.460	62.48	252	5980

<sup>(1)</sup> Ampacities based on 90°C conductor and 30°C ambient temperature per Table 400.5(A)(2) of the National Electrical Code®.

\* Non-stock item; minimum quantity purchase required.

\*\* Green conductor for grounding only.


<sup>(5)</sup> Actual shipping weight may vary.





# Super Vu-Tron® Type G and Type G-GC Round

90°C (UL), 2000 Volt Portable Power Cable



### 3 CONDUCTOR – TYPE G-GC – 2000 VOLT

CATALOG NUMBER	NO. OF COND.	AWG OR kcmil	COND. STRAND	NOMINAL COND. O.D.		YELLOW GROUND CHECK AWG SIZE	GREEN GROUND COND. AWG SIZE	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURR. AMPS <sup>(1)</sup>	APPROX. NET WT. LBS/M <sup>(5)</sup>
				INCHES	mm			INCHES	mm	INCHES	mm		
82313	3	8	133	0.160	4.06	10	2#10	0.060	1.52	0.965	24.51	65	600
82623	3	6	259	0.198	5.03	10	2#10	0.060	1.52	1.025	26.04	87	770
82643	3	4	259	0.245	6.22	10	2#8	0.060	1.52	1.130	28.70	114	1015
82663	3	2	259	0.297	7.54	8	2#7	0.080	2.03	1.345	34.16	152	1480
82373	3	1	259	0.353	8.97	8	2#6	0.080	2.03	1.455	36.96	177	1795
82383	3	1/0	259	0.385	9.78	8	2#5	0.080	2.03	1.585	40.26	205	2245
82393	3	2/0	259	0.442	11.23	8	2#4	0.080	2.03	1.675	42.55	237	2570
82403	3	3/0	259	0.480	12.19	8	2#3	0.080	2.03	1.810	45.97	274	3230
82413	3	4/0	259	0.555	14.10	8	2#2	0.080	2.03	1.950	49.53	316	3700
82423 <sup>(2)*</sup>	3	250	627	0.615	15.62	8	2#2	0.095	2.41	2.390	60.71	352	6060
82443 <sup>(2)*</sup>	3	350	855	0.725	18.42	8	2#1/0	0.095	2.41	2.680	68.07	433	7400
82473 <sup>(2)*</sup>	3	500	1235	0.880	22.35	8	2#2/0	0.095	2.41	3.030	76.96	536	10100

### 4 CONDUCTOR – TYPE G – 600/2000 VOLT

CATALOG NUMBER	NO. OF COND.	AWG OR kcmil	COND. STRAND	NOMINAL COND. O.D.		GREEN COND. AWG SIZE	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS <sup>(1)</sup>	APPROX. NET WT. LBS/M <sup>(5)</sup>
				INCHES	mm		INCHES	mm	INCHES	mm		
82314	4	8	133	0.160	4.06	4#12	0.060	1.52	1.045	26.54	52	690
82624	4	6	259	0.198	5.03	4#12	0.060	1.52	1.125	28.58	70	880
82644	4	4	259	0.245	6.22	4#10	0.060	1.52	1.225	31.12	91	1160
82664	4	2	259	0.297	7.54	4#9	0.080	2.03	1.435	36.45	122	1720
82374*	4	1	259	0.353	8.97	4#8	0.080	2.03	1.590	40.39	142	2200
82384	4	1/0	259	0.385	9.78	4#7	0.080	2.03	1.730	43.94	164	2705
82394	4	2/0	259	0.442	11.23	4#6	0.080	2.03	1.855	47.12	190	3190
82404	4	3/0	259	0.480	12.19	4#5	0.080	2.03	2.040	51.82	219	4005
82414	4	4/0	259	0.555	14.10	4#4	0.080	2.03	2.145	54.48	253	4560

<sup>(1)</sup> Ampacities based on 90°C conductor and 30°C ambient temperature per Table 400.5(A)(2) of the National Electrical Code®.

<sup>(2)</sup> UL Listed and c(UL) Certified.

\* Non-stock item; minimum quantity purchase required.

<sup>(5)</sup> Actual shipping weight may vary.

#### Product Construction:

##### Conductor:

- 8 AWG through 500 kcmil fully annealed stranded bare copper

##### Insulation:

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below
- Insulated grounds and ground checks

##### Jacket:

- Super Vu-Tron® 90°C, black
- Temperature range: -40°C to +90°C

##### Jacket Marking:

- TYPE G-GC (4/0 AND SMALLER) – CAROL SUPER VU-TRON® SIZE (mm<sup>2</sup>) TYPE G-GC PORTABLE POWER CABLE (UL) 2000 V DRY 90°C WET 75°C SUN RES P-7K-123049-MSHA --- CSA TYPE G-CG (-40°C) 2 KV FT5 MADE IN USA
- TYPE G-GC (LARGER THAN 4/0) - (SIZE) TYPE G-GC CAROL SUPER VU-TRON® 90°C DRY AND WATER RESISTANT 75°C 2000 V SUN RES (UL) P-7K-123049 MSHA LR27161 MADE IN USA
- TYPE G - CAROL SUPER VU-TRON® SIZE (mm<sup>2</sup>) TYPE G PORTABLE POWER CABLE (UL) 600/2000 V DRY 90°C WET 75°C SUN RES P-7K-123049 MSHA --- CSA TYPE G (-40°C) 2 KV FT5 MADE IN USA

#### Applications:

- Industrial and light- to medium-duty mining applications
- Heavy-duty service as power supply cable
- Mobile and portable electrical equipment
- 3- and 4-conductor—use on three-phase AC systems where grounding is required

#### Features:

- Excellent impact and abrasion resistance
- Withstands exposure to oil, acids, alkalies, heat, moisture and most chemicals
- Suitable for immersion in water\*
- Indent-printed for easy identification
- Rope lay stranding for maximum flex life
- Cable core bound for superior flexibility and toughness
- Non-wicking rubber fillers (G-GC)
- Canadian color code available upon request
- Sunlight-resistant

#### Industry Approvals:

- UL Type G, G-GC
- CSA
- MSHA Approved
- RoHS Compliant

#### Packaging:

- Lengths cut to order

\* Suitable for immersion in water if properly sealed and terminated.

#### COLOR CODE CHART

NO. OF CONDUCTORS	COLOR
3	Black, White, Red
4	Black, White, Red, Orange



# Super Vu-Tron<sup>®</sup> Canadian Type G-GC Round

90°C, 2000 Volt Portable Power Cable

**Product Construction:**

**Conductor:**

- 6 AWG through 4/0 AWG fully annealed stranded bare copper

**Insulation:**

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below
- Insulated yellow ground check

**Jacket:**

- Super Vu-Tron<sup>®</sup> 90°C, black
- Temperature range: -40°C to +90°C

**Jacket Marking:**

- CAROL SUPER VU-TRON<sup>®</sup> SIZE (mm<sup>2</sup>)  
TYPE G-GC 2 KV 90°C (-40°C) FT5 CSA LR92874  
P-7K-123049-MSHA MADE IN USA



**3 CONDUCTOR – TYPE G-GC – 2000 VOLT**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL COND. O.D.		YELLOW GROUND CHECK AWG SIZE	GROUND COND. AWG SIZE	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURR. AMPS <sup>(1)</sup>	APPROX. NET WT. LBS/ M <sup>(2)</sup>
				INCHES	mm			INCHES	mm	INCHES	mm		
83103	3	8	133	0.160	4.06	10	2#10	0.060	1.52	0.945	24.00	65	827
83113	3	6	259	0.198	5.03	10	2#10	0.060	1.52	1.025	26.04	87	770
83123	3	4	259	0.245	6.22	10	2#8	0.060	1.52	1.140	28.96	114	1015
83133	3	2	259	0.297	7.54	8	2#6	0.080	2.03	1.345	34.16	152	1480
83143	3	1	259	0.353	8.97	8	2#6	0.080	2.03	1.455	36.96	177	1795
83153	3	1/0	259	0.385	9.78	8	2#4	0.080	2.03	1.585	40.26	205	2245
83163	3	2/0	259	0.442	11.23	8	2#4	0.080	2.03	1.685	42.80	237	2570
83183	3	4/0	259	0.555	14.10	8	2#2	0.080	2.03	1.975	50.17	316	3700

<sup>(1)</sup> Ampacity rating based on CEC/CSA.

<sup>(2)</sup> Actual shipping weight may vary.

**Applications:**

- Industrial and light- to medium-duty mining applications
- Heavy-duty service as power supply cable
- Mobile and portable electrical equipment
- 3- and 4-conductor—use on three-phase AC systems where grounding is required

**Features:**

- Excellent impact and abrasion resistance
- Withstands exposure to oil, acids, alkalis, heat, moisture and most chemicals
- Indent-printed for easy identification
- Rope lay stranding for maximum flex life
- Cable core bound for superior flexibility and toughness
- Non-wicking rubber fillers (GGC)
- Canadian color code
- Sunlight-resistant

**Industry Approvals:**

- CSA Flexible Cord - C22.2-96
- MSHA Approved
- RoHS Compliant

**Packaging:**

- Lengths cut to order


**COLOR CODE CHART**

NO. OF CONDUCTORS	COLOR
3	Black, Red, Blue



# Super Vu-Tron® III Types SJOOW/SOOW

105°C, 300 and 600 Volt, UL/CSA Portable Cord



**Product Construction:**

**Conductors:**

- 18 through 10 AWG fully annealed stranded bare copper

**Insulation:**

- Premium-grade, color-coded, oil-resistant 105°C EPDM
- Color code: See chart below

**Jacket:**

- Super Vu-Tron® III, yellow
- Temperature range: -50°C to +105°C UL/CSA
- Voltage rating: 300 volts Type SJOOW, 600 volts Type SOOW

**Jacket Marking:**

- SUPER VU-TRON® III SJOOW - CAROL SUPER VU-TRON® III (SIZE) (mm<sup>2</sup>) 105°C (UL) WATER RESISTANT SJOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)
- SUPER VU-TRON® III SOOW - CAROL SUPER VU-TRON® III (SIZE) (mm<sup>2</sup>) 105°C (UL) WATER RESISTANT SOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)

**Applications:**

- Machine tools
- Power tools
- Dockside power applications
- Motor leads
- Portable machinery
- Cranes
- Submersible pumps

**Features:**

- Excellent flexibility in cold temperatures
- Last longer in flex applications
- Integral Flexfill®
- Ozone-, sunlight (UV)- and weather-resistant
- UL Listed and CSA Certified for indoor and outdoor use
- Water-resistant\*
- Safety-colored
- High heat and flame resistance
- Resistant to oils, acids and chemicals
- Excellent abrasion and cut resistance
- TRU-Mark® sequential footage marking

**Industry Approvals:**

- UL Flexible Cord - UL 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- RoHS Compliant

**Packaging:**

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order

\* Suitable for immersion in water if properly sealed and terminated.

**COLOR CODE CHART**

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Green, Orange

**TYPE SJOOW – 300 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	STD. CTN.
				INCHES	mm	INCHES	mm			
02001*	2	18	41/34	0.030	0.76	0.310	8.00	10	56	1000'
02002*	3	18	41/34	0.030	0.76	0.320	8.12	10	65	1000'
02003*	4	18	41/34	0.030	0.76	0.345	8.76	7	80	250'
02004*	2	16	65/34	0.030	0.76	0.315	8.00	13	68	1000'
02005*	3	16	65/34	0.030	0.76	0.335	8.51	13	80	250'
02006*	4	16	65/34	0.030	0.76	0.370	9.40	10	95	250'
02007*	2	14	41/30	0.030	0.76	0.370	9.40	18	90	250'
02008*	3	14	41/30	0.030	0.76	0.375	9.52	18	110	250'
02009*	4	14	41/30	0.030	0.76	0.405	10.29	15	130	250'

**TYPE SOOW – 600 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	STD. CTN.
				INCHES	mm	INCHES	mm			
02031*	2	18	41/34	0.030	0.76	0.365	9.27	10	75	250'
02032*	3	18	41/34	0.030	0.76	0.375	9.53	10	80	250'
02033*	4	18	41/34	0.030	0.76	0.400	10.16	7	110	250'
02034*	2	16	65/34	0.030	0.76	0.370	9.40	13	75	250'
02035*	3	16	65/34	0.030	0.76	0.395	10.80	13	100	250'
02036*	4	16	65/34	0.030	0.76	0.425	10.80	10	120	250'
02021*	5	16	65/34	0.030	0.76	0.515	13.08	8	150	250'
02037*	2	14	41/30	0.045	1.14	0.510	12.95	18	155	250'
02038*	3	14	41/30	0.045	1.14	0.525	13.34	18	165	250'
02039*	4	14	41/30	0.045	1.14	0.575	14.61	15	215	250'
02022*	5	14	41/30	0.045	1.14	0.675	17.15	12	285	250'
02041*	2	12	65/30	0.045	1.14	0.590	14.99	25	200	250'
02042*	3	12	65/30	0.045	1.14	0.600	15.24	25	250	250'
02043*	4	12	65/30	0.045	1.14	0.650	16.51	20	280	250'
02023*	5	12	65/30	0.045	1.14	0.730	18.54	16	315	250'
02045*	3	10	104/30	0.045	1.14	0.660	16.76	30	320	250'
02046*	4	10	104/30	0.045	1.14	0.710	18.03	25	375	250'
02024*	5	10	104/30	0.045	1.14	0.770	19.56	20	432	250'

\* Non-stock item available by special order; minimum quantity purchase required.  
 † Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).  
 (S) Actual shipping weight may vary.



# Super Vu-Tron® Supreme Types SJOOW/SOOW

105°C, 300 and 600 Volt, UL/CSA Portable Cord



**Product Construction:**

**Conductors:**

- 18 through 10 AWG fully annealed stranded tinned copper

**Insulation:**


- Premium-grade, color-coded, oil-resistant 105°C EPDM
- Color code: See chart below

**Jacket:**

- Super Vu-Tron® Supreme, yellow
- Temperature range: -50°C to +105°C UL/CSA
- Voltage rating: 300 volts Type SJOOW, 600 volts Type SOOW

**Jacket Marking:**

- SUPER VU-TRON® SUPREME SJOOW - CAROL SUPER VU-TRON® SUPREME (SIZE) (mm<sup>2</sup>) 105°C (UL) WATER RESISTANT SJOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 300 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)
- SUPER VU-TRON® SUPREME SOOW - CAROL SUPER VU-TRON® SUPREME (SIZE) (mm<sup>2</sup>) 105°C (UL) WATER RESISTANT SOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 600 VOLT ROHS MADE IN USA (TRU-MARK SEQUENTIAL FOOTAGE)



**TYPE SJOOW – 300 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	STRAND O.D.	NOM. INS. THICKNESS		JACKET NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	COPPER WT. LBS/M'	STD. CTN.
					INCHES	mm	INCHES	mm				
02601	2	18	41/34	.048"	0.030	0.76	0.310	7.87	10	56	10	1000'
02602	3	18	41/34	.048"	0.030	0.76	0.320	8.13	10	66	15	1000'
02603	4	18	41/34	.048"	0.030	0.76	0.345	8.76	7	79	20	250'
02604	2	16	65/34	.057"	0.030	0.76	0.315	8.00	13	62	16	1000'
02605	3	16	65/34	.057"	0.030	0.76	0.335	8.51	13	77	24	250'
02606	4	16	65/34	.057"	0.030	0.76	0.370	9.40	10	98	32	250'
02607	2	14	105/34	.077"	0.030	0.76	0.370	9.40	18	75	24	250'
02608	3	14	105/34	.077"	0.030	0.76	0.375	9.53	18	99	36	250'
02609	4	14	105/34	.077"	0.030	0.76	0.405	10.29	15	122	48	250'

**TYPE SOOW – 600 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INS. THICKNESS		JACKET NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	COPPER WT. LBS/M'	STD. CTN.
				INCHES	mm	INCHES	mm				
02631*	2	18	41/34	0.030	0.76	0.365	9.27	10	75	10	250'
02632	3	18	41/34	0.030	0.76	0.375	9.53	10	84	15	250'
02633*	4	18	41/34	0.030	0.76	0.400	10.16	7	110	21	250'
02634	2	16	65/34	0.030	0.76	0.370	9.40	13	80	16	250'
02635	3	16	65/34	0.030	0.76	0.395	10.03	13	96	24	250'
02636	4	16	65/34	0.030	0.76	0.425	10.80	10	118	32	250'
02621	5	16	65/34	0.030	0.76	0.515	13.08	8	166	40	250'
02637*	2	14	105/34	0.045	1.14	0.510	12.95	18	153	24	250'
02638	3	14	105/34	0.045	1.14	0.525	13.34	18	164	36	250'
02639	4	14	105/34	0.045	1.14	0.575	14.61	15	204	48	250'
02622*	5	14	105/34	0.045	1.14	0.675	17.15	12	279	60	250'
02641*	2	12	168/34	0.045	1.14	0.590	14.99	25	198	38	250'
02642	3	12	168/34	0.045	1.14	0.600	15.24	25	224	57	250'
02643	4	12	168/34	0.045	1.14	0.650	16.51	20	270	76	250'
02623*	5	12	168/34	0.045	1.14	0.730	18.54	16	308	96	250'
02645	3	10	259/34	0.045	1.14	0.660	16.76	30	295	99	250'
02646	4	10	259/34	0.045	1.14	0.710	18.03	25	365	132	250'
02624*	5	10	259/34	0.045	1.14	0.770	19.56	20	422	168	250'

**Applications:**

- Machine tools
- Power tools
- Dockside power applications
- Motor leads
- Portable machinery
- Cranes
- Submersible pumps
- Where water immersion is required
- Severe environment OEM/MRO applications

**Features:**

- Excellent flexibility in cold temperatures
- Lasts longer in flex applications (extra-flexible Class M stranding)
- Integral Flexfill®
- Ozone-, sunlight (UV)- and weather-resistant
- UL Listed and CSA Certified for indoor and outdoor use
- Water-resistant\*
- Safety-colored, with high-visibility yellow jacket
- High heat and flame resistance
- Resistant to sunlight, oils, acids and chemicals
- Excellent abrasion and cut resistance
- TRU-Mark® sequential footage marking
- Tinned copper conductors – corrosion/oxidation-resistant

**Industry Approvals:**

- UL Flexible Cord - UL 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order

\* Suitable for immersion in water if properly sealed and terminated.

**TOP PERFORMANCE IN THE TOUGHEST ENVIRONMENTS**

Volume change (%) of SUPER VU-TRON® SUPREME after 28 days at room temperature in the following materials			
ACETIC ACID (30%)	+19.00	LINSEED OIL	+1.04
AMMONIA HYDROXIDE	+3.12	LUBE OIL	-1.82
ASTM 3 OIL	+0.26	MILK	+4.16
BEER	+4.42	NITRIC ACID (10%)	+7.29
BLEACH WATER	+2.60	SAE 30 OIL	-1.30
BUTYL ALCOHOL	-1.82	SKYDROL 500	+17.10
CORN OIL	0.00	SODIUM HYDROXIDE	+10.90
FORMALDEHYDE	+3.38	SULFURIC ACID (10%)	+2.34
GLYCOL (ANTI-FREEZE)	-2.60	TOLUENE	+30.20
HYDROCHLORIC ACID (20%)	+10.60	UNLEADED GAS	+22.10
JP-4	+10.90	WATER	+2.86
KEROSENE	+10.60		

\* Non-stock item; minimum quantity purchase required.

† Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).

(S) Actual shipping weight may vary.

**COLOR CODE CHART**

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green/Yellow
4	Black, White, Red, Green/Yellow
5	Black, White, Red, Green/Yellow, Orange




# Super Vu-Tron® Supreme Types SJOOW/SOOW with GenClean™

105°C, 300 and 600 Volt, UL/CSA Portable Cord



**ENHANCED CLEANABILITY**



**Product Construction:**

**Conductors:**

- 18 through 10 AWG fully annealed stranded tinned copper

**Insulation:**

- Premium-grade, color-coded, oil-resistant 105°C EPDM
- Color code: See chart below

**Jacket:**

- Super Vu-Tron® Supreme, yellow, with GenClean™ technology
- Temperature range: -50°C to +105°C UL/CSA
- Voltage rating: 300 volts Type SJOOW, 600 volts Type SOOW

**Jacket Marking:**

- SUPER VU-TRON® SUPREME SJOOW - CAROL SUPER VU-TRON® SUPREME FEATURING GENCLEAN™ JACKET (SIZE) (mm<sup>2</sup>) 105°C (UL) WATER RESISTANT SJOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 300 VOLT ROHS MADE IN USA
- SUPER VU-TRON® SUPREME SOOW - CAROL SUPER VU-TRON® SUPREME FEATURING GENCLEAN™ JACKET (SIZE) (mm<sup>2</sup>) 105°C (UL) WATER RESISTANT SOOW CSA (-50°C) FT1 --- P-07-KA120015-MSHA 600 VOLT ROHS MADE IN USA

**TYPE SJOOW – 300 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	STRAND O.D.	NOM. INS. THICKNESS		JACKET NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	COPPER WT. LBS/M <sup>(S)</sup>	STD. CTN.
					INCHES	mm	INCHES	mm				
GC601	2	18	41/34	.048"	0.030	0.76	0.310	7.87	10	56	10	1000'
GC602	3	18	41/34	.048"	0.030	0.76	0.320	8.13	10	66	15	1000'
GC603	4	18	41/34	.048"	0.030	0.76	0.345	8.76	7	79	21	250'
GC604	2	16	65/34	.057"	0.030	0.76	0.315	8.00	13	62	16	1000'
GC605	3	16	65/34	.057"	0.030	0.76	0.335	8.51	13	77	24	250'
GC606	4	16	65/34	.057"	0.030	0.76	0.370	9.40	10	98	32	250'
GC607	2	14	105/34	.077"	0.030	0.76	0.370	9.40	18	75	24	250'
GC608	3	14	105/34	.077"	0.030	0.76	0.375	9.53	18	99	36	250'
GC609	4	14	105/34	.077"	0.030	0.76	0.405	10.29	15	122	48	250'

**TYPE SOOW – 600 VOLT – UL/CSA**

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INS. THICKNESS		JACKET NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M <sup>(S)</sup>	COPPER WT. LBS/M <sup>(S)</sup>	STD. CTN.
				INCHES	mm	INCHES	mm				
GC631*	2	18	41/34	0.030	0.76	0.365	9.27	10	75	10	250'
GC632	3	18	41/34	0.030	0.76	0.375	9.53	10	84	15	250'
GC633*	4	18	41/34	0.030	0.76	0.400	10.16	7	110	21	250'
GC634	2	16	65/34	0.030	0.76	0.370	9.40	13	80	16	250'
GC635	3	16	65/34	0.030	0.76	0.395	10.03	13	96	24	250'
GC636	4	16	65/34	0.030	0.76	0.425	10.80	10	118	32	250'
GC621	5	16	65/34	0.030	0.76	0.515	13.08	8	166	40	250'
GC637*	2	14	105/34	0.045	1.14	0.510	12.95	18	153	24	250'
GC638	3	14	105/34	0.045	1.14	0.525	13.34	18	164	36	250'
GC639	4	14	105/34	0.045	1.14	0.575	14.61	15	204	48	250'
GC622*	5	14	105/34	0.045	1.14	0.675	17.15	12	279	60	250'
GC641*	2	12	168/34	0.045	1.14	0.590	14.99	25	198	38	250'
GC642	3	12	168/34	0.045	1.14	0.600	15.24	25	224	57	250'
GC643	4	12	168/34	0.045	1.14	0.650	16.51	20	270	76	250'
GC623*	5	12	168/34	0.045	1.14	0.730	18.54	16	308	96	250'
GC645	3	10	259/34	0.045	1.14	0.660	16.76	30	295	99	250'
GC646	4	10	259/34	0.045	1.14	0.710	18.03	25	365	132	250'
GC624*	5	10	259/34	0.045	1.14	0.770	19.56	20	422	168	250'

**Target Applications/Markets:**

- Food/beverage manufacturing
- Marine manufacturing
- Manufactured structures
- Severe environments
- Docksides power
- Health care

**Features:**

- Cleanable rubber jacket
- Excellent flexibility in cold temperatures
- Lasts longer in flex applications (extra-flexible Class M stranding)
- Integral Flexfill®
- Enhanced cleanability
- Reduced scuffing
- Ozone-, sunlight (UV)- and weather-resistant
- UL Listed and CSA Certified for indoor and outdoor use
- Water-resistant\*
- Safety-colored, with high-visibility yellow jacket
- High heat and flame resistance
- Resistant to sunlight, oils, acids and chemicals
- Excellent abrasion and cut resistance
- Tinned copper conductors – corrosion/oxidation-resistant

**Industry Approvals:**

- UL Flexible Cord - UL 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order

\* Suitable for immersion in water if properly sealed and terminated.

**TOP PERFORMANCE IN THE TOUGHEST ENVIRONMENTS**

Volume change (%) of SUPER VU-TRON® SUPREME after 28 days at room temperature in the following materials		
ACETIC ACID (30%)	+19.00	LINSEED OIL +1.04
AMMONIA HYDROXIDE	+3.12	LUBE OIL -1.82
ASTM 3 OIL	+0.26	MILK +4.16
BEER	+4.42	NITRIC ACID (10%) +7.29
BLEACH WATER	+2.60	SAE 30 OIL -1.30
BUTYL ALCOHOL	-1.82	SKYDROL 500 +17.10
CORN OIL	0.00	SODIUM HYDROXIDE +10.90
FORMALDEHYDE	+3.38	SULFURIC ACID (10%) +2.34
GLYCOL (ANTI-FREEZE)	-2.60	TOLUENE +30.20
HYDROCHLORIC ACID (20%)	+10.60	UNLEADED GAS +22.10
JP-4	+10.90	WATER +2.86
KEROSENE	+10.60	

\* Non-stock item; minimum quantity purchase required.  
 † Green conductor for grounding only. Ampacities based on NEC Table 400.5(A)(1).  
 (S) Actual shipping weight may vary.

**COLOR CODE CHART**

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green/Yellow
4	Black, White, Red, Green/Yellow
5	Black, White, Red, Green/Yellow, Orange



# Industrial Cable Solutions for Variable Frequency Drives

Tough challenges call for innovative solutions, and General Cable is your worldwide source for new products and a wide range of industry-leading industrial cables. General Cable provides a line of cables for Variable Frequency Drives (VFD) in both unarmored and armored designs as well as in many power ratings.

The following highlights the features and benefits of specially engineered cable designs for use with AC motors controlled by pulse-width modulated inverters in VFD applications rated up to 1000 V, 2000 V, 5 kV and 8 kV:

## CVTC® VFD Low-Voltage Power Type TC-ER

Compressed stranding to reduce overall cable diameter


Dual copper tape shields provide maximum shield coverage required for Variable Frequency Drive applications

Symmetrically placed annealed bare copper grounding conductors in direct contact with shield

Designed to reduce the risk of Electromagnetic Interference (EMI), which can lead to malfunction

Meets crush and impact requirements of Type MC cable

Permitted for use in Class I, Division 2 industrial hazardous locations per NEC



## CCW® VFD Low- & Medium-Voltage Power Type MC-HL

Compact or compressed stranding to reduce conductor size

XLPE insulation with high impulse voltage breakdown level resists degradation

Symmetrically placed annealed bare copper grounding conductors in direct contact with shield

Compact conductors provide reduced conductor size

Pure EPR insulation system has outstanding corona resistance and high dielectric strength, providing electrical stability under stress

Triple Extrusion applies strand shield, EPR insulation and insulation shield in one operation, eliminating exposure to contamination and providing maximum control and consistency



### Additional Benefits of CCW® VFD Low- & Medium-Voltage Power Cable

Continuously Corrugated Welded armor:

- Provides impervious barrier to moisture, gas and liquids
- Provides EMI shielding performance
- Factory assembled and tested for use as an economical, rugged and reliable alternative to cable in conduit wiring systems

Armored constructions suitable for use in Class I, II, & III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505

### VFD Cable Advantages in Industrial Automation Applications

Today's manufacturing and processing environments are relying on increased automation to improve productivity. As a result, there is more focus and awareness around minimizing downtime and improving safety. The use of Variable Frequency Drive (VFD) cable in industrial automation applications provides a reliable solution to address these issues.

### When Are VFD Cables Needed?

Whenever you are installing a VFD system, VFD cables should be strongly considered for use between the inverter and the motor. Standard power cable is not designed to handle the high frequency components of the drive's inverter output. Some applicable market applications are shown in the chart below.

### Why Are VFD Cables Needed?

Many problems that are common in VFD systems can be fixed or their impact lessened by simply using a properly terminated VFD cable. These problems include but are not limited to:

- intermittent issues with other factory control or communication systems
- alarm system malfunctions
- premature motor bearing failure
- premature cable failure
- drive failure and drive problems
- shock hazards (to maintenance and other personnel)

### How Does a VFD Cable Address These Issues?

VFD cable features a properly designed overall electrical shield, symmetrically designed conductors, and thermoset insulation with a low dielectric constant.

### Proper Shielding

VFD cable is designed with an overall electrical shield in the form of armor, copper tape or a copper braid. General Cable offers all three designs so you can choose the construction that best meets your needs. However, not all shields are created equal. The shield must be designed to effectively handle the high frequency components of the inverter waveform and minimize inductive loading.

This shield, along with proper cable termination, will minimize electromagnetic radiation broadcast from the cable. Unshielded cable acts like a broadcast antenna, radiating these unwanted electrical signals in the form of noise throughout your plant. This radiation can cause issues with alarm systems, other control and communication systems, and other drives. As factories become more automated, these issues become more prevalent.

Shielding also minimizes electromagnetic induction (a signal produced in nearby electrical circuits when they are exposed to a varying magnetic field). It has been shown that when unshielded inverter-motor

MARKETS	VFD OFFERING		
	Unarmored VFD (CVTC®)	Armored VFD (CCW®)	Applications
Marine		X	Fluid/flow control – process pumps/drilling and pumps (Note: TYPE P VFD cable for flex applications)
Power & Energy Management	X	X	Process & flow control, cooling towers
Pulp & Paper	X	X	Conveyors, process equipment
Automotive & Tire	X	X	Material handling, process equipment, conveyors
Global Machine & Equip	X	X	Packaging, material handling, equipment, cranes, conveyors
Oil, Gas & Petrochemical	X	X	Fluid/flow control – process pumps and cooling towers, terminals and pipelines
Specialty Chemical	X	X	Fluid/flow control, process pumps, rotary equipment
Water & Waste	X	X	Process/flow control pumps, rotary equipment



cables are installed in tray, a potentially lethal current can be induced in a cable that is locked out from the electromagnetic induction generated by the other energized cables in the tray. Many people feel that human safety alone justifies the utilization of VFD cables for their motor-inverter connections.

Shielding also has the effect of reducing the risk of premature motor bearing failure by providing a low impedance path for common mode current to return to the inverter frame. Without this low impedance path, the current can end up flowing through motor bearings, causing bearing fluting.<sup>1</sup>

### **Proper Conductor Design**

Common mode (CM) current is a frequent cause of drive system issues (including false trips). One way to deal with CM current is to direct it back to the inverter frame via the shield. Some VFD cables go further and actually reduce the generation of CM current. A cable designed with a symmetrical relationship between the phase conductors and the grounds provides the cancellation effects that will minimize the CM current in the system. These designs typically have three phase conductors with three ground conductors in the interstices of the phase conductors.

### **Proper Insulation**

Cable insulation also plays a critical role in keeping your VFD system performing reliably. VFD cables should have a thermoset, cross-linked insulation which will provide more protection than less expensive PVC insulation. General Cable uses thermoset, cross-linked insulations in all their VFD cable constructions. Using THHN cable as your inverter motor cable is not recommended. The PVC insulation on THHN cable possesses two undesirable characteristics in VFD applications:

- (1) It is hydroscopic, meaning it can absorb moisture from the air, which drops its dielectric withstand to as low as 55% of its rated voltage.
- (2) It can experience cold-flow, causing the insulation to displace when under pressure, resulting in the reduction of insulation wall thickness.

Furthermore, THHN cable is rated for 600 volts RMS or 850 volts peak, but reflected waves (standing waves) in VFD cables can reach 1300 volts in a run as short as 35 feet. The 1300 volts places a lot of stress on a cable that is rated for 850 volts. When you factor in the decreased insulation strength due to moisture and the decreased wall thickness, you may experience problems.

In addition, PVC insulated cables have a high capacitance associated with them, causing the cable to leak current through the insulation, resulting in false trips. The cables also have a higher charging current associated with them, which requires a drive with more power (and more cost). In order to minimize these problems, choose a cable with thermoset insulation that is rated to handle the peak standing wave voltage.

### **The Right Cable Solution for VFD Applications**

VFD cable offers three key attributes to mitigate the issues that arise in these applications: shielding, robust insulation and symmetrical design. VFD cable is a more expensive alternative to standard power cables, but in today's environment with increased automation, more focus on safety and limited tolerance for downtime, it proves to be a very wise investment.

<sup>1</sup> Bearing fluting is addressed in further detail in the white paper *General Cable VFD Cables, An Overview of Variable Frequency Drive Cables*, November 2013.



# Table of Contents

## VARIABLE FREQUENCY DRIVE

	SPEC NO.	DESCRIPTION	PAGE
<b>CCW®</b>	9600	600 V Power, 3/C VFD and 4/C UL Type MC-HL, XLPE, 90°C, ABS CWCMC	76-77
	9605	600 V Power, 3/C VFD and 4/C UL Type MC-HL, XLPE, 90°C, ABS CWCMC	78-79
	9615	2000 V Power, 3/C VFD UL Type MC-HL, XLPE, 90°C, ABS CWCMC	80-81
	9675	1000 V Power, 3/C VFD CSA Type RA90, HL, XLPE, 90°C	82-83
	9700	2.4 kV Power, Nonshielded, 3/C VFD UL Type MC-HL or MV-90, EPR, 105°C, ABS CWCMC	84-85
	9800	5 kV 133%/8 kV 100% Power, Shielded, 3/C VFD UL Type MC-HL or MV-105, EPR, 105°C, ABS CWCMC	86-87
	9805	5 kV 133%/8 kV 100% Power, Shielded, 3/C VFD UL Type MC-HL or MV-105, EPR, 105°C, ABS CWCMC	88-89
	9815	8 kV 133% Power, Shielded, 3/C VFD UL Type MC-HL or MV-105, EPR, 105°C, ABS CWCMC	90-91
<b>CVTC®</b>	4560	XLPE/PVC, Low-Voltage Power, Al/Polyester + TC Braid Shielded, 1000 V, UL Flexible Motor Supply, 600 V, UL Type TC-ER – Method 4 Color Code w/Green/Yellow Ground	92
	4565	XLPE/PVC, Low-Voltage Power, Al/Polyester/Al TC Braid Shielded, 1000 V, UL Flexible Motor Supply, 600 V, UL Type TC-ER – Method 4 Color Code w/Green/Yellow Ground and Signal Pair	93
	4570	XLPE/PVC, Low-Voltage Power, Dual Copper Tape Shielded, 1000 V, UL Flexible Motor Supply, 600 V, UL Type TC-ER – Method 4 Color Code	94
	4575	XLPE/PVC, Low-Voltage Power, Shielded 2000 V, UL Type TC-ER—Method 4 Color Code	95
	4580	XLPE/PVC, Low-Voltage Power, Copper Tape Shielded 2000 V, UL Type TC-ER—Method 4 Color Code	96

**CCW<sup>®</sup> Armored Power, 3/C VFD and 4/C**

UL Type MC-HL, CSA Type HL, XLPE, 600 V, 90°C, Cable Tray Use, Sunlight-Resistant Direct Burial, UL Marine Shipboard Cable, ABS CWCMC

**Product Construction:**

- Bare annealed copper per ASTM B3
- 10 AWG and smaller are Class B compressed stranding per ASTM B8
- 8 AWG and larger are compact stranding per ASTM B496

**Insulation:**

- Cross-linked Polyethylene (XLPE) insulation per ICEA S-95-658 and UL 44, Listed XHHW-2
- 6 AWG and smaller are color-coded per ICEA Method 1, Table E2
- 4 AWG and larger are black with printed numbers per ICEA Method 4
- Color-coded per CSA C22.2 No. 123 where applicable

**Grounding Conductor(s):**

- Class B stranded bare annealed copper per ASTM B3 and B8
- Where specified, single or three split grounding wires are sized in accordance with NEC Table 250.122

**Cable Assembly:**

- Insulated conductors and grounding wire(s) are cabled together with non-hygroscopic fillers when required
- A binder tape is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL 1569 and UL 2225
- CCW armor conductivity meets the grounding requirements of NEC Article 250

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), black
- Low temperature performance meets ASTM D746 brittleness temperature at or below -40°C
- Meets CSA Low Acid Gas requirements

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- For use as services, feeders and branch circuits for power, lighting, control, and signal circuits in accordance with NEC Articles 330 and 725
- Installed indoors or outdoors, wet or dry locations, directly buried, embedded in concrete, in a raceway, as aerial cable on a messenger, in cable trays, or as exposed runs secured to supports in accordance with NEC Article 330
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- 3-conductor CCW power cables with three grounding wires are recommended for use with pulse-width modulated AC drives
- CCW armor provides an impervious barrier to moisture, gas and liquids
- CCW armor provides EMI shielding performance
- Factory assembled and tested cable for use as an alternative to cable in conduit wiring systems

**Features (cont'd.):**

- Meets cold impact at -40°C
- 90°C continuous operating temperature, wet or dry
- 130°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-95-658/WC70 Standard for Non-Shielded Power Cable, 2 kV or Less
- UL 44 Rubber Insulated Wires and Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable
- CSA C22.2 No. 123 Metal Sheathed Cables
- CSA C22.2 No. 174 Cables and Cable Glands for Use in Hazardous Locations

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1581 (70,000 BTU/hr)
- IEC 60332-3 Cat. A

**Compliances:**

- UL Type MC-HL, XHHW-2, SUN RES, CT USE, DIR BUR, -40°C, UL File # E90496
- UL Listed Marine Shipboard, UL File # E85994
- American Bureau of Shipping (ABS) Listed for CWCMC
- CSA certified<sup>1</sup> Type RA90, XLPE, HL, SR, FT4, and -40°C, CSA File # 7319
- RoHS Compliant

<sup>1</sup> Standard cables are also marked CSA Type RA90, except four (4) conductor cables which require a different color code, which may be special-ordered.

# CCW<sup>®</sup> Armored Power, 3/C VFD and 4/C

UL Type MC-HL, CSA Type HL, XLPE, 600 V, 90°C, Cable Tray Use, Sunlight-Resistant Direct Burial, UL Marine Shipboard Cable, ABS CWCMC

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NO. OF COND.	INSULATION THICKNESS		BARE GROUND (AWG)	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		CROSS-SECTIONAL AREA <sup>1</sup> SQ. IN.	APPROXIMATE NET WEIGHT		90°C AMPACITY @ 30°C AMBIENT <sup>2</sup>
			mils	mm		INCHES	mm	INCHES	mm	mils	mm	INCHES	mm		LBS/1000 FT	kg/1000 m	
9600.01403318	14 (7/W) (2.08 mm <sup>2</sup> )	3	30	0.76	3 x #18	0.33	8.4	0.53	13.5	50	1.27	0.64	16.3	0.33	163	242	15
9600.01404318		4	30	0.76	3 x #18	0.37	9.4	0.58	14.7	50	1.27	0.69	17.5	0.38	226	336	15
9600.01203316	12 (7/W) (3.31 mm <sup>2</sup> )	3	30	0.76	3 x #16	0.37	9.4	0.58	14.7	50	1.27	0.69	17.5	0.38	243	362	20
9600.01204316		4	30	0.76	3 x #16	0.45	11.4	0.67	17.0	50	1.27	0.78	19.8	0.48	291	433	20
9600.01003314	10 (7/W) (5.26 mm <sup>2</sup> )	3	30	0.76	3 x #14	0.41	10.4	0.62	15.7	50	1.27	0.73	18.5	0.42	305	454	30
9600.01004314		4	30	0.76	3 x #14	0.45	11.4	0.67	17.0	50	1.27	0.78	19.8	0.48	354	527	30
9600.00803314	8 (7/W) (8.36 mm <sup>2</sup> )	3	45	1.14	3 x #14	0.50	12.7	0.71	18.0	50	1.27	0.81	20.6	0.52	392	583	55
9600.00804110		4	45	1.14	1 x #10	0.58	14.7	0.80	20.3	50	1.27	0.90	22.9	0.64	473	704	44
9600.00603312	6 (7/W) (13.3 mm <sup>2</sup> )	3	45	1.14	3 x #12	0.58	14.7	0.80	20.3	50	1.27	0.90	22.9	0.64	534	795	75
9600.00604108		4	45	1.14	1 x #8	0.66	16.8	0.89	22.6	50	1.27	0.99	25.1	0.78	641	954	60
9600.00403312	4 (7/W) (21.2 mm <sup>2</sup> )	3	45	1.14	3 x #12	0.68	17.3	0.89	22.6	50	1.27	0.99	25.1	0.78	716	1,066	95
9600.00404108		4	45	1.14	1 x #8	0.77	19.6	0.97	24.6	50	1.27	1.08	27.4	0.93	860	1,280	76
9600.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	45	1.14	3 x #10	0.80	20.3	1.02	25.9	50	1.27	1.13	28.7	1.02	1,013	1,507	130
9600.00204106		4	45	1.14	1 x #6	0.92	23.4	1.15	29.2	50	1.27	1.26	32.0	1.26	1,267	1,885	104
9600.00103310	1 (19/W) (42.4 mm <sup>2</sup> )	3	55	1.40	3 x #10	0.92	23.4	1.15	29.2	50	1.27	1.26	32.0	1.26	1,119	1,666	150
9600.00104106		4	55	1.40	1 x #6	1.04	26.4	1.29	32.8	50	1.27	1.40	35.6	1.56	1,526	2,272	120
9600.11003310	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	55	1.40	3 x #10	1.00	25.4	1.24	31.5	50	1.27	1.34	34.0	1.43	1,496	2,226	170
9600.11004106		4	55	1.40	1 x #6	1.12	28.4	1.37	34.8	50	1.27	1.48	37.6	1.74	1,862	2,771	136
9600.21003310	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	55	1.40	3 x #10	1.09	27.7	1.34	34.0	50	1.27	1.44	36.6	1.65	1,801	2,681	195
9600.21004106		4	55	1.40	1 x #6	1.23	31.2	1.51	38.4	60	1.52	1.64	41.7	2.14	2,351	3,498	156
9600.31003308	3/0 (19/W) (85.0 mm <sup>2</sup> )	3	55	1.40	3 x #8	1.21	30.7	1.47	37.3	60	1.52	1.58	40.1	1.99	2,262	3,367	225
9600.31004104		4	55	1.40	1 x #4	1.36	34.5	1.65	41.9	60	1.52	1.78	45.2	2.52	2,921	4,346	180
9600.41003308	4/0 (19/W) (107 mm <sup>2</sup> )	3	55	1.40	3 x #8	1.33	33.8	1.60	40.6	60	1.52	1.73	43.9	2.38	2,722	4,051	260
9600.41004104		4	55	1.40	1 x #4	1.49	37.8	1.78	45.2	60	1.52	1.91	48.5	2.90	3,491	5,194	208
9600.25003308	250 (37/W) (127 mm <sup>2</sup> )	3	65	1.65	3 x #8	1.48	37.6	1.74	44.2	60	1.52	1.87	47.5	—	3,195	4,755	290
9600.25004104		4	65	1.65	1 x #4	1.64	41.7	1.96	49.8	60	1.52	2.09	53.1	—	4,142	6,164	232
9600.35003307	350 (37/W) (177 mm <sup>2</sup> )	3	65	1.65	3 x #7	1.66	42.2	1.96	49.8	60	1.52	2.09	53.1	—	4,284	6,376	350
9600.35004103		4	65	1.65	1 x #3	1.89	48.0	2.19	55.6	75	1.91	2.35	59.7	—	5,536	8,238	280
9600.50003306	500 (37/W) (253 mm <sup>2</sup> )	3	65	1.65	3 x #6	1.94	49.3	2.28	57.9	75	1.91	2.44	62.0	—	6,035	8,981	430
9600.50004102		4	65	1.65	1 x #2	2.14	54.4	2.49	63.2	75	1.91	2.65	67.3	—	7,704	11,464	344
9600.75003305	750 (61/W) (380 mm <sup>2</sup> )	3	80	2.03	3 x #5	2.37	60.2	2.75	69.9	75	1.91	2.92	74.2	—	8,854	13,176	535
9600.75004101		4	80	2.03	1 x #1	2.61	66.3	3.03	77.0	85	2.16	3.21	81.5	—	11,449	17,037	428
9600.100031110	1000 (61/W) (507 mm <sup>2</sup> )	3	80	2.03	1 x #1/0	2.67	67.8	3.11	79.0	85	2.16	3.30	83.8	—	11,611	17,280	615
9600.100041110		4	80	2.03	1 x #1/0	3.07	78.0	3.63	92.2	85	2.16	3.81	96.8	—	15,377	22,883	492

Dimensions and weights are nominal; subject to industry tolerances.

<sup>1</sup> Cross-sectional area for cable tray fill is in accordance with NEC Section 392.22.

<sup>2</sup> Ampacities in accordance with NEC Article 310 and Table 310.15(B)(16).

Note: Three (3) conductors, 6 AWG and smaller are also marked CSA Type RA90. One (1) AWG and larger are also marked CSA Type RA90.



**CCW<sup>®</sup> Armored Power, 3/C VFD and 4/C**

UL Type MC-HL, XLPE, 600 V, 90°C, Cable Tray Use, Sunlight-Resistant Direct Burial, UL Marine Shipboard Cable, ABS CWCMC, Arctic-Grade

**Product Construction:****Conductor:**

- Bare annealed copper per ASTM B3
- 10 AWG and smaller are Class B compressed stranding per ASTM B8
- 8 AWG and larger are compact stranding per ASTM B496

**Insulation:**

- Cross-linked Polyethylene (XLPE) insulation per ICEA S-95-658 and UL 44, Listed XHHW-2
- 6 AWG and smaller are color-coded per ICEA Method 1, Table E2
- 4 AWG and larger are black with printed numbers per ICEA Method 4
- Color-coded per CSA C22.2 No. 123 where applicable

**Grounding Conductor:**

- Class B stranded bare annealed copper per ASTM B3 and B8
- Where specified, single or three split grounding wires are sized in accordance with NEC Table 250.122

**Cable Assembly:**

- Insulated conductors and grounding wire are cabled together with non-hydroscopic fillers when required
- A binder tape, when required, is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL Standards 1569 and 2225
- CCW armor conductivity meets the grounding requirements of NEC Article 250

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), black
- Low temperature performance meets ASTM D746 brittleness temperature at or below -60°C

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- For use as services, feeders and branch circuits for power, lighting, control, and signal circuits in accordance with NEC Articles 330 and 725
- Installed indoors or outdoors, wet or dry locations, directly buried, embedded in concrete, in a raceway, as aerial cable on a messenger, in cable trays, or as exposed runs secured to supports in accordance with NEC Article 330
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- 3-conductor CCW power cables with three grounding wires are recommended for use with pulse-width modulated AC drives
- CCW armor provides an impervious barrier to moisture, gas and liquids
- CCW armor provides EMI shielding performance
- Factory assembled and tested cable for use as an alternate to cable in conduit wiring systems

**Features (cont'd.):**

- Meets cold bend at -55°C
- 90°C continuous operating temperature, wet or dry
- 130°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-95-658/WC70 Standard for Non-Shielded Power Cable, 2 kV or Less
- UL 44 Rubber Insulated Wires and Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable
- CSA C22.2 No. 123 Metal Sheathed Cables
- CSA C22.2 No. 174 Cables and Cable Glands for Use in Hazardous Locations

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1581 (70,000 BTU/hr)
- IEC 60332-3 Cat. A

**Compliances:**

- UL Type MC-HL, XHHW-2, SUN RES, CT USE, DIR BUR, -40°C, UL File # E90496
- UL Listed Marine Shipboard, UL File # E85994
- American Bureau of Shipping (ABS) Listed for CWCMC
- RoHS Compliant



# CCW<sup>®</sup> Armored Power, 3/C VFD and 4/C

UL Type MC-HL, XLPE, 600 V, 90°C, Cable Tray Use, Sunlight-Resistant  
Direct Burial, UL Marine Shipboard Cable, ABS CWCMC, Arctic-Grade

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NO. OF COND.	INSULATION THICKNESS		BARE GROUND (AWG)	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		CROSS-SECTIONAL AREA <sup>1</sup> SQ. IN.	APPROXIMATE NET WEIGHT		90°C AMPACITY @ 30°C AMBIENT <sup>2</sup>
			mils	mm		INCHES	mm	INCHES	mm	mils	mm	INCHES	mm		LBS/1000 FT	kg/1000 m	
9605.01403318	14 (7/W) (2.08 mm <sup>2</sup> )	3	30	0.76	3 x #18	0.33	8.4	0.53	13.5	50	1.27	0.64	16.3	0.33	163	242	15
9605.01404216		4	30	0.76	2 x #16	0.33	8.4	0.51	13.0	50	1.27	0.62	15.7	0.30	221	330	15
9605.01404318		4	30	0.76	3 x #18	0.37	9.4	0.58	14.7	50	1.27	0.69	17.5	0.38	226	336	15
9605.01203316	12 (7/W) (3.31 mm <sup>2</sup> )	3	30	0.76	3 x #16	0.37	9.4	0.58	14.7	50	1.27	0.69	17.5	0.38	243	362	20
9605.01204316		4	30	0.76	3 x #16	0.45	11.4	0.67	17.0	50	1.27	0.78	19.8	0.48	291	433	20
9605.01003314	10 (7/W) (5.26 mm <sup>2</sup> )	3	30	0.76	3 x #14	0.41	10.4	0.62	15.7	50	1.27	0.73	18.5	0.42	305	454	30
9605.01004314		4	30	0.76	3 x #14	0.45	11.4	0.67	17.0	50	1.27	0.78	19.8	0.48	354	527	30
9605.00803314	8 (7/W) (8.36 mm <sup>2</sup> )	3	45	1.14	3 x #14	0.50	12.7	0.71	18.0	50	1.27	0.81	20.6	0.52	392	583	55
9605.00804110		4	45	1.14	1 x #10	0.58	14.7	0.80	20.3	50	1.27	0.90	22.9	0.64	473	704	44
9605.00804212		4	45	1.14	2 x #12	0.57	14.5	0.77	19.6	50	1.27	0.88	22.4	0.61	491	731	44
9605.00603312	6 (7/W) (13.3 mm <sup>2</sup> )	3	45	1.14	3 x #12	0.58	14.7	0.80	20.3	50	1.27	0.90	22.9	0.64	534	795	75
9605.00604108		4	45	1.14	1 x #8	0.66	16.8	0.89	22.6	50	1.27	0.99	25.1	0.78	641	954	60
9605.00604210		4	45	1.14	2 x #10	0.66	16.8	0.88	22.4	50	1.27	0.99	25.1	0.78	679	1,012	60
9605.00403312	4 (7/W) (21.2 mm <sup>2</sup> )	3	45	1.14	3 x #12	0.68	17.3	0.89	22.6	50	1.27	0.99	25.1	0.78	716	1,066	95
9605.00404108		4	45	1.14	1 x #8	0.77	19.6	0.97	24.6	50	1.27	1.08	27.4	0.93	860	1,280	76
9605.00404210		4	45	1.14	2 x #10	0.76	19.3	1.00	25.4	50	1.27	1.11	28.2	0.97	950	1,415	76
9605.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	45	1.14	3 x #10	0.80	20.3	1.02	25.9	50	1.27	1.13	28.7	1.02	1,013	1,507	130
9605.00204106		4	45	1.14	1 x #6	0.92	23.4	1.15	29.2	50	1.27	1.26	32.0	1.26	1,267	1,885	104
9605.00204208		4	45	1.14	2 x #8	0.89	22.6	1.16	29.5	50	1.27	1.27	32.3	1.27	1,371	2,043	104
9605.00103310	1 (19/W) (42.4 mm <sup>2</sup> )	3	55	1.40	3 x #10	0.92	23.4	1.15	29.2	50	1.27	1.26	32.0	1.26	1,119	1,666	150
9605.00104106		4	55	1.40	1 x #6	1.04	26.4	1.29	32.8	50	1.27	1.40	35.6	1.56	1,526	2,272	120
9605.11003310	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	55	1.40	3 x #10	1.00	25.4	1.24	31.5	50	1.27	1.34	34.0	1.43	1,496	2,226	170
9605.11004106		4	55	1.40	1 x #6	1.12	28.4	1.37	34.8	50	1.27	1.48	37.6	1.74	1,862	2,771	136
9605.21003310	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	55	1.40	3 x #10	1.09	27.7	1.34	34.0	50	1.27	1.44	36.6	1.65	1,801	2,681	195
9605.21004106		4	55	1.40	1 x #6	1.23	31.2	1.51	38.4	60	1.52	1.64	41.7	2.14	2,351	3,498	156
9605.31003308	3/0 (19/W) (85.0 mm <sup>2</sup> )	3	55	1.40	3 x #8	1.21	30.7	1.47	37.3	60	1.52	1.58	40.1	1.99	2,262	3,367	225
9605.31004104		4	55	1.40	1 x #4	1.36	34.5	1.65	41.9	60	1.52	1.78	45.2	2.52	2,921	4,346	180
9605.41003308	4/0 (19/W) (107 mm <sup>2</sup> )	3	55	1.40	3 x #8	1.33	33.8	1.60	40.6	60	1.52	1.73	43.9	2.38	2,722	4,051	260
9605.41004104		4	55	1.40	1 x #4	1.49	37.8	1.78	45.2	60	1.52	1.91	48.5	2.87	3,491	5,194	208
9605.25003308	250 (37/W) (127 mm <sup>2</sup> )	3	65	1.65	3 x #8	1.48	37.6	1.74	44.2	60	1.52	1.87	47.5	2.75	3,195	4,755	290
9605.25004104		4	65	1.65	1 x #4	1.64	41.7	1.96	49.8	60	1.52	2.09	53.1	3.43	4,142	6,164	232
9605.35003307	350 (37/W) (177 mm <sup>2</sup> )	3	65	1.65	3 x #7	1.66	42.2	1.96	49.8	60	1.52	2.09	53.1	3.43	4,284	6,376	350
9605.35003306		3	65	1.65	3 x #6	1.63	41.4	1.95	49.5	60	1.52	2.09	53.1	3.43	4,329	6,443	350
9605.35004103		4	65	1.65	1 x #3	1.89	48.0	2.19	55.6	75	1.91	2.35	59.7	4.34	5,536	8,238	280
9605.50003306	500 (37/W) (253 mm <sup>2</sup> )	3	65	1.65	3 x #6	1.94	49.3	2.28	57.9	75	1.91	2.44	62.0	4.68	6,035	8,981	430
9605.50004102		4	65	1.65	1 x #2	2.14	54.4	2.49	63.2	75	1.91	2.65	67.3	5.52	7,704	11,464	344
9605.75003305	750 (61/W) (380 mm <sup>2</sup> )	3	80	2.03	3 x #5	2.37	60.2	2.75	69.9	75	1.91	2.92	74.2	6.70	8,854	13,176	535
9605.75003304		3	80	2.03	3 x #4	2.32	58.9	2.71	68.8	75	1.91	2.86	72.6	6.42	8,926	13,293	535
9605.75004101		4	80	2.03	1 x #1	2.61	66.3	3.03	77.0	85	2.16	3.21	81.5	8.09	11,449	17,037	428
9605.100031110	1000 (61/W) (507 mm <sup>2</sup> )	3	80	2.03	1 x #1/0	2.67	67.8	3.11	79.0	85	2.16	3.30	83.8	8.55	11,611	17,280	615
9605.100041110		4	80	2.03	1 x #1/0	3.07	78.0	3.63	92.2	85	2.16	3.81	96.8	11.40	15,377	22,883	492

Dimensions and weights are nominal; subject to industry tolerances.  
<sup>1</sup> Cross-sectional area for cable tray fill is in accordance with NEC Section 392.22.  
<sup>2</sup> Ampacities in accordance with NEC Article 310 and Table 310.15(B)(16).





# CCW<sup>®</sup> Armored Power, 3/C VFD

UL Type MC-HL, XLPE, 2000 V, 90°C, Cable Tray Use, Sunlight-Resistant, Direct Burial  
UL Marine Shipboard Cable, ABS CWCMC

**Product Construction:****Conductor:**

- Bare annealed copper per ASTM B3
- 10 AWG and smaller are Class B compressed stranding per ASTM B8
- 8 AWG and larger are compact standing per ASTM B496

**Insulation:**

- Cross-linked Polyethylene (XLPE) insulation, 2000 V thicknesses per ICEA S-95-658
- Color-coded black with printed numbers per ICEA Method 4

**Grounding Conductors:**

- Class B stranded bare annealed copper per ASTM B3 and B8
- Three (3) split grounding wires per specification 9615 exceed the minimum required in NEC Table 250.122

**Cable Assembly:**

- Insulated conductors and grounding wires are cabled together with non-hygroscopic fillers when required
- A binder tape is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL 1569 and UL 2225
- CCW armor conductivity meets the grounding requirements of NEC Article 250

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC) — Black
- Low temperature performance meets ASTM D746 brittleness temperature at or below -40°C

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires is the preferred wiring method for use with AC motors controlled by pulse-width modulated Inverters in VFD applications
- CCW armored cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502 and 503
- For use as services, feeders and branch circuits for power, lighting, control, and signal circuits in accordance with NEC Articles 330 and 725
- Installed indoors or outdoors, wet or dry locations, directly buried, embedded in concrete, in a raceway, as aerial cable on a messenger, in cable trays, or as exposed runs secured to supports in accordance with NEC Article 330
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- 90°C, 2000 V rated XLPE insulation with a dielectric constant less than 3.0 to withstand momentary voltage spikes common in certain VFD applications
- Three (3) oversized, symmetrical grounding wires recommended for use with pulse-width modulated AC drives
- CCW armor provides an impervious barrier to moisture, gas and liquids

**Features (cont'd.):**

- CCW armor provides EMI shielding performance
- Factory assembled and tested cable for use as an alternative to cable in conduit wiring systems
- Meets cold impact at -40°C
- 90°C continuous operating temperature, wet or dry
- 130°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-95-658/WC70 Standard for Non-Shielded Power Cable, 2 kV or Less
- UL 44 Rubber Insulated Wires and Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1581 (70,000 BTU/hr)
- IEC 332-3 Cat. A

**Compliances:**

- UL Type MC-HL, SUN RES, CT USE, DIR BUR, -40°C, UL File # E90496
- UL Listed Marine Shipboard, UL File # E85994
- American Bureau of Shipping (ABS) Listed for CWCMC
- RoHS Compliant



# CCW<sup>®</sup> Armored Power, 3/C VFD

UL Type MC-HL, XLPE, 2000 V, 90°C, Cable Tray Use, Sunlight-Resistant, Direct Burial  
UL Marine Shipboard Cable, ABS CWCMC

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NO. OF COND.	INSULATION THICKNESS		BARE GROUND (AWG)	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		APPROXIMATE NET WEIGHT		90°C AMPACITY @ 30°C AMBIENT <sup>1</sup>
			mils	mm		INCHES	mm	INCHES	mm	mils	mm	INCHES	mm	LBS/1000 FT	kg/1000 m	
9615.01403318	14 (7/W) (2.08 mm <sup>2</sup> )	3	60	1.52	3 x #18	0.44	11.1	0.62	15.2	50	1.27	0.73	17.9	267	397	15
9615.01203316	12 (7/W) (3.31 mm <sup>2</sup> )	3	60	1.52	3 x #16	0.47	11.9	0.66	16.2	50	1.27	0.77	18.9	324	482	20
9615.01003314	10 (7/W) (5.26 mm <sup>2</sup> )	3	60	1.52	3 x #14	0.53	13.3	0.73	17.8	50	1.27	0.84	20.5	400	595	30
9615.00803314	8 (7/W) (8.36 mm <sup>2</sup> )	3	70	1.78	3 x #14	0.65	16.5	0.86	21.1	50	1.27	0.97	23.8	524	780	55
9615.00603312	6 (7/W) (13.3 mm <sup>2</sup> )	3	70	1.78	3 x #12	0.71	18.0	0.96	23.4	50	1.27	1.07	26.1	697	1,037	75
9615.00403312	4 (7/W) (21.2 mm <sup>2</sup> )	3	70	1.78	3 x #12	0.81	20.6	1.09	26.6	50	1.27	1.23	30.1	1,000	1,488	95
9615.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	70	1.78	3 x #10	0.94	23.9	1.25	30.6	50	1.27	1.36	33.3	1,285	1,912	130
9615.00103310	1 (19/W) (42.4 mm <sup>2</sup> )	3	90	2.29	3 x #10	1.13	28.7	1.48	36.1	50	1.27	1.59	38.8	1,595	2,374	150
9615.11003310	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	90	2.29	3 x #10	1.21	30.6	1.55	38.0	60	1.52	1.68	41.2	1,930	2,872	170
9615.21003306	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	90	2.29	3 x #6	1.30	32.9	1.68	41.0	60	1.52	1.81	44.2	2,507	3,731	195
9615.41003304	4/0 (19/W) (107 mm <sup>2</sup> )	3	90	2.29	3 x #4	1.53	38.7	1.91	46.7	60	1.52	2.04	49.9	3,590	5,342	260
9615.25003304	250 (37/W) (127 mm <sup>2</sup> )	3	105	2.67	3 x #4	1.71	43.4	2.12	51.8	60	1.52	2.25	55.1	4,150	6,176	290
9615.35003302	350 (37/W) (177 mm <sup>2</sup> )	3	105	2.67	3 x #2	1.93	48.9	2.41	58.9	75	1.91	2.57	62.8	5,214	7,759	350
9615.50003301	500 (37/W) (253 mm <sup>2</sup> )	3	105	2.67	3 x #1	2.20	55.8	2.68	65.5	75	1.91	2.84	69.5	6,977	10,382	430

Dimensions and weights are nominal; subject to industry tolerances.  
<sup>1</sup> Ampacities in accordance with NEC Article 310 and Table 310.15(B)(16).



# CCW<sup>®</sup> Armored Power, 1000 V, 3/C VFD

CSA Type RA90, XLPE, 1000 V, 90°C, Cable Tray Use, Sunlight-Resistant Direct Burial, FT4, -40°C, AG14, HL



## Product Construction:

### Conductor:

- Bare annealed copper per ASTM B3
- Sizes 10 AWG and smaller are Class B compressed stranding per ASTM B8
- Sizes 8 AWG and larger are compact stranding per ASTM B496

### Insulation:

- Cross-linked Polyethylene (XLPE) insulation rated 1000 Volts, RW90 per CSA C22.2 No. 38
- Sizes 2 AWG and smaller utilize a single color insulation: black, red and blue
- Sizes 1 AWG and larger utilize black insulation with printed number/color, 1-black, 2-red, 3-blue

### Bonding/Grounding Conductors:

- Class B stranded bare annealed copper per ASTM B3 and B8
- Three (3) symmetrical grounding wires are sized in accordance with CEC Table 16

### Cable Assembly:

- Three symmetrical grounding wires are cabled within the interstices of the phase conductors
- Non-hygroscopic fillers when required
- A binder tape is applied over the cabled core

### CCW Armor:

- Impervious, continuously welded and corrugated aluminum alloy sheath per C22.2 No. 123

### Jacket:

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), black
- Meets CSA Low Gas Emission requirements, AG14

### Applications:

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use in industrial and commercial installations including hazardous locations in accordance with the CEC
- Can be installed in wet or dry locations, indoors or outdoors, in cable trays, in a raceway, or direct buried in accordance with the CEC

### Features:

- 90°C, 1000 V wet or dry XLPE insulation and three (3) symmetrical grounding wires, recommended for use with pulse-width modulated AC drives
- XLPE insulation has a dielectric constant less than 3.0 to withstand momentary voltage spikes common with VFD applications

### Features (cont'd.):

- CCW armor provides an impervious barrier to moisture, gas and liquids
- CCW armor provides EMI shielding performance
- Factory assembled and tested cable for use as an alternative to cable in conduit wiring systems
- Meets cold impact at -40°C
- 90°C continuous operating temperature, wet or dry
- 130°C emergency rating
- 250°C short circuit rating

### Specifications:

#### Design Adherence:

- CSA C22.2 No. 38 Thermoset-Insulated Wires and Cables
- CSA C22.2 No. 123 Metal Sheathed Cables
- CSA C22.2 No. 174 Cables and Cable Glands for Use in Hazardous Locations

#### Flame Tests:

- CSA FT4
- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- IEEE 1202 (70,000 BTU/hr)

#### Compliances:

- CSA Certified Type RA90, XLPE, HL, SR, FT4, AG14 and -40°C, CSA File # 7319
- RoHS Compliant

# CCW<sup>®</sup> Armored Power, 1000 V, 3/C VFD

CSA Type RA90, XLPE, 1000 V, 90°C, Cable Tray Use, Sunlight-Resistant  
Direct Burial, FT4, -40°C, AG14, HL

CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NO. OF COND.	INSULATION THICKNESS		BARE GROUND COND. (AWG)	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		APPROXIMATE NET WEIGHT		MIN. BEND RADIUS <sup>1</sup>		90°C AMPACITY @ 30°C AMBIENT <sup>2</sup>
			mils	mm		INCHES	mm	INCHES	mm	mils	mm	INCHES	mm	LBS/1000 FT	kg/1000 m	INCHES	mm	
9675.01203318	12 (7/W) (3.31 mm <sup>2</sup> )	3	45	1.14	3 x #18	0.40	10.2	0.60	15.3	50	1.27	0.70	17.8	249	370	7.0	178	30
9675.01003316	10 (7/W) (5.26 mm <sup>2</sup> )	3	45	1.14	3 x #16	0.45	11.5	0.63	16.1	50	1.27	0.73	18.6	299	445	7.3	185	40
9675.00803314	8 (7/W) (8.36 mm <sup>2</sup> )	3	45	1.14	3 x #14	0.50	12.7	0.76	19.2	50	1.27	0.86	21.9	417	620	8.6	218	55
9675.00603312	6 (7/W) (13.3 mm <sup>2</sup> )	3	60	1.52	3 x #12	0.64	16.3	0.91	23.2	50	1.27	1.02	26.0	601	895	12.2	311	75
9675.00403312	4 (7/W) (21.2 mm <sup>2</sup> )	3	60	1.52	3 x #12	0.74	18.7	0.98	24.8	50	1.27	1.08	27.4	763	1,135	12.9	329	95
9675.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	60	1.52	3 x #10	0.86	21.8	1.18	29.9	50	1.27	1.28	32.5	1,122	1,670	15.4	390	130
9675.00103310	1 (19/W) (42.4 mm <sup>2</sup> )	3	80	2.03	3 x #10	1.01	25.7	1.36	34.6	50	1.27	1.46	37.1	1,404	2,090	17.5	445	145
9675.11003310	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	80	2.03	3 x #10	1.09	27.8	1.42	36.0	50	1.27	1.52	38.6	1,623	2,415	18.2	462	170
9675.21003310	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	80	2.03	3 x #10	1.18	30.0	1.56	39.6	50	1.27	1.66	42.2	2,043	3,040	20.0	506	195
9675.41003308	4/0 (19/W) (107 mm <sup>2</sup> )	3	80	2.03	3 x #8	1.40	35.5	1.75	44.4	50	1.27	1.85	47.0	2,950	4,390	22.2	564	260
9675.25003308	250 (37/W) (127 mm <sup>2</sup> )	3	90	2.29	3 x #8	1.49	37.8	1.90	48.2	50	1.27	2.01	51.1	3,380	5,030	24.1	612	290
9675.35003308	350 (37/W) (177 mm <sup>2</sup> )	3	90	2.29	3 x #8	1.74	44.3	2.22	56.4	50	1.27	2.33	59.2	4,465	6,645	27.9	710	350
9675.50003306	500 (37/W) (253 mm <sup>2</sup> )	3	90	2.29	3 x #6	2.00	50.9	2.48	63.0	50	1.27	2.59	65.8	6,152	9,155	31.0	789	430

Dimensions and weights are nominal; subject to industry tolerances.  
<sup>1</sup> Minimum bend radius per Canadian Electrical Code, Part I, Section 12-712.  
<sup>2</sup> Ampacity per Table #2, Canadian Electrical Code.



**CCW<sup>®</sup> Armored Power, 2.4 kV, Nonshielded, 3/C VFD**UL Type MC-HL or MV-90, EPR, 105°C, Cable Tray Use, Sunlight-Resistant  
Direct Burial, ABS CWCMC**Product Construction:****Conductor:**

- Bare annealed copper per ASTM B3
- Compact stranding per ASTM B496

**Extruded Strand Shield (ESS):**

- Extruded thermoset semi-conductor stress control layer over conductor per ICEA S-96-659 and UL 1072

**Insulation:**

- 90 mils Ethylene Propylene Rubber (EPR) insulation per ICEA S-96-659 and UL 1072
- Insulation is printed 1-black, 2-red and 3-blue for phase identification

**Grounding Conductors:**

- Three (3) split Class B stranded bare annealed copper grounding conductors
- Sized in accordance with UL 1072 and NEC Table 250.122

**Cable Assembly:**

- Insulated and grounding conductors are cabled together with non-hygroscopic fillers when required
- Binder tape is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL 1072 and UL 1569
- CCW armor conductivity meets the grounding requirements of NEC Article 250

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), yellow
- Low temperature performance meets ASTM D746 brittleness temperature at or below -40°C

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored medium-voltage power cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use on feeders and branch circuits in industrial power distribution systems per NEC Articles 328 and 330
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- Installed on metal racks, troughs, in raceways, in cable trays or secured to supports spaced not more than six feet apart
- Installed in both exposed and concealed work, wet or dry locations, directly buried or embedded in concrete
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- CCW armor provides an impervious barrier to moisture, gas and liquids and meets the grounding requirements of UL 1072 and the NEC
- Factory assembled and tested cable for use as an alternative to cable in conduit wiring systems

**Features (cont'd.):**

- General Cable's EPR insulation system has outstanding corona resistance and high dielectric strength, and it provides electrical stability under stress
- Cable meets cold impact at -40°C
- 90°C continuous operating temperature, wet or dry
- 140°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-96-659/WC71 Standard for Nonshielded Cables Rated 2001 – 5000 Volts
- UL 1072 Medium-Voltage Power Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1072
- IEC 60332-3 Category A

**Compliances:**

- UL Type MV-90 or MC-HL, SUN RES, CT USE, DIR BUR, -40°C, FT4, UL File # E90501
- UL Listed Marine Shipboard, UL File # E85994
- American Bureau of Shipping (ABS) Listed for CWCMC

# CCW<sup>®</sup> Armored Power, 2.4 kV, Nonshielded, 3/C VFD

UL Type MC-HL or MV-90, EPR, 105°C, Cable Tray Use, Sunlight-Resistant  
Direct Burial, ABS CWCMC

CATALOG NUMBER	COND. SIZE	NO. OF COND.	INSULATION THICKNESS		NOMINAL O.D. OVER INSULATION		BARE GROUND	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		APPROXIMATE NET WEIGHT		AMPACITY	
	AWG (kcmil)		mils	mm	INCHES	mm	AWG	INCHES	mm	INCHES	mm	mils	mm	INCHES	mm	LBS/1000 FT	kg/1000 m	IN AIR <sup>1</sup>	DIRECT BURIAL <sup>2</sup>
<b>3/C WITH GROUND MC-HL OR MV-90, 90 MILS EPR, 2.4 KV, YELLOW JACKET</b>																			
9700.00803312	8 (7/W) (8.36 mm <sup>2</sup> )	3	90	2.3	0.36	9.1	3 x #12	0.77	19.6	0.97	24.6	50	1.27	1.08	27.4	570	848	59	85
9700.00603310	6 (7/W) (13.3 mm <sup>2</sup> )	3	90	2.3	0.38	9.6	3 x #10	0.85	21.6	1.06	26.9	50	1.27	1.17	29.7	745	1,109	79	105
9700.00403310	4 (7/W) (21.2 mm <sup>2</sup> )	3	90	2.3	0.43	10.8	3 x #10	0.97	24.6	1.19	30.2	50	1.27	1.30	33.0	965	1,436	105	135
9700.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	90	2.3	0.48	12.1	3 x #10	1.10	27.9	1.34	34.0	50	1.27	1.45	36.8	1,275	1,897	140	180
9700.00103308	1 (19/W) (42.4 mm <sup>2</sup> )	3	90	2.3	0.52	13.1	3 x #8	1.16	29.5	1.42	36.1	50	1.27	1.53	38.9	1,525	2,269	160	200
9700.11003308	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	90	2.3	0.55	13.9	3 x #8	1.23	31.2	1.51	38.4	60	1.52	1.65	41.9	1,840	2,738	185	230
9700.21003308	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	90	2.3	0.59	14.9	3 x #8	1.33	33.8	1.60	40.6	60	1.52	1.73	43.9	2,165	3,222	215	260
9700.41003307	4/0 (19/W) (107 mm <sup>2</sup> )	3	90	2.3	0.69	17.4	3 x #7	1.53	38.9	1.83	46.5	60	1.52	1.96	49.8	3,080	4,584	285	335
9700.25003307	250 (37/W) (127 mm <sup>2</sup> )	3	90	2.3	0.74	18.7	3 x #7	1.64	41.7	1.96	49.8	60	1.52	2.09	53.1	3,475	5,171	320	365
9700.35003306	350 (37/W) (177 mm <sup>2</sup> )	3	90	2.3	0.83	21.0	3 x #6	1.86	47.2	2.19	55.6	60	1.52	2.32	58.9	4,710	7,009	395	440
9700.50003305	500 (37/W) (253 mm <sup>2</sup> )	3	90	2.3	0.95	24.0	3 x #5	2.10	53.3	2.45	62.2	75	1.91	2.61	66.3	6,410	9,539	485	530
9700.75003304	750 (61/W) (380 mm <sup>2</sup> )	3	90	2.3	1.12	28.3	3 x #4	2.51	63.8	2.93	74.4	75	1.91	3.10	78.7	9,225	13,728	615	650
9700.10003304	1000 (61/W) (507 mm <sup>2</sup> )	3	90	2.3	1.27	32.2	3 x #4	2.90	73.7	3.41	86.6	80	2.03	3.59	91.2	12,080	17,977	705	730

Dimensions and weights are nominal, subject to industry tolerances.

<sup>1</sup> In-air ampacities are per NEC Table 310.60(C)(71) for three insulated copper conductors rated 90°C, cabled with an overall covering and isolated in air at 40°C ambient temperature.

<sup>2</sup> Direct burial ampacities are per NEC Table 310.60(C)(83) for three insulated copper conductors rated 90°C, cabled within an overall covering and directly buried in earth at 20°C ambient earth temperature.



**CCW<sup>®</sup> Armored Power, 5 kV 133%/8 kV 100%, Shielded, 3/C VFD**

UL Type MC-HL or MV-105, CSA Type HL, EPR, 105°C, Cable Tray Use, Sunlight-Resistant Direct Burial, ABS CWCMC

**Product Construction:****Conductor:**

- Bare annealed copper per ASTM B3
- Compact stranding per ASTM B496

**Extruded Strand Shield (ESS):**

- Extruded thermoset semi-conductor stress control layer over the conductor per ICEA S-93-639 and UL 1072

**Insulation:**

- 115 mils Ethylene Propylene Rubber (EPR) insulation per ICEA S-93-639 and UL 1072

**Extruded Insulation Shield (EIS):**

- Thermoset semi-conducting polymeric layer, free stripping from the insulation per ICEA S-93-639 and UL 1072

**Shield:**

- 5 mil annealed bare copper tape with 25% overlap

**Phase Identification:**

- Color-coded polymeric identification tape laid under the shield — black, red and blue

**Grounding Conductors:**

- Three (3) split Class B stranded bare annealed copper grounding conductors
- Sized in accordance with UL 1072 and NEC Article 250

**Cable Assembly:**

- Insulated and grounding conductors are cabled together with non-hygroscopic fillers when required
- Binder tape is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL 1072 and UL 1569
- CCW armor conductivity meets the grounding requirements of NEC Article 250

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), yellow
- Low temperature performance meets ASTM D746 brittleness temperature at or below -40°C

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored medium-voltage power cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use on feeders and branch circuits in industrial power distribution systems per NEC Articles 328 and 330
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- Installed on metal racks, troughs, in raceways, in cable trays or secured to supports spaced not more than six feet apart
- Installed in both exposed and concealed work, wet or dry locations, directly buried or embedded in concrete
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- CCW armor provides an impervious barrier to moisture, gas and liquids and meets the grounding requirements of UL 1072 and the NEC

**Features (cont'd.):**

- Triple Extrusion: The strand shield, EPR insulation and insulation shield are all extruded in one operation
- General Cable's EPR insulation system has outstanding corona resistance and high dielectric strength, and it provides electrical stability under stress
- Cable meets cold impact at -40°C
- 105°C continuous operating temperature, wet or dry
- 140°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-93-639/WC74, 5-46 kV Shielded Power Cable
- AEIC CS8 Specification for Shielded Power Cable, 5-46 kV
- UL 1072 Medium-Voltage Power Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable
- CSA 68.10

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1072
- IEC 60332-3 Category A

**Compliances:**

- UL Type MV-105 or MC-HL, SUN RES, CT USE, DIR BUR, -40°C, FT4, UL File # E90501
- UL Listed Marine Shipboard, UL File # E85994
- CSA Type HL, SR, FT4, -40°C, CSA File # 27161
- American Bureau of Shipping (ABS) Listed for CWCMC



**CCW® Armored Power, 5 kV 133%/8 kV 100%, Shielded, 3/C VFD**  
UL Type MC-HL or MV-105, CSA Type HL, EPR, 105°C, Cable Tray Use, Sunlight-Resistant Direct Burial, ABS CWCMC

CATALOG NUMBER	COND. SIZE	NO. OF COND.	INSULATION THICKNESS		NOMINAL O.D. OVER INSULATION		BARE GROUND	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		APPROXIMATE NET WEIGHT		5 kV <sup>3</sup> AMPACITY	
	AWG (kcmil)		mils	mm	INCHES	mm	AWG	INCHES	mm	INCHES	mm	mils	mm	INCHES	mm	LBS/1000 FT	kg/1000 m	IN AIR <sup>1</sup>	DIRECT BURIAL <sup>2</sup>
<b>3/C WITH GROUND MC-HL OR MV-105, 115 MILS EPR, 5 kV 133% AND 8 kV 100% INSULATION LEVEL</b>																			
9800.00603310	6 (7/W) (13.3 mm <sup>2</sup> )	3	115	2.9	0.43	10.9	3 x #10	1.15	29.2	1.37	34.8	50	1.27	1.48	37.6	1,121	1,668	88	115
9800.00403310	4 (7/W) (21.2 mm <sup>2</sup> )	3	115	2.9	0.48	12.2	3 x #10	1.24	31.5	1.51	38.4	60	1.52	1.65	41.9	1,418	2,110	115	150
9800.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	115	2.9	0.53	13.5	3 x #10	1.37	34.8	1.64	41.7	60	1.52	1.78	45.2	1,731	2,576	154	190
9800.00103308	1 (19/W) (42.4 mm <sup>2</sup> )	3	115	2.9	0.57	14.5	3 x #8	1.47	37.3	1.69	42.9	60	1.52	1.82	46.2	1,978	2,944	180	215
9800.11003308	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	115	2.9	0.60	15.2	3 x #8	1.56	39.6	1.78	45.2	60	1.52	1.91	48.5	2,259	3,362	205	245
9800.21003308	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	115	2.9	0.64	16.3	3 x #8	1.61	40.9	1.92	48.8	60	1.52	2.05	52.1	2,626	3,908	240	280
9800.41003307	4/0 (19/W) (107 mm <sup>2</sup> )	3	115	2.9	0.74	18.8	3 x #7	1.82	46.2	2.15	54.6	60	1.52	2.28	57.9	3,650	5,432	320	360
9800.25003306	250 (37/W) (127 mm <sup>2</sup> )	3	115	2.9	0.80	20.3	3 x #6	2.01	51.1	2.23	56.6	60	1.52	2.36	59.9	4,060	6,042	355	395
9800.35003306	350 (37/W) (177 mm <sup>2</sup> )	3	115	2.9	0.89	22.6	3 x #6	2.10	53.3	2.45	62.2	75	1.91	2.61	66.3	5,045	7,508	440	475
9800.50003305	500 (37/W) (253 mm <sup>2</sup> )	3	115	2.9	1.01	25.7	3 x #5	2.39	60.7	2.75	69.9	75	1.91	2.92	74.2	7,137	10,621	545	570
9800.75003304	750 (61/W) (380 mm <sup>2</sup> )	3	115	2.9	1.19	30.2	3 x #4	3.07	78.0	3.32	84.3	85	2.16	3.50	88.9	10,268	15,280	685	700
9800.10003304	1000 (61/W) (507 mm <sup>2</sup> )	3	115	2.9	1.34	34.0	3 x #4	3.43	87.1	3.76	95.5	85	2.16	3.94	100.1	13,051	19,422	790	785

Dimensions and weights are nominal; subject to industry tolerances.

<sup>1</sup> In-air ampacities are per NEC Table 310.60(C)(71) for three insulated copper conductors rated 105°C, cabled with an overall covering and isolated in air at 40°C ambient temperature.

<sup>2</sup> Direct burial ampacities are per NEC Table 310.60(C)(83) for three insulated copper conductors rated 105°C, cabled within an overall covering and directly buried in earth at 20°C ambient earth temperature.

<sup>3</sup> For 8 kV ampacities, refer to NEC Tables 310.60(C)(71) and 310.60(C)(83) for cables listed 5001-35,000 volts.



**CCW® Armored Power, 5 kV 133%/8 kV 100%, Shielded, 3/C VFD**

UL Type MC-HL or MV-105, CSA Type HL, EPR, 105°C, Cable Tray Use

Sunlight-Resistant, Direct Burial, UL Marine Shipboard Cable, ABS CWCMC, Arctic-Grade

**Product Construction:****Conductor:**

- Bare annealed copper per ASTM B3
- Compact stranding per ASTM B496

**Extruded Strand Shield (ESS):**

- Extruded thermoset semi-conductor stress control layer over the conductor per ICEA S-93-639 and UL 1072

**Insulation:**

- 115 mils Ethylene Propylene Rubber (EPR) insulation per ICEA S-93-639 and UL 1072

**Extruded Insulation Shield (EIS):**

- Thermoset semi-conducting polymeric layer, free stripping from the insulation per ICEA S-93-639 and UL 1072

**Shield:**

- 5 mil annealed bare copper tape with 25% overlap

**Phase Identification:**

- Color-coded polymeric identification tape laid under the shield – black, red and blue

**Grounding Conductors:**

- Three (2) split Class B stranded bare annealed copper grounding conductors
- Sized in accordance with UL 1072 and NEC Article 250

**Cable Assembly:**

- Insulated and grounding conductors are cabled together with non-hydroscopic fillers when required
- Binder tape is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL Standards 1569 and 2225
- CCW armor conductivity meets the grounding requirements of NEC Article 250

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), black
- Low temperature performance meets ASTM D746 brittleness temperature at or below -60°C

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored medium-voltage power cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use on feeders and branch circuits for power distribution systems per NEC Articles 328 and 330
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- Installed on metal racks, troughs, in raceways, in cable trays or secured to supports spaced not more than six feet apart
- Installed in both exposed and concealed work, wet or dry locations, directly buried or embedded in concrete
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- CCW armor provides an impervious barrier to moisture, gas and liquids and meets grounding requirements of UL 1072 and the NEC

**Features (cont'd.):**

- Triple Extrusion: The strand shield, EPR insulation and insulation shield are all extruded in one operation
- General Cable's EPR insulation system has outstanding corona resistance and high dielectric strength, and it provides electrical stability under stress
- Meets cold bend at -55°C
- 105°C continuous operating temperature, wet or dry
- 140°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-93-639/WC74, 5-46 kV Shielded Power Cables
- AEIC CS8 Specification for Shielded Power Cable, 5 – 46 kV
- UL 1072 Medium-Voltage Power Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable
- CSA C68.10

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1581 (70,000 BTU/hr)
- IEC 60332-3 Cat. A

**Compliances:**

- UL Type MV-105 or UL Type MC-HL, SUN RES, CT USE, DIR BUR, -40°C, FT4, UL File # E90501
- UL Listed Marine Shipboard, UL File # E85994
- CSA Type HL, SR, FT4, -40°C, CSA File # 27161
- American Bureau of Shipping (ABS) Listed for CWCMC

# CCW<sup>®</sup> Armored Power, 5 kV 133%/8 kV 100%, Shielded, 3/C VFD

UL Type MC-HL or MV-105, CSA Type HL, EPR, 105°C, Cable Tray Use  
Sunlight-Resistant, Direct Burial, UL Marine Shipboard Cable, ABS CWCMC, Arctic-Grade



CATALOG NUMBER	COND. SIZE (AWG/kcmil)	NO. OF COND.	INSULATION THICKNESS		NOMINAL O.D. OVER INSULATION		BARE GROUND (AWG)	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		APPROXIMATE NET WEIGHT		5 kV <sup>3</sup> AMPACITY		
			mils	mm	INCHES	mm		INCHES	mm	INCHES	mm	INCHES	mm	INCHES	mm	LBS/1000 FT	kg/1000 m	IN AIR <sup>1</sup>	DIRECT BURIAL <sup>2</sup>	
<b>3/C WITH GROUND MC-HL OR MV-105, 115 MILS EPR, 5 kV 133% AND 8 kV 100% INSULATION LEVEL</b>																				
9805.00603310	6 (7/W) (13.3 mm <sup>2</sup> )	3	115	2.9	0.43	10.9	3 x #10	1.15	29.2	1.37	34.8	50	1.27	1.48	37.6	1,121	1,668	88	115	
9805.00403310	4 (7/W) (21.2 mm <sup>2</sup> )	3	115	2.9	0.48	12.2	3 x #10	1.24	31.5	1.51	38.4	60	1.52	1.65	41.9	1,418	2,110	115	150	
9805.00203310	3 (7/W) (33.6 mm <sup>2</sup> )	3	115	2.9	0.53	13.5	3 x #10	1.37	34.8	1.64	41.7	60	1.52	1.78	45.2	1,731	2,576	154	190	
9805.00103308	1 (19/W) (42.4 mm <sup>2</sup> )	3	115	2.9	0.57	14.5	3 x #8	1.47	37.3	1.69	42.9	60	1.52	1.82	46.2	1,978	2,944	180	215	
9805.11003308	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	115	2.9	0.60	15.2	3 x #8	1.56	39.6	1.78	45.2	60	1.52	1.91	48.5	2,259	3,362	205	245	
9805.21003308	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	115	2.9	0.64	16.3	3 x #8	1.61	40.9	1.92	48.8	60	1.52	2.05	52.1	2,626	3,908	240	280	
9805.41003307	4/0 (19/W) (107 mm <sup>2</sup> )	3	115	2.9	0.74	18.8	3 x #7	1.82	46.2	2.15	54.6	60	1.52	2.28	57.9	3,650	5,432	320	360	
9805.25003306	250 (37/W) (127 mm <sup>2</sup> )	3	115	2.9	0.80	20.3	3 x #6	2.01	51.1	2.23	56.6	60	1.52	2.36	59.9	4,060	6,042	355	395	
9805.35003306	350 (37/W) (177 mm <sup>2</sup> )	3	115	2.9	0.89	22.6	3 x #6	2.10	53.3	2.45	62.2	75	1.91	2.61	66.3	5,045	7,508	440	475	
9805.50003305	500 (37/W) (253 mm <sup>2</sup> )	3	115	2.9	1.01	25.7	3 x #5	2.39	60.7	2.75	69.9	75	1.91	2.92	74.2	7,137	10,621	545	570	
9805.75003304	750 (61/W) (380 mm <sup>2</sup> )	3	115	2.9	1.19	30.2	3 x #4	3.07	78.0	3.32	84.3	85	2.16	3.50	88.9	10,268	15,280	685	700	
9805.10003304	1000 (61/W) (507 mm <sup>2</sup> )	3	115	2.9	1.34	34.0	3 x #4	3.43	87.1	3.76	95.5	85	2.16	3.94	100.1	13,051	19,422	790	785	

Dimensions and weights are nominal; subject to industry tolerances.  
<sup>1</sup> In-air ampacities are per NEC Table 310.60(C)(71) for three insulated copper conductors rated 105°C, cabled with an overall covering and isolated in air at 40°C ambient temperature.  
<sup>2</sup> Direct burial ampacities are per NEC Table 310.60(C)(83) for three insulated copper conductors rated 105°C, cabled within an overall covering and directly buried in earth at 20°C ambient earth temperature.  
<sup>3</sup> For 8 kV ampacities, refer to NEC Tables 310.60(C)(71) and 310.60(C)(83) for cables listed 5,001-35,000 volts.



**CCW<sup>®</sup> Armored Power, 8 kV 133%, Shielded, 3/C VFD**

UL Type MC-HL or MV-105, CSA Type HL, EPR, 105°C, Cable Tray Use, Sunlight-Resistant Direct Burial, ABS CWCMC

**Product Construction:****Conductor:**

- Bare annealed copper per ASTM B3
- Compact stranding per ASTM B496

**Extruded Strand Shield (ESS):**

- Extruded thermoset semi-conductor stress control layer over the conductor per ICEA S-93-639 and UL 1072

**Insulation:**

- 140 mils Ethylene Propylene Rubber (EPR) insulation per ICEA S-93-639 and UL 1072

**Extruded Insulation Shield (EIS):**

- Thermoset semi-conducting polymeric layer, free stripping from the insulation per ICEA S-93-639 and UL 1072

**Shield:**

- 5 mil annealed bare copper tape with 25% overlap

**Phase Identification:**

- Color-coded polymeric identification tape laid under the shield - black, red and blue

**Grounding Conductors:**

- Three (3) split Class B stranded bare annealed copper grounding conductors
- Sized in accordance with UL 1072 and NEC Article 250

**Cable Assembly:**

- Insulated and grounding conductors are cabled together with non-hygroscopic fillers when required
- Binder tape is applied over the cabled core

**CCW Armor:**

- Impervious, continuously welded and corrugated aluminum alloy sheath per UL 1072 and UL 1569
- CCW armor conductivity meets the grounding requirements of the NEC

**Jacket:**

- Flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC), yellow
- Low temperature performance meets ASTM D746 brittleness temperature at or below -40°C

**Applications:**

- Variable Frequency Drives: 3-conductor CCW armored cables with three (3) symmetrical grounding wires are the preferred wiring method for use with AC motors controlled by pulse-width modulated inverters in VFD applications
- CCW armored medium-voltage power cables offer an economical, rugged and reliable alternative to labor-intensive cable in conduit wiring methods
- For use on feeders and branch circuits in industrial power distribution systems per NEC Articles 328 and 330
- For use in Class I, II and III, Divisions 1 and 2; and Class I, Zones 1 and 2 hazardous locations per NEC Articles 501, 502, 503 and 505
- Installed on metal racks, troughs, in raceways, in cable trays or secured to supports spaced not more than six feet apart
- Installed in both exposed and concealed work, wet or dry locations, directly buried or embedded in concrete
- Recognized for use on fixed or floating offshore petroleum facilities as recommended by the American Petroleum Institute

**Features:**

- CCW armor provides an impervious barrier to moisture, gas and liquids and meets the grounding requirements of UL 1072 and the NEC

**Features (cont'd.):**

- Triple Extrusion: The strand shield, EPR insulation and insulation shield are all extruded in one operation
- General Cable's EPR insulation system has outstanding corona resistance and high dielectric strength, and it provides electrical stability under stress
- Cable meets cold impact at -40°C
- 105°C continuous operating temperature, wet or dry
- 140°C emergency rating
- 250°C short circuit rating

**Specifications:****Design Adherence:**

- ICEA S-93-639/WC74, 5-46 kV Shielded Power Cable
- AEIC CS8 Specification for Shielded Power Cable, 5-46 kV
- UL 1072 Medium-Voltage Power Cables
- UL 1569 Metal Clad Cables
- UL 2225 Cables and Cable Fittings for Use in Hazardous Locations
- UL 1309 Marine Shipboard Cable
- CSA 68.10

**Flame Tests:**

- ICEA T-29-520 (210,000 BTU/hr)
- IEEE 383 (70,000 BTU/hr)
- CSA FT4
- IEEE 1202 (70,000 BTU/hr)
- UL 1072
- IEC 60332-3 Category A

**Compliances:**

- UL Type MV-105 or MC-HL, SUN RES, CT USE, DIR BUR, -40°C, FT4, UL File # E90501
- UL Listed Marine Shipboard, UL File # E85994
- CSA Type HL, SR, FT4, -40°C, CSA File # 27161
- American Bureau of Shipping (ABS) Listed for CWCMC

**CCW® Armored Power, 8 kV 133%, Shielded, 3/C VFD**  
 UL Type MC-HL or MV-105, CSA Type HL, EPR, 105°C, Cable Tray Use, Sunlight-Resistant  
 Direct Burial, ABS CWCMC

CATALOG NUMBER	COND. SIZE	NO. OF COND.	INSULATION THICKNESS		NOMINAL O.D. OVER INSULATION		BARE GROUND	NOMINAL CORE O.D.		NOMINAL ARMOR O.D.		JACKET THICKNESS		NOMINAL OVERALL O.D.		APPROXIMATE NET WEIGHT		AMPACITY	
	AWG (kcmil)		mils	mm	INCHES	mm	AWG	INCHES	mm	INCHES	mm	mils	mm	INCHES	mm	LBS/1000 FT	kg/1000 m	IN AIR <sup>1</sup>	DIRECT BURIAL <sup>2</sup>
<b>3/C WITH GROUND MC-HL OR MV-105, 140 MILS EPR, 8 kV 133% INSULATION LEVEL</b>																			
9815.00603310	6 (7/W) (13.3 mm <sup>2</sup> )	3	140	3.6	0.48	12.2	3 x #10	1.20	30.5	1.60	40.6	60	1.52	1.73	43.9	1,350	2,009	105	120
9815.00403310	4 (7/W) (21.2 mm <sup>2</sup> )	3	140	3.6	0.53	13.5	3 x #10	1.29	32.8	1.70	43.2	60	1.52	1.83	46.5	1,600	2,381	135	155
9815.00203310	2 (7/W) (33.6 mm <sup>2</sup> )	3	140	3.6	0.58	14.7	3 x #10	1.42	36.1	1.85	47.0	60	1.52	1.98	50.3	2,000	2,976	185	200
9815.00103308	1 (19/W) (42.4 mm <sup>2</sup> )	3	140	3.6	0.62	15.7	3 x #8	1.52	38.6	1.93	49.0	60	1.52	2.06	52.3	2,275	3,386	210	225
9815.11003308	1/0 (19/W) (53.5 mm <sup>2</sup> )	3	140	3.6	0.65	16.5	3 x #8	1.61	40.9	2.03	51.6	60	1.52	2.16	54.9	2,600	3,869	240	255
9815.21003308	2/0 (19/W) (67.4 mm <sup>2</sup> )	3	140	3.6	0.69	17.5	3 x #8	1.66	42.2	2.14	54.4	60	1.52	2.27	57.7	2,950	4,390	275	290
9815.41003307	4/0 (19/W) (107 mm <sup>2</sup> )	3	140	3.6	0.79	20.1	3 x #7	1.87	47.5	2.40	61.0	75	1.91	2.56	65.0	4,025	5,990	360	375
9815.25003306	250 (37/W) (127 mm <sup>2</sup> )	3	140	3.6	0.85	21.6	3 x #6	2.06	52.3	2.59	65.8	75	1.91	2.75	69.9	4,600	6,846	400	410
9815.35003306	350 (37/W) (177 mm <sup>2</sup> )	3	140	3.6	0.94	23.9	3 x #6	2.15	54.6	2.85	72.4	75	1.91	3.01	76.5	5,800	8,631	490	495
9815.50003305	500 (37/W) (253 mm <sup>2</sup> )	3	140	3.6	1.06	26.9	3 x #5	2.44	62.0	3.19	81.0	85	2.16	3.37	85.6	7,800	11,608	600	590
9815.75003304	750 (61/W) (380 mm <sup>2</sup> )	3	140	3.6	1.26	32.0	3 x #4	3.19	81.0	3.68	93.5	85	2.16	3.86	98.0	10,750	15,998	745	720
9815.10003304	1000 (61/W) (507 mm <sup>2</sup> )	3	140	3.6	1.42	36.1	3 x #4	3.48	88.4	3.98	101.1	85	2.16	4.16	105.7	13,550	20,165	860	810

Dimensions and weights are nominal; subject to industry tolerances.

<sup>1</sup> In-air ampacities are per NEC Table 310.60(C)(71) for three insulated copper conductors rated 105°C, cabled with an overall covering and isolated in air at 40°C ambient temperature.

<sup>2</sup> Direct burial ampacities are per NEC Table 310.60(C)(83) for three insulated copper conductors rated 105°C, cabled within an overall covering and directly buried in earth at 20°C ambient earth temperature.





# CVTC® VFD - Flexible Motor Supply Cable

XLPE/PVC, Low-Voltage Power, Al/Polyester/Al + TC Braid Shielded, 1000 V UL Flexible Motor Supply and WTTC, 600 V UL Type TC-ER—Method 4 Color Code w/Green/Yellow Ground

**Product Construction:**

**Conductor:**

- 16 AWG thru 10 AWG tinned copper per ASTM B33. Class K stranding per ASTM B172
- 8 AWG thru 2 AWG tinned copper per ASTM B33. Class H stranding per ASTM B173

**Insulation:**

- Flame-retardant Cross-linked Polyethylene (XLPE) 90°C, VW-1
- Color-coded per ICEA Method 4; individual conductors colored black with conductor number surface printed in contrasting ink

**Ground:**

- One full-sized green/yellow insulated ground, same AWG size as circuit conductors

**Metallic Shield:**

- Overall aluminum/polyester/aluminum shield with 25% minimum overlap in conjunction with overall tinned copper braid with 85% coverage and full-sized tinned copper drain wire(s)

**Jacket:**

- Lead-free, flame-retardant, sunlight-resistant Polyvinyl Chloride (PVC), black

**Print:**

- GENERAL CABLE® (PLANT OF MFG) CVTC® VFD XX/C XXAWG SHIELDED WITH GRND XLPE/PVC TYPE RHH OR RHW-2\* CDRS 90°C WET OR DRY 600 V TYPE TC-ER OR 1000 V FLEX MOTOR SUPPLY OR 1000 V WTTC SUN RES (UL) DAY/MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK

\* 16 AWG conductors are not listed as RHH or RHW-2



**Options:**

- Colored jackets available upon request
- 2000 V rated designs

**Applications:**

- For use with AC motors controlled by pulse-width modulated inverter in VFD applications rated up to 1000 V
- In free air, raceways or direct burial
- For use in aerial, conduit, open tray and underground duct/installations
- Permitted for use in Class I, Div. 2 industrial hazardous locations per NEC
- Permitted for Exposed Run (ER) use in accordance with NEC

**Features:**

- Rated at 90°C wet or dry
- Combination foil/braid shield provides maximum shield coverage required for Variable Frequency Drive (VFD) applications
- Meets cold bend test at -25°C
- TC-ER listing meets crush and impact requirements for Type MC cables
- Abrasion- and chemical-resistant
- Stable electrical properties over a broad temperature range
- UV/sunlight-resistant

**Features (cont'd.):**

- Flexible strand conductors for all sizes to allow for ease of installation and long-term performance in light duty flexing applications

**Compliances:**

- **Industry Compliances:**
  - UL 2277 1000 V Flexible Motor Supply Cable and 1000 V Wind Turbine Tray Cable
  - UL 1277 600 V Type TC-ER UL File # E57179
  - UL 44 Type RHH or RHW-2 conductors
  - ICEA S-95-658/NEMA WC70

**Flame Test Compliances:**

- UL 1581 VW-1
- IEEE 1202/CSA FT4
- UL 1685

**Other Compliances:**

- EPA 40 CFR, Part 261 for leachable lead content per TCLP
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- Material cut to length and shipped on non-returnable wood reels

CATALOG NUMBER	NO. OF COND.	COND. SIZE (AWG/kcmil)	COND. STRAND	INSULATED GROUND WIRE SIZE (AWG)	DRAIN WIRE NUMBER X SIZE (AWG)	NOMINAL CONDUCTOR DIAMETER		MINIMUM AVG. INSULATION THICKNESS		MINIMUM AVG. JACKET THICKNESS		NOMINAL CABLE O.D.		NET WEIGHT	
						INCHES	mm	INCHES	mm	INCHES	mm	INCHES	mm	LBS/1000 FT	kg/km
16 AWG - 2 AWG MULTI-CONDUCTORS															
438070	3	16	26W	16	1 x 16	0.057	1.40	0.045	1.14	0.045	1.14	0.535	13.59	175	260
438080	3	14	41W	14	1 x 14	0.071	1.80	0.045	1.14	0.060	1.52	0.608	15.44	213	317
438090	3	12	65W	12	1 x 12	0.088	2.20	0.045	1.14	0.060	1.52	0.653	16.59	285	424
438100	3	10	105W	10	1 x 10	0.112	2.80	0.045	1.14	0.060	1.52	0.690	17.53	362	539
438110	3	8	133W	8	4 x 14	0.164	4.17	0.060	1.52	0.080	2.03	0.931	23.65	638	949
438120	3	6	133W	6	4 x 12	0.204	5.18	0.060	1.52	0.080	2.03	1.028	26.11	894	1330
438130	3	4	133W	4	4 x 10	0.260	6.60	0.060	1.52	0.080	2.03	1.163	29.54	1202	1789
438140	3	2	133W	2	4 x 8	0.327	8.31	0.060	1.52	0.080	2.03	1.314	33.38	1665	2478

Dimensions and weights are nominal, subject to industry tolerances.



# CVTC® VFD - Flexible Motor Supply Cable

XLPE/PVC, Low-Voltage Power, Al/Polyester/Al TC Braid Shielded, 1000 V UL Flexible Motor Supply and WTTC, 600 V UL Type TC-ER— Method 4 Color Code w/Green/Yellow Ground and Signal Pair



**Product Construction:**

**Conductor:**

- 16 AWG to 10 AWG tinned copper per ASTM B33
- Class K stranding per ASTM B172

**Insulation:**

- Flame-retardant Cross-linked Polyethylene (XLPE) 90°C, VW-1
- Color-coded per ICEA Method 4; individual conductors colored black with conductor number surface printed in contrasting ink

**Ground:**

- One full-sized green/yellow insulated ground, same AWG size as circuit conductors

**Metallic Shield:**

- Overall aluminum/polyester/aluminum shield with 25% minimum overlap in conjunction with overall tinned copper braid with 85% coverage and full-sized tinned copper drain wire(s)

**Signal Pair for Brake:**

- One 16 AWG (26 x 30) tinned copper signal pair with an overall aluminum foil shield and 18 AWG drain wire
- Black/White color code

**Jacket:**

- Lead-free, flame-retardant, sunlight-resistant Polyvinyl Chloride (PVC), black

**Print:**

- GENERAL CABLE® (PLANT OF MFG) CVTC® VFD XX/C XXAWG SHIELDED WITH GRND XLPE/PVC TYPE RHH OR RHW-2\* CDRS 90°C WET OR DRY 600 V TYPE TC-ER OR 1000 V FLEX MOTOR SUPPLY OR 1000 V WTTC SUN RES (UL) DAY/MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK

\* 16 AWG conductors are not listed as RHH or RHW-2

**Options:**

- Colored jackets available upon request
- 2000 V rated designs

**Applications:**

- For use with AC motors controlled by pulse-width modulated inverter in VFD applications rated up to 1000 V
- In free air, raceways or direct burial
- For use in aerial, conduit, open tray and underground duct/installations
- Permitted for use in Class I, Div. 2 industrial hazardous locations per NEC
- Permitted for Exposed Run (ER) use in accordance with NEC

**Features:**

- Rated at 90°C wet or dry
- Combination foil/braid shield provides maximum shield coverage required for Variable Frequency Drive (VFD) applications
- Meets cold bend test at -25°C
- TC-ER listing meets crush and impact requirements for Type MC cables
- Abrasion- and chemical-resistant
- Stable electrical properties over a broad temperature range
- UV/sunlight-resistant
- Flexible strand conductors for all sizes to allow for ease of installation and long-term performance in light duty flexing applications

**Compliances:**

**Industry Compliances:**

- UL 2277 1000 V Flexible Motor Supply Cable and 1000 V Wind Turbine Tray Cable
- UL 1277 600 V Type TC-ER UL File # E57179
- UL 44 Type RHH or RHW-2 conductors
- ICEA S-95-658/NEMA WC70

**Flame Test Compliances:**

- UL 1581 VW-1
- IEEE 1202/CSA FT4
- UL 1685

**Other Compliances:**

- EPA 40 CFR, Part 261 for leachable lead content per TCLP
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- Material cut to length and shipped on non-returnable wood reels

CATALOG NUMBER	NO. OF COND.	COND. SIZE (AWG/kcmil)	COND. STRAND	INSULATED GROUND WIRE SIZE (AWG)	DRAIN WIRE SIZE (AWG)	SIGNAL PAIR (AWG)	NOMINAL CONDUCTOR DIAMETER		MINIMUM AVG. INSULATION THICKNESS		MINIMUM AVG. JACKET THICKNESS		NOMINAL CABLE O.D.		NET WEIGHT	
							INCHES	mm	INCHES	mm	INCHES	mm	INCHES	mm	LBS/ 1000 FT	kg/km
<b>16 AWG - 10 AWG MULTI-CONDUCTORS</b>																
438150*	3	16	26W	16	16	16	0.057	1.40	0.045	1.14	0.060	1.52	0.750	19.05	324	482
438160*	3	14	41W	14	14	16	0.071	1.80	0.045	1.14	0.060	1.52	0.823	20.90	340	506
438170*	3	12	65W	12	12	16	0.088	2.20	0.045	1.14	0.080	2.03	0.909	23.09	438	652
438180*	3	10	105W	10	10	16	0.112	2.80	0.045	1.14	0.080	2.03	0.997	25.32	563	838

Dimensions and weights are nominal, subject to industry tolerances.

\* Non-stock item; minimum runs apply. Please consult customer service for price and delivery.



# CVTC® VFD - Flexible Motor Supply Cable

XLPE/PVC, Low-Voltage Power, Dual Copper Tape Shielded, 1000 V UL Flexible Motor Supply and WTTC, 600 V UL Type TC-ER—Method 4 Color Code

**Product Construction:**

**Conductor:**

- 1 AWG thru 4/0 AWG tinned copper
- Class I stranding per ASTM B33, B172

**Insulation:**

- Flame-retardant Cross-linked Polyethylene (XLPE) 90°C, VW-1
- Color-coded per ICEA Method 4; individual conductors colored black with conductor number surface printed in contrasting ink

**Ground:**

- Three symmetrical stranded annealed bare copper grounds per ASTM B8

**Metallic Shield:**

- Two spirally applied 2 mil copper tapes providing 100% coverage

**Jacket:**

- Lead-free, flame-retardant, sunlight-resistant Polyvinyl Chloride (PVC), black

**Print:**

- GENERAL CABLE® (PLANT OF MFG) CVTC® VFD XX/C XXAWG SHIELDED WITH GRND XLPE/PVC TYPE XHHW-2 CDRS 90°C WET OR DRY 600 V TYPE TC-ER OR 1000 V FLEX MOTOR SUPPLY OR 1000 V WTTC SUN RES (UL) DAY/MONTH/YEAR OF MFG SEQUENTIAL FOOTAGE MARK

**Options:**

- Colored jackets available upon request



**Applications:**

- For use with AC motors controlled by pulse-width modulated inverter in VFD applications rated up to 1000 V
- In free air, raceways or direct burial
- For use in aerial, conduit, open tray and underground duct/installations
- Permitted for use in Class I, Div. 2 industrial hazardous locations per NEC
- Permitted for Exposed Run (ER) use in accordance with NEC

**Features:**

- Rated at 90°C wet or dry
- Dual copper tape shield provides 100% shield coverage
- Meets cold bend test at -25°C
- TC-ER rating meets crush and impact requirements for Type MC cables
- Abrasion- and chemical-resistant
- Stable electrical properties over a broad temperature range
- UV/sunlight-resistant

**Features (cont'd.):**

- Flexible strand conductors for all sizes to allow for ease of installation

**Compliances:**

**Industry Compliances:**

- UL 2277 1000 V Flexible Motor Supply Cable and 1000 V Wind Turbine Tray Cable
- UL 1277 600 V Type TC-ER UL File # E57179
- UL 44 Type XHHW-2 conductors
- ICEA S-95-658/NEMA WC70

**Flame Test Compliances:**

- UL 1581 VW-1
- IEEE 1202/CSA FT4
- UL 1685

**Other Compliances:**

- EPA 40 CFR, Part 261 for leachable lead content per TCLP
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- Material cut to length and shipped on non-returnable wood reels

CATALOG NUMBER	NO. OF COND.	COND. SIZE (AWG/kcmil)	COND. STRAND	GROUND WIRE SIZE (AWG)	NOMINAL CONDUCTOR DIAMETER		MINIMUM AVG. INSULATION THICKNESS		MINIMUM AVG. JACKET THICKNESS		NOMINAL CABLE O.D.		NET WEIGHT	
					INCHES	mm	INCHES	mm	INCHES	mm	INCHES	mm	LBS/1000 FT	kg/km

**1 AWG - 4/0 AWG MULTI-CONDUCTORS**

<b>438190*</b>	3	1	224W	3 x 6	0.380	9.65	0.055	1.40	0.080	2.03	1.205	30.61	1610	2396
<b>438200</b>	3	1/0	273W	3 x 4	0.410	10.41	0.055	1.40	0.080	2.03	1.295	32.89	2020	3006
<b>438210</b>	3	2/0	323W	3 x 4	0.470	11.90	0.055	1.40	0.080	2.03	1.408	35.76	2325	3460
<b>438220*</b>	3	3/0	456W	3 x 4	0.549	13.94	0.055	1.40	0.080	2.03	1.524	38.71	2680	3988
<b>438230</b>	3	4/0	551W	3 x 2	0.593	14.70	0.055	1.40	0.110	2.80	1.682	42.72	3694	5497


Dimensions and weights are nominal, subject to industry tolerances.

\* Non-stock item; minimum runs apply. Please consult customer service for price and delivery.

# CVTC® VFD

## XLPE/PVC, Low-Voltage Power, Shielded

### 2000 V, UL Type TC-ER<sup>1</sup> – Method 4 Color Code



**Features:**

- Rated at 90°C wet or dry
- Dual shield provides maximum shield coverage required for Variable Frequency Drive (VFD) applications
- Meets cold bend test at -25°C
- Meets crush and impact requirements to Type MC cable
- Abrasion- and chemical-resistant
- Excellent electrical properties
- Sunlight- and weather-resistant

**Product Construction:**

**Conductor:**

- 14 AWG thru 500 kcmil fully annealed tinned stranded copper
- Class B stranding per ASTM B8

**Insulation:**

- Flame-retardant Cross-linked Polyethylene (XLPE)—90°C, VW-1
- Color-coded per ICEA Method 4; individual conductors colored black with conductor number surface printed in contrasting ink

**Ground:**

- 3 symmetrically placed annealed tinned copper conductors in direct contact with shield
- Class B stranding per ASTM B8

**Dual Shield:**

- Overall tinned copper braided shield in conjunction with an aluminum/polymer tape shield

**Jacket:**

- Lead-free, flame-retardant, sunlight-resistant Polyvinyl Chloride (PVC)

**Print:**

- GENERAL CABLE® (PLANT OF MFG) CVTC® VFD XX/C XXAWG WITH GRND FR-XLP/PVC (UL) TYPE TC-ER RHH or RHW-2 CDRS 90°C WET OR DRY 2000 V DIR BUR SUN RES DAY/MONTH/YEAR SEQUENTIAL FOOTAGE MARK

**Applications:**

- For use with AC motors controlled by pulse-width modulated inverter in VFD applications rated up to 2000 volts. These motor drive systems require cables that are designed to prevent radio frequency interference (RFI) which can lead to malfunction
- In raceways, cable trays or direct burial
- In wet or dry locations
- Permitted for use in Class I, Division 2 industrial hazardous locations per NEC
- Permitted for Exposed Run (ER) use in accordance with NEC

**Compliances:**

**Industry Compliances:**

- UL 1277 Type TC-ER, UL File # E57179
- UL Type RHH or RHW-2 conductors per UL 44

**Flame Test Compliances:**

- UL 1581/UL 2556 VW-1
- UL 1685 Vertical Flame Test
- IEEE 383
- IEEE 1202
- ICEA T-29-520 (210,000 BTU/hr)

**Other Compliances:**

- EPA 40 CFR, Part 261 for leachable lead content per TCLP
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- Material cut to length and shipped on non-returnable wood reels

CATALOG NUMBER	NO. OF COND.	COND. SIZE (AWG/kcmil)	COND. STRAND	GROUND WIRE SIZE (AWG)	MINIMUM AVG. INSULATION THICKNESS		MINIMUM AVG. JACKET THICKNESS		NOMINAL CABLE O.D.		COPPER WEIGHT		NET WEIGHT	
					INCHES	mm	INCHES	mm	INCHES	mm	LBS/1000 FT	kg/km	LBS/1000 FT	kg/km
<b>14 AWG - 500 kcmil MULTI-CONDUCTORS</b>														
384730*	3	14	7W	3 x 18	0.060	1.52	0.060	1.52	0.565	14.35	79	118	190	283
384740*	3	12	7W	3 x 16	0.060	1.52	0.060	1.52	0.605	15.37	114	170	236	351
384750*	3	10	7W	3 x 14	0.060	1.52	0.060	1.52	0.665	16.89	172	256	313	466
384760*	3	8	7W	3 x 14	0.070	1.78	0.060	1.52	0.785	19.94	234	348	420	625
384770*	3	6	7W	3 x 12	0.070	1.78	0.080	2.03	0.910	23.11	354	527	605	900
384780*	3	4	7W	3 x 12	0.070	1.78	0.080	2.03	1.010	25.65	507	755	800	1191
384790*	3	2	7W	3 x 10	0.070	1.78	0.080	2.03	1.315	28.83	783	1165	1126	1676
384800*	3	1/0	19W	3 x 6	0.090	2.29	0.080	2.03	1.390	35.31	1251	1861	1832	2726
384810*	3	2/0	19W	3 x 6	0.090	2.29	0.080	2.03	1.490	37.85	1511	2248	2134	3175
384820*	3	3/0	19W	3 x 5	0.090	2.29	0.080	2.03	1.595	40.51	1897	2823	2553	3799
384830*	3	4/0	19W	3 x 4	0.090	2.29	0.110	2.79	1.775	45.09	2355	3504	3254	4842
384840*	3	250	37W	3 x 4	0.105	2.67	0.110	2.79	1.940	49.28	2719	4046	3726	5544
384850*	3	350	37W	3 x 2	0.105	2.67	0.110	2.79	2.160	54.86	3883	5778	5040	7500
384860*	3	500	37W	3 x 1	0.105	2.67	0.110	2.79	2.440	61.98	5507	8194	6809	10132

Dimensions and weights are nominal; subject to industry tolerances.  
 \* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.  
<sup>1</sup> Approved as TYPE TC-ER for Exposed Run applications of 3 or more conductors as defined by NEC.



# CVTC® VFD

## XLPE/PVC, Low-Voltage Power, Copper Tape Shielded 2000 V, UL Type TC-ER<sup>1</sup> – Method 4 Color Code

**Product Construction:**

**Conductor:**

- 14 AWG thru 500 kcmil fully annealed bare stranded copper
- Class B stranding per ASTM B8

**Insulation:**

- Flame-retardant Cross-linked Polyethylene (XLPE) –90°C, VW-1
- Color-coded per ICEA Method 4; individual conductors colored black with conductor number surface printed in contrasting ink

**Ground:**

- 3 symmetrically placed annealed bare copper conductors in direct contact with shield
- Class B stranding per ASTM B8

**Metallic Shield:**

- Overall 5 mil annealed bare copper tape shield with 50% overlap

**Jacket:**

- Lead-free, flame-retardant, sunlight-resistant Polyvinyl Chloride (PVC)

**Print:**

- GENERAL CABLE® (PLANT OF MFG) CVTC® VFD XX/C XXAWG WITH GRNDS FR-XLP/PVC (UL) TYPE TC-ER RHH or RHW-2 CDRS 90°C WET OR DRY 2000 V DIR BUR SUN RES DAY/MONTH/YEAR SEQUENTIAL FOOTAGE MARK



**Applications:**

- For use with AC motors controlled by pulse-width modulated inverter in VFD applications rated up to 2000 volts. These motor drive systems require cables that are designed to prevent radio frequency interference (RFI) which can lead to malfunction
- In raceways, cable trays or direct burial
- In wet or dry locations
- Permitted for use in Class I, Division 2 industrial hazardous locations per NEC
- Permitted for Exposed Run (ER) use in accordance with NEC

**Features:**

- Rated at 90°C wet or dry
- Overlapped bare copper tape shield provides necessary shield coverage required for Variable Frequency Drive (VFD) applications
- Meets cold bend test at -25°C
- Meets crush and impact requirements for Type MC cable
- Abrasion- and chemical-resistant
- Excellent electrical properties
- Sunlight- and weather-resistant

**Compliances:**

**Industry Compliances:**

- UL 1277 Type TC-ER, 2000 V, UL File # E57179
- UL Type RHH or RHW-2 conductors per UL 44

**Flame Test Compliances:**

- UL 1581/UL 2556 VW-1
- UL 1685 Vertical Flame Test
- IEEE 383
- IEEE 1202
- ICEA T-29-520 (210,000 BTU/hr)

**Other Compliances:**

- EPA 40 CFR, Part 261 for leachable lead content per TCLP
- OSHA Acceptable
- RoHS Compliant

**Packaging:**

- Material cut to length and shipped on non-returnable wood reels

CATALOG NUMBER	NO. OF COND.	COND. SIZE (AWG/kcmil)	COND. STRAND	GROUND WIRE SIZE (AWG)	MINIMUM AVG. INSULATION THICKNESS		MINIMUM AVG. JACKET THICKNESS		NOMINAL CABLE O.D.		COPPER WEIGHT		NET WEIGHT	
					INCHES	mm	INCHES	mm	INCHES	mm	LBS/1000 FT	kg/km	LBS/1000 FT	kg/km

**14 AWG - 500 kcmil MULTI-CONDUCTORS**

395070V	3	14	7W	3 x 18	0.060	1.52	0.060	1.52	0.580	14.73	91	135	212	315
395080V	3	12	7W	3 x 16	0.060	1.52	0.060	1.52	0.615	15.37	127	189	260	387
395090V	3	10	7W	3 x 14	0.060	1.52	0.060	1.52	0.670	17.02	183	272	329	490
395100V	3	8	7W	3 x 14	0.070	1.78	0.060	1.52	0.770	19.56	246	366	441	656
395110V	3	6	7W	3 x 12	0.070	1.78	0.080	2.03	0.895	22.73	368	548	618	920
395120V	3	4	7W	3 x 12	0.070	1.78	0.080	2.03	0.995	25.27	522	777	830	1235
395130V	3	2	7W	3 x 10	0.070	1.78	0.080	2.03	1.125	28.58	801	1192	1152	1714
395140V	3	1/0	19W	3 x 6	0.090	2.29	0.080	2.03	1.385	35.18	1348	2006	1853	2757
395150V	3	2/0	19W	3 x 6	0.090	2.29	0.080	2.03	1.480	37.59	1616	2405	2169	3227
395160V*	3	3/0	19W	3 x 5	0.090	2.29	0.080	2.03	1.590	40.39	2010	2991	2619	3897
395170V	3	4/0	19W	3 x 4	0.090	2.29	0.110	2.79	1.780	45.21	2517	3745	3241	4823
395180V*	3	250	37W	3 x 4	0.105	2.67	0.110	2.79	1.940	49.28	2895	4308	3763	5599
395190V	3	350	37W	3 x 2	0.105	2.67	0.110	2.79	2.160	54.86	4089	6084	5109	7602
395200V	3	500	37W	3 x 1	0.105	2.67	0.110	2.79	2.455	62.36	5693	8471	6933	10316

Dimensions and weights are nominal; subject to industry tolerances.

\* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.

<sup>1</sup> Approved as TYPE TC-ER for Exposed Run applications of 3 or more conductors as defined by NEC.

# Table of Contents

## TECHNICAL INFORMATION

<b>DESCRIPTION</b>	<b>PAGE</b>
Industrial Automation General Cable to Belden Cross-Reference	98-99
Industrial Communication Protocol Cables Cross-Reference	100-112
Catalog Number Index	113-117

# Industrial Automation General Cable to Belden Cross-Reference

General Cable, a leading wire and cable innovator for over 170 years, knows that factory productivity is key to your business success. Trusting your automation infrastructure puts your mind at ease. General Cable is proud to introduce its new line of DeviceNet™, ControlNet™ and Industrial Ethernet products. As *One Company* and one source, General Cable is ready to respond to your changing requirements and help you achieve continuous productivity savings.

### CAN OPEN/HART/RS-485 SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
24 AWG 1 Pair Tinned Copper Foil and Braid Shield	C4841A	9841
24 AWG 2 Pair Tinned Copper Foil and Braid Shield	C4842A	9842
24 AWG 3 Pair Tinned Copper Foil and Braid Shield	C4843A	9843
24 AWG 4 Pair Tinned Copper Foil and Braid Shield	C4844A	9844
24 AWG 1 Pair Tinned Copper Foil and Braid Shield Plenum	C4851A	82841
24 AWG 2 Pair Tinned Copper Foil and Braid Shield Plenum	C4852A	82842
22 AWG 1 Pair LO-CAP® Tinned Plated Copper Braid	C7112A	3105A
22 AWG 2 Pair LO-CAP Tinned Plated Copper Braid	C7114A	3107A
22 AWG 3 Pair LO-CAP Tinned Plated Copper Braid	C7116A	3108A
22 AWG 4 Pair LO-CAP Tinned Plated Copper Braid	C7118A	3109A
22 AWG 1 Pair + 1 Conductor LO-CAP Tinned Copper Braid and Foil Shield	GCR1310	3106A

### CONTROLNET™ SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
18 AWG RG-6 ControlNet Quad Shield	GCR1309	3092A
18 AWG RG-6 ControlNet Quad Shield Aluminum Braid Flex Shield	GCR1309F	3092F
18 AWG RG-6 ControlNet Quad Shield Copper Braid	GCR1309FC	YR28690
18 AWG RG-6 ControlNet Quad Shield Plenum	GCR1309P	3093A
18 AWG RG-6 ControlNet Quad Shield Aluminum Armored	GCR1309A	123092A
18 AWG RG-6 ControlNet Quad Shield Steel Armor	GCR1309S	133092A
18 AWG RG-6 ControlNet Quad Shield CCW®	GCR1309CC	183092A

### DATA HIGHWAY & DATA HIGHWAY PLUS SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
18 AWG 2 Conductor Dual Shielded Twinaxial	GCR1300	3072F
20 AWG 2 Conductor Dual Shielded Twinaxial	GCR1314	9463
20 AWG 2 Conductor Dual Shielded Twinaxial Aluminum Armor	GCR1314A	129463
20 AWG 2 Conductor Dual Shielded Twinaxial CCW®	GCR1314CC	189463
20 AWG 2 Conductor Dual Shielded Twinaxial Direct Burial	GCR1314D	9463DB
20 AWG 2 Conductor Dual Shielded Twinaxial Flexible Jacket	GCR1314F	9463F
20 AWG 2 Conductor Dual Shielded Twinaxial Plenum	GCR1314P	89463
20 AWG 2 Conductor Dual Shielded Twinaxial Steel Armor	GCR1314S	139463
20 AWG 2 Conductor Heavy Duty Tough Shielded Twinaxial	GCR1314T	YR28764
20 AWG 2 Conductor Dual Shielded Low-Smoke Zero-Halogen	GCR1314ZH	YR41104

### DEVICENET™ SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
15 AWG 2 Conductor + 18 AWG 2 Conductor Shielded DeviceNet	GCR1305	3082A
15 AWG 2 Conductor + 18 AWG 2 Conductor Shielded Flexible DeviceNet	GCR1305F	3082F
15 AWG 2 Conductor + 18 AWG 2 Conductor Shielded CPE DeviceNet	GCR1306	3083A
22 AWG 2 Conductor + 24 AWG 2 Conductor Shielded DeviceNet	GCR1307	3084A
22 AWG 2 Conductor + 24 AWG 2 Conductor Shielded Flexible DeviceNet	GCR1307F	3084F
22 AWG 2 Conductor + 24 AWG 2 Conductor Shielded CPE DeviceNet	GCR1308	3085A
16 AWG 2 Conductor + 18 AWG 2 Conductor Individually Shielded DeviceNet	GCR1311	7896A
15 AWG 2 Conductor + 18 AWG 2 Conductor Individually Shielded DeviceNet	GCR1312	7897A
16 AWG 2 Conductor + 18 AWG 2 Conductor Unshielded DeviceNet	GCR1313	7900A
18 AWG 2 Conductor + 20 AWG 2 Conductor Shielded DeviceNet	GCR1317	7895A



Please consult your General Cable representative for additional information (800) 950-3512



# Industrial Automation General Cable to Belden Cross-Reference

## CC-LINK SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
20 AWG 3 Conductor Dual Shielded CC-Link	GCR1315	1348A
20 AWG 3 Conductor Shielded + 18 AWG 2 Conductor Composite & CC-Link	GCR1316	1349A

## INDUSTRIAL ETHERNET SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet UTP Cable Waterblocked	5136100	7934A
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet UTP Cable Waterblocked Armored	5136101	
23 AWG 4 Pair Multi-Conductor Category 6 Industrial Ethernet UTP Cable Waterblocked	7136100	
24 AWG 2 Pair Multi-Conductor Category 5e Industrial Ethernet UTP Cable 600 V UL AWM	GCR1402	7932A
24 AWG 2 Pair Multi-Conductor Category 5e Industrial Ethernet F/UTP Cable Shielded 600 V UL AWM	GCR1403	7933A
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet UTP Cable 600 V UL AWM	GCR1404*	7918A/7923A
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet F/UTP Cable Shielded, 600 V UL AWM	GCR1405*	7929A/7958A
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet SF/UTP Cable 600 V UL AWM	GCR1407	7921A/7957A
22 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet UTP Cable PLTC 600 V UL AWM	GCR1408	7922A
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet UTP Cable Armored	GCR1410	121700A
24 AWG 4 Pair Multi-Conductor Category 5e Industrial Ethernet F/UTP Cable 600 V UL AWM	GCR1419	7919A
23 AWG 4 Pair Multi-Conductor Category 6 Industrial Ethernet UTP Cable 600 V UL AWM	GCR1440	7940A
23 AWG 4 Pair Multi-Conductor Category 6 Industrial Ethernet UTP Cable Enhanced 600 V UL AWM	GCR1450	7927A
23 AWG 4 Pair Multi-Conductor Category 6 Industrial Ethernet UTP Cable Shielded 600 V UL AWM	GCR1452	7953A

\* MSHA rating pending approval.

Seriplex® is a registered trademark of Belden CDT Inc.  
 DeviceNet™ is a trademark of Open DeviceNet™ Vendor Assoc.  
 ControlNet™ is a trademark of Open DeviceNet™ Vendor Assoc.  
 Lo-Cap® and CCW® are trademarks of General Cable Technologies Corporation.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

Please consult your General Cable representative for additional information (800) 950-3512

## FOUNDATION™ FIELDBUS SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
18 AWG 1 Pair Shielded Foundation Fieldbus or Profibus	GCR1302	3076F
22 AWG 1 Pair Shielded Foundation Fieldbus	GCR1303	3077F

## INTERBUS/LONWORKS®/MODBUS/PROFIBUS OP-FMS-PA SERIPLEX®/SMART DISTRIBUTED SYSTEM

PART DESCRIPTION	GENERAL CABLE CATALOG NUMBER	BELDEN EQUIVALENT
24 AWG 3 Pair + 18 AWG 3 Conductor Shielded Interbus	GCR1318	3119A
24 AWG 3 Pair Shielded Interbus	GCR1319	3120A
22 AWG 3 Pair Individually Shielded Modbus	GCR1320	8777
22 AWG 3 Pair Individually Shielded LS PVC Jacket	GCR1320P	82777
22 AWG 3 Pair Individually Shielded Aluminum Armor Modbus	GCR1320A	128777
22 AWG 3 Pair Flexible Individually Shielded Plenum Modbus	GCR1320FP	88777
22 AWG 3 Pair Individually Shielded Steel Armor Modbus	GCR1320S	138777
22 AWG 2 Conductor Shielded Profibus	GCR1304	3079A
22 AWG 2 Conductor Shielded Flexible Profibus	GCR1304F	3079E
18 AWG 2 Conductor + 22 AWG 2 Conductor Shielded Seriplex	GCR1330	3124A
18 AWG 2 Conductor + 22 AWG 2 Conductor Shielded Aluminum Armored Seriplex	GCR1330A	123124A
16 AWG 2 Conductor + 22 AWG 2 Conductor Shielded Seriplex	GCR1331	3125A
16 AWG 2 Conductor + 22 AWG 2 Conductor Shielded Aluminum Armored Seriplex	GCR1331A	123125A
16 AWG 2 Conductor + 22 AWG 2 Conductor + 12 AWG 2 Conductor Shielded Seriplex	GCR1333	3126A
16 AWG 2 Conductor + 22 AWG 2 Conductor + 12 AWG 2 Conductor Shielded Aluminum Armored Seriplex	GCR1333A	123126A
16 AWG 1 Pair + 20 AWG 1 Pair Individually Shielded SDS	GCR1332	3086A
22 AWG 2 Pair Individually Shielded SDS	GCR1334	3087A

# Industrial Communication Protocol Cables Cross-Reference

CANOpen® Network Cables typically are 2 pairs, either 24 AWG or 22 AWG. The final decision on the wire size, capacitance, impedance, shielding, and other electrical specifications is a function of the application. General Cable Corporation cannot specify a specific cable for these applications. General Cable Corporation offers different cable constructions to function in many CANOpen® applications.

### CANOpen® NETWORK CABLES OPTIONS

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	UL/CSA LISTINGS	PAGE NUMBER
C4842A	9842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4842A -- 75C E105765-H CM (UL) C(UL) CMH OR 80CAWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4852A	82842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4852A -- 2/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	CMP c(UL)	40
C7114A	3107A	2 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114A -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7114AF		2 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114AF -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39

CiA® and CANOpen® are registered Community Trademarks of CAN in Automotive e.V

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

CC-Link cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### CC-LINK CABLES

MITSUBISHI PART NUMBER	GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
BA1SJ61-5	GCR1315	1348A	3 Cond. 20 AWG (7x28) BC, OFS + Braid 78% TC/PVC Print Legend: GENERAL CABLE (F) -- GCR1315 -- 3/C 20 AWG SHIELDED (UL) TYPE CM 75C --- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	CC-Link Cable Version 1.10, 2.0, industrial environments, relatively clean, minimum temperature changes	CM, c(UL)	34
BA1SJ61-P	GCR1316	1349A	Data: 3 Cond. 20 AWG (7x28) BC, OFS + Braid 78% TC/PVC Power: 2 Cond. 18 AWG (7x26) BC Print Legend: GENERAL CABLE (F) -- GCR1316 -- 1/PR18 AWG + 1/PR20 SHIELDED (UL) TYPE PLTC OR CM 75C -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	CC-Link Cable Version 1.10, 2.0, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	34

CC-Link Cables: reference CC-Link Partner Association

Information contained on these pages is intended for evaluation by technically skilled persons. Any person relying on this document does so at his/her own independent discretion and sole risk and assumes all risks, liability and obligations whatsoever in connection with such use. General Cable Corporation and its subsidiaries will have no liability with respect thereto, whether the claim is based in contract, tort or other legal theory. General Cable Corporation and its subsidiaries make no representations or warranties, expressed or implied, with respect to the accuracy, completeness or reliability of this information.

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables

## Cross-Reference

ControlNet™ cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### ControlNet™ CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1309	3092A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC Print Legend: GENERAL CABLE (F) – GCR1309 – ODVA ControlNet™ VEN #1293 RG6/U TYPE 75 OHM QUAD SHIELD – 3.0 GHZ – 18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE-- MADE IN USA AAAAA MM/YY XXXXFT	Industrial environments, relatively clean, minimum temperature changes	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32
GCR1309P	3093A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVDF Print Legend: GENERAL CABLE (F) – GCR1309P -- ODVA ControlNet™ VEN #1293 RG-6/U TYPE 75 OHM QUAD SHIELD – 3.0 GHZ – 18 AWG 150C (ETL) CL2P - CATVP OR CMP c(ETL)us FT6 3084997 – ROHS/CE – MADE IN USA AAAAA MM/YY XXXXFT	Plenum rated, FEP/PVDF construction, suitable for high and low temperatures (-40°C+150°C)	CL2P, CMP, CATVP, FT6 c(ETL)	32
GCR1309F	3092F	RG-6/U 20 AWG (105x40) BC, Quad Shield OFS(2) 60/40% AL Braid/PVC Print Legend: GENERAL CABLE (F) – GCR1309F -- ODVA ControlNet™ VEN #1293 RG-6/U TYPE 75 OHM FLEXIBLE QUAD SHIELD – 3.0 GHZ – 20 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE-- MADE IN USA AAAAA MM/YY XXXXFT	High Flex version of GCR1309 (note higher attenuation)	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32
GCR1309FC	YR28690*	RG-6/U 20 AWG (105x40) BC, Quad Shield OFS(2) 65/60% TC Braid/PVC Print Legend: GENERAL CABLE (F) – GCR1309FC -- ODVA ControlNet™ VEN #1293 RG-6/U TYPE FLEXIBLE 75 OHM QUAD SHIELD – 20 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE – MADE IN USA AAAAA MM/YY XXXXFT	High Flex version of GCR1309 higher braid coverage for improved noise immunity (note higher attenuation)	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32
GCR1309A	123092A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC/AIA/PVC Print Legend: GENERAL CABLE (F) – GCR1309A -- ODVA ControlNet™ VEN #1293 ALUM-ARMORED RG-6/U TYPE 75 OHM QUAD SHIELD SUN RES DIR BUR – 3.0 GHZ – 18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE -- MADE IN USA AAAAA MM/YY XXXXFT	Aluminum Interlock Armor (AIA), PVC jacket, alternative to conduit installation, additional mechanical and electrical shielding	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32
GCR1309S	133092A*	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC/GSIA/PVC Print Legend: GENERAL CABLE (F) – GCR1309S – ODVA ControlNet™ VEN #1293 STEEL ARMORED RG-6/U TYPE 75 OHM QUAD SHIELD SUN RES DIR BUR – 3.0 GHZ – 18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE -- MADE IN USA AAAAA MM/YY XXXXFT	Galvanized Steel Interlock Armor (GSIA), PVC jacket, alternate to conduit installation, additional mechanical and crush resistance, electrical shielding	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32
GCR1309CC	183092A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC/CCW/PVC Print Legend: GENERAL CABLE (F) – GCR1309CC -- ODVA ControlNet™ VEN #1293 CCW-ARMORED RG-6/U TYPE 75 OHM QUAD SHIELD SUN RES DIR BUR – 3.0 GHZ – 18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE -- MADE IN USA AAAAA MM/YY XXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EM), impervious to moisture and dust	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32

ControlNet™ is a trademark of Open DeviceNet Vendor Association, Inc. (ODVA)

\* Belden special make-to-order cables.

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables Cross-Reference

DeviceNet™ cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### DeviceNet™ CABLES

ROCKWELL AUTOMATION CABLE TYPE	GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
1485C-P1A	GCR1305	3082A	Power: 1 pr 15 AWG (19x28) TC OFS, Data: 1 pr 18 AWG (19x30) TC OFS, + Braid 65% TC/PVC Thick, ODVA Class 2 Print Legend: GENERAL CABLE (F) – GCR1305 – ODVA DEVICENET™ VEN #1293 THICK CABLE -- 1/PR18 AWG + 1/PR16 SHIELDED (UL) TYPE PLTC OR CM CMG C(UL)US FT4 75C SUN RES OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Industrial environments, relatively clean, minimum temperature changes	CM, c(UL), CL2, PLTC-ER, AWM 20201 600 V, CSA AWM I/IIA 80°C, FT4	36
1485C-F1A	GCR1305F	3082F	Power: 1 pr 15 AWG (65x33) TC OFS, Data: 1 pr 18 AWG (65x36) TC OFS, + Braid 65% TC/PVC Thick, ODVA Class 2 Print Legend: GENERAL CABLE (F) – GCR1305F – ODVA DEVICENET™ VEN #1293 FLEXIBLE THICK CABLE --1/PR18 AWG + 1/PR16 SHIELDED (UL) TYPE PLTC OR CM CMG C(UL)US FT4 75C SUN RES OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	High Flex version of GCR1305	CM, c(UL), CL2, PLTC-ER, AWM 20201 600 V, CSA AWM I/IIA 80°C, FT4	36
1485C-P1A	GCR1306	3083A	Power: 1 pr 15 AWG (19x28) TC OFS, Data: 1 pr 18 AWG (19x30) TC OFS, + Braid 65% TC/CPE Thick, ODVA Class 2 Print Legend: GENERAL CABLE (F) – GCR1306 – ODVA DEVICENET™ VEN #1293 THICK CABLE -- 1/PR18 AWG + 1/PR16 SHIELDED (UL) TYPE PLTC-ER OR CL2 OR CMG c(UL)us FT4 75C SUN RES OIL RES -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Same as GCR1305 except CPE jacket for extremely harsh industrial environments	CM, c(UL), CL2, PLTC-ER, AWM 20201 600 V, CSA AWM I/IIA 80°C, FT4	36
1485C-P1B (ODVA Type V)	GCR1312	7897A	Power: 1 pr 15 AWG (19x28) TC OFS, Data: 1 pr 18 AWG (19x30) TC OFS, + Braid 65% TC/PVC Thick, ODVA Cable II, Class 1 Print Legend: GENERAL CABLE (F) – GCR1312 – ODVA DEVICENET™ VEN #1293 CABLE-II THICK CABLE 1/PR18 AWG & 1/PR15 AWG SHIELDED (UL) TYPE TC-ER 75C 600 V SUN RES OIL RES -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Class 1, 600 V rated for cable tray use and able to occupy the same tray or conduit as 600 V rated cables	TC-ER, CSA AWM I/II A/B 80°C FT1	36
1485C-P1B (ODVA Type V)	GCR1311	7896A	Power: 1 pr 16 AWG (19x29) TC Ind Shield, Data: 1 pr 18 AWG (19x30) TC Ind Shield, + Braid 65% TC/PVC Thick, ODVA Cable V, Class 1 Print Legend: GENERAL CABLE (F) – GCR1311 – ODVA DEVICENET™ VEN #1293 CABLE-V THICK CABLE 1/PR18 AWG & 1/PR16 AWG SHIELDED (UL) TYPE TC-ER 75C 600 V SUN RES OIL RES DIR BUR -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Class 1, 600 V rated for cable tray use and able to occupy the same tray or conduit as 600 V rated cables	TC-ER, CSA AWM I/II A/B 80°C FT1	36
2100H-DNRC1 (ODVA Type IV)	GCR1313	7900A	Power: 1 pr 18 AWG (19x30) TC, Data: 1 pr 20 AWG (19x32) TC Unshielded/PVC Thick, ODVA Cable IV, Class 1 Print Legend: GENERAL CABLE (F) – GCR1313 – ODVA DEVICENET™ VEN #1293 CABLE-IV THICK CABLE 1/PR18 AWG & 1/PR16 AWG (UL) TYPE TC-ER 75C SUN RES OIL RES -- ROHS/CE --MADE IN USA AAAAA MO/YR XXXXXFT	Drop Cable Class 1, 600 V rated for cable tray use and able to occupy the same tray or conduit as 600 V rated cables: note unshielded	TC-ER, CSA AWM I/II A/B 80°C FT1	36
	GCR1317	7895A	Power: 1 pr 18 AWG (19x30) TC OFS, Data: 1 pr 20 AWG (19x32) TC OFS, + Braid 65% TC/PVC Thick, ODVA Cable III, Class 2 Print Legend: GENERAL CABLE (F) – GCR1317 – ODVA DEVICENET™ VEN #1293 CABLE-III 1/PR18 AWG + 1/PR 20 AWG SHIELDED (UL) TYPE PLTC OR CM CMG C(UL) FT4 75C SUN RES OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Mid Cable III, Class 2 300 V rated, can be used for trunk or drop applications	CM, CMG, c(UL), PLTC-ER, AWM 20201 600 V, FT4	36

DeviceNet™ is a trademark of Open DeviceNet Vendor Association, Inc. (ODVA)

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables

## Cross-Reference

### DeviceNet™ CABLES

ROCKWELL AUTOMATION CABLE TYPE	GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
1485C-P1CG	GCR1307	3084A	Power: 1 pr 22 AWG (19x34) TC OFS, Data: 1 pr 24 AWG (19x36) TC OFS, + Braid 65% TC/PVC, ODVA Class 2 Thin Cable Print Legend: GENERAL CABLE (F) -- GCR1307 - ODVA CABLE-1 DEVICENET™ VEN #1293 THIN CABLE -- 1/PR22 AWG + 1/PR24 AWG SHIELDED (UL) TYPE CL2 OR CM CMG c(UL)us FT4 75C OR AWM 20201 600 V -- CSA AWM I/II A 80C 300 V FT4 - SUN RES ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Thin Cable, Class 2 300 V rated, can be used for trunk or drop applications	CL2, CM, CMG, c(UL), CSA AWM I/II A/B 80°C FT1	36
1485C-F1G	GCR1307F	3084F	Power: 1 pr 22 AWG (19x34) TC OFS, Data: 1 pr 24 AWG (19x36) TC OFS, + Braid 65% TC/PVC, ODVA Class 2 Thin Cable Print Legend: GENERAL CABLE (F) -- GCR1307F - ODVA CABLE-1 DEVICENET™ VEN #1293 FLEXIBLE THIN CABLE -- 1/PR22 AWG + 1/PR24 AWG SHIELDED (UL) TYPE CL2 OR CM CMG c(UL)us FT4 75C OR AWM 20201 600 V -- SUN RES ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	High Flex version of GCR1307	CL2, CM, CMG, c(UL), CSA AWM I/II A/B 80°C FT1	36
1485C-P1C	GCR1308	3085A	Power: 1 pr 22 AWG (19x34) TC OFS, Data: 1 pr 24 AWG (19x36) TC OFS, + Braid 65% TC/CPE, ODVA Class 2 Thin Cable Print Legend: GENERAL CABLE (F) -- GCR1308 - ODVA CABLE-1 DEVICENET™ VEN #1293 THIN CABLE -- 1/PR22 AWG + 1/PR24 AWG SHIELDED (UL) TYPE CL2 OR CM C(UL) 75C SUN RES OIL RES DIR BUR - ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Same as GCR1307 except CPE jacket for extremely harsh industrial environments	CL2, CM, CMG, c(UL), CSA AWM I/II A/B 80°C FT1	36

DeviceNet™ is a trademark of Open DeviceNet Vendor Association, Inc. (ODVA)

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables

## Cross-Reference

Foundation™ Fieldbus cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### FOUNDATION™ FIELDBUS CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1302	3076F	1 pr 18 AWG (7x26) TC OFS, PVC Foundation™ Fieldbus Type A Print Legend: GENERAL CABLE (F) – GCR1302 -- FIELDBUS 1/PR 18 AWG SHIELDED (UL) TYPE PLTC OR ITC OR CM CMG C(UL) US FT4 75C -- SUN RES OIL RES --- ROHS/CE – MADE IN USA AAAAA MO/YR XXXXXFT	Industrial environments, relatively clean, minimum temperature changes, trunk and/or spur	CM, c(UL), ITC-ER, CMG 80°C, FT4	34
GCR1303	3077F	1 pr 22 AWG (7x30) TC OFS, PVC Foundation™ Fieldbus Type B Print Legend: GENERAL CABLE (F) – GCR1303 -- FIELDBUS 1/PR 22 AWG SHIELDED (UL) TYPE CM 75C -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	Industrial environments, relatively clean, minimum temperature changes, spur connections only	CM, c(UL), ITC-ER, CMG 80°C, FT4	34
9899.FB01801120	*183076F	1 pr 18 AWG (7x 0.152") TC, XLPE Ins. OFS, PVC/CCW/PVC Black Jacket, Foundation™ Fieldbus Type A Print Legend: GENERAL CABLE (WC) CCW ARCTIC ARMOR FIELDBUS 1 PAIR 18 AWG CU SHIELDED 600 V (UL) TYPE MC-HL 90C-40C SUN RES OR ABS TYPE CWC MC DAY/MONTH/YEAR XXXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust, trunk and/or spur Arctic Armor grade +90° -40°C, direct burial	MC-HL 600 V, Sun Res, Direct Burial, CSA FT4, IEEE 1202	35
9899.FB01802120	-	2 pr 18 AWG (7x0.152") TC, XLPE Ins. IFS +OFS, PVC/CCW/PVC Black Jacket, Foundation™ Fieldbus Type A Print Legend: GENERAL CABLE (WC) CCW ARCTIC ARMOR FIELDBUS 2 PAIR 18 AWG CU SHIELDED 600 V (UL) TYPE MC-HL 90C-40C SUN RES OR ABS TYPE CWC MC DAY/MONTH/YEAR XXXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust, trunk and/or spur Arctic Armor grade +90° -40°C, direct burial	MC-HL 600 V, Sun Res, Direct Burial, CSA FT4, IEEE 1202	35
9899.FB01804120	-	4 pr 18 AWG (7x0.152") TC, XLPE Ins. IFS +OFS, PVC/CCW/PVC Black Jacket, Foundation™ Fieldbus Type A Print Legend: GENERAL CABLE (WC) CCW ARCTIC ARMOR FIELDBUS 4 PAIR 18 AWG CU SHIELDED 600 V (UL) TYPE MC-HL 90C-40C SUN RES OR ABS TYPE CWC MC DAY/MONTH/YEAR XXXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust, trunk and/or spur Arctic Armor grade +90° -40°C, direct burial	MC-HL 600 V, Sun Res, Direct Burial, CSA FT4, IEEE 1202	35
9899.FB01602118	-	2 pr 16 AWG (7x0.192") TC, XLPE Ins. IFS +OFS, PVC/CCW/PVC Black Jacket, Foundation™ Fieldbus Type A Print Legend: GENERAL CABLE (WC) CCW ARCTIC ARMOR FIELDBUS 2 PAIR 16 AWG CU SHIELDED 600 V (UL) TYPE MC-HL 90C-40C SUN RES OR ABS TYPE CWC MC DAY/MONTH/YEAR XXXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust, trunk and/or spur Arctic Armor grade +90° -40°C, direct burial	MC-HL 600 V, Sun Res, Direct Burial, CSA FT4, IEEE 1202	35
9899.FB01604118	-	4 pr 16 AWG (7x0.192") TC, XLPE Ins. IFS +OFS, PVC/CCW/PVC Black Jacket, Foundation™ Fieldbus Type A Print Legend: GENERAL CABLE (WC) CCW ARCTIC ARMOR FIELDBUS 4 PAIR 16 AWG CU SHIELDED 600 V (UL) TYPE MC-HL 90C-40C SUN RES OR ABS TYPE CWC MC DAY/MONTH/YEAR XXXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust, trunk and/or spur Arctic Armor grade +90° -40°C, direct burial	MC-HL 600 V, Sun Res, Direct Burial, CSA FT4, IEEE 1202	35

Foundation™ is a trademark of Fieldbus Foundation      \*Belden 183076F has an orange jacket color

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**





# Industrial Communication Protocol Cables

## Cross-Reference

The final decision on the number of pairs, wire size, capacitance, impedance, shielding, and other electrical specifications is a function of the application. General Cable Corporation cannot specify a specific cable for these applications. General Cable Corporation offers different cable constructions to function in many HART® applications.

### HART® NETWORK CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	UL/CSA LISTINGS	PAGE NUMBER
C4841A	9841	1 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4841A -- 75C E105765-H CM (UL) C(UL) CMH OR 80CAWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4851A	82841	1 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4851A -- 1/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	CMP c(UL)	40
C4842A	9842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4842A -- 75C E105765-H CM (UL) C(UL) CMH OR 80CAWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4852A	82842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4852A -- 2/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	CMP c(UL)	40
C4843A	9843	3 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4843A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4844A	9844	4 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4844A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C7112A	3105A	1 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7112A -- 1/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7114A	3107A	3 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114A -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7116A	3108A	3 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7116A -- 3/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7116AF		3 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7116AF -- 3/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7118A	3109A	4 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7118A -- 4/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7118AF		4 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7118AF -- 4/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C2534A	8760	1 pr 18 AWG (16x30) TC, OFS/PVC Print Legend: CAROL® 18 AWG -- C2534A -- 75C E105765-H CM (UL) C(UL) CMH OR AWM STYLE 2092 --ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2092	40
C8123	82760	1 pr 18 AWG (16x30) TC, OFS/LS PVC Print Legend: CAROL® 18 AWG -- C2534A -- 75C E105765-H CM (UL) C(UL) CMH OR AWM STYLE 2092 -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CMP c(UL)	40
C8101	88760	1 pr 18 AWG (16x30) TC, OFS/FEP (high and low temperatures (-70°C+200°C), corrosive environments) Print Legend: GENERAL CABLE (F) - C8101 - 2C 18 AWG SHIELDED CMP (UL) C(UL) FEP/FEP--GAS AND OIL RESISTANT --- ROHS AAAAA*	CMP c(UL)	40

HART® is a registered trademark of the HART Communication Foundation.

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables Cross-Reference

Interbus cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### INTERBUS CABLES

PHOENIX CONTACT PART NUMBER	GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
E-T-2723149	GCR1319	3120A	Data: 3 pr 24 AWG (7x32) TC OFS + Braid 90% TC/TPU Print Legend: GENERAL CABLE (F) - GCR1319 - 3/PR 24 AWG SHIELDED AWM STYLE 20233 80C 300 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Interbus cable, industrial environments, relatively clean, minimum temperature changes	AWM 20233 80°C 300 V	37
E-T-2723152	GCR1318	3119A	Data: 3 pr 24 AWG (7x32) TC OFS + Braid 90% TC/TPU, Power: 3 Cond. 18 AWG (7x26) TC Print Legend: GENERAL CABLE (F) - GCR1318 - 3/C 18 AWG + 3/PR 24 AWG SHIELDED AWM STYLE 20233 80C 300 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Interbus cable, industrial environments, relatively clean, minimum temperature changes	AWM 20233 80°C 300 V	37

Interbus System developed by Phoenix Contact.  
Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

LonWorks® based communications protocol is one of the most widely deployed technologies worldwide. LonWorks is suited to be used with different types of cables such as twisted pair cables, power line, RF, fiber optics and industrial Ethernet cables. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### LonWorks® CABLE CONSTRUCTION OPTIONS

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
C8601		1 pr 22 AWG (7x.0096") BC, UTP Level 4 Print Legend: XXXX/XXXX feet ECHELON GUIDELINE COMPLIANT 22 AWG UTP LEVEL-4 TYPE CMP (UL) c(UL) 75C E105765-F ROHS/CE AAAAA	Industrial environments	CMP c(UL)	41
C8611		1 pr 22 AWG (7x.0096") BC, ScTP Level 4 Print Legend: XXXX/XXXX feet ECHELON GUIDELINE COMPLIANT 22 AWG SCREENED STP LEVEL-4 TYPE CMP (UL) c(UL) 75C E105765-F ROHS/CE AAAAA	Industrial environments	CMP c(UL)	37
C8641		1 pr 22 AWG (7x.0096") BC, UTP Level 4 Print Legend: XXXX/XXXX feet ECHELON GUIDELINE COMPLIANT 22 AWG UTP LEVEL-4 TYPE CM (UL) c(UL) 75C E105765-F ROHS/CE AAAAA	Industrial environments	CM c(UL)	41
C8651		1 pr 22 AWG (7x.0096") BC, ScTP Level 4 Print Legend: XXXX/XXXX feet ECHELON GUIDELINE COMPLIANT 22 AWG SCREENED STP LEVEL-4 TYPE CM (UL) c(UL) 75C E105765-F ROHS/CE AAAAA	Industrial environments	CM c(UL)	37
C8621	85102	1 pr 16 AWG (19x.0116") TC Unshielded Print Legend: XXXX/XXXX feet ECHELON GUIDELINE COMPLIANT 16 AWG (UL) TYPE CL2P OR CMP (UL) c(UL) 75C E105765-F ROHS/CE AAAAA	Industrial environments	CL2P, CMP c(UL)	41
C8661	8471	1 pr 16 AWG (19x.0116") TC Unshielded Print Legend: XXXX/XXXX feet ECHELON GUIDELINE COMPLIANT 16 AWG (UL) TYPE CL2 OR CM CMG (UL) c(UL) 75C E105765-F ROHS/CE AAAAA	Industrial environments	CM c(UL)	41
GCR1404	7918A/7923A	4 UTP 24 AWG SBC, Category 5e Print Legend: **** GENERAL CABLE * GCR1404 INDUSTRIAL CAT 5E 4PR/24AWG RISER C(UL)US CMX OUTDOOR - CMR 75C UV RES VERIFIED (UL) ANSI/TIA-568C.2 CAT-5E AWM 21047 75C 600V-- FT4 OIL RES P-07-KA140022-MSHA ODVA ETHERNET/IP™ VEN 1293 PAT 5767441 CAT 5E	Industrial Ethernet environments	CMR c(UL) 600 V	9
C2104A	8917	1 C 16 AWG (26x30) TC PVC Insulation Print Legend: CAROL 16 AWG RU AWM 105C VW-1 600 V E18621-8 --- CSA TEW 105C LL69381 --- MADE IN USA	Jumper wire	AWM 1015, CSA TEW 600 V	-

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

Information contained on these pages is intended for evaluation by technically skilled persons. Any person relying on this document does so at his/her own independent discretion and sole risk and assumes all risks, liability and obligations whatsoever in connection with such use. General Cable Corporation and its subsidiaries will have no liability with respect thereto, whether the claim is based in contract, tort or other legal theory. General Cable Corporation and its subsidiaries make no representations or warranties, expressed or implied, with respect to the accuracy, completeness or reliability of this product training manual.



This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

# Industrial Communication Protocol Cables

## Cross-Reference

Modbus cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### MODBUS CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1320	8777	3pr 22 AWG (7x30) TC, Ind Shield prs./PVC Print Legend: GENERAL CABLE (F) – GCR1320 – 3/PR 22 AWG SHIELDED (UL) TYPE CM OR AWM 2919 -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	RS-232, industrial environments, relatively clean, minimum temperature changes	CM, c(UL) AWM 2919	38
GCR1320P	82777	3pr 22 AWG (7x30) TC, Ind Shield prs./LS PVC Print Legend: GENERAL CABLE (F) – GCR1320P -- 3PR 22 AWG SHIELDED CMP (UL) c(UL)us 75C – ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Plenum rated, (-10°C+75°C), RS-232, light industrial environments, relatively clean, minimum temperature changes	CMP c(UL)	38
GCR1320FP	88777	3pr 22 AWG (7x30) TC, Ind Shield prs./FEP Print Legend: GENERAL CABLE (F) – GCR1320FP -- 3PR 22 AWG SHIELDED CMP (UL) c(UL)us FEP/FEP --- GAS AND OIL RESISTANCE -- ROHS/CE -- MADE IN USA XXXXFT	Plenum rated, FEP/FEP construction, RS-232, suitable for high and low temperatures (-70°C+200°C), corrosive environments	CMP c(UL)	38
GCR1320A	128777	3pr 22 AWG (7x30) TC, Ind Shield prs./PVC/AIA/PVC Print Legend: GENERAL CABLE (F) – GCR1320A – ARMORED 3/PR 22 AWG SHIELDED (UL) TYPE CM OR AWM 2919 -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Aluminum Interlock Armor (AIA), PVC jacket, RS-232, alternative to conduit installation, additional mechanical and electrical shielding	CM, c(UL) AWM 2919	38
C4841A	9841	1 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4841A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	RS-485, industrial environments, relatively clean, minimum temperature changes	CM, CMH c(UL) AWM 2919	39
C4851A	82841	1 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4851A -- 1/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA – MM/YY AAAAA XXXXXFT	Plenum rated, (-10°C+75°C), RS-485, light industrial environments, relatively clean, minimum temperature changes	CMP c(UL)	40
C4842A	9842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4842A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	RS-485, industrial environments, relatively clean, minimum temperature changes	CM, CMH c(UL) AWM 2919	39
C4852A	82842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4852A -- 2/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA – MM/YY AAAAA XXXXXFT	Plenum rated, (-10°C+75°C), RS-485, industrial environments, relatively clean, minimum temperature changes	CMP c(UL)	40
C4843A	9843	3 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4843A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	RS-485, industrial environments, relatively clean, minimum temperature changes	CM, CMH c(UL) AWM 2919	39
C4844A	9844	4 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4844A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	RS-485, industrial environments, relatively clean, minimum temperature changes	CM, CMH c(UL) AWM 2919	39
C7112A	3105A	1 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7112A -- 1/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- ROHS/CE -- MADE IN USA – MM/YY AAAAA XXXXXFT	RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39

\* Belden special make-to-order cables.

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables Cross-Reference

## MODBUS CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
C7112AF		1 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7112AF -- 1/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	High Flex version of C7112A, RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
GCR1310	3106A	1.5pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC, Sun Res Oil Res Print Legend: GENERAL CABLE (F) - GCR1310 -- 3/C 22 AWG RS-485 SHIELDED (UL) TYPE PLTC OR CM C(UL) FT1 SUN RES -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	RS-485, industrial environments, relatively clean, minimum temperature changes	CL2, CM, c(UL), CSA AWM I/II A 80°C, FT1	38
C7114A	3107A	2 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114A -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
C7114AF		2 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114AF -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	High Flex version of C7114A, RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
C7116A	3108A	3 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7116A -- 3/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
C7116AF		3 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7116AF -- 3/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	High Flex version of C7116A, RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
C7118A	3109A	4 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7118A -- 4/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
C7118AF		4 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7118AF -- 4/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	High Flex version of C7118A, RS-485, industrial environments, relatively clean, minimum temperature changes	PLTC, CM c(UL)	39
GCR1309	3092A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC Print Legend: GENERAL CABLE (F) - GCR1309 - ODVA ControlNet™ VEN #1293 RG-6/U TYPE 75 OHM QUAD SHIELD - 3.0 GHZ - 18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 - ROHS/CE-- MADE IN USA AAAAA MM/YY XXXXFT	Remote I/O, industrial environments, relatively clean, minimum temperature changes	CL2R, CMR, CMG, CATVR, FT4 c(ETL)	32
GCR1309P	3093A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVDF Print Legend: GENERAL CABLE (F) - GCR1309P - ODVA ControlNet™ VEN #1293 RG-6/U TYPE 75 OHM QUAD SHIELD - 3.0 GHZ - 18 AWG 150C (ETL) CL2P - CATVP OR CMP c(ETL)us FT6 3084997 - ROHS/CE - MADE IN USA AAAAA MM/YY XXXXFT	Remote I/O, plenum rated, FEP/PVDF construction, suitable for high and low temperatures (-40°C+150°C)	CL2P, CMP, CATVP, FT6, c(ETL)	32
GCR1309F	3092F	RG-6/U 20 AWG (105x40) BC, Quad Shield OFS(2) 60/40% AL Braid/PVC Print Legend: GENERAL CABLE (F) - GCR1309F - ODVA ControlNet™ VEN #1293 RG-6/U TYPE 75 OHM FLEXIBLE QUAD SHIELD - 3.0 GHZ - 20 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 - ROHS/CE-- MADE IN USA AAAAA MM/YY XXXXFT	Remote I/O, High Flex version of GCR 1309 (note higher attenuation)	CL2R, CMR, CMG, FT4, CATVR c(ETL)	32
GCR1309A	123092A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC/AIA/PVC Print Legend: GENERAL CABLE (F) - GCR1309A - ODVA ControlNet™ VEN #1293 ALUM-ARMORED RG-6/U TYPE 75 OHM QUAD SHIELD SUN RES DIR BUR - 3.0 GHZ -18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 - ROHS/CE -- MADE IN USA AAAAA MM/YY XXXXFT	Remote I/O, Aluminum Interlock Armor (AIA), PVC jacket, alternative to conduit installation, additional mechanical and electrical shielding	CL2R, CMR, CMG, FT4, CATVR c(ETL)	32

\* Belden special make-to-order cables.

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables

## Cross-Reference

### MODBUS CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1309S	133092A*	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC/GSIA/PVC Print Legend: GENERAL CABLE (F) – GCR1309S – ODVA ControlNet™ VEN #1293 STEEL ARMORED RG-6/U TYPE 75 OHM QUAD SHIELD SUN RES DIR BUR – 3.0 GHZ –18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE -- MADE IN USA AAAAA MM/YY XXXXFT	Remote I/O, Galvanized Steel Interlock Armor (GSIA), PVC jacket, alternate to conduit installation, additional mechanical and crush resistance, electrical shielding	CL2R, CMR, CMG, CATVR c(ETL)	32
GCR1309CC	183092A	RG-6/U 18 AWG CCS, Quad Shield OFS(2) 60/40% AL Braid/PVC/CCW/PVC Print Legend: GENERAL CABLE (F) – GCR1309CC -- ODVA ControlNet™ VEN #1293 CCW-ARMORED RG-6/U TYPE 75 OHM QUAD SHIELD SUN RES DIR BUR – 3.0 GHZ –18 AWG 75C (ETL) CL2R - CATVR OR CMR c(ETL)us CMG FT4 3084997 – ROHS/CE -- MADE IN USA AAAAA MM/YY XXXXFT	Remote I/O, Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust	CL2R, CMR, CMG, FT4, CATVR c(ETL)	32

\* Belden special make-to-order cables.

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

Information contained on these pages is intended for evaluation by technically skilled persons. Any person relying on this document does so at his/her own independent discretion and sole risk and assumes all risks, liability and obligations whatsoever in connection with such use. General Cable Corporation and its subsidiaries will have no liability with respect thereto, whether the claim is based in contract, tort or other legal theory. General Cable Corporation and its subsidiaries make no representations or warranties, expressed or implied, with respect to the accuracy, completeness or reliability of this information.

Profibus DP and Profibus PA cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### Profibus DP CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1304	3079A	1 pr 22 AWG (solid) BC OFS + 65% TC Braid, 150Ω imp. PVC, Profibus DP Type A Print Legend: GENERAL CABLE (F) – GCR1304 -- PROFIBUS 1/PR 22 AWG SHIELDED (UL) TYPE PLTC OR CM CMG c(UL)us FT4 75C -- SUN RES OR AWM 20201 600 V – ROHS/CE – MADE IN USA AAAAA MO/YR XXXXXXFT	Industrial environments, relatively clean, minimum temperature changes, trunk and/or spur	CM, c(UL), PLTC-ER, CMG 80°C, FT4, AWM 20201 600 V	34
GCR1304F	3079E	1 pr 22 AWG (19x34) TC OFS + 65% TC Braid, 150Ω imp. PVC, Profibus DP Type A Print Legend: GENERAL CABLE (F) – GCR1304F -- PROFIBUS FLEXIBLE 1/PR 22 AWG SHIELDED (UL) TYPE PLTC OR CM CMG c(UL)us FT4 75C -- SUN RES OR AWM 20201 600 V – ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	High Flex version of GCR 1304 light industrial environments, relatively clean, minimum temperature changes, spur connections only	CM, c(UL), PLTC-ER, CMG 80°C, FT4, AWM 20201 600 V	34
9899.PB02201000	183079A	1 pr 22 AWG (solid) BC OFS + 65% TC Braid, 150Ω imp. Fluoropolymer Ins/Fluoropolymer Inner Jacket/CCW/PVC Outer Jacket Purple Profibus DP Type A Print Legend: GENERAL CABLE (WC) CCW PROFIBUS 1 PAIR 22 AWG CU FEP INSUL (UL) TYPE ITC-HL -40C DIR BUR SUN RES 105C FT4/IEEE 1202 DAY/MONTH/YEAR XXXXXXFT	Continuously Corrugated Welded Armor (CCW) provides mechanical protection, electrical shielding (EMI), impervious to moisture and dust, trunk and/or spur Arctic Armor grade +105° -40°C, direct burial	ITC-HL, 300 V, CT use, CSA FT4, IEEE 1202	35
GCR1302	3076F**	1 pr 18 AWG (7x26) TC OFS, PVC Foundation™ Fieldbus Type A per ISA/SP 50 for Profibus PA applications Print Legend: GENERAL CABLE (F) – GCR1302 -- FIELDBUS 1/PR 18 AWG SHIELDED (UL) TYPE PLTC OR ITC OR CM CMG c(UL) US FT4 75C -- SUN RES OIL RES --- ROHS/CE – MADE IN USA AAAAA MO/YR XXXXXXFT	Industrial environments, relatively clean, minimum temperature changes, trunk and/or spur	CM, c(UL), ITC-ER, CMG 80°C, FT4	34

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

\*\*Note: Profibus PA Type A and Type B cables and Foundation™ Fieldbus Cable Type A and Type B are in accordance with IEC 61158-2. Profibus PA Type A cable and Foundation™ Fieldbus Type A cables can be used, but note the color code of the conductors are not the same. ISA Standard SP50 requires the color code of the conductors to be orange(+) and blue(-) with an orange jacket or sheath. The inner conductors color code for Profibus PA are red(+) and green(-). The electrical specifications are the same in accordance with IEC 61158-2.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.



# Industrial Communication Protocol Cables Cross-Reference

RS-485 cables are used extensively in industrial environments. Typical applications include process automation (chemicals, paper mills), factory automation, HVAC, security, motion control and motor controls.

RS-485 network cables typically are either 24 AWG or 22 AWG. The final decision on the number of pairs, wire size, capacitance, impedance, shielding, and other electrical specifications is a function of the application. General Cable Corporation cannot specify a specific cable for these applications. General Cable Corporation offers different cable constructions to function in many RS-485 applications.

### RS-485 NETWORK CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	UL/CSA LISTINGS	PAGE NUMBER
C4841A	9841	1 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4841A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4851A	82841	1 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4851A -- 1/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	CMP c(UL)	40
C4842A	9842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4842A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4852A	82842	2 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/LS PVC Print Legend: CAROL® -- C4852A -- 2/PR 24 AWG SHIELDED LOW CAP RS-485 TYPE CMP (UL) C(UL) 75C E105765-F -- ROHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	CMP c(UL)	40
C4843A	9843	3 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4843A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C4844A	9844	4 pr 24 AWG (7x32) TC, OFS + 90% TC Braid/PVC Print Legend: CAROL® 24 AWG -- C4844A -- 75C E105765-H CM (UL) C(UL) CMH OR 80C AWM STYLE 2919 30 V LOW VOLTAGE COMPUTER CABLE -- ROHS/CE -- MADE IN USA (date code - MM/YY) (sequential footage)	CM, CMH c(UL) AWM 2919	39
C7112A	3105A	1 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7112A -- 1/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7112AF		1 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7112AF -- 1/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
GCR1310	3106A	1.5pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC, Sun Res Oil Res Print Legend: GENERAL CABLE (F) -- GCR1310 -- 3/C 22 AWG RS-485 SHIELDED (UL) TYPE PLTC OR CM CMG C(UL)US FT4 75C SUN RES -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	CL2, CM, c(UL), CSA AWM I/II A 80°C, FT1	38
C7114A	3107A	2 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114A -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7114AF		2 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7114AF -- 2/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7116A	3108A	3 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7116A -- 3/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7116AF		3 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7116AF -- 3/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA -- MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**





# Industrial Communication Protocol Cables

## Cross-Reference

### RS-485 NETWORK CABLES

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	UL/CSA LISTINGS	PAGE NUMBER
C7118A	3109A	4 pr 22 AWG (7x30) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7118A -- 4/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
C7118AF		4 pr 22 AWG (26x36) TC, OFS + 65% TC Braid/PVC Print Legend: CAROL® -- C7118AF -- 4/PR 22 AWG SHIELDED LOW CAP RS-485 (UL) PLTC OR CM C(UL) 75C E60233-F -- RoHS/CE -- MADE IN USA - MM/YY AAAAA XXXXXFT	PLTC, CM c(UL)	39
GCR1301	3704F	1 pr 18 AWG (7x26) TC, OFS + 60% TC Braid/PVC, Sun Res Oil Res, Direct Burial Print Legend: GENERAL CABLE (F) - GCR1301 -- 1/PR 18 AWG SHIELDED LOW CAP (UL) TYPE TC 600 V 75C DRY OR PLTC OR ITC OR CMG C(UL)US FT4 -- SUN RES OIL RES DIR BUR --- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	TC-ER, PLTC, ITC-ER, CSA CMG, FT4	40

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

Smart Distributed Systems (SDS) cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### SMART DISTRIBUTED SYSTEM (SDS) CABLE

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1332	3086A	Power: 1 pr 16 AWG (19x0.0117") TC, OFS Data: 1 pr 20 AWG (19x32) TC OFS, Common Drain Wire, 120Ω imp. PVC Print Legend: GENERAL CABLE (F) - GCR1332 - 1/PR 16 AWG + 1/PR 20 AWG SHIELDED (UL) TYPE CL2 OR AWM 2464 300 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Light industrial environments, relatively clean, minimum temperature changes, trunk and/or branch	CL2, AWM 2464 300 V	34
GCR1334	3087A	Power: 1 pr 22 AWG (19x34) TC, OFS Data: 1 pr 22 AWG (19x34) TC OFS, Common Drain Wire, 120Ω imp. PVC Print Legend: GENERAL CABLE (F) - GCR1334 - SYSTEM (SOS) - 2/PR 22 AWG SHIELDED (UL) TYPE CL2 OR AWM 2464 300 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXFT	Light industrial environments, relatively clean, minimum temperature changes, branch	CL2, AWM 2464 300 V	34

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

Information contained on these pages is intended for evaluation by technically skilled persons. Any person relying on this document does so at his/her own independent discretion and sole risk and assumes all risks, liability and obligations whatsoever in connection with such use. General Cable Corporation and its subsidiaries will have no liability with respect thereto, whether the claim is based in contract, tort or other legal theory. General Cable Corporation and its subsidiaries make no representations or warranties, expressed or implied, with respect to the accuracy, completeness or reliability of this information.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**



# Industrial Communication Protocol Cables Cross-Reference

Seriplex® cables are used extensively in industrial environments. The cable application is dependent on where the cables are to be residing. Factory floor environments can range from general light duty, clean environments to more severe environments that may be subject to moisture, chemicals, extreme temperature ranges, physical or outdoor environments that could cause premature failure of a cable that was just designed for indoor enterprise applications.

### SERIPLEX® CABLE CONSTRUCTION OPTIONS

GCC PART NUMBER	BELDEN PART NUMBER	CABLE DESCRIPTION	APPLICATIONS	UL/CSA LISTINGS	PAGE NUMBER
GCR1330	3124A	Power: 1 pr 18 AWG (16x30) TC, Data: 1 pr 22 AWG (7x30) TC OFS/PVC, SquareD/Seriplex Print Legend: GENERAL CABLE (F) – GCR1330 -- 2/C 18 AWG + 2/C 22 AWG SHIELDED (UL) TYPE CL2 OR CM c(UL)us OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	Industrial environments, relatively clean, minimum temperature changes	CM, c(UL), CL2, AWM 20201 600 V, 80°C	37
GCR1330A	123124A	Power: 1 pr 18 AWG (16x30) TC, Data: 1 pr 22 AWG (7x30) TC OFS/PVC/AIA/PVC, SquareD/Seriplex Print Legend: GENERAL CABLE (F) – GCR1330A -- ARMORED 2/C 18 AWG + 2/C 22 AWG SHIELDED (UL) TYPE CL2 OR CM c(UL)us OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	Aluminum Interlock Armor (AIA), PVC jacket, alternative to conduit installation, additional mechanical and electrical shielding	CM, c(UL), CL2, AWM 20201 600 V, 80°C	37
GCR1331	3125A	Power: 1 pr 16 AWG (26x30) TC, Data: 1 pr 22 AWG (7x30) TC OFS/PVC, SquareD/Seriplex Print Legend: GENERAL CABLE (F) – GCR1331 -- 2/C 16 AWG + 2/C 22 AWG SHIELDED (UL) TYPE CL2 OR CM c(UL)us OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	Industrial environments, relatively clean, minimum temperature changes	CM, c(UL), CL2, AWM 20201 600 V, 80°C	37
GCR1331A	123125A	Power: 1 pr 16 AWG (26x30) TC, Data: 1 pr 22 AWG (7x30) TC OFS/PVC/AIA/PVC, SquareD/Seriplex Print Legend: GENERAL CABLE (F) – GCR1331A -- ARMORED 2/C 16 AWG + 2/C 22 AWG SHIELDED (UL) TYPE CL2 OR CM c(UL)us OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	Aluminum Interlock Armor (AIA), PVC jacket, alternative to conduit installation, additional mechanical and electrical shielding	CM, c(UL), CL2, AWM 20201 600V, 80°C	37
GCR1333	3126A	Power: 1 pr 12 AWG (65x30) TC, Data: 1 pr 22 AWG (7x30) TC, Control: 1 pr 16 AWG (26x30) OFS/PVC, SquareD/Seriplex Print Legend: GENERAL CABLE (F) – GCR1333 -- 2/C 16 AWG + 2/C 22 AWG + 2/C 12 AWG SHIELDED (UL) TYPE CL2 OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	Industrial environments, relatively clean, minimum temperature changes	CL2, AWM 20201 600 V, 80°C	37
GCR1333A	123126A	Power: 1 pr 12 AWG (65x30) TC, Data: 1 pr 22 AWG (7x30) TC, Control: 1 pr 16 AWG (26x30) OFS/PVC/AIA/PVC, SquareD/Seriplex Print Legend: GENERAL CABLE (F) – GCR1333A -- ARMORED 2/C 16 AWG + 2/C 22 AWG + 2/C 12 AWG SHIELDED (UL) TYPE CL2 OR AWM 20201 600 V -- ROHS/CE -- MADE IN USA AAAAA MO/YR XXXXXXFT	Aluminum Interlock Armor (AIA), PVC jacket, alternative to conduit installation, additional mechanical and electrical shielding	CL2, AWM 20201 600 V, 80°C	37

Guidelines for the environment of automation applications may be classified by ANSI/TIA 1005. Levels (MICE) Mechanical, Ingress, Climatic, Chemical and Electromagnetic.

Information contained on these pages is intended for evaluation by technically skilled persons. Any person relying on this document does so at his/her own independent discretion and sole risk and assumes all risks, liability and obligations whatsoever in connection with such use. General Cable Corporation and its subsidiaries will have no liability with respect thereto, whether the claim is based in contract, tort or other legal theory. General Cable Corporation and its subsidiaries make no representations or warranties, expressed or implied, with respect to the accuracy, completeness or reliability of this information.

This cross-reference guide should be used in conjunction with the product information in our catalog or on our website. It should be used for suggested alternative items which are functionally equal. Constructional differences are not indicated. General Cable is not responsible for variances due to competitor and industry constructional changes or agency updates.

**Please consult your General Cable representative for additional information (800) 950-3512**

# Catalog Number Index

CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE
02001	69	02645	70	4780.37014	58	4790.37012	60
02002	69	02646	70	4785.03016	59	4790.37014	60
02003	69	4775.03016	57	4785.03018	59	09005	64
02004	69	4775.03018	57	4785.04016	59	09006	64
02005	69	4775.04016	57	4785.04018	59	09007	64
02006	69	4775.04018	57	4785.05016	59	09008	64
02007	69	4775.05016	57	4785.05018	59	09010	64
02008	69	4775.05018	57	4785.07016	59	09012	64
02009	69	4775.07016	57	4785.07018	59	09016	64
02021	69	4775.07018	57	4785.09016	59	09020	64
02022	69	4775.09016	57	4785.09018	59	09205	64
02023	69	4775.09018	57	4785.12016	59	09206	64
02024	69	4775.12016	57	4785.12018	59	09207	64
02031	69	4775.12018	57	4785.19016	59	09208	64
02032	69	4775.16016	57	4785.19018	59	09209	64
02033	69	4775.16018	57	4785.25016	59	09210	64
02034	69	4775.19016	57	4785.25018	59	09212	64
02035	69	4775.19018	57	4785.30016	59	09214	64
02036	69	4775.25016	57	4785.30018	59	09216	64
02037	69	4775.25018	57	4785.37016	59	09218	64
02038	69	4775.30016	57	4785.37018	59	09220	64
02039	69	4775.30018	57	4790.03010	60	09224	64
02041	69	4775.37016	57	4790.03012	60	09226	64
02042	69	4775.37018	57	4790.03014	60	09227	64
02043	69	4780.03010	58	4790.04002	60	09228	64
02045	69	4780.03012	58	4790.04004	60	09230	64
02046	69	4780.03014	58	4790.04006	60	09405	64
02601	70	4780.04010	58	4790.04008	60	09406	64
02602	70	4780.04012	58	4790.04010	60	09407	64
02603	70	4780.04014	58	4790.04012	60	09408	64
02604	70	4780.05010	58	4790.04014	60	09409	64
02605	70	4780.05012	58	4790.05010	60	09410	64
02606	70	4780.05014	58	4790.05012	60	09412	64
02607	70	4780.07010	58	4790.05014	60	09414	64
02608	70	4780.07012	58	4790.07010	60	09416	64
02609	70	4780.07014	58	4790.07012	60	09418	64
02621	70	4780.09010	58	4790.07014	60	09420	64
02622	70	4780.09012	58	4790.09010	60	09424	64
02623	70	4780.09014	58	4790.09012	60	09428	64
02624	70	4780.12010	58	4790.09014	60	09430	64
02631	70	4780.12012	58	4790.12010	60	9600.00103310	77
02632	70	4780.12014	58	4790.12012	60	9600.00104106	77
02633	70	4780.19010	58	4790.12014	60	9600.00203310	77
02634	70	4780.19012	58	4790.19010	60	9600.00204106	77
02635	70	4780.19014	58	4790.19012	60	9600.00403312	77
02636	70	4780.25010	58	4790.19014	60	9600.00404108	77
02637	70	4780.25012	58	4790.25010	60	9600.00603312	77
02638	70	4780.25014	58	4790.25012	60	9600.00604108	77
02639	70	4780.30010	58	4790.25014	60	9600.00803314	77
02641	70	4780.30012	58	4790.30010	60	9600.00804110	77
02642	70	4780.30014	58	4790.30012	60	9600.01003314	77
02643	70	4780.37012	58	4790.30014	60	9600.01004314	77

# Catalog Number Index

CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE
9600.01203316.....	77	9605.35003306.....	79	9675.50003306.....	83	9815.25003306.....	91
9600.01204316.....	77	9605.35003307.....	79	9700.00103308.....	85	9815.35003306.....	91
9600.01403318.....	77	9605.35004103.....	79	9700.00203310.....	85	9815.41003307.....	91
9600.01404318.....	77	9605.41003308.....	79	9700.00403310.....	85	9815.50003305.....	91
9600.11003310.....	77	9605.41004104.....	79	9700.00603310.....	85	9815.75003304.....	91
9600.11004106.....	77	9605.50003306.....	79	9700.00803312.....	85	09816 .....	63
9600.21003310.....	77	9605.50004102.....	79	9700.10003304.....	85	09818 .....	63
9600.21004106.....	77	9605.75003304.....	79	9700.11003308.....	85	09820 .....	63
9600.25003308.....	77	9605.75003305.....	79	9700.21003308.....	85	09822 .....	63
9600.25004104.....	77	9605.75004101.....	79	9700.25003307.....	85	09824 .....	63
9600.31003308.....	77	9605.100031110.....	79	9700.35003306.....	85	09827 .....	63
9600.31004104.....	77	9605.100041110.....	79	9700.41003307.....	85	09830 .....	63
9600.35003307.....	77	09606 .....	63	9700.50003305.....	85	9899.CT02104000 .....	14
9600.35004103.....	77	09607 .....	63	9700.75003304.....	85	9899.FB01601118 .....	35
9600.41003308.....	77	09608 .....	63	9800.00103308.....	87	9899.FB01602118 .....	35
9600.41004104.....	77	09609 .....	63	9800.00203310.....	87	9899.FB01604118 .....	35
9600.50003306.....	77	09610 .....	63	9800.00403310.....	87	9899.FB01801120 .....	35
9600.50004102.....	77	09612 .....	63	9800.00603310.....	87	9899.FB01802120 .....	35
9600.75003305.....	77	09614 .....	63	9800.10003304.....	87	9899.FB01804120 .....	35
9600.75004101.....	77	9615.00103310.....	81	9800.11003308.....	87	9899.PB02201000 .....	35
9600.100031110.....	77	9615.00203310.....	81	9800.21003308.....	87	14407.247000.....	53
9600.100041110.....	77	9615.00403312.....	81	9800.25003306.....	87	14407.546500.....	53
09605 .....	63	9615.00603312.....	81	9800.35003306.....	87	14407.547000.....	53
9605.00103310.....	79	9615.00803314.....	81	9800.41003307.....	87	14428.030100.....	56
9605.00104106.....	79	9615.01003314.....	81	9800.50003305.....	87	14428.030200.....	56
9605.00203310.....	79	9615.01203316.....	81	9800.75003304.....	87	14428.030400.....	56
9605.00204106.....	79	9615.01403318.....	81	09805 .....	63	14428.030600.....	56
9605.00204208.....	79	9615.11003310.....	81	9805.00103308.....	89	14428.030800.....	56
9605.00403312.....	79	9615.21003306.....	81	9805.00203310.....	89	14428.035100.....	56
9605.00404108.....	79	9615.25003304.....	81	9805.00403310.....	89	14428.035200.....	56
9605.00404210.....	79	9615.35003302.....	81	9805.00603310.....	89	14428.035300.....	56
9605.00603312.....	79	9615.41003304.....	81	9805.10003304.....	89	14428.035400.....	56
9605.00604108.....	79	9615.50003301.....	81	9805.11003308.....	89	14428.036000.....	56
9605.00604210.....	79	09616 .....	63	9805.21003308.....	89	14428.036200.....	56
9605.00803314.....	79	09618 .....	63	9805.25003306.....	89	14428.036500.....	56
9605.00804110.....	79	09620 .....	63	9805.35003306.....	89	14428.037000.....	56
9605.00804212.....	79	09622 .....	63	9805.41003307.....	89	14428.040100.....	56
9605.01003314.....	79	09624 .....	63	9805.50003305.....	89	14428.040200.....	56
9605.01004314.....	79	09626 .....	63	9805.75003304.....	89	14428.040400.....	56
9605.01203316.....	79	09630 .....	63	09806 .....	63	14428.040600.....	56
9605.01204316.....	79	9675.00103310.....	83	09807 .....	63	14428.040800.....	56
9605.01403318.....	79	9675.00203310.....	83	09808 .....	63	14428.045100.....	56
9605.01404216.....	79	9675.00403312.....	83	09810 .....	63	14428.045200.....	56
9605.01404318.....	79	9675.00603312.....	83	09812 .....	63	14428.045300.....	56
9605.11003310.....	79	9675.00803314.....	83	09814 .....	63	14428.045400.....	56
9605.11004106.....	79	9675.01003316.....	83	9815.00103308.....	91	14428.046000.....	56
9605.21003310.....	79	9675.01203318.....	83	9815.00203310.....	91	14428.046200.....	56
9605.21004106.....	79	9675.11003310.....	83	9815.00403310.....	91	14428.046500.....	56
9605.25003308.....	79	9675.21003310.....	83	9815.00603310.....	91	14428.047000.....	56
9605.25004104.....	79	9675.25003308.....	83	9815.10003304.....	91	77453 .....	62
9605.31003308.....	79	9675.35003308.....	83	9815.11003308.....	91	77463 .....	62
9605.31004104.....	79	9675.41003308.....	83	9815.21003308.....	91	77473 .....	62

# Catalog Number Index

CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE
77483	62	82414	67	279840	50	283210	53
77493	62	82423	67	279850	51	283220	53
81312	66	82443	67	279870	50	284560	53
81313	66	82473	67	279880	50	287410	46
81314	66	82623	67	279890	50	287650	44
81315	66	82624	67	279900	50	288250	45
81372	66	82643	67	279910	51	288260	45
81373	66	82644	67	279920	51	293600	53
81374	66	82663	67	279930	51	294530	53
81375	66	82664	67	280170	50	294540	46
81382	66	83001	65	280180	50	294580	44
81383	66	83002	65	280190	50	295360	53
81384	66	83004	65	280200	50	295390	53
81385	66	83006	65	280210	50	295400	50
81392	66	83008	65	280230	51	295890	53
81393	66	83010	65	280240	51	296440	53
81394	66	83020	65	280250	51	296450	53
81395	66	83030	65	280260	51	297730	53
81402	66	83040	65	280270	51	298020	53
81403	66	83103	68	280280	51	300380	53
81404	66	83113	68	280290	51	300780	53
81405	66	83123	68	280300	50	301870	50
81412	66	83133	68	280310	50	305300	52
81413	66	83143	68	280320	50	305320	50
81414	66	83153	68	280330	50	305340	50
81415	66	83163	68	280340	50	305360	52
81423	66	83183	68	280350	51	307690	50
81443	66	83250	65	280360	51	311900	52
81473	66	83350	65	280370	51	311910	52
81622	66	83500	65	280380	51	314960	44
81623	66	279560	50	280390	51	319250	46
81624	66	279570	50	280400	51	319260	46
81625	66	279580	50	280410	50	319270	45
81642	66	279590	50	280420	51	325110	53
81643	66	279600	50	280430	51	325120	53
81644	66	279610	50	280470	52	325250	44
81645	66	279620	50	280490	52	325700	53
81662	66	279630	50	280500	45	326640	52
81663	66	279640	50	280520	45	326650	52
81664	66	279650	50	280530	45	326660	52
81665	66	279660	53	280540	45	326670	52
82313	67	279670	53	280590	51	330800	51
82314	67	279680	50	280600	51	330990	51
82373	67	279690	44	280950	46	337010	44
82374	67	279700	45	280960	46	337020	44
82383	67	279710	45	280970	46	337030	44
82384	67	279720	45	280980	52	337040	44
82393	67	279730	45	280990	45	337050	44
82394	67	279740	45	283170	44	337060	44
82403	67	279750	45	283180	44	337070	44
82404	67	279760	45	283190	44	337080	44
82413	67	279770	45	283200	53	337090	44

# Catalog Number Index

CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE
337100.....	44	384750.....	95	394080.....	48	394600.....	54
337110.....	44	384760.....	95	394090.....	48	394610.....	54
337120.....	44	384770.....	95	394100.....	48	394630.....	55
337130.....	44	384780.....	95	394110.....	48	394640.....	55
337140.....	44	384790.....	95	394120.....	49	394650.....	55
337150.....	46	384800.....	95	394130.....	49	394660.....	55
337160.....	46	384810.....	95	394140.....	49	394670.....	55
337170.....	46	384820.....	95	394150.....	49	394680.....	55
337180.....	46	384830.....	95	394160.....	49	394690.....	55
337190.....	46	384840.....	95	394170.....	49	394700.....	55
337200.....	46	384850.....	95	394180.....	49	394710.....	55
337210.....	46	384860.....	95	394190.....	49	394720.....	55
337220.....	46	385350.....	51	394200.....	49	394730.....	55
337230.....	46	385360.....	51	394210.....	49	394740.....	55
337240.....	45	385370.....	51	394220.....	49	394750.....	55
337250.....	45	393710.....	47	394230.....	49	394760.....	55
337260.....	45	393720.....	47	394240.....	49	394770.....	55
346980.....	53	393730.....	47	394250.....	49	394780.....	55
346990.....	53	393740.....	47	394260.....	49	394790.....	55
347000.....	53	393750.....	47	394270.....	49	394800.....	55
347080.....	50	393760.....	47	394280.....	54	394810.....	55
347100.....	50	393770.....	47	394290.....	54	394820.....	55
354800.....	52	393780.....	47	394300.....	54	394830.....	55
354810.....	52	393790.....	47	394310.....	54	394840.....	55
354820.....	52	393800.....	47	394320.....	54	394850.....	55
354830.....	52	393810.....	47	394330.....	54	394860.....	55
356740.....	53	393820.....	47	394340.....	54	394870.....	55
365750.....	53	393830.....	47	394350.....	54	394880.....	55
367120.....	52	393840.....	47	394360.....	54	394890.....	55
367130.....	52	393850.....	47	394370.....	54	394900.....	55
367140.....	52	393860.....	47	394380.....	54	394910.....	55
367150.....	52	393870.....	47	394390.....	54	394920.....	55
367160.....	52	393880.....	47	394400.....	54	394930.....	56
367170.....	52	393890.....	47	394410.....	54	394940.....	56
367180.....	52	393900.....	47	394420.....	54	394950.....	56
367190.....	52	393910.....	47	394430.....	54	394960.....	55
367200.....	52	393920.....	47	394440.....	54	395070V.....	96
367210.....	52	393930.....	48	394450.....	54	395080V.....	96
367220.....	52	393940.....	48	394460.....	54	395090V.....	96
367230.....	52	393950.....	48	394470.....	54	395100V.....	96
367240.....	52	393960.....	48	394480.....	54	395110V.....	96
367250.....	52	393970.....	48	394490.....	54	395120V.....	96
367260.....	52	393980.....	48	394500.....	54	395130V.....	96
367270.....	52	393990.....	48	394510.....	54	395140V.....	96
382880.....	51	394000.....	48	394520.....	54	395150V.....	96
383830.....	53	394010.....	48	394530.....	54	395160V.....	96
383930.....	51	394020.....	48	394540.....	54	395170V.....	96
383940.....	51	394030.....	48	394550.....	54	395180V.....	96
383950.....	51	394040.....	48	394560.....	54	395190V.....	96
383970.....	51	394050.....	48	394570.....	54	395200V.....	96
384730.....	95	394060.....	48	394580.....	54	438070.....	92
384740.....	95	394070.....	48	394590.....	54	438080.....	92



# Catalog Number Index

CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE	CATALOG NUMBER	PAGE
438090.....	92	GC622.....	71	GCR1318.....	37	XX0241ANR.BK.....	27
438100.....	92	GC623.....	71	GCR1319.....	37	XX0241ANU.BK.....	27
438110.....	92	GC624.....	71	GCR1320.....	38	XX0241P1R.....	25
438120.....	92	GC631.....	71	GCR1320A.....	38	XX0241PNR-ILRA.....	26
438130.....	92	GC632.....	71	GCR1320FP.....	38	XX0241PNU.....	25
438140.....	92	GC633.....	71	GCR1320P.....	38	XX0241PNU-ILPA.....	26
438150.....	93	GC634.....	71	GCR1320S.....	38	XX0244H1A-DWB.....	28
438160.....	93	GC635.....	71	GCR1324.....	33	XX0244M1A-DWB.....	28
438170.....	93	GC636.....	71	GCR1324A.....	33	XX0244M1D-DT.....	27
438180.....	93	GC637.....	71	GCR1330.....	37	XX0484H1A-DWB.....	28
438190.....	94	GC638.....	71	GCR1330A.....	37	XX0484M1A-DWB.....	28
438200.....	94	GC639.....	71	GCR1331.....	37	XX0724H1A-DWB.....	28
438210.....	94	GC641.....	71	GCR1331A.....	37	XX0724M1A-DWB.....	28
438220.....	94	GC642.....	71	GCR1332.....	34		
438230.....	94	GC643.....	71	GCR1333.....	37		
5136100.....	16	GC645.....	71	GCR1333A.....	37		
5136101.....	17	GC646.....	71	GCR1334.....	34		
7136100.....	22	GCR1300.....	33	GCR1402.....	8		
C2534A.....	40	GCR1301.....	40	GCR1403.....	11		
C4841A.....	39	GCR1302.....	34	GCR1404.....	9		
C4842A.....	39	GCR1303.....	34	GCR1405.....	13		
C4843A.....	39	GCR1304.....	34	GCR1407.....	15		
C4844A.....	39	GCR1304F.....	34	GCR1408.....	10		
C4851A.....	40	GCR1305.....	36	GCR1410.....	18		
C4852A.....	40	GCR1305F.....	36	GCR1419.....	12		
C7112A.....	39	GCR1306.....	36	GCR1440.....	19		
C7112AF.....	39	GCR1307.....	36	GCR1450.....	20		
C7114A.....	39	GCR1307F.....	36	GCR1452.....	21		
C7114AF.....	39	GCR1308.....	36	XX0021ANR.BK.....	27		
C7116A.....	39	GCR1309.....	32	XX0021ANU.BK.....	27		
C7116AF.....	39	GCR1309A.....	32	XX0021PNR.....	25		
C7118A.....	39	GCR1309CC.....	32	XX0021PNR-ILRA.....	26		
C7118AF.....	39	GCR1309F.....	32	XX0021PNU.....	25		
C8101.....	40	GCR1309FC.....	32	XX0021PNU-ILPA.....	26		
C8123.....	40	GCR1309P.....	32	XX0041PNR-ILRA.....	26		
C8601.....	41	GCR1309S.....	32	XX0041PNU-ILPA.....	26		
C8611.....	37	GCR1310.....	38	XX0061ANR.BK.....	27		
C8621.....	41	GCR1311.....	36	XX0061ANU.BK.....	27		
C8641.....	41	GCR1312.....	36	XX0061PNR.....	25		
C8651.....	37	GCR1313.....	36	XX0061PNR-ILRA.....	26		
C8661.....	41	GCR1314.....	33	XX0061PNU.....	25		
C9530ZH.....	36	GCR1314A.....	33	XX0061PNU-ILPA.....	26		
GC601.....	71	GCR1314CC.....	33	XX0064M1D-DT.....	27		
GC602.....	71	GCR1314D.....	33	XX0121ANR.BK.....	27		
GC603.....	71	GCR1314F.....	33	XX0121ANU.BK.....	27		
GC604.....	71	GCR1314P.....	33	XX0121PNR.....	25		
GC605.....	71	GCR1314S.....	33	XX0121PNR-ILRA.....	26		
GC606.....	71	GCR1314T.....	33	XX0121PNU.....	25		
GC607.....	71	GCR1314ZH.....	33	XX0121PNU-ILPA.....	26		
GC608.....	71	GCR1315.....	34	XX0124H1A-DWB.....	28		
GC609.....	71	GCR1316.....	34	XX0124M1A-DWB.....	28		
GC621.....	71	GCR1317.....	36	XX0124M1D-DT.....	27		

# One Company Connecting The World™

## POWERFUL PRESENCE · PRODUCTS PERFORMANCE · PEOPLE

General Cable has been a wire and cable innovator for over 170 years, always dedicated to connecting and powering people's lives. Today, with approximately 14,000 employees and approaching \$6 billion in revenues, we are one of the largest wire and cable manufacturers in the world.

Our company serves customers through a network of 38 manufacturing facilities in our core markets and has worldwide sales representation and distribution. We are dedicated to the production of high-quality aluminum, copper and fiber optic wire and cable and systems solutions for the energy, construction, industrial, specialty and communications sectors. With a vast portfolio of products to meet thousands of diverse application requirements, we continue to invest in research and development in order to maintain and extend our technology leadership by developing new materials, designing new products, and creating new solutions to meet tomorrow's market challenges.

In addition to our strong brand recognition and strengths in technology and manufacturing, General Cable is also competitive in such areas as distribution and logistics, marketing, sales and customer service. This combination enables us to better serve our customers globally and as they expand into new geographic markets.

**General Cable offers our customers all the strengths and value of a large company, but our people give us the agility and responsiveness of a small one. We service you globally and locally.**



Visit our Website at  
[www.generalcable.com](http://www.generalcable.com)



# Corporate Social Responsibility

CREATING SHARED VALUE

General Cable believes corporate social responsibility (CSR) is about creating shared value. That means keeping a dual focus in our business decisions: what is good for us as a company and what contributes to the greater good of the communities in which we live and work.



## SAFETY

### Working safer by working together

General Cable has one worldwide safety vision and goal – **ZERO & BEYOND**. We measure safety performance globally, share best practices and implement sound health and safety management systems. Many of our facilities worldwide are OHSAS 18001 (safety management system) certified. All North American facilities have implemented an equivalent health and safety management system. General Cable was a pioneer in obtaining the OHSAS 18001 Certificate for Occupational Health and Safety Management Systems in Europe and North Africa.



## SUSTAINABILITY

### Responsible practices in daily operations

As a global leader in the wire and cable industry, General Cable recognizes its role and responsibility in promoting sustainability. Our strongest business value is continuous improvement in all areas of our company. Across our many businesses, the quest to introduce new and better products through continuous improvement in environmental designs reflects our commitment to achieving industry-leading standards and responding proactively to global environmental issues. General Cable was the first cable manufacturer to obtain certification for its environmental management system, in accordance with the ISO 14001 and EMAS Standards.



## CITIZENSHIP

### A commitment to being good citizens

Being responsible citizens in our communities is of the utmost importance to us. Unequivocal honesty, integrity, forthrightness and fair dealing have long been part of General Cable's core values and are expected globally in all of our business relationships with our customers, employees, suppliers, neighbors and competitors. Our company leaders and employees strive to make a difference throughout a host of volunteer activities and financial support, improving the communities in which we live and work.



## INNOVATION

### Technologies that power and connect the world

General Cable is delivering innovation that matters. We are focusing on R&D expertise and investing in developing wire and cable solutions that meet the challenges confronting our customers and the world. In working together and using all the ingenuity and creativity we have, we will reach the goal of being the preeminent supplier of wire and cabling solutions in the industry, with both green constructions and designs for the ever-growing renewable energy market.



A commitment to achieving industry-leading standards and responding proactively to environmental global issues.


+1.859.572.8000  
info@generalcable.com

Visit [www.GeneralCableCSR.com](http://www.GeneralCableCSR.com)  
to learn more.



# Notes

## Global Reach



General Cable, a leading wire and cable innovator for over 170 years, serves customers through a network of 38 manufacturing facilities in our core markets and has worldwide sales representation and distribution. The Company is dedicated to the production of high-quality aluminum, copper and fiber optic wire and cable and systems solutions for the energy, construction, industrial, specialty and communications sectors. In addition to our strong brand recognition and strengths in technology and manufacturing, General Cable is also competitive in such areas as distribution and logistics, marketing, sales and customer service. This combination enables General Cable to better serve its customers as they expand into new geographic markets.

### General Cable

4 Tesseneer Drive  
Highland Heights, Kentucky 41076-9753  
Telephone: 800.950.3512  
859.572.8000

Email: [info@generalcable.com](mailto:info@generalcable.com)  
[www.generalcable.com](http://www.generalcable.com)

©2015. General Cable Technologies Corporation. Highland Heights, KY 41076  
All rights reserved. Printed in USA.